

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331604-830

Luminaire Tested: **S122DIW-S1005D1240U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331604-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8201.8 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.0	2.2
10°-20°	520.4	6.3
20°-30°	755.2	9.2
30°-40°	796.9	9.7
40°-50°	705.6	8.6
50°-60°	563.1	6.9
60°-70°	382.7	4.7
70°-80°	196.2	2.4
80°-90°	53.1	0.6
90°-100°	91.8	1.1
100°-110°	285.0	3.5
110°-120°	487.2	5.9
120°-130°	640.7	7.8
130°-140°	719.1	8.8
140°-150°	705.1	8.6
150°-160°	591.4	7.2
160°-170°	392.2	4.8
170°-180°	137.1	1.7
0°-30°	1454.6	17.7
0°-40°	2251.5	27.5
0°-60°	3520.2	42.9
0°-90°	4152.3	50.6
90°-120°	864.0	10.5
90°-150°	2928.8	35.7
90°-180°	4050.0	49.4
0°-180°	8201.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	44
90°	42	1	42	1	42	20
95°	76	64	76	64	76	84
105°	271	263	271	263	271	285
115°	489	489	489	489	489	483
125°	714	711	714	711	714	636
135°	931	920	931	920	931	717
145°	1129	1117	1129	1117	1129	705
155°	1287	1277	1287	1277	1287	592
165°	1391	1390	1391	1390	1391	392
175°	1441	1446	1441	1446	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	23.4	23.3	23.8	23.2	23.1	23.8	23.8	23.4	24.0	24.7	24.1
90°	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7	42.2	42.8	36.8
92.5°	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1	38.9	38.8	37.4
95°	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2	78.2	78.2	77.7
97.5°	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5	131.5	131.5	130.4
100°	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6	168.6	168.6	167.9
102.5°	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2	209.0	208.8	207.7
105°	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9	269.4	268.9	268.3
107.5°	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5	335.4	335.1	335.1
110°	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7	425.4	426.0	426.2
115°	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2	493.5	493.7	494.3
117.5°	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4	560.1	560.7	562.2
120°	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7	603.7	603.7	605.9
122.5°	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4	650.0	650.6	652.1
125°	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0	717.8	718.6	719.4
127.5°	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7	783.6	784.6	785.6
130°	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6	828.0	828.6	829.2
132.5°	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2	872.4	873.5	873.5
135°	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7	935.9	936.1	935.7
137.5°	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3	997.6	997.8	997.0
140°	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8	1038.8	1038.8	1037.5
142.5°	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4	1076.2	1076.0	1075.1
145°	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5	1133.2	1132.9	1131.3
147.5°	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5	1182.9	1182.3	1181.2
150°	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6	1212.5
152.5°	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9	1243.6
155°	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2	1285.8	1284.5	1283.6
157.5°	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4	1322.5	1320.7	1320.1
160°	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4	1344.7	1343.1	1342.8
162.5°	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4	1364.5	1362.7	1362.4
165°	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1	1390.3	1388.4	1388.4
167.5°	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4	1411.6	1409.6	1409.7
170°	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1	1423.2	1421.4	1421.6
172.5°	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0	1432.1	1430.1	1430.4
175°	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5	1441.6	1439.6	1440.2
177.5°	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3	1445.8
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	23.5	22.3	21.1	21.3	18.9	18.3	15.4	12.9	13.0	13.1	12.6
90°	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2	4.5	7.7	11.0
92.5°	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8	24.1	26.6	28.9
95°	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5	66.3	69.0	71.7
97.5°	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1	118.5	120.9	123.3
100°	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2	157.4	159.6	161.7
102.5°	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2	198.0	199.7	201.5
105°	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8	263.5	264.4	265.2
107.5°	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7	330.9	332.2	333.3
110°	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8	374.4	376.0	377.7





TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7	421.3	422.9	424.6
115°	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9	490.5	492.1	493.7
117.5°	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8	560.0	562.1	564.3
120°	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	605.9	608.1	610.3
122.5°	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7	648.4	651.0	653.6
125°	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2	713.7	716.1	718.6
127.5°	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1	778.2	781.3	784.4
130°	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2	818.7	822.3	825.8
132.5°	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2	863.0	865.9	868.7
135°	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3	923.2	926.2	929.3
137.5°	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5	986.0	988.4	990.9
140°	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7	1024.2	1026.6	1029.1
142.5°	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8	1063.3	1065.7	1068.2
145°	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0	1119.0	1120.9	1122.8
147.5°	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2	1169.4	1171.7	1174.0
150°	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4	1203.0	1204.7	1206.3
152.5°	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7	1233.3	1234.9	1236.5
155°	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1	1278.0	1278.7	1279.6
157.5°	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0	1316.5	1317.1	1317.7
160°	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4	1340.0	1340.6	1341.1
162.5°	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9	1361.1	1361.2	1361.3
165°	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6	1389.3	1389.0	1388.7
167.5°	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5	1412.7	1411.9	1411.1
170°	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3	1425.4	1424.7	1423.8
172.5°	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0	1434.3	1433.4	1432.6
175°	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8	1445.0	1444.2	1443.3
177.5°	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2	1449.5	1448.9	1448.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	12.6	13.0	13.7	14.8	15.5	16.0	15.4	15.3	15.2	13.9	13.9
90°	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7	41.2	40.6	40.4
92.5°	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1	39.2	39.3	39.4
95°	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2	78.2	78.2	77.9
97.5°	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5	131.5	131.5	131.5
100°	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6	168.6	168.6	168.5
102.5°	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2	209.4	209.6	209.6
105°	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9	270.5	271.1	271.4
107.5°	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5	335.7	336.0	335.5
110°	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	379.7



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7	424.0	423.4	422.8
115°	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2	492.9	492.7	492.1
117.5°	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4	558.7	558.1	557.4
120°	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7	603.7	603.7	603.3
122.5°	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4	648.8	648.1	647.4
125°	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0	716.1	715.4	714.8
127.5°	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7	781.7	780.7	779.8
130°	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6	827.0	826.4	825.7
132.5°	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2	870.0	868.8	867.8
135°	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7	935.4	935.1	934.5
137.5°	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3	997.1	996.9	996.3
140°	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8	1038.8	1038.8	1038.3
142.5°	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4	1076.7	1076.9	1076.4
145°	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5	1133.8	1134.0	1133.6
147.5°	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5	1184.1	1184.7	1184.5
150°	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8
152.5°	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0
155°	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2	1288.5	1289.9	1290.2
157.5°	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4	1326.2	1328.0	1328.3
160°	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4	1348.0	1349.6	1349.9
162.5°	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4	1368.2	1370.1	1370.4
165°	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1	1394.0	1396.0	1396.2
167.5°	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4	1415.3	1417.2	1417.5
170°	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1	1427.0	1429.0	1429.1
172.5°	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0	1435.9	1437.8	1437.8
175°	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5	1445.4	1447.3	1447.5
177.5°	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	13.9	13.4	13.5	12.9	13.5	13.4	13.9	13.9	13.9	15.2	15.3
90°	40.7	41.0	41.3	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7
92.5°	39.4	39.5	39.6	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1
95°	77.4	76.8	76.3	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2
97.5°	131.4	131.4	131.3	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5
100°	168.2	168.0	167.7	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6
102.5°	209.3	209.1	208.8	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2
105°	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9
107.5°	334.2	333.0	331.7	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5
110°	378.9	378.1	377.2	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	422.2	421.6	421.0	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7
115°	491.3	490.5	489.7	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2
117.5°	556.6	555.7	555.0	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4
120°	602.5	601.7	600.9	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7
122.5°	646.9	646.2	645.6	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4
125°	714.5	714.3	714.0	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0
127.5°	778.9	778.1	777.2	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7
130°	824.5	823.5	822.4	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6
132.5°	867.0	866.0	865.2	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2
135°	933.7	932.9	932.1	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7
137.5°	995.1	994.1	993.0	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3
140°	1037.2	1036.1	1035.0	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8
142.5°	1075.3	1074.2	1073.2	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4
145°	1132.6	1131.4	1130.4	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5
147.5°	1183.5	1182.4	1181.4	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5
150°	1216.1	1215.2	1214.4	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2
152.5°	1247.9	1247.0	1245.9	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0
155°	1289.4	1288.5	1287.7	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2
157.5°	1327.0	1325.7	1324.4	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4
160°	1348.9	1347.7	1346.7	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4
162.5°	1369.0	1367.7	1366.4	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4
165°	1394.9	1393.5	1392.1	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1
167.5°	1416.1	1414.7	1413.2	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4
170°	1427.5	1425.9	1424.2	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1
172.5°	1436.2	1434.6	1433.0	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0
175°	1445.8	1444.2	1442.6	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5
177.5°	1449.3	1447.9	1446.6	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	15.4	16.0	15.5	14.8	13.7	13.0	12.6	12.6	13.1	13.0	12.9
90°	42.2	42.8	36.8	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2
92.5°	38.9	38.8	37.4	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8
95°	78.2	78.2	77.7	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5
97.5°	131.5	131.5	130.4	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1
100°	168.6	168.6	167.9	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2
102.5°	209.0	208.8	207.7	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2
105°	269.4	268.9	268.3	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8
107.5°	335.4	335.1	335.1	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7
110°	380.1	380.1	380.1	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	425.4	426.0	426.2	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7
115°	493.5	493.7	494.3	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9
117.5°	560.1	560.7	562.2	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8
120°	603.7	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7
122.5°	650.0	650.6	652.1	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7
125°	717.8	718.6	719.4	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2
127.5°	783.6	784.6	785.6	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1
130°	828.0	828.6	829.2	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2
132.5°	872.4	873.5	873.5	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2
135°	935.9	936.1	935.7	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3
137.5°	997.6	997.8	997.0	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5
140°	1038.8	1038.8	1037.5	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7
142.5°	1076.2	1076.0	1075.1	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8
145°	1133.2	1132.9	1131.3	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0
147.5°	1182.9	1182.3	1181.2	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2
150°	1214.4	1213.6	1212.5	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4
152.5°	1245.9	1244.9	1243.6	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7
155°	1285.8	1284.5	1283.6	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1
157.5°	1322.5	1320.7	1320.1	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0
160°	1344.7	1343.1	1342.8	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4
162.5°	1364.5	1362.7	1362.4	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9
165°	1390.3	1388.4	1388.4	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6
167.5°	1411.6	1409.6	1409.7	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5
170°	1423.2	1421.4	1421.6	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3
172.5°	1432.1	1430.1	1430.4	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0
175°	1441.6	1439.6	1440.2	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8
177.5°	1446.6	1445.3	1445.8	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	15.4	18.3	18.9	21.3	21.1	22.3	23.5	24.1	24.7	24.0	23.4
90°	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7
92.5°	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1
95°	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2
97.5°	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5
100°	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6
102.5°	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2
105°	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9
107.5°	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5
110°	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1





TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7
115°	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2
117.5°	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4
120°	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7
122.5°	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4
125°	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0
127.5°	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7
130°	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6
132.5°	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2
135°	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7
137.5°	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3
140°	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8
142.5°	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4
145°	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5
147.5°	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5
150°	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2
152.5°	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0
155°	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2
157.5°	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4
160°	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4
162.5°	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4
165°	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1
167.5°	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4
170°	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1
172.5°	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0
175°	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5
177.5°	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	23.8	23.8	23.1	23.2	23.8	23.3	23.4
90°	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331604-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)