

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331607-830

Luminaire Tested: **S122DIW-S1005D1240U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331607-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8495.4 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	79	71	68	66	58	56	54	46	44	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	52	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	1.7
10°-20°	397.5	4.7
20°-30°	584.2	6.9
30°-40°	678.6	8.0
40°-50°	677.9	8.0
50°-60°	591.2	7.0
60°-70°	437.1	5.1
70°-80°	247.6	2.9
80°-90°	70.5	0.8
90°-100°	53.1	0.6
100°-110°	194.9	2.3
110°-120°	521.0	6.1
120°-130°	860.1	10.1
130°-140°	914.7	10.8
140°-150°	850.1	10.0
150°-160°	683.5	8.0
160°-170°	440.5	5.2
170°-180°	151.6	1.8
0°-30°	1123.0	13.2
0°-40°	1801.6	21.2
0°-60°	3070.7	36.1
0°-90°	3825.9	45.0
90°-120°	769.1	9.1
90°-150°	3394.0	40.0
90°-180°	4670.0	55.0
0°-180°	8495.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	14	23	29	31	6
95°	75	39	45	50	50	92
105°	350	366	70	83	88	375
115°	663	683	711	203	94	653
125°	937	953	974	982	986	835
135°	1160	1178	1189	1200	1198	896
145°	1346	1346	1364	1371	1366	841
155°	1482	1472	1485	1491	1483	682
165°	1561	1555	1558	1565	1558	441
175°	1597	1589	1591	1598	1588	152
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.1	21.1	21.2	21.2	21.2	21.1	21.0	20.9	20.8	20.3
90°	1.1	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3
92.5°	23.3	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4
95°	74.9	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3
97.5°	148.7	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2
100°	204.1	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8
102.5°	264.9	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2
105°	350.5	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1
107.5°	448.1	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6
110°	510.8	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2



TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.8	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5
115°	663.0	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8
117.5°	746.2	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2
120°	807.1	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2
122.5°	858.8	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4
125°	937.4	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1
127.5°	1008.6	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2
130°	1053.9	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8
132.5°	1099.9	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7
135°	1159.9	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3
137.5°	1220.5	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7
140°	1260.2	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4
142.5°	1293.5	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3
145°	1345.5	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7
147.5°	1390.9	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3
150°	1420.5	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4
152.5°	1445.4	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5
155°	1481.6	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6
157.5°	1510.0	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6
160°	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0
162.5°	1541.3	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1
165°	1561.1	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4
167.5°	1575.9	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0
170°	1584.2	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4
172.5°	1589.7	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9
175°	1596.9	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9
177.5°	1598.0	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	19.8	19.2	18.8	18.4	18.3	18.1	17.9	17.8
90°	25.6	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.1	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	47.5	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	62.2	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	69.8	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	72.9	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	76.0	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	92.7	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	150.5	124.9	99.2	87.0	88.0	89.1	90.1	91.0





TEST NUMBER: P331607-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.0	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	474.1	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	730.6	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	851.3	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	903.2	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	977.9	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1046.8	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1090.6	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1133.1	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1193.8	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1250.2	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1286.8	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1320.4	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1367.5	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1408.6	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1433.9	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1457.0	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1488.1	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1514.4	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1529.7	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1543.9	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1575.7	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1583.2	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1588.7	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1594.7	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1595.3	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)