

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331535

Luminaire Tested: **S122DIW-S675D710U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331535  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D710U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5538.7 lumens  
Efficiency: N/A  
Efficacy: 123.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41					41			
2	89	81	75	70	82	75	70	65	63	60	56	53	50	47	43	41	39	34					34			
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29					29			
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25					25			
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25	22					22			
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19					19			
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17					17			
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15					15			
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14					14			
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12					12			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.8	1.8
10°-20°	280.9	5.1
20°-30°	412.9	7.5
30°-40°	479.6	8.7
40°-50°	479.1	8.6
50°-60°	417.8	7.5
60°-70°	308.9	5.6
70°-80°	175.0	3.2
80°-90°	49.4	0.9
90°-100°	32.3	0.6
100°-110°	118.3	2.1
110°-120°	316.3	5.7
120°-130°	522.2	9.4
130°-140°	555.4	10.0
140°-150°	516.2	9.3
150°-160°	415.0	7.5
160°-170°	267.4	4.8
170°-180°	92.1	1.7
0°-30°	793.6	14.3
0°-40°	1273.2	23.0
0°-60°	2170.1	39.2
0°-90°	2703.5	48.8
90°-120°	467.0	8.4
90°-150°	2060.7	37.2
90°-180°	2835.0	51.2
0°-180°	5538.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	1	8	14	17	19	4
95°	46	24	27	31	30	56
105°	213	222	43	50	53	227
115°	402	415	432	123	57	396
125°	569	578	592	596	598	507
135°	704	715	722	728	727	544
145°	817	817	828	833	830	511
155°	900	894	902	905	900	414
165°	948	944	946	950	946	268
175°	970	965	966	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	14.8	14.8	14.8	14.8	14.8	14.7	14.6	14.5	14.3	14.2	13.8
90°	0.7	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8
92.5°	14.1	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6
95°	45.5	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1
97.5°	90.3	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2
100°	123.9	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1
102.5°	160.9	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6
105°	212.8	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4
107.5°	272.0	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0
110°	310.1	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0



TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.0	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3
115°	402.5	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9
117.5°	453.1	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0
120°	490.0	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0
122.5°	521.4	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3
125°	569.1	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6
127.5°	612.4	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0
130°	639.8	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5
132.5°	667.9	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5
135°	704.3	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3
137.5°	741.1	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6
140°	765.2	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9
142.5°	785.3	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5
145°	817.0	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3
147.5°	844.5	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5
150°	862.5	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7
152.5°	877.6	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7
155°	899.6	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6
157.5°	916.8	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4
160°	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8
162.5°	935.8	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3
165°	947.9	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9
167.5°	956.8	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7
170°	961.9	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2
172.5°	965.2	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5
175°	969.6	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2
177.5°	970.3	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	13.5	13.1	12.7	12.4	12.3	12.2	12.1	11.9
90°	15.6	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.1	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	28.9	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	37.8	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	42.4	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	44.3	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	46.1	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	56.3	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	91.4	75.8	60.3	52.8	53.4	54.1	54.7	55.3





TEST NUMBER: P331535

CATALOG NUMBER: S122DIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	195.5	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	287.9	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	443.6	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	516.9	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	548.4	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	593.7	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	635.6	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	662.2	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	688.0	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	724.9	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	759.1	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	781.3	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	801.7	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	830.3	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	855.3	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	870.6	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	884.6	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	903.5	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	919.5	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	928.7	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	937.4	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	956.8	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	961.3	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	964.6	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	968.3	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	968.7	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)