

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331608-830

Luminaire Tested: **S122DIW-S1005D1240U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331608-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7877.3 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	1.8
10°-20°	397.5	5.0
20°-30°	584.2	7.4
30°-40°	678.6	8.6
40°-50°	677.9	8.6
50°-60°	591.2	7.5
60°-70°	437.1	5.5
70°-80°	247.6	3.1
80°-90°	72.4	0.9
90°-100°	91.8	1.2
100°-110°	285.0	3.6
110°-120°	487.2	6.2
120°-130°	640.7	8.1
130°-140°	719.1	9.1
140°-150°	705.1	9.0
150°-160°	591.4	7.5
160°-170°	392.2	5.0
170°-180°	137.1	1.7
0°-30°	1123.0	14.3
0°-40°	1801.6	22.9
0°-60°	3070.7	39.0
0°-90°	3827.7	48.6
90°-120°	864.0	11.0
90°-150°	2928.8	37.2
90°-180°	4050.0	51.4
0°-180°	7877.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	17	43	40	42	6
95°	64	75	78	78	76	73
105°	263	266	269	271	271	277
115°	489	496	494	492	489	483
125°	711	721	719	715	714	635
135°	920	933	936	935	931	711
145°	1117	1126	1133	1134	1129	698
155°	1277	1281	1284	1290	1287	588
165°	1390	1388	1388	1396	1391	392
175°	1446	1442	1440	1447	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.2	21.3	21.5	21.6	22.0	22.7	23.4	24.0	24.7	23.8
90°	1.2	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2
92.5°	21.8	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9
95°	63.5	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2
97.5°	116.1	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5
100°	155.2	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6
102.5°	196.2	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0
105°	262.8	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4
107.5°	329.7	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4
110°	372.8	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.7	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4
115°	488.9	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5
117.5°	557.8	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1
120°	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7
122.5°	645.7	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0
125°	711.2	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8
127.5°	775.1	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6
130°	815.2	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0
132.5°	860.2	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4
135°	920.3	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9
137.5°	983.5	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6
140°	1021.7	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8
142.5°	1060.8	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2
145°	1117.0	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2
147.5°	1167.2	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9
150°	1201.4	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4
152.5°	1231.7	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9
155°	1277.1	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8
157.5°	1316.0	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5
160°	1339.4	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7
162.5°	1360.9	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5
165°	1389.6	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3
167.5°	1413.5	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6
170°	1426.3	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2
172.5°	1435.0	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1
175°	1445.8	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6
177.5°	1450.2	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	23.0	22.1	21.2	20.6	20.5	20.3	20.1	19.9
90°	41.7	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.1	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.2	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	269.9	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.5	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	380.1	379.7	378.9	378.1	377.2	376.5





TEST NUMBER: P331608-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	424.7	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	493.2	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	559.4	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	649.4	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	717.0	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	782.7	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.6	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	871.2	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.7	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.3	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.4	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.5	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1183.5	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1287.2	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1324.4	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1346.4	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1366.4	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1392.1	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1413.4	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1425.1	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1434.0	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1443.5	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)