

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331597-830

Luminaire Tested: **S122DIW-S1005D970U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331597-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7797.1 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	2.3
10°-20°	520.4	6.7
20°-30°	755.2	9.7
30°-40°	796.9	10.2
40°-50°	705.6	9.0
50°-60°	563.1	7.2
60°-70°	382.7	4.9
70°-80°	196.2	2.5
80°-90°	50.4	0.6
90°-100°	41.5	0.5
100°-110°	152.3	2.0
110°-120°	407.0	5.2
120°-130°	671.8	8.6
130°-140°	714.5	9.2
140°-150°	664.1	8.5
150°-160°	533.9	6.8
160°-170°	344.1	4.4
170°-180°	118.4	1.5
0°-30°	1454.6	18.7
0°-40°	2251.5	28.9
0°-60°	3520.2	45.1
0°-90°	4149.6	53.2
90°-120°	600.8	7.7
90°-150°	2651.1	34.0
90°-180°	3648.0	46.8
0°-180°	7797.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	43
90°	24	1	24	1	24	13
95°	39	58	39	58	39	36
105°	68	274	68	274	68	71
115°	74	518	74	518	74	185
125°	770	732	770	732	770	666
135°	936	906	936	906	936	721
145°	1067	1051	1067	1051	1067	667
155°	1158	1157	1158	1157	1158	534
165°	1217	1220	1217	1220	1217	344
175°	1240	1247	1240	1247	1240	118
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	19.9	19.8	20.3	19.6	19.6	20.0	19.8	19.0	19.4	19.8	20.1
90°	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0	19.0	18.0	16.4
92.5°	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0	21.4	20.9	20.1
95°	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1	36.1	35.2	33.7
97.5°	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6	47.8	47.0	43.7
100°	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6	53.0	51.4	48.0
102.5°	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9	54.9	52.8	81.2
105°	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4	57.1	55.0	109.6
107.5°	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4	74.6	76.9	142.4
110°	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5	137.6	157.6	215.5



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5	324.5	397.6	411.8
115°	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3	463.0	555.7	550.7
117.5°	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6	593.0	615.5	612.1
120°	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0	662.6	660.2	656.6
122.5°	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6	704.1	702.7	698.7
125°	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8	762.4	761.0	757.2
127.5°	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7	815.7	813.6	810.8
130°	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9	849.7	847.5	845.3
132.5°	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1	883.3	881.4	879.1
135°	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6	930.6	928.6	926.7
137.5°	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6	974.7	972.7	970.6
140°	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1	1003.3	1001.5	999.3
142.5°	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4	1029.8	1028.1	1025.7
145°	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3	1066.9	1065.5	1062.1
147.5°	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3	1099.3	1098.3	1094.9
150°	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1	1118.9	1117.7	1114.5
152.5°	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1	1136.9	1135.7	1132.7
155°	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4	1161.2	1160.0	1157.6
157.5°	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9	1181.6	1180.2	1178.5
160°	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9	1193.6	1192.4	1191.3
162.5°	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0	1204.6	1203.2	1202.2
165°	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7	1216.2
167.5°	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9	1229.5	1228.1	1227.6
170°	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7	1235.3	1233.9	1233.5
172.5°	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0	1239.6	1238.2	1237.7
175°	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7	1244.3	1242.8	1242.5
177.5°	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2	1245.1	1244.0	1243.8
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	20.3	20.0	19.7	20.5	18.3	17.8	15.1	12.9	12.7	12.6	11.9
90°	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2	18.0	17.8	17.6
95°	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5	51.9	45.3	38.7
97.5°	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2	97.6	79.0	60.3
100°	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4	132.0	104.5	77.2
102.5°	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0	201.1	195.4	189.5
105°	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8	279.8	285.8	291.8
107.5°	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0	354.9	359.7	364.5
110°	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0	403.2	407.4	411.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1	448.8	452.5	456.3
115°	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8	521.2	524.7	528.1
117.5°	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9	586.7	590.5	594.3
120°	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5	633.5	636.4	639.4
122.5°	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8	673.9	677.1	680.2
125°	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2	734.8	737.4	740.0
127.5°	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9	790.8	793.6	796.5
130°	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2	826.4	829.6	832.7
132.5°	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2	862.0	864.7	867.3
135°	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1	909.3	912.5	915.7
137.5°	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4	955.6	957.9	960.2
140°	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4	986.0	987.6	989.2
142.5°	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3	1011.7	1013.2	1014.6
145°	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0	1050.8	1050.7	1050.5
147.5°	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6	1085.7	1085.0	1084.2
150°	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6	1108.1	1106.7	1105.4
152.5°	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1	1127.5	1125.9	1124.4
155°	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3	1155.5	1153.7	1151.9
157.5°	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5	1178.0	1176.4	1174.9
160°	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1191.3	1190.1	1188.8
162.5°	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0	1202.8	1201.6	1200.3
165°	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5	1218.2	1217.0	1215.9
167.5°	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0	1229.7	1228.6	1227.4
170°	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5	1236.2	1235.1	1233.9
172.5°	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8	1240.6	1239.3	1238.2
175°	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4	1245.9	1244.5	1243.2
177.5°	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3	1247.2	1246.0	1244.9
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	11.8	11.6	11.3	11.6	11.4	11.1	10.7	10.9	11.1	10.2	10.4
90°	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.1	22.7
92.5°	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0	22.4	23.0	23.4
95°	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1	38.2	39.1	39.5
97.5°	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6	49.4	50.2	50.7
100°	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6	56.2	57.8	58.7
102.5°	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9	59.0	61.1	62.4
105°	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4	61.5	63.7	65.2
107.5°	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4	70.2	68.0	67.2
110°	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5	97.6	77.6	68.0



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5	178.5	105.5	69.3
115°	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3	277.7	185.0	131.5
117.5°	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6	548.3	525.8	491.0
120°	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0	667.3	669.8	657.4
122.5°	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6	707.0	708.4	706.5
125°	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8	765.3	766.7	767.6
127.5°	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7	819.7	821.8	822.8
130°	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9	854.1	856.3	857.3
132.5°	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1	887.0	888.9	889.8
135°	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6	934.5	936.5	937.4
137.5°	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6	978.5	980.5	981.2
140°	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1	1006.9	1008.7	1009.1
142.5°	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4	1033.1	1034.7	1035.0
145°	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3	1069.7	1071.0	1071.3
147.5°	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3	1101.4	1102.4	1102.5
150°	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1	1121.2	1122.5	1122.6
152.5°	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1	1139.3	1140.5	1140.5
155°	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4	1163.6	1164.8	1164.6
157.5°	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9	1184.3	1185.6	1185.5
160°	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9	1196.0	1197.2	1197.1
162.5°	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0	1207.3	1208.7	1208.5
165°	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4
167.5°	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9	1232.3	1233.7	1233.5
170°	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7	1238.0	1239.4	1239.3
172.5°	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0	1242.4	1243.8	1243.6
175°	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7	1247.1	1248.5	1248.2
177.5°	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2	1247.3	1248.4	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	10.4	9.9	10.0	9.5	10.0	9.9	10.4	10.4	10.2	11.1	10.9
90°	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0
92.5°	23.6	23.8	24.0	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0
95°	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1
97.5°	51.0	51.2	51.5	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6
100°	59.1	59.6	59.9	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6
102.5°	63.0	63.5	64.1	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9
105°	66.1	66.8	67.7	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4
107.5°	68.1	68.8	69.7	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4
110°	68.7	69.6	70.3	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	69.9	70.6	71.3	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5
115°	117.1	102.6	88.2	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3
117.5°	443.6	396.2	348.9	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6
120°	630.5	603.4	576.4	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0
122.5°	701.3	696.1	690.8	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6
125°	768.3	768.8	769.4	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8
127.5°	823.0	823.1	823.2	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7
130°	857.1	856.9	856.7	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9
132.5°	889.5	889.3	889.1	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1
135°	937.0	936.5	936.1	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6
137.5°	980.5	979.8	979.1	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6
140°	1008.1	1007.1	1006.1	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1
142.5°	1034.1	1033.0	1032.1	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4
145°	1070.3	1069.2	1068.3	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3
147.5°	1101.6	1100.8	1099.9	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3
150°	1121.6	1120.6	1119.6	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1
152.5°	1139.2	1137.8	1136.5	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1
155°	1163.0	1161.4	1159.8	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4
157.5°	1183.9	1182.4	1180.8	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9
160°	1195.7	1194.3	1193.0	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9
162.5°	1206.7	1205.0	1203.3	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0
165°	1221.0	1219.6	1218.1	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6
167.5°	1231.7	1229.9	1228.1	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9
170°	1237.5	1235.7	1233.9	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7
172.5°	1241.8	1240.0	1238.2	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0
175°	1246.1	1244.2	1242.2	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7
177.5°	1246.8	1245.4	1244.0	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	10.7	11.1	11.4	11.6	11.3	11.6	11.8	11.9	12.6	12.7	12.9
90°	19.0	18.0	16.4	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9
92.5°	21.4	20.9	20.1	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2
95°	36.1	35.2	33.7	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5
97.5°	47.8	47.0	43.7	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2
100°	53.0	51.4	48.0	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4
102.5°	54.9	52.8	81.2	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0
105°	57.1	55.0	109.6	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8
107.5°	74.6	76.9	142.4	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0
110°	137.6	157.6	215.5	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.5	397.6	411.8	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1
115°	463.0	555.7	550.7	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8
117.5°	593.0	615.5	612.1	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9
120°	662.6	660.2	656.6	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5
122.5°	704.1	702.7	698.7	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8
125°	762.4	761.0	757.2	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2
127.5°	815.7	813.6	810.8	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9
130°	849.7	847.5	845.3	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2
132.5°	883.3	881.4	879.1	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2
135°	930.6	928.6	926.7	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1
137.5°	974.7	972.7	970.6	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4
140°	1003.3	1001.5	999.3	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4
142.5°	1029.8	1028.1	1025.7	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3
145°	1066.9	1065.5	1062.1	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0
147.5°	1099.3	1098.3	1094.9	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6
150°	1118.9	1117.7	1114.5	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6
152.5°	1136.9	1135.7	1132.7	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1
155°	1161.2	1160.0	1157.6	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3
157.5°	1181.6	1180.2	1178.5	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5
160°	1193.6	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4
162.5°	1204.6	1203.2	1202.2	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0
165°	1218.1	1216.7	1216.2	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5
167.5°	1229.5	1228.1	1227.6	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0
170°	1235.3	1233.9	1233.5	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5
172.5°	1239.6	1238.2	1237.7	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8
175°	1244.3	1242.8	1242.5	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4
177.5°	1245.1	1244.0	1243.8	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	15.1	17.8	18.3	20.5	19.7	20.0	20.3	20.1	19.8	19.4	19.0
90°	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0
92.5°	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0
95°	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1
97.5°	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6
100°	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6
102.5°	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9
105°	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4
107.5°	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4
110°	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5
115°	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3
117.5°	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6
120°	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0
122.5°	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6
125°	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8
127.5°	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7
130°	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9
132.5°	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1
135°	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6
137.5°	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6
140°	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1
142.5°	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4
145°	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3
147.5°	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3
150°	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1
152.5°	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1
155°	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4
157.5°	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9
160°	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9
162.5°	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0
165°	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6
167.5°	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9
170°	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7
172.5°	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0
175°	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7
177.5°	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	19.8	20.0	19.6	19.6	20.3	19.8	19.9
90°	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331597-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)