

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331573

Luminaire Tested: **S122DIW-S865D1240U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331573
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8767.5 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43																				
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37																				
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24																				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21																				
6	63	51	43	38	58	47	41	35	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17																				
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15																				
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	1.9
10°-20°	478.0	5.5
20°-30°	693.8	7.9
30°-40°	732.1	8.4
40°-50°	648.2	7.4
50°-60°	517.3	5.9
60°-70°	351.6	4.0
70°-80°	180.3	2.1
80°-90°	47.6	0.5
90°-100°	56.4	0.6
100°-110°	206.8	2.4
110°-120°	552.8	6.3
120°-130°	912.5	10.4
130°-140°	970.4	11.1
140°-150°	902.0	10.3
150°-160°	725.2	8.3
160°-170°	467.3	5.3
170°-180°	160.9	1.8
0°-30°	1336.2	15.2
0°-40°	2068.3	23.6
0°-60°	3233.8	36.9
0°-90°	3813.3	43.5
90°-120°	816.0	9.3
90°-150°	3600.9	41.1
90°-180°	4954.0	56.5
0°-180°	8767.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	33	1	33	1	33	16
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	703	100	703	100	251
125°	1046	994	1046	994	1046	905
135°	1271	1231	1271	1231	1271	980
145°	1450	1428	1450	1428	1450	907
155°	1573	1572	1573	1572	1573	726
165°	1653	1656	1653	1656	1653	467
175°	1684	1694	1684	1694	1684	160
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	20.4	20.3	20.7	20.1	20.0	20.3	20.0	19.2	19.5	19.8	19.9
90°	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2	25.8	24.5	22.3
92.5°	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8	29.1	28.4	27.3
95°	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4	49.1	47.7	45.8
97.5°	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0	64.9	63.9	59.5
100°	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1	71.9	69.7	65.1
102.5°	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3	74.5	71.7	110.3
105°	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6	77.6	74.6	148.8
107.5°	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4	101.4	104.5	193.5
110°	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7	186.9	214.1	292.6



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6	440.8	539.9	559.4
115°	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0	628.9	754.8	748.0
117.5°	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1	805.5	836.0	831.3
120°	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2	899.9	896.6	891.8
122.5°	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3	956.3	954.4	949.1
125°	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5	1035.6	1033.7	1028.5
127.5°	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6	1107.9	1105.1	1101.2
130°	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1	1154.1	1151.1	1148.1
132.5°	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2	1199.6	1197.1	1194.1
135°	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6	1263.9	1261.2	1258.7
137.5°	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4	1323.8	1321.1	1318.3
140°	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2	1362.7	1360.3	1357.3
142.5°	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9	1398.7	1396.5	1393.0
145°	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9	1449.0	1447.1	1442.5
147.5°	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5	1493.1	1491.6	1487.1
150°	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3	1519.7	1518.1	1513.7
152.5°	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8	1544.2	1542.5	1538.4
155°	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8	1577.2	1575.6	1572.3
157.5°	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7	1604.8	1603.0	1600.7
160°	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9	1621.2	1619.6	1618.0
162.5°	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0	1636.1	1634.3	1632.9
165°	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6	1651.8
167.5°	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8	1669.9	1668.0	1667.3
170°	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7	1677.8	1675.9	1675.3
172.5°	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5	1683.6	1681.7	1681.2
175°	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9	1690.0	1688.1	1687.6
177.5°	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6	1691.1	1689.6	1689.3
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	19.9	19.5	19.1	19.6	17.4	16.8	14.1	11.9	12.0	12.1	11.6
90°	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7	24.4	24.2	23.9
95°	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5	70.5	61.6	52.6
97.5°	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8	132.5	107.2	82.0
100°	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5	179.3	142.0	104.8
102.5°	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1	273.2	265.3	257.5
105°	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9	380.0	388.2	396.3
107.5°	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4	481.9	488.5	495.1
110°	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9	547.6	553.3	559.0



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5	609.6	614.6	619.7
115°	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4	708.0	712.6	717.2
117.5°	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7	796.9	802.0	807.2
120°	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3	860.4	864.4	868.5
122.5°	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1	915.4	919.7	924.0
125°	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5	998.0	1001.6	1005.1
127.5°	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1	1074.0	1077.9	1081.9
130°	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1	1122.4	1126.8	1131.1
132.5°	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0	1170.7	1174.4	1178.1
135°	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6	1234.9	1239.3	1243.6
137.5°	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9	1298.0	1301.0	1304.1
140°	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0	1339.2	1341.4	1343.5
142.5°	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3	1374.2	1376.2	1378.1
145°	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5	1427.3	1427.0	1426.7
147.5°	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7	1474.7	1473.7	1472.6
150°	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1	1505.2	1503.3	1501.3
152.5°	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5	1531.4	1529.2	1527.1
155°	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9	1569.4	1567.0	1564.5
157.5°	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0	1599.9	1597.8	1595.8
160°	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1618.0	1616.3	1614.7
162.5°	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3	1633.6	1632.0	1630.4
165°	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3	1654.7	1653.0	1651.4
167.5°	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0	1670.3	1668.7	1667.1
170°	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8	1679.1	1677.5	1675.9
172.5°	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6	1685.0	1683.4	1681.7
175°	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2	1692.3	1690.4	1688.5
177.5°	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4	1693.9	1692.4	1690.9
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	11.7	11.6	11.6	12.0	11.9	11.8	11.5	11.8	12.1	11.3	11.5
90°	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2	28.5	29.9	30.9
92.5°	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8	30.5	31.2	31.7
95°	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4	51.8	53.1	53.7
97.5°	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0	67.1	68.2	68.9
100°	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1	76.2	78.4	79.8
102.5°	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3	80.2	83.0	84.8
105°	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6	83.6	86.6	88.6
107.5°	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4	95.3	92.3	91.3
110°	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7	132.5	105.3	92.3



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6	242.5	143.3	94.1
115°	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0	377.2	251.3	178.6
117.5°	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1	744.6	714.2	666.8
120°	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2	906.4	909.7	893.0
122.5°	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3	960.3	962.2	959.6
125°	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5	1039.4	1041.3	1042.6
127.5°	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6	1113.4	1116.2	1117.7
130°	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1	1160.1	1163.0	1164.4
132.5°	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2	1204.7	1207.3	1208.4
135°	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6	1269.3	1272.1	1273.1
137.5°	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4	1329.1	1331.8	1332.6
140°	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2	1367.6	1370.1	1370.6
142.5°	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9	1403.2	1405.4	1405.8
145°	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9	1452.8	1454.7	1455.0
147.5°	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5	1495.9	1497.3	1497.4
150°	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3	1523.0	1524.6	1524.7
152.5°	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8	1547.4	1549.1	1549.0
155°	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8	1580.5	1582.1	1581.8
157.5°	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7	1608.5	1610.4	1610.2
160°	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9	1624.5	1626.1	1626.0
162.5°	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0	1639.8	1641.7	1641.4
165°	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2
167.5°	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8	1673.7	1675.6	1675.4
170°	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7	1681.6	1683.5	1683.2
172.5°	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5	1687.4	1689.3	1689.1
175°	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9	1693.8	1695.7	1695.3
177.5°	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6	1694.1	1695.7	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	11.6	11.2	11.3	10.9	11.3	11.2	11.6	11.5	11.3	12.1	11.8
90°	31.4	31.9	32.5	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2
92.5°	32.0	32.4	32.7	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8
95°	53.4	53.1	52.9	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4
97.5°	69.2	69.6	69.9	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0
100°	80.3	80.9	81.4	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1
102.5°	85.5	86.3	87.1	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3
105°	89.7	90.8	91.9	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6
107.5°	92.4	93.5	94.6	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4
110°	93.4	94.5	95.6	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.0	95.9	96.7	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6
115°	159.0	139.5	119.9	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0
117.5°	602.5	538.2	473.9	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1
120°	856.3	819.6	782.9	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2
122.5°	952.5	945.4	938.3	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3
125°	1043.4	1044.3	1045.1	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5
127.5°	1117.8	1118.0	1118.1	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6
130°	1164.1	1163.9	1163.6	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1
132.5°	1208.2	1207.9	1207.6	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2
135°	1272.6	1272.1	1271.5	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6
137.5°	1331.7	1330.8	1329.9	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4
140°	1369.2	1367.9	1366.5	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2
142.5°	1404.5	1403.1	1401.7	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9
145°	1453.6	1452.3	1450.9	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9
147.5°	1496.3	1495.1	1494.0	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5
150°	1523.4	1522.0	1520.6	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3
152.5°	1547.2	1545.4	1543.6	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8
155°	1579.6	1577.5	1575.3	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8
157.5°	1608.1	1606.0	1603.9	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7
160°	1624.1	1622.2	1620.3	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9
162.5°	1639.1	1636.7	1634.4	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0
165°	1658.3	1656.4	1654.5	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4
167.5°	1672.9	1670.5	1668.0	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8
170°	1680.8	1678.3	1675.9	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7
172.5°	1686.6	1684.2	1681.7	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5
175°	1692.6	1689.9	1687.1	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9
177.5°	1693.5	1691.5	1689.6	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	11.5	11.8	11.9	12.0	11.6	11.6	11.7	11.6	12.1	12.0	11.9
90°	25.8	24.5	22.3	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7
95°	49.1	47.7	45.8	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5
97.5°	64.9	63.9	59.5	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8
100°	71.9	69.7	65.1	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5
102.5°	74.5	71.7	110.3	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1
105°	77.6	74.6	148.8	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9
107.5°	101.4	104.5	193.5	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4
110°	186.9	214.1	292.6	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	440.8	539.9	559.4	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5
115°	628.9	754.8	748.0	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4
117.5°	805.5	836.0	831.3	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7
120°	899.9	896.6	891.8	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3
122.5°	956.3	954.4	949.1	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1
125°	1035.6	1033.7	1028.5	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5
127.5°	1107.9	1105.1	1101.2	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1
130°	1154.1	1151.1	1148.1	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1
132.5°	1199.6	1197.1	1194.1	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0
135°	1263.9	1261.2	1258.7	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6
137.5°	1323.8	1321.1	1318.3	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9
140°	1362.7	1360.3	1357.3	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0
142.5°	1398.7	1396.5	1393.0	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3
145°	1449.0	1447.1	1442.5	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5
147.5°	1493.1	1491.6	1487.1	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7
150°	1519.7	1518.1	1513.7	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1
152.5°	1544.2	1542.5	1538.4	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5
155°	1577.2	1575.6	1572.3	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9
157.5°	1604.8	1603.0	1600.7	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0
160°	1621.2	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6
162.5°	1636.1	1634.3	1632.9	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3
165°	1654.5	1652.6	1651.8	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3
167.5°	1669.9	1668.0	1667.3	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0
170°	1677.8	1675.9	1675.3	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8
172.5°	1683.6	1681.7	1681.2	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6
175°	1690.0	1688.1	1687.6	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2
177.5°	1691.1	1689.6	1689.3	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	14.1	16.8	17.4	19.6	19.1	19.5	19.9	19.9	19.8	19.5	19.2
90°	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2
92.5°	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8
95°	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4
97.5°	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0
100°	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1
102.5°	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3
105°	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6
107.5°	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4
110°	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6
115°	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0
117.5°	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1
120°	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2
122.5°	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3
125°	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5
127.5°	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6
130°	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1
132.5°	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2
135°	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6
137.5°	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4
140°	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2
142.5°	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9
145°	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9
147.5°	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5
150°	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3
152.5°	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8
155°	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8
157.5°	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7
160°	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9
162.5°	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0
165°	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4
167.5°	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8
170°	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7
172.5°	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5
175°	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9
177.5°	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	20.0	20.3	20.0	20.1	20.7	20.3	20.4
90°	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331573

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)