

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331574

Luminaire Tested: **S122DIW-S865D1240U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331574
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8111.6 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				40	
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39				35	
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34				30	
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30				26	
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26				23	
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23				20	
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	2.0
10°-20°	478.0	5.9
20°-30°	693.8	8.6
30°-40°	732.1	9.0
40°-50°	648.2	8.0
50°-60°	517.3	6.4
60°-70°	351.6	4.3
70°-80°	180.3	2.2
80°-90°	49.6	0.6
90°-100°	97.4	1.2
100°-110°	302.4	3.7
110°-120°	516.9	6.4
120°-130°	679.7	8.4
130°-140°	762.9	9.4
140°-150°	748.1	9.2
150°-160°	627.4	7.7
160°-170°	416.2	5.1
170°-180°	145.5	1.8
0°-30°	1336.2	16.5
0°-40°	2068.3	25.5
0°-60°	3233.8	39.9
0°-90°	3815.2	47.0
90°-120°	916.6	11.3
90°-150°	3107.4	38.3
90°-180°	4296.0	53.0
0°-180°	8111.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	44	1	44	1	44	21
95°	80	67	80	67	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	512
125°	757	755	757	755	757	675
135°	988	976	988	976	988	761
145°	1198	1185	1198	1185	1198	748
155°	1365	1355	1365	1355	1365	628
165°	1476	1474	1476	1474	1476	416
175°	1529	1534	1529	1534	1529	145
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	22.6	22.6	23.0	22.4	22.4	22.9	23.1	22.6	23.3	23.9	23.2
90°	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2	44.8	45.4	39.0
92.5°	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5	41.3	41.2	39.7
95°	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0	83.0	83.0	82.4
97.5°	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5	139.5	139.5	138.4
100°	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9	178.9	178.9	178.1
102.5°	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9	221.7	221.5	220.4
105°	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4	285.8	285.3	284.7
107.5°	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0	355.8	355.5	355.5
110°	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6	451.3	452.0	452.2
115°	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3	523.6	523.8	524.4
117.5°	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5	594.2	594.9	596.5
120°	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5	640.5	640.5	642.8
122.5°	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0	689.6	690.3	691.9
125°	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7	761.6	762.4	763.3
127.5°	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4	831.4	832.4	833.5
130°	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0	878.5	879.1	879.7
132.5°	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3	925.6	926.8	926.7
135°	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7	992.9	993.2	992.7
137.5°	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1	1058.4	1058.6	1057.8
140°	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1	1102.1	1102.1	1100.7
142.5°	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0	1141.8	1141.6	1140.6
145°	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6	1202.3	1202.0	1200.3
147.5°	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6	1255.0	1254.4	1253.2
150°	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6	1286.4
152.5°	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8	1319.4
155°	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7	1364.2	1362.8	1361.9
157.5°	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1	1403.1	1401.2	1400.6
160°	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5	1426.7	1425.0	1424.7
162.5°	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7	1447.7	1445.8	1445.5
165°	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0	1475.0	1473.0	1473.0
167.5°	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6	1497.6	1495.5	1495.6
170°	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0	1510.0	1508.0	1508.3
172.5°	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4	1519.4	1517.3	1517.6
175°	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5	1529.5	1527.4	1528.0
177.5°	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4	1533.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	22.5	21.2	19.9	20.0	17.7	17.0	14.2	11.9	12.1	12.3	11.9
90°	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1	25.6	28.2	30.7
95°	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4	70.3	73.2	76.1
97.5°	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2	125.7	128.3	130.8
100°	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7	167.0	169.3	171.6
102.5°	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2	210.1	211.9	213.8
105°	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8	279.6	280.5	281.4
107.5°	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8	351.1	352.4	353.6
110°	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5	397.2	398.9	400.7



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3	447.0	448.7	450.5
115°	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7	520.4	522.1	523.8
117.5°	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8	594.1	596.4	598.7
120°	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	642.8	645.2	647.5
122.5°	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1	687.9	690.7	693.4
125°	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6	757.2	759.8	762.4
127.5°	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3	825.6	828.9	832.2
130°	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9	868.6	872.4	876.1
132.5°	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6	915.6	918.7	921.7
135°	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4	979.5	982.7	985.9
137.5°	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5	1046.1	1048.7	1051.3
140°	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0	1086.6	1089.2	1091.8
142.5°	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5	1128.1	1130.7	1133.3
145°	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1	1187.2	1189.2	1191.2
147.5°	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3	1240.7	1243.1	1245.6
150°	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6	1276.3	1278.1	1279.8
152.5°	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8	1308.5	1310.2	1311.9
155°	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0	1355.9	1356.7	1357.6
157.5°	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2	1396.8	1397.4	1398.0
160°	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1	1421.7	1422.3	1422.9
162.5°	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9	1444.1	1444.2	1444.3
165°	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3	1474.0	1473.7	1473.4
167.5°	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7	1498.8	1498.0	1497.1
170°	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2	1512.3	1511.5	1510.6
172.5°	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5	1521.7	1520.8	1519.9
175°	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9	1533.1	1532.2	1531.3
177.5°	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6	1537.9	1537.2	1536.5
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	12.0	12.5	13.2	14.5	15.2	16.0	15.3	15.2	15.1	13.9	13.9
90°	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2	43.7	43.1	42.9
92.5°	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5	41.6	41.7	41.8
95°	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0	83.0	83.0	82.7
97.5°	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5	139.5	139.5	139.5
100°	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9	178.9	178.9	178.8
102.5°	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9	222.2	222.4	222.4
105°	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4	287.0	287.6	287.9
107.5°	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0	356.2	356.5	355.9
110°	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	402.8



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6	449.9	449.2	448.6
115°	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3	523.0	522.7	522.1
117.5°	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5	592.8	592.1	591.4
120°	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5	640.5	640.5	640.1
122.5°	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0	688.3	687.6	686.9
125°	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7	759.8	759.0	758.4
127.5°	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4	829.3	828.3	827.3
130°	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0	877.4	876.8	876.0
132.5°	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3	923.0	921.8	920.7
135°	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7	992.4	992.1	991.5
137.5°	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1	1057.9	1057.7	1057.0
140°	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1	1102.1	1102.1	1101.6
142.5°	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0	1142.3	1142.5	1142.0
145°	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6	1202.9	1203.1	1202.7
147.5°	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6	1256.3	1256.9	1256.7
150°	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0
152.5°	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1
155°	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7	1367.1	1368.5	1368.8
157.5°	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1	1407.0	1409.0	1409.3
160°	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5	1430.2	1431.9	1432.2
162.5°	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7	1451.6	1453.6	1453.9
165°	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0	1479.0	1481.1	1481.3
167.5°	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6	1501.6	1503.6	1503.9
170°	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0	1514.0	1516.1	1516.2
172.5°	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4	1523.4	1525.4	1525.5
175°	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5	1533.5	1535.5	1535.7
177.5°	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	14.0	13.5	13.5	13.1	13.5	13.5	14.0	13.9	13.9	15.1	15.2
90°	43.2	43.5	43.8	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5
95°	82.1	81.5	81.0	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0
97.5°	139.4	139.4	139.3	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5
100°	178.5	178.2	177.9	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9
102.5°	222.1	221.8	221.5	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9
105°	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4
107.5°	354.6	353.3	351.9	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0
110°	402.0	401.1	400.2	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	447.9	447.3	446.7	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6
115°	521.3	520.4	519.5	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3
117.5°	590.5	589.6	588.8	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5
120°	639.2	638.4	637.5	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5
122.5°	686.3	685.6	685.0	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0
125°	758.1	757.8	757.5	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7
127.5°	826.4	825.5	824.6	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4
130°	874.8	873.7	872.5	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0
132.5°	919.8	918.8	917.9	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3
135°	990.6	989.8	988.9	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7
137.5°	1055.8	1054.7	1053.5	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1
140°	1100.4	1099.3	1098.1	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1
142.5°	1140.9	1139.7	1138.6	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0
145°	1201.6	1200.4	1199.3	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6
147.5°	1255.6	1254.5	1253.4	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6
150°	1290.2	1289.3	1288.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3
152.5°	1324.0	1323.0	1321.9	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0
155°	1368.0	1367.1	1366.2	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7
157.5°	1407.9	1406.5	1405.1	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1
160°	1431.1	1429.9	1428.8	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5
162.5°	1452.5	1451.1	1449.7	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7
165°	1479.9	1478.5	1477.0	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0
167.5°	1502.4	1500.9	1499.4	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6
170°	1514.5	1512.8	1511.0	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0
172.5°	1523.8	1522.1	1520.4	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4
175°	1533.9	1532.2	1530.5	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5
177.5°	1537.6	1536.2	1534.8	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	15.3	16.0	15.2	14.5	13.2	12.5	12.0	11.9	12.3	12.1	11.9
90°	44.8	45.4	39.0	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3
92.5°	41.3	41.2	39.7	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1
95°	83.0	83.0	82.4	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4
97.5°	139.5	139.5	138.4	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2
100°	178.9	178.9	178.1	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7
102.5°	221.7	221.5	220.4	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2
105°	285.8	285.3	284.7	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8
107.5°	355.8	355.5	355.5	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8
110°	403.3	403.3	403.3	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.3	452.0	452.2	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3
115°	523.6	523.8	524.4	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7
117.5°	594.2	594.9	596.5	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8
120°	640.5	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5
122.5°	689.6	690.3	691.9	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1
125°	761.6	762.4	763.3	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6
127.5°	831.4	832.4	833.5	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3
130°	878.5	879.1	879.7	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9
132.5°	925.6	926.8	926.7	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6
135°	992.9	993.2	992.7	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4
137.5°	1058.4	1058.6	1057.8	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5
140°	1102.1	1102.1	1100.7	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0
142.5°	1141.8	1141.6	1140.6	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5
145°	1202.3	1202.0	1200.3	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1
147.5°	1255.0	1254.4	1253.2	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3
150°	1288.4	1287.6	1286.4	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6
152.5°	1321.9	1320.8	1319.4	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8
155°	1364.2	1362.8	1361.9	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0
157.5°	1403.1	1401.2	1400.6	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2
160°	1426.7	1425.0	1424.7	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1
162.5°	1447.7	1445.8	1445.5	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9
165°	1475.0	1473.0	1473.0	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3
167.5°	1497.6	1495.5	1495.6	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7
170°	1510.0	1508.0	1508.3	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2
172.5°	1519.4	1517.3	1517.6	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5
175°	1529.5	1527.4	1528.0	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9
177.5°	1534.8	1533.4	1533.9	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	14.2	17.0	17.7	20.0	19.9	21.2	22.5	23.2	23.9	23.3	22.6
90°	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2
92.5°	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5
95°	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0
97.5°	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5
100°	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9
102.5°	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9
105°	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4
107.5°	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0
110°	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6
115°	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3
117.5°	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5
120°	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5
122.5°	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0
125°	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7
127.5°	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4
130°	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0
132.5°	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3
135°	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7
137.5°	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1
140°	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1
142.5°	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0
145°	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6
147.5°	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6
150°	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3
152.5°	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0
155°	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7
157.5°	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1
160°	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5
162.5°	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7
165°	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0
167.5°	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6
170°	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0
172.5°	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4
175°	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5
177.5°	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	23.1	22.9	22.4	22.4	23.0	22.6	22.6
90°	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331574

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)