

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331469-830

Luminaire Tested: **S122DIW-S290D435U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331469-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D435U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2765.8 lumens  
Efficiency: N/A  
Efficacy: 120.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	42	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.9	1.5
10°-20°	117.8	4.3
20°-30°	173.2	6.3
30°-40°	201.2	7.3
40°-50°	200.9	7.3
50°-60°	175.2	6.3
60°-70°	129.6	4.7
70°-80°	73.4	2.7
80°-90°	21.1	0.8
90°-100°	18.6	0.7
100°-110°	68.1	2.5
110°-120°	182.0	6.6
120°-130°	300.5	10.9
130°-140°	319.6	11.6
140°-150°	297.0	10.7
150°-160°	238.8	8.6
160°-170°	153.9	5.6
170°-180°	53.0	1.9
0°-30°	332.9	12.0
0°-40°	534.0	19.3
0°-60°	910.2	32.9
0°-90°	1134.3	41.0
90°-120°	268.7	9.7
90°-150°	1185.9	42.9
90°-180°	1632.0	59.0
0°-180°	2765.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	0	5	8	10	11	2
95°	26	14	16	18	17	32
105°	122	128	25	29	31	131
115°	232	239	248	71	33	228
125°	328	333	340	343	344	292
135°	405	412	415	419	419	313
145°	470	470	476	479	477	294
155°	518	514	519	521	518	238
165°	545	543	544	547	544	154
175°	558	555	556	558	555	53
180°	557	557	557	557	557	



TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.2	6.3	6.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.3
90°	0.4	1.4	2.4	3.4	4.3	5.2	5.9	6.6	7.4	8.0	8.5
92.5°	8.1	8.0	7.9	7.8	7.8	7.9	8.3	8.7	9.0	9.3	9.6
95°	26.2	23.2	20.3	17.3	14.3	13.2	13.9	14.4	15.1	15.7	16.1
97.5°	51.9	43.6	35.3	27.0	18.7	15.3	16.7	18.1	19.6	21.0	21.4
100°	71.4	59.0	46.8	34.5	22.2	16.9	18.4	19.9	21.4	23.0	23.7
102.5°	92.6	90.0	87.4	84.8	82.2	74.6	61.8	49.1	36.4	23.6	24.5
105°	122.4	125.2	127.8	130.5	133.2	122.3	97.9	73.4	49.0	24.6	25.5
107.5°	156.6	158.7	160.9	163.1	165.2	151.7	122.3	93.0	63.7	34.4	33.4
110°	178.4	180.3	182.2	184.1	186.0	174.0	148.1	122.2	96.3	70.5	61.5



TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.1	200.8	202.5	204.1	205.8	203.4	197.0	190.6	184.2	177.9	145.2
115°	231.7	233.2	234.7	236.2	237.7	239.6	241.9	244.1	246.3	248.5	207.1
117.5°	260.7	262.4	264.1	265.8	267.5	269.2	270.7	272.2	273.8	275.3	265.3
120°	282.0	283.3	284.6	286.1	287.4	288.9	290.5	292.1	293.7	295.3	296.3
122.5°	300.0	301.4	302.8	304.3	305.7	307.3	309.1	310.8	312.5	314.3	315.0
125°	327.5	328.7	329.9	331.0	332.2	333.6	335.4	337.1	338.7	340.4	341.0
127.5°	352.4	353.7	355.0	356.3	357.6	358.8	360.1	361.4	362.7	363.9	364.9
130°	368.3	369.7	371.1	372.5	373.9	375.1	376.2	377.1	378.1	379.1	380.0
132.5°	384.4	385.5	386.7	388.0	389.2	390.3	391.2	392.3	393.2	394.3	395.1
135°	405.3	406.7	408.1	409.5	411.0	412.1	412.9	413.8	414.5	415.4	416.2
137.5°	426.5	427.4	428.5	429.5	430.5	431.4	432.3	433.3	434.1	435.1	435.9
140°	440.4	441.0	441.8	442.4	443.2	444.0	445.1	446.0	447.0	448.0	448.7
142.5°	451.9	452.6	453.2	453.8	454.5	455.4	456.5	457.6	458.7	459.9	460.6
145°	470.1	470.0	470.0	469.9	469.8	470.5	472.0	473.5	475.0	476.5	477.2
147.5°	486.0	485.7	485.3	485.0	484.7	485.2	486.7	488.2	489.7	491.3	491.7
150°	496.3	495.7	495.0	494.5	493.8	494.2	495.7	497.1	498.5	499.9	500.5
152.5°	505.0	504.4	503.6	502.9	502.2	502.6	503.9	505.3	506.6	508.0	508.5
155°	517.6	516.9	516.0	515.3	514.4	514.6	515.7	516.7	517.8	518.9	519.4
157.5°	527.5	526.9	526.2	525.6	524.9	524.9	525.7	526.4	527.2	527.9	528.5
160°	533.4	532.8	532.3	531.8	531.2	531.2	531.8	532.3	532.8	533.4	534.0
162.5°	538.6	538.0	537.4	537.0	536.4	536.4	536.8	537.2	537.7	538.2	538.9
165°	545.4	545.0	544.4	543.8	543.3	543.2	543.5	543.8	544.0	544.2	544.9
167.5°	550.6	550.1	549.6	549.0	548.5	548.4	548.6	548.8	549.1	549.3	550.0
170°	553.6	553.0	552.4	552.0	551.4	551.2	551.4	551.6	551.8	552.0	552.5
172.5°	555.4	555.0	554.4	553.8	553.3	553.2	553.3	553.5	553.6	553.8	554.5
175°	558.0	557.3	556.7	556.1	555.4	555.3	555.4	555.6	555.7	555.9	556.6
177.5°	558.4	557.9	557.3	556.9	556.4	556.1	556.2	556.3	556.4	556.4	556.9
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8



TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	6.1	6.0	5.8	5.7	5.7	5.7	5.7	5.6
90°	9.0	9.4	9.8	10.2	10.4	10.6	10.7	10.8
92.5°	9.8	10.1	10.3	10.5	10.6	10.7	10.7	10.8
95°	16.6	17.1	17.5	17.7	17.6	17.5	17.4	17.3
97.5°	21.8	22.1	22.4	22.7	22.8	22.9	23.0	23.1
100°	24.4	25.1	25.8	26.3	26.5	26.7	26.8	27.0
102.5°	25.4	26.4	27.3	27.9	28.2	28.5	28.7	28.9
105°	26.6	27.5	28.6	29.2	29.5	29.9	30.3	30.6
107.5°	32.4	31.4	30.3	30.1	30.4	30.8	31.1	31.5
110°	52.6	43.6	34.7	30.3	30.7	31.1	31.5	31.9





TEST NUMBER: P331469-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.5	79.8	47.2	31.0	31.3	31.6	31.9	32.1
115°	165.7	124.2	82.8	58.8	52.4	45.9	39.5	33.0
117.5°	255.2	245.2	235.2	219.6	198.4	177.2	156.1	134.9
120°	297.5	298.5	299.6	294.1	282.0	269.9	257.8	245.7
122.5°	315.6	316.2	316.9	316.0	313.7	311.3	309.0	306.6
125°	341.7	342.3	342.9	343.4	343.7	343.9	344.2	344.4
127.5°	365.8	366.6	367.6	368.1	368.2	368.2	368.3	368.3
130°	381.1	382.0	383.0	383.5	383.4	383.3	383.2	383.1
132.5°	396.0	396.7	397.6	397.9	397.8	397.8	397.8	397.7
135°	417.2	418.0	419.0	419.2	419.1	419.0	418.8	418.6
137.5°	436.9	437.7	438.6	438.8	438.6	438.3	438.0	437.6
140°	449.6	450.4	451.2	451.4	450.9	450.4	450.1	449.6
142.5°	461.4	462.1	462.9	463.0	462.5	462.1	461.7	461.2
145°	477.9	478.4	479.1	479.2	478.7	478.2	477.9	477.4
147.5°	492.2	492.7	493.1	493.1	492.8	492.4	492.0	491.6
150°	501.1	501.5	502.1	502.2	501.7	501.2	500.8	500.4
152.5°	509.1	509.6	510.2	510.1	509.5	509.0	508.3	507.7
155°	520.0	520.5	521.0	520.9	520.2	519.5	518.8	518.1
157.5°	529.1	529.7	530.4	530.3	529.6	528.9	528.2	527.5
160°	534.4	535.0	535.6	535.5	534.9	534.2	533.6	533.0
162.5°	539.4	540.1	540.6	540.5	539.8	539.0	538.3	537.5
165°	545.5	546.1	546.8	546.8	546.1	545.5	544.9	544.2
167.5°	550.6	551.2	551.9	551.8	550.9	550.2	549.3	548.6
170°	553.2	553.8	554.4	554.3	553.6	552.7	552.0	551.1
172.5°	555.1	555.7	556.4	556.3	555.4	554.7	553.8	553.1
175°	557.2	557.8	558.5	558.4	557.4	556.6	555.6	554.8
177.5°	557.4	557.9	558.5	558.4	557.7	557.0	556.4	555.8
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8

(END OF REPORT)