

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331578

Luminaire Tested: **S122DIW-S865D1240U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331578
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7813.5 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45					45			
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38					38			
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32					32			
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27					27			
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23					23			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20					20			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18					18			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16					16			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14					14			
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13					13			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22281	22281	22281
5°	22366	22044	22174
10°	22233	21820	21930
15°	21959	21538	21514
20°	21569	21113	21089
25°	21180	20591	20591
30°	20681	20113	19939
35°	20217	19537	19249
40°	19633	18963	18598
45°	19057	18393	17938
50°	18432	17799	17166
55°	17779	17106	16473
60°	17053	16281	15684
65°	16275	15461	14751
70°	15286	14469	13780
75°	13905	13325	12994
80°	12338	11967	11353
85°	10078	9596	8596



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	1.7
10°-20°	365.1	4.7
20°-30°	536.7	6.9
30°-40°	623.4	8.0
40°-50°	622.7	8.0
50°-60°	543.1	7.0
60°-70°	401.6	5.1
70°-80°	227.4	2.9
80°-90°	67.3	0.9
90°-100°	97.4	1.2
100°-110°	302.4	3.9
110°-120°	516.9	6.6
120°-130°	679.7	8.7
130°-140°	762.9	9.8
140°-150°	748.1	9.6
150°-160°	627.4	8.0
160°-170°	416.2	5.3
170°-180°	145.5	1.9
0°-30°	1031.6	13.2
0°-40°	1655.0	21.2
0°-60°	2820.8	36.1
0°-90°	3517.1	45.0
90°-120°	916.6	11.7
90°-150°	3107.4	39.8
90°-180°	4296.0	55.0
0°-180°	7813.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1380	1374	1360	1370	1368	131
15°	1314	1305	1288	1293	1287	370
25°	1189	1178	1156	1158	1156	547
35°	1026	1012	991	983	977	640
45°	835	825	806	791	786	644
55°	632	623	608	592	585	565
65°	426	418	405	393	386	421
75°	223	220	214	206	208	238
85°	54	53	52	48	46	62
90°	1	18	45	43	44	6
95°	67	80	83	83	80	77
105°	279	283	285	288	288	294
115°	519	526	524	522	519	513
125°	755	765	762	759	757	674
135°	976	990	993	992	988	754
145°	1185	1194	1202	1203	1198	740
155°	1355	1359	1363	1369	1365	623
165°	1474	1473	1473	1481	1476	416
175°	1534	1530	1527	1536	1529	146
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1386.4	1385.2	1384.0	1382.9	1381.7	1379.8	1377.2	1374.6	1372.0	1369.4	1371.8
5°	1380.0	1378.8	1377.7	1376.5	1375.3	1373.1	1369.9	1366.6	1363.4	1360.1	1362.5
7.5°	1367.8	1366.0	1364.2	1362.3	1360.5	1357.9	1354.6	1351.3	1348.0	1344.7	1347.1
10°	1356.1	1354.1	1352.0	1349.9	1347.9	1345.1	1341.5	1338.0	1334.5	1330.9	1333.3
12.5°	1340.2	1338.4	1336.6	1334.7	1332.9	1330.2	1326.7	1323.1	1319.6	1316.1	1317.7
15°	1313.7	1311.9	1310.1	1308.4	1306.6	1303.8	1300.0	1296.1	1292.3	1288.5	1289.6
17.5°	1279.7	1277.9	1276.2	1274.4	1272.6	1269.8	1265.9	1262.0	1258.1	1254.2	1255.6
20°	1255.3	1253.5	1251.8	1250.0	1248.2	1245.3	1241.1	1237.0	1232.9	1228.8	1229.6
22.5°	1230.9	1228.4	1225.9	1223.4	1221.0	1217.8	1213.9	1210.0	1206.1	1202.2	1202.4
25°	1188.9	1186.6	1184.2	1181.9	1179.5	1175.8	1170.8	1165.8	1160.8	1155.8	1156.4
27.5°	1141.2	1139.1	1136.9	1134.8	1132.7	1129.6	1125.7	1121.7	1117.8	1113.8	1113.0
30°	1109.3	1107.0	1104.6	1102.3	1099.9	1096.5	1092.1	1087.7	1083.2	1078.8	1077.9
32.5°	1075.4	1073.5	1071.6	1069.7	1067.8	1064.5	1059.9	1055.2	1050.6	1045.9	1044.3
35°	1025.7	1022.8	1019.8	1016.9	1013.9	1010.1	1005.4	1000.7	995.9	991.2	989.5
37.5°	969.7	967.1	964.5	961.9	959.4	955.7	951.0	946.3	941.5	936.8	934.6
40°	931.5	929.2	926.8	924.4	922.1	918.5	913.8	909.1	904.4	899.7	897.0
42.5°	894.4	892.0	889.6	887.3	884.9	881.4	876.7	872.0	867.2	862.5	859.6
45°	834.6	832.6	830.5	828.5	826.4	823.1	818.7	814.3	809.9	805.5	802.2
47.5°	775.2	773.3	771.3	769.4	767.4	764.1	759.5	754.9	750.3	745.7	742.3
50°	733.8	732.3	730.9	729.4	727.9	725.1	721.0	716.8	712.7	708.6	704.5
52.5°	693.5	691.5	689.6	687.6	685.7	682.8	678.9	675.0	671.1	667.2	663.8
55°	631.6	629.9	628.1	626.3	624.5	621.9	618.4	614.8	611.3	607.7	604.2
57.5°	569.5	568.1	566.7	565.3	563.9	561.2	557.3	553.4	549.5	545.6	542.2
60°	528.1	526.9	525.8	524.6	523.4	520.8	516.6	512.5	508.4	504.2	501.0
62.5°	487.8	485.9	484.0	482.1	480.2	477.7	474.5	471.3	468.1	465.0	462.0
65°	426.0	424.2	422.4	420.6	418.9	416.5	413.6	410.6	407.7	404.7	402.1
67.5°	363.1	361.6	360.2	358.8	357.4	355.4	352.7	350.0	347.4	344.7	342.7
70°	323.8	322.6	321.4	320.2	319.1	317.1	314.5	311.8	309.2	306.5	304.5
72.5°	283.4	282.3	281.1	279.9	278.7	277.3	275.6	273.9	272.1	270.4	268.4
75°	222.9	222.3	221.7	221.2	220.6	219.5	218.1	216.6	215.1	213.6	211.9
77.5°	168.8	167.8	166.8	165.8	164.8	164.0	163.4	162.8	162.2	161.6	160.7
80°	132.7	132.4	132.1	131.8	131.5	131.1	130.5	129.9	129.3	128.7	127.8
82.5°	98.7	98.7	98.6	98.5	98.5	98.3	97.9	97.6	97.2	96.9	95.7
85°	54.4	54.1	53.8	53.5	53.2	52.9	52.6	52.3	52.0	51.8	50.9
87.5°	19.4	19.6	19.8	20.0	20.2	20.8	21.6	22.3	23.1	23.9	23.1
90°	1.3	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8
92.5°	23.1	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3
95°	67.4	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0
97.5°	123.2	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5
100°	164.7	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9
102.5°	208.2	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7
105°	278.8	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8
107.5°	349.8	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8
110°	395.5	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.3	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3
115°	518.7	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6
117.5°	591.8	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2
120°	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5
122.5°	685.1	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6
125°	754.6	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6
127.5°	822.3	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4
130°	864.9	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5
132.5°	912.6	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6
135°	976.4	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9
137.5°	1043.5	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4
140°	1084.0	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1
142.5°	1125.5	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8
145°	1185.1	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3
147.5°	1238.3	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0
150°	1274.6	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4
152.5°	1306.8	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9
155°	1355.0	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2
157.5°	1396.2	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1
160°	1421.1	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7
162.5°	1443.9	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7
165°	1474.3	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0
167.5°	1499.7	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6
170°	1513.2	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0
172.5°	1522.5	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4
175°	1533.9	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5
177.5°	1538.6	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1374.1	1376.5	1378.8	1379.8	1379.3	1378.8	1378.4	1377.9
5°	1364.8	1367.2	1369.6	1370.4	1369.9	1369.3	1368.7	1368.1
7.5°	1349.4	1351.8	1354.2	1355.0	1354.4	1353.7	1353.1	1352.4
10°	1335.6	1338.0	1340.4	1341.1	1340.2	1339.3	1338.4	1337.6
12.5°	1319.4	1321.0	1322.7	1323.2	1322.5	1321.9	1321.2	1320.6
15°	1290.8	1292.0	1293.2	1293.0	1291.6	1290.1	1288.6	1287.1
17.5°	1256.9	1258.3	1259.7	1259.6	1258.2	1256.8	1255.4	1254.0
20°	1230.5	1231.4	1232.3	1232.1	1231.0	1229.8	1228.6	1227.4
22.5°	1202.6	1202.7	1202.9	1202.7	1201.9	1201.2	1200.5	1199.8
25°	1157.0	1157.5	1158.1	1158.1	1157.5	1157.0	1156.4	1155.8
27.5°	1112.1	1111.2	1110.3	1109.2	1107.7	1106.3	1104.9	1103.5
30°	1077.0	1076.2	1075.3	1074.2	1073.1	1071.9	1070.7	1069.5
32.5°	1042.7	1041.1	1039.5	1038.1	1037.0	1035.8	1034.6	1033.4
35°	987.7	985.9	984.2	982.5	981.1	979.6	978.1	976.6
37.5°	932.5	930.3	928.1	926.3	924.9	923.5	922.1	920.6
40°	894.4	891.7	889.1	887.1	886.0	884.8	883.6	882.4
42.5°	856.7	853.8	851.0	848.7	847.0	845.4	843.7	842.1
45°	799.0	795.7	792.5	790.3	789.1	787.9	786.7	785.6
47.5°	738.9	735.5	732.1	729.5	727.8	726.1	724.4	722.7
50°	700.3	696.2	692.1	689.3	687.8	686.3	684.9	683.4
52.5°	660.3	656.9	653.5	650.8	648.9	646.9	645.0	643.0
55°	600.7	597.1	593.6	591.1	589.6	588.1	586.7	585.2
57.5°	538.7	535.2	531.7	529.4	528.3	527.2	526.1	524.9
60°	497.8	494.5	491.3	489.2	488.3	487.4	486.5	485.7
62.5°	458.9	455.9	452.9	450.9	449.7	448.6	447.5	446.4
65°	399.4	396.8	394.1	392.0	390.6	389.1	387.6	386.1
67.5°	340.6	338.5	336.5	334.9	333.7	332.5	331.3	330.1
70°	302.4	300.3	298.3	296.6	295.5	294.3	293.1	291.9
72.5°	266.3	264.2	262.2	260.7	259.7	258.8	257.8	256.9
75°	210.1	208.3	206.6	206.0	206.6	207.2	207.7	208.3
77.5°	159.9	159.0	158.1	157.2	156.4	155.6	154.8	153.9
80°	126.9	126.1	125.2	124.4	123.8	123.3	122.7	122.1
82.5°	94.6	93.5	92.4	91.8	91.6	91.5	91.4	91.3
85°	50.0	49.1	48.2	47.6	47.3	47.0	46.7	46.4
87.5°	22.3	21.5	20.6	20.1	20.0	19.8	19.6	19.4
90°	44.2	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.5	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	221.9	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	286.4	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.0	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331578

CATALOG NUMBER: S122DIW-S865D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.6	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.3	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	593.5	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	689.0	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	760.7	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	830.4	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	878.0	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	924.3	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.7	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1058.1	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.0	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.6	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1255.6	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1365.7	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1405.1	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1428.5	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1449.7	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1477.0	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1499.6	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1512.0	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1521.4	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1531.5	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)