

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331584

Luminaire Tested: **S122DIW-S865D1440U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331584
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8513.3 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22281	22281	22281
5°	22366	22044	22174
10°	22233	21820	21930
15°	21959	21538	21514
20°	21569	21113	21089
25°	21180	20591	20591
30°	20681	20113	19939
35°	20217	19537	19249
40°	19633	18963	18598
45°	19057	18393	17938
50°	18432	17799	17166
55°	17779	17106	16473
60°	17053	16281	15684
65°	16275	15461	14751
70°	15286	14469	13780
75°	13905	13325	12994
80°	12338	11967	11353
85°	10078	9596	8596



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	1.5
10°-20°	365.1	4.3
20°-30°	536.7	6.3
30°-40°	623.4	7.3
40°-50°	622.7	7.3
50°-60°	543.1	6.4
60°-70°	401.6	4.7
70°-80°	227.4	2.7
80°-90°	68.3	0.8
90°-100°	113.2	1.3
100°-110°	351.6	4.1
110°-120°	601.0	7.1
120°-130°	790.3	9.3
130°-140°	887.0	10.4
140°-150°	869.7	10.2
150°-160°	729.5	8.6
160°-170°	483.8	5.7
170°-180°	169.1	2.0
0°-30°	1031.6	12.1
0°-40°	1655.0	19.4
0°-60°	2820.8	33.1
0°-90°	3518.1	41.3
90°-120°	1065.7	12.5
90°-150°	3612.8	42.4
90°-180°	4995.0	58.7
0°-180°	8513.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1380	1374	1360	1370	1368	131
15°	1314	1305	1288	1293	1287	370
25°	1189	1178	1156	1158	1156	547
35°	1026	1012	991	983	977	640
45°	835	825	806	791	786	644
55°	632	623	608	592	585	565
65°	426	418	405	393	386	421
75°	223	220	214	206	208	238
85°	54	53	52	48	46	62
90°	2	20	53	50	51	7
95°	78	93	96	96	94	90
105°	324	329	332	334	335	342
115°	603	611	609	607	603	596
125°	877	890	886	882	880	784
135°	1135	1151	1155	1153	1149	877
145°	1378	1388	1398	1399	1393	860
155°	1575	1580	1584	1591	1588	725
165°	1714	1713	1713	1722	1716	483
175°	1783	1779	1776	1785	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1386.4	1385.2	1384.0	1382.9	1381.7	1379.8	1377.2	1374.6	1372.0	1369.4	1371.8
5°	1380.0	1378.8	1377.7	1376.5	1375.3	1373.1	1369.9	1366.6	1363.4	1360.1	1362.5
7.5°	1367.8	1366.0	1364.2	1362.3	1360.5	1357.9	1354.6	1351.3	1348.0	1344.7	1347.1
10°	1356.1	1354.1	1352.0	1349.9	1347.9	1345.1	1341.5	1338.0	1334.5	1330.9	1333.3
12.5°	1340.2	1338.4	1336.6	1334.7	1332.9	1330.2	1326.7	1323.1	1319.6	1316.1	1317.7
15°	1313.7	1311.9	1310.1	1308.4	1306.6	1303.8	1300.0	1296.1	1292.3	1288.5	1289.6
17.5°	1279.7	1277.9	1276.2	1274.4	1272.6	1269.8	1265.9	1262.0	1258.1	1254.2	1255.6
20°	1255.3	1253.5	1251.8	1250.0	1248.2	1245.3	1241.1	1237.0	1232.9	1228.8	1229.6
22.5°	1230.9	1228.4	1225.9	1223.4	1221.0	1217.8	1213.9	1210.0	1206.1	1202.2	1202.4
25°	1188.9	1186.6	1184.2	1181.9	1179.5	1175.8	1170.8	1165.8	1160.8	1155.8	1156.4
27.5°	1141.2	1139.1	1136.9	1134.8	1132.7	1129.6	1125.7	1121.7	1117.8	1113.8	1113.0
30°	1109.3	1107.0	1104.6	1102.3	1099.9	1096.5	1092.1	1087.7	1083.2	1078.8	1077.9
32.5°	1075.4	1073.5	1071.6	1069.7	1067.8	1064.5	1059.9	1055.2	1050.6	1045.9	1044.3
35°	1025.7	1022.8	1019.8	1016.9	1013.9	1010.1	1005.4	1000.7	995.9	991.2	989.5
37.5°	969.7	967.1	964.5	961.9	959.4	955.7	951.0	946.3	941.5	936.8	934.6
40°	931.5	929.2	926.8	924.4	922.1	918.5	913.8	909.1	904.4	899.7	897.0
42.5°	894.4	892.0	889.6	887.3	884.9	881.4	876.7	872.0	867.2	862.5	859.6
45°	834.6	832.6	830.5	828.5	826.4	823.1	818.7	814.3	809.9	805.5	802.2
47.5°	775.2	773.3	771.3	769.4	767.4	764.1	759.5	754.9	750.3	745.7	742.3
50°	733.8	732.3	730.9	729.4	727.9	725.1	721.0	716.8	712.7	708.6	704.5
52.5°	693.5	691.5	689.6	687.6	685.7	682.8	678.9	675.0	671.1	667.2	663.8
55°	631.6	629.9	628.1	626.3	624.5	621.9	618.4	614.8	611.3	607.7	604.2
57.5°	569.5	568.1	566.7	565.3	563.9	561.2	557.3	553.4	549.5	545.6	542.2
60°	528.1	526.9	525.8	524.6	523.4	520.8	516.6	512.5	508.4	504.2	501.0
62.5°	487.8	485.9	484.0	482.1	480.2	477.7	474.5	471.3	468.1	465.0	462.0
65°	426.0	424.2	422.4	420.6	418.9	416.5	413.6	410.6	407.7	404.7	402.1
67.5°	363.1	361.6	360.2	358.8	357.4	355.4	352.7	350.0	347.4	344.7	342.7
70°	323.8	322.6	321.4	320.2	319.1	317.1	314.5	311.8	309.2	306.5	304.5
72.5°	283.4	282.3	281.1	279.9	278.7	277.3	275.6	273.9	272.1	270.4	268.4
75°	222.9	222.3	221.7	221.2	220.6	219.5	218.1	216.6	215.1	213.6	211.9
77.5°	168.8	167.8	166.8	165.8	164.8	164.0	163.4	162.8	162.2	161.6	160.7
80°	132.7	132.4	132.1	131.8	131.5	131.1	130.5	129.9	129.3	128.7	127.8
82.5°	98.7	98.7	98.6	98.5	98.5	98.3	97.9	97.6	97.2	96.9	95.7
85°	54.4	54.1	53.8	53.5	53.2	52.9	52.6	52.3	52.0	51.8	50.9
87.5°	19.4	19.7	20.1	20.4	20.7	21.4	22.4	23.4	24.4	25.4	24.6
90°	1.5	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1
92.5°	26.8	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1
95°	78.4	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5
97.5°	143.2	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2
100°	191.5	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0
102.5°	242.1	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8
105°	324.1	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3
107.5°	406.7	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6
110°	459.8	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	517.7	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7
115°	603.0	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7
117.5°	688.1	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9
120°	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7
122.5°	796.6	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8
125°	877.4	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4
127.5°	956.1	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6
130°	1005.5	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5
132.5°	1061.0	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1
135°	1135.2	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5
137.5°	1213.3	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5
140°	1260.3	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4
142.5°	1308.6	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5
145°	1377.9	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8
147.5°	1439.7	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2
150°	1481.9	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0
152.5°	1519.3	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9
155°	1575.4	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1
157.5°	1623.3	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3
160°	1652.3	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8
162.5°	1678.8	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2
165°	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9
167.5°	1743.6	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2
170°	1759.3	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6
172.5°	1770.2	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5
175°	1783.4	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3
177.5°	1788.9	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1374.1	1376.5	1378.8	1379.8	1379.3	1378.8	1378.4	1377.9
5°	1364.8	1367.2	1369.6	1370.4	1369.9	1369.3	1368.7	1368.1
7.5°	1349.4	1351.8	1354.2	1355.0	1354.4	1353.7	1353.1	1352.4
10°	1335.6	1338.0	1340.4	1341.1	1340.2	1339.3	1338.4	1337.6
12.5°	1319.4	1321.0	1322.7	1323.2	1322.5	1321.9	1321.2	1320.6
15°	1290.8	1292.0	1293.2	1293.0	1291.6	1290.1	1288.6	1287.1
17.5°	1256.9	1258.3	1259.7	1259.6	1258.2	1256.8	1255.4	1254.0
20°	1230.5	1231.4	1232.3	1232.1	1231.0	1229.8	1228.6	1227.4
22.5°	1202.6	1202.7	1202.9	1202.7	1201.9	1201.2	1200.5	1199.8
25°	1157.0	1157.5	1158.1	1158.1	1157.5	1157.0	1156.4	1155.8
27.5°	1112.1	1111.2	1110.3	1109.2	1107.7	1106.3	1104.9	1103.5
30°	1077.0	1076.2	1075.3	1074.2	1073.1	1071.9	1070.7	1069.5
32.5°	1042.7	1041.1	1039.5	1038.1	1037.0	1035.8	1034.6	1033.4
35°	987.7	985.9	984.2	982.5	981.1	979.6	978.1	976.6
37.5°	932.5	930.3	928.1	926.3	924.9	923.5	922.1	920.6
40°	894.4	891.7	889.1	887.1	886.0	884.8	883.6	882.4
42.5°	856.7	853.8	851.0	848.7	847.0	845.4	843.7	842.1
45°	799.0	795.7	792.5	790.3	789.1	787.9	786.7	785.6
47.5°	738.9	735.5	732.1	729.5	727.8	726.1	724.4	722.7
50°	700.3	696.2	692.1	689.3	687.8	686.3	684.9	683.4
52.5°	660.3	656.9	653.5	650.8	648.9	646.9	645.0	643.0
55°	600.7	597.1	593.6	591.1	589.6	588.1	586.7	585.2
57.5°	538.7	535.2	531.7	529.4	528.3	527.2	526.1	524.9
60°	497.8	494.5	491.3	489.2	488.3	487.4	486.5	485.7
62.5°	458.9	455.9	452.9	450.9	449.7	448.6	447.5	446.4
65°	399.4	396.8	394.1	392.0	390.6	389.1	387.6	386.1
67.5°	340.6	338.5	336.5	334.9	333.7	332.5	331.3	330.1
70°	302.4	300.3	298.3	296.6	295.5	294.3	293.1	291.9
72.5°	266.3	264.2	262.2	260.7	259.7	258.8	257.8	256.9
75°	210.1	208.3	206.6	206.0	206.6	207.2	207.7	208.3
77.5°	159.9	159.0	158.1	157.2	156.4	155.6	154.8	153.9
80°	126.9	126.1	125.2	124.4	123.8	123.3	122.7	122.1
82.5°	94.6	93.5	92.4	91.8	91.6	91.5	91.4	91.3
85°	50.0	49.1	48.2	47.6	47.3	47.0	46.7	46.4
87.5°	23.7	22.9	22.0	21.5	21.4	21.2	21.0	20.9
90°	51.4	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.2	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.0	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.0	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	413.9	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331584

CATALOG NUMBER: S122DIW-S865D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	523.9	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.4	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	690.1	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	801.0	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	884.4	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	965.4	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.8	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1074.7	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1154.1	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.2	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1327.8	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.2	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1459.9	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1587.8	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1633.6	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1660.8	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1685.5	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1717.3	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1743.5	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1758.0	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1768.8	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1780.6	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)