

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331482-830

Luminaire Tested: **S122DIW-S290D970U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331482-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4300.6 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.0
10°-20°	117.8	2.7
20°-30°	173.2	4.0
30°-40°	201.2	4.7
40°-50°	200.9	4.7
50°-60°	175.2	4.1
60°-70°	129.6	3.0
70°-80°	73.4	1.7
80°-90°	24.3	0.6
90°-100°	71.7	1.7
100°-110°	222.6	5.2
110°-120°	380.6	8.8
120°-130°	500.5	11.6
130°-140°	561.7	13.1
140°-150°	550.8	12.8
150°-160°	462.0	10.7
160°-170°	306.4	7.1
170°-180°	107.1	2.5
0°-30°	332.9	7.7
0°-40°	534.0	12.4
0°-60°	910.2	21.2
0°-90°	1137.4	26.4
90°-120°	674.9	15.7
90°-150°	2287.8	53.2
90°-180°	3163.0	73.5
0°-180°	4300.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	13	33	32	32	3
95°	50	59	61	61	59	57
105°	205	208	210	212	212	217
115°	382	387	386	385	382	378
125°	556	564	561	559	558	496
135°	719	729	731	730	728	555
145°	872	879	885	886	882	545
155°	998	1000	1003	1008	1005	459
165°	1085	1085	1084	1090	1086	306
175°	1129	1126	1124	1131	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.3	6.7	7.1	7.4	7.8	8.4	9.1	9.9	10.7	11.5	11.1
90°	0.9	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0
92.5°	17.0	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4
95°	49.7	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1
97.5°	90.7	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7
100°	121.2	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8
102.5°	153.4	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2
105°	205.3	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5
107.5°	257.6	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9
110°	291.2	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.8	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2
115°	381.8	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5
117.5°	435.7	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5
120°	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6
122.5°	504.4	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7
125°	555.6	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7
127.5°	605.5	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1
130°	636.8	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9
132.5°	671.8	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5
135°	718.9	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0
137.5°	768.3	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2
140°	798.1	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4
142.5°	828.7	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7
145°	872.5	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1
147.5°	911.7	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0
150°	938.4	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6
152.5°	962.1	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2
155°	997.6	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4
157.5°	1027.9	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0
160°	1046.3	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5
162.5°	1063.1	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9
165°	1085.4	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0
167.5°	1104.2	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6
170°	1114.1	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7
172.5°	1121.0	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6
175°	1129.4	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1
177.5°	1132.8	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	10.8	10.6	10.2	10.1	10.0	10.0	10.0	9.9
90°	32.5	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.5	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.4	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	210.8	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.1	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.9	296.6	296.0	295.3	294.6	294.1



TEST NUMBER: P331482-830

CATALOG NUMBER: S122DIW-S290D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.8	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.2	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	437.0	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	507.3	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	560.1	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	611.3	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.4	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	680.5	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.8	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	779.0	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	840.8	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.4	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.4	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1005.5	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1034.5	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1051.7	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1067.3	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1087.5	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1104.1	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1113.2	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1120.1	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1127.6	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)