

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331555

Luminaire Tested: **S122DIW-S865D435U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331555  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D435U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5541.6 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																				
1	103	98	95	91	97	93	90	87	83	81	79	74	72	71	66	65	63	59																				
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	51																				
3	86	77	70	64	81	73	67	61	66	61	56	59	55	52	53	50	47	44																				
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38																				
5	73	62	54	48	69	59	51	46	53	47	43	48	43	39	43	39	36	34																				
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32	30																				
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27																				
8	59	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24																				
9	55	42	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22																				
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.4	3.0
10°-20°	478.0	8.6
20°-30°	693.8	12.5
30°-40°	732.1	13.2
40°-50°	648.2	11.7
50°-60°	517.3	9.3
60°-70°	351.6	6.3
70°-80°	180.3	3.3
80°-90°	44.9	0.8
90°-100°	19.7	0.4
100°-110°	72.3	1.3
110°-120°	193.1	3.5
120°-130°	318.8	5.8
130°-140°	339.1	6.1
140°-150°	315.2	5.7
150°-160°	253.4	4.6
160°-170°	163.3	2.9
170°-180°	56.2	1.0
0°-30°	1336.2	24.1
0°-40°	2068.3	37.3
0°-60°	3233.8	58.4
0°-90°	3810.6	68.8
90°-120°	285.1	5.1
90°-150°	1258.2	22.7
90°-180°	1731.0	31.2
0°-180°	5541.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	39
90°	12	0	12	0	12	7
95°	18	28	18	28	18	17
105°	32	130	32	130	32	34
115°	35	246	35	246	35	88
125°	365	348	365	348	365	316
135°	444	430	444	430	444	342
145°	506	499	506	499	506	317
155°	550	549	550	549	550	254
165°	577	579	577	579	577	163
175°	589	592	589	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	16.1	16.1	16.6	16.0	16.0	16.4	16.3	15.7	16.1	16.6	17.0
90°	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5	9.0	8.5	7.8
92.5°	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4	10.2	9.9	9.5
95°	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6	17.1	16.7	16.0
97.5°	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1	22.7	22.3	20.8
100°	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9	25.1	24.4	22.7
102.5°	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0	26.0	25.0	38.6
105°	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2	27.1	26.1	52.0
107.5°	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4	35.4	36.5	67.6
110°	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8	65.3	74.8	102.2



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4	154.0	188.7	195.4
115°	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8	219.7	263.7	261.3
117.5°	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8	281.5	292.1	290.5
120°	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6	314.4	313.3	311.6
122.5°	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8	334.2	333.5	331.6
125°	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5	361.8	361.2	359.4
127.5°	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1	387.1	386.1	384.8
130°	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3	403.2	402.2	401.2
132.5°	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1	419.2	418.3	417.2
135°	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6	441.6	440.7	439.8
137.5°	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5	462.5	461.6	460.6
140°	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0	476.1	475.3	474.2
142.5°	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5	488.7	487.9	486.7
145°	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0	506.3	505.6	504.0
147.5°	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2	521.7	521.2	519.6
150°	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6	531.0	530.4	528.9
152.5°	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1	539.5	539.0	537.5
155°	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7	551.1	550.5	549.4
157.5°	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4	560.7	560.1	559.3
160°	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0	566.5	565.9	565.3
162.5°	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3	571.7	571.0	570.5
165°	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4	577.2
167.5°	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2	583.5	582.8	582.6
170°	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9	586.2	585.6	585.4
172.5°	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9	588.3	587.6	587.4
175°	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2	590.5	589.8	589.6
177.5°	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4	590.9	590.3	590.3
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	17.3	17.2	17.0	17.9	16.1	15.9	13.6	11.8	11.4	11.1	10.3
90°	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8	24.6	21.5	18.4
97.5°	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1	46.3	37.5	28.6
100°	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7	62.6	49.6	36.6
102.5°	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2	95.5	92.7	90.0
105°	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9	132.8	135.6	138.5
107.5°	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1	168.4	170.7	173.0
110°	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3	191.3	193.3	195.3





TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2	213.0	214.8	216.5
115°	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8	247.4	249.0	250.6
117.5°	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6	278.4	280.2	282.0
120°	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2	300.6	302.0	303.5
122.5°	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3	319.8	321.3	322.8
125°	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5	348.7	350.0	351.2
127.5°	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9	375.3	376.6	378.0
130°	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7	392.2	393.7	395.2
132.5°	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8	409.0	410.3	411.6
135°	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0	431.5	433.0	434.5
137.5°	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5	453.5	454.6	455.7
140°	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2	467.9	468.7	469.4
142.5°	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5	480.2	480.8	481.5
145°	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5
147.5°	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6	515.3	514.9	514.6
150°	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6	525.9	525.2	524.6
152.5°	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8	535.1	534.3	533.6
155°	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2	548.4	547.5	546.7
157.5°	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7	559.0	558.3	557.6
160°	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	565.3	564.8	564.2
162.5°	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4	570.8	570.2	569.7
165°	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7	578.2	577.6	577.0
167.5°	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2	583.6	583.1	582.5
170°	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3	586.7	586.1	585.6
172.5°	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3	588.8	588.2	587.6
175°	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0	591.3	590.6	590.0
177.5°	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4	591.9	591.3	590.8
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	9.9	9.6	9.2	9.4	9.0	8.6	8.2	8.3	8.4	7.4	7.5
90°	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5	10.0	10.4	10.8
92.5°	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4	10.7	10.9	11.1
95°	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6	18.1	18.6	18.8
97.5°	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1	23.5	23.8	24.1
100°	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9	26.6	27.4	27.9
102.5°	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0	28.0	29.0	29.6
105°	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2	29.2	30.3	31.0
107.5°	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4	33.3	32.2	31.9
110°	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8	46.3	36.8	32.2



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4	84.7	50.1	32.9
115°	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8	131.8	87.8	62.4
117.5°	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8	260.2	249.5	233.0
120°	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6	316.7	317.9	312.0
122.5°	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8	335.5	336.2	335.3
125°	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5	363.2	363.8	364.3
127.5°	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1	389.0	390.0	390.5
130°	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3	405.3	406.4	406.9
132.5°	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1	420.9	421.8	422.2
135°	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6	443.5	444.5	444.8
137.5°	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5	464.4	465.3	465.6
140°	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0	477.9	478.7	478.9
142.5°	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5	490.3	491.1	491.2
145°	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0	507.6	508.3	508.4
147.5°	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2	522.7	523.2	523.2
150°	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6	532.1	532.7	532.8
152.5°	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1	540.7	541.3	541.2
155°	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7	552.2	552.8	552.7
157.5°	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4	562.0	562.7	562.6
160°	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0	567.6	568.2	568.1
162.5°	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3	573.0	573.6	573.5
165°	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8	579.4	580.1	580.1
167.5°	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2	584.8	585.5	585.4
170°	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9	587.6	588.2	588.1
172.5°	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9	589.6	590.3	590.2
175°	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2	591.8	592.5	592.4
177.5°	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4	591.9	592.5	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	7.5	7.0	7.0	6.6	7.0	7.0	7.5	7.5	7.4	8.4	8.3
90°	11.0	11.2	11.4	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4
95°	18.7	18.6	18.5	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6
97.5°	24.2	24.3	24.4	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1
100°	28.1	28.3	28.4	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9
102.5°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0
105°	31.3	31.7	32.1	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2
107.5°	32.3	32.7	33.0	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4
110°	32.6	33.0	33.4	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.2	33.5	33.8	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4
115°	55.6	48.7	41.9	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8
117.5°	210.5	188.0	165.6	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8
120°	299.2	286.4	273.5	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6
122.5°	332.8	330.3	327.8	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8
125°	364.6	364.9	365.2	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5
127.5°	390.6	390.6	390.7	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1
130°	406.8	406.7	406.6	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3
132.5°	422.1	422.0	422.0	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1
135°	444.7	444.5	444.3	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6
137.5°	465.3	465.0	464.7	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5
140°	478.4	477.9	477.5	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0
142.5°	490.7	490.3	489.8	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5
145°	507.9	507.4	507.0	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0
147.5°	522.8	522.4	522.0	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2
150°	532.3	531.8	531.3	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6
152.5°	540.6	540.0	539.3	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1
155°	551.9	551.2	550.4	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7
157.5°	561.9	561.1	560.4	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4
160°	567.5	566.8	566.1	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0
162.5°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3
165°	579.4	578.8	578.1	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8
167.5°	584.5	583.7	582.8	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2
170°	587.3	586.4	585.6	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9
172.5°	589.3	588.5	587.6	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9
175°	591.4	590.5	589.5	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2
177.5°	591.7	591.0	590.3	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	8.2	8.6	9.0	9.4	9.2	9.6	9.9	10.3	11.1	11.4	11.8
90°	9.0	8.5	7.8	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4
92.5°	10.2	9.9	9.5	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6
95°	17.1	16.7	16.0	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8
97.5°	22.7	22.3	20.8	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1
100°	25.1	24.4	22.7	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7
102.5°	26.0	25.0	38.6	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2
105°	27.1	26.1	52.0	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9
107.5°	35.4	36.5	67.6	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1
110°	65.3	74.8	102.2	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.0	188.7	195.4	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2
115°	219.7	263.7	261.3	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8
117.5°	281.5	292.1	290.5	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6
120°	314.4	313.3	311.6	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2
122.5°	334.2	333.5	331.6	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3
125°	361.8	361.2	359.4	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5
127.5°	387.1	386.1	384.8	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9
130°	403.2	402.2	401.2	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7
132.5°	419.2	418.3	417.2	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8
135°	441.6	440.7	439.8	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0
137.5°	462.5	461.6	460.6	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5
140°	476.1	475.3	474.2	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2
142.5°	488.7	487.9	486.7	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5
145°	506.3	505.6	504.0	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8
147.5°	521.7	521.2	519.6	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6
150°	531.0	530.4	528.9	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6
152.5°	539.5	539.0	537.5	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8
155°	551.1	550.5	549.4	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2
157.5°	560.7	560.1	559.3	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7
160°	566.5	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9
162.5°	571.7	571.0	570.5	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4
165°	578.1	577.4	577.2	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7
167.5°	583.5	582.8	582.6	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2
170°	586.2	585.6	585.4	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3
172.5°	588.3	587.6	587.4	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3
175°	590.5	589.8	589.6	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0
177.5°	590.9	590.3	590.3	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.6	15.9	16.1	17.9	17.0	17.2	17.3	17.0	16.6	16.1	15.7
90°	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4
95°	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6
97.5°	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1
100°	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9
102.5°	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0
105°	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2
107.5°	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4
110°	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8





TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4
115°	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8
117.5°	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8
120°	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6
122.5°	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8
125°	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5
127.5°	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1
130°	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3
132.5°	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1
135°	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6
137.5°	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5
140°	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0
142.5°	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5
145°	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0
147.5°	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2
150°	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6
152.5°	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1
155°	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7
157.5°	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4
160°	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0
162.5°	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3
165°	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8
167.5°	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2
170°	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9
172.5°	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9
175°	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2
177.5°	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	16.3	16.4	16.0	16.0	16.6	16.1	16.1
90°	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331555

CATALOG NUMBER: S122DIW-S865D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)