

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331517-830

Luminaire Tested: **S122DIW-S485D1240U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331517-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6536.0 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	20	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.1
10°-20°	193.7	3.0
20°-30°	284.7	4.4
30°-40°	330.7	5.1
40°-50°	330.4	5.1
50°-60°	288.1	4.4
60°-70°	213.0	3.3
70°-80°	120.7	1.8
80°-90°	36.4	0.6
90°-100°	53.1	0.8
100°-110°	194.9	3.0
110°-120°	521.0	8.0
120°-130°	860.1	13.2
130°-140°	914.7	14.0
140°-150°	850.1	13.0
150°-160°	683.5	10.5
160°-170°	440.5	6.7
170°-180°	151.6	2.3
0°-30°	547.2	8.4
0°-40°	878.0	13.4
0°-60°	1496.4	22.9
0°-90°	1866.4	28.6
90°-120°	769.1	11.8
90°-150°	3394.0	51.9
90°-180°	4670.0	71.5
0°-180°	6536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	14	23	29	31	5
95°	75	39	45	50	50	92
105°	350	366	70	83	88	375
115°	663	683	711	203	94	653
125°	937	953	974	982	986	835
135°	1160	1178	1189	1200	1198	896
145°	1346	1346	1364	1371	1366	841
155°	1482	1472	1485	1491	1483	682
165°	1561	1555	1558	1565	1558	441
175°	1597	1589	1591	1598	1588	152
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.4	10.7	11.0	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.3
90°	1.1	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3
92.5°	23.3	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4
95°	74.9	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3
97.5°	148.7	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2
100°	204.1	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8
102.5°	264.9	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2
105°	350.5	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1
107.5°	448.1	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6
110°	510.8	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.8	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5
115°	663.0	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8
117.5°	746.2	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2
120°	807.1	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2
122.5°	858.8	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4
125°	937.4	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1
127.5°	1008.6	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2
130°	1053.9	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8
132.5°	1099.9	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7
135°	1159.9	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3
137.5°	1220.5	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7
140°	1260.2	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4
142.5°	1293.5	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3
145°	1345.5	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7
147.5°	1390.9	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3
150°	1420.5	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4
152.5°	1445.4	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5
155°	1481.6	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6
157.5°	1510.0	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6
160°	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0
162.5°	1541.3	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1
165°	1561.1	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4
167.5°	1575.9	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0
170°	1584.2	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4
172.5°	1589.7	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9
175°	1596.9	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9
177.5°	1598.0	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	12.3	12.2	12.1	12.0	12.0	11.9	11.9	11.9
90°	25.6	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.1	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	47.5	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	62.2	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	69.8	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	72.9	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	76.0	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	92.7	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	150.5	124.9	99.2	87.0	88.0	89.1	90.1	91.0



TEST NUMBER: P331517-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.0	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	474.1	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	730.6	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	851.3	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	903.2	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	977.9	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1046.8	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1090.6	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1133.1	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1193.8	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1250.2	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1286.8	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1320.4	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1367.5	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1408.6	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1433.9	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1457.0	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1488.1	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1514.4	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1529.7	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1543.9	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1575.7	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1583.2	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1588.7	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1594.7	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1595.3	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)