

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331518-830

Luminaire Tested: **S122DIW-S485D1240U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331518-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5917.8 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.2
10°-20°	193.7	3.3
20°-30°	284.7	4.8
30°-40°	330.7	5.6
40°-50°	330.4	5.6
50°-60°	288.1	4.9
60°-70°	213.0	3.6
70°-80°	120.7	2.0
80°-90°	38.2	0.6
90°-100°	91.8	1.6
100°-110°	285.0	4.8
110°-120°	487.2	8.2
120°-130°	640.7	10.8
130°-140°	719.1	12.2
140°-150°	705.1	11.9
150°-160°	591.4	10.0
160°-170°	392.2	6.6
170°-180°	137.1	2.3
0°-30°	547.2	9.2
0°-40°	878.0	14.8
0°-60°	1496.4	25.3
0°-90°	1868.3	31.6
90°-120°	864.0	14.6
90°-150°	2928.8	49.5
90°-180°	4050.0	68.4
0°-180°	5917.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	17	43	40	42	5
95°	64	75	78	78	76	73
105°	263	266	269	271	271	277
115°	489	496	494	492	489	483
125°	711	721	719	715	714	635
135°	920	933	936	935	931	711
145°	1117	1126	1133	1134	1129	698
155°	1277	1281	1284	1290	1287	588
165°	1390	1388	1388	1396	1391	392
175°	1446	1442	1440	1447	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.4	10.7	11.2	11.6	12.0	12.6	13.6	14.5	15.5	16.4	15.9
90°	1.2	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2
92.5°	21.8	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9
95°	63.5	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2
97.5°	116.1	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5
100°	155.2	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6
102.5°	196.2	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0
105°	262.8	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4
107.5°	329.7	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4
110°	372.8	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.7	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4
115°	488.9	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5
117.5°	557.8	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1
120°	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7
122.5°	645.7	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0
125°	711.2	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8
127.5°	775.1	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6
130°	815.2	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0
132.5°	860.2	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4
135°	920.3	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9
137.5°	983.5	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6
140°	1021.7	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8
142.5°	1060.8	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2
145°	1117.0	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2
147.5°	1167.2	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9
150°	1201.4	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4
152.5°	1231.7	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9
155°	1277.1	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8
157.5°	1316.0	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5
160°	1339.4	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7
162.5°	1360.9	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5
165°	1389.6	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3
167.5°	1413.5	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6
170°	1426.3	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2
172.5°	1435.0	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1
175°	1445.8	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6
177.5°	1450.2	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	15.5	15.0	14.5	14.2	14.1	14.0	14.0	13.9
90°	41.7	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.1	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.2	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	269.9	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.5	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331518-830

CATALOG NUMBER: S122DIW-S485D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	424.7	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	493.2	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	559.4	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	649.4	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	717.0	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	782.7	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.6	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	871.2	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.7	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.3	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.4	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.5	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1183.5	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1287.2	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1324.4	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1346.4	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1366.4	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1392.1	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1413.4	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1425.1	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1434.0	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1443.5	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)