

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331505-830

Luminaire Tested: **S122DIW-S485D710U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331505-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4537.1 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.5
10°-20°	193.7	4.3
20°-30°	284.7	6.3
30°-40°	330.7	7.3
40°-50°	330.4	7.3
50°-60°	288.1	6.3
60°-70°	213.0	4.7
70°-80°	120.7	2.7
80°-90°	34.7	0.8
90°-100°	30.4	0.7
100°-110°	111.6	2.5
110°-120°	298.2	6.6
120°-130°	492.2	10.8
130°-140°	523.5	11.5
140°-150°	486.5	10.7
150°-160°	391.2	8.6
160°-170°	252.1	5.6
170°-180°	86.8	1.9
0°-30°	547.2	12.1
0°-40°	878.0	19.4
0°-60°	1496.4	33.0
0°-90°	1864.8	41.1
90°-120°	440.1	9.7
90°-150°	1942.3	42.8
90°-180°	2672.0	58.9
0°-180°	4537.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	8	13	16	18	3
95°	43	23	26	29	28	52
105°	201	209	40	47	50	214
115°	379	391	407	116	54	373
125°	536	545	558	562	564	478
135°	664	674	680	686	686	512
145°	770	770	781	785	782	481
155°	848	843	850	853	849	391
165°	893	890	892	896	892	252
175°	914	910	911	915	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.3	10.4	10.4	10.5	10.6	10.6	10.6	10.6	10.6	10.6	10.3
90°	0.7	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9
92.5°	13.3	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6
95°	42.9	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5
97.5°	85.1	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1
100°	116.8	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7
102.5°	151.7	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2
105°	200.6	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8
107.5°	256.4	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7
110°	292.3	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	326.1	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8
115°	379.4	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2
117.5°	427.1	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5
120°	461.8	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4
122.5°	491.4	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9
125°	536.4	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6
127.5°	577.2	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6
130°	603.0	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5
132.5°	629.5	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1
135°	663.8	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7
137.5°	698.5	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1
140°	721.2	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1
142.5°	740.2	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5
145°	770.1	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7
147.5°	796.0	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4
150°	812.9	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7
152.5°	827.2	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9
155°	847.9	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7
157.5°	864.1	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6
160°	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5
162.5°	882.0	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5
165°	893.4	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5
167.5°	901.8	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8
170°	906.6	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0
172.5°	909.7	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1
175°	913.9	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6
177.5°	914.5	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	10.1	9.8	9.6	9.4	9.4	9.3	9.2	9.2
90°	14.7	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.1	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.2	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	35.6	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	40.0	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	41.8	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	43.5	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	53.1	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	86.1	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331505-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	184.3	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	271.4	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	418.1	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	487.2	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	516.9	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	559.6	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	599.1	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	624.2	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	648.5	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	683.2	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	715.5	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	736.4	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	755.6	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	782.6	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.2	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	820.6	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	833.8	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	851.6	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	866.7	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	875.3	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	883.5	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	901.8	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	906.1	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	909.2	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	912.7	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.0	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)