

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331858

Luminaire Tested: **S122RDIW-S1005D1240U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331858
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8114.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	2.6
10°-20°	582.5	7.2
20°-30°	750.7	9.3
30°-40°	713.4	8.8
40°-50°	611.1	7.5
50°-60°	465.4	5.7
60°-70°	294.2	3.6
70°-80°	146.9	1.8
80°-90°	44.4	0.5
90°-100°	97.4	1.2
100°-110°	302.4	3.7
110°-120°	516.9	6.4
120°-130°	679.7	8.4
130°-140°	762.9	9.4
140°-150°	748.1	9.2
150°-160°	627.4	7.7
160°-170°	416.2	5.1
170°-180°	145.5	1.8
0°-30°	1542.3	19.0
0°-40°	2255.7	27.8
0°-60°	3332.1	41.1
0°-90°	3817.6	47.0
90°-120°	916.6	11.3
90°-150°	3107.4	38.3
90°-180°	4296.0	52.9
0°-180°	8114.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	31
90°	44	1	44	1	44	20
95°	80	67	80	67	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	512
125°	757	755	757	755	757	675
135°	988	976	988	976	988	761
145°	1198	1185	1198	1185	1198	748
155°	1365	1355	1365	1355	1365	628
165°	1476	1474	1476	1474	1476	416
175°	1529	1534	1529	1534	1529	145
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	18.6	19.2	19.1	19.1	19.0	19.0	19.2	19.9	19.4	20.1	18.2
90°	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2	44.8	45.4	39.0
92.5°	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5	41.3	41.2	39.7
95°	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0	83.0	83.0	82.4
97.5°	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5	139.5	139.5	138.4
100°	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9	178.9	178.9	178.1
102.5°	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9	221.7	221.5	220.4
105°	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4	285.8	285.3	284.7
107.5°	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0	355.8	355.5	355.5
110°	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6	451.3	452.0	452.2
115°	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3	523.6	523.8	524.4
117.5°	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5	594.2	594.9	596.5
120°	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5	640.5	640.5	642.8
122.5°	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0	689.6	690.3	691.9
125°	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7	761.6	762.4	763.3
127.5°	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4	831.4	832.4	833.5
130°	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0	878.5	879.1	879.7
132.5°	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3	925.6	926.8	926.7
135°	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7	992.9	993.2	992.7
137.5°	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1	1058.4	1058.6	1057.8
140°	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1	1102.1	1102.1	1100.7
142.5°	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0	1141.8	1141.6	1140.6
145°	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6	1202.3	1202.0	1200.3
147.5°	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6	1255.0	1254.4	1253.2
150°	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6	1286.4
152.5°	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8	1319.4
155°	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7	1364.2	1362.8	1361.9
157.5°	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1	1403.1	1401.2	1400.6
160°	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5	1426.7	1425.0	1424.7
162.5°	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7	1447.7	1445.8	1445.5
165°	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0	1475.0	1473.0	1473.0
167.5°	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6	1497.6	1495.5	1495.6
170°	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0	1510.0	1508.0	1508.3
172.5°	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4	1519.4	1517.3	1517.6
175°	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5	1529.5	1527.4	1528.0
177.5°	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4	1533.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	17.0	16.3	15.0	13.4	13.4	13.3	15.7	18.0	16.3	15.1	14.6
90°	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1	25.6	28.2	30.7
95°	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4	70.3	73.2	76.1
97.5°	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2	125.7	128.3	130.8
100°	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7	167.0	169.3	171.6
102.5°	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2	210.1	211.9	213.8
105°	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8	279.6	280.5	281.4
107.5°	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8	351.1	352.4	353.6
110°	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5	397.2	398.9	400.7



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3	447.0	448.7	450.5
115°	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7	520.4	522.1	523.8
117.5°	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8	594.1	596.4	598.7
120°	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	642.8	645.2	647.5
122.5°	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1	687.9	690.7	693.4
125°	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6	757.2	759.8	762.4
127.5°	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3	825.6	828.9	832.2
130°	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9	868.6	872.4	876.1
132.5°	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6	915.6	918.7	921.7
135°	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4	979.5	982.7	985.9
137.5°	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5	1046.1	1048.7	1051.3
140°	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0	1086.6	1089.2	1091.8
142.5°	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5	1128.1	1130.7	1133.3
145°	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1	1187.2	1189.2	1191.2
147.5°	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3	1240.7	1243.1	1245.6
150°	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6	1276.3	1278.1	1279.8
152.5°	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8	1308.5	1310.2	1311.9
155°	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0	1355.9	1356.7	1357.6
157.5°	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2	1396.8	1397.4	1398.0
160°	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1	1421.7	1422.3	1422.9
162.5°	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9	1444.1	1444.2	1444.3
165°	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3	1474.0	1473.7	1473.4
167.5°	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7	1498.8	1498.0	1497.1
170°	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2	1512.3	1511.5	1510.6
172.5°	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5	1521.7	1520.8	1519.9
175°	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9	1533.1	1532.2	1531.3
177.5°	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6	1537.9	1537.2	1536.5
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	14.7	15.0	15.1	16.3	17.6	18.3	18.2	17.4	17.3	17.2	16.6
90°	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2	43.7	43.1	42.9
92.5°	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5	41.6	41.7	41.8
95°	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0	83.0	83.0	82.7
97.5°	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5	139.5	139.5	139.5
100°	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9	178.9	178.9	178.8
102.5°	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9	222.2	222.4	222.4
105°	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4	287.0	287.6	287.9
107.5°	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0	356.2	356.5	355.9
110°	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	402.8



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6	449.9	449.2	448.6
115°	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3	523.0	522.7	522.1
117.5°	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5	592.8	592.1	591.4
120°	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5	640.5	640.5	640.1
122.5°	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0	688.3	687.6	686.9
125°	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7	759.8	759.0	758.4
127.5°	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4	829.3	828.3	827.3
130°	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0	877.4	876.8	876.0
132.5°	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3	923.0	921.8	920.7
135°	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7	992.4	992.1	991.5
137.5°	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1	1057.9	1057.7	1057.0
140°	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1	1102.1	1102.1	1101.6
142.5°	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0	1142.3	1142.5	1142.0
145°	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6	1202.9	1203.1	1202.7
147.5°	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6	1256.3	1256.9	1256.7
150°	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0
152.5°	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1
155°	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7	1367.1	1368.5	1368.8
157.5°	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1	1407.0	1409.0	1409.3
160°	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5	1430.2	1431.9	1432.2
162.5°	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7	1451.6	1453.6	1453.9
165°	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0	1479.0	1481.1	1481.3
167.5°	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6	1501.6	1503.6	1503.9
170°	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0	1514.0	1516.1	1516.2
172.5°	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4	1523.4	1525.4	1525.5
175°	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5	1533.5	1535.5	1535.7
177.5°	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	16.6	16.1	16.7	16.2	16.7	16.1	16.6	16.6	17.2	17.3	17.4
90°	43.2	43.5	43.8	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5
95°	82.1	81.5	81.0	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0
97.5°	139.4	139.4	139.3	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5
100°	178.5	178.2	177.9	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9
102.5°	222.1	221.8	221.5	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9
105°	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4
107.5°	354.6	353.3	351.9	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0
110°	402.0	401.1	400.2	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	447.9	447.3	446.7	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6
115°	521.3	520.4	519.5	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3
117.5°	590.5	589.6	588.8	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5
120°	639.2	638.4	637.5	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5
122.5°	686.3	685.6	685.0	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0
125°	758.1	757.8	757.5	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7
127.5°	826.4	825.5	824.6	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4
130°	874.8	873.7	872.5	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0
132.5°	919.8	918.8	917.9	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3
135°	990.6	989.8	988.9	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7
137.5°	1055.8	1054.7	1053.5	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1
140°	1100.4	1099.3	1098.1	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1
142.5°	1140.9	1139.7	1138.6	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0
145°	1201.6	1200.4	1199.3	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6
147.5°	1255.6	1254.5	1253.4	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6
150°	1290.2	1289.3	1288.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3
152.5°	1324.0	1323.0	1321.9	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0
155°	1368.0	1367.1	1366.2	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7
157.5°	1407.9	1406.5	1405.1	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1
160°	1431.1	1429.9	1428.8	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5
162.5°	1452.5	1451.1	1449.7	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7
165°	1479.9	1478.5	1477.0	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0
167.5°	1502.4	1500.9	1499.4	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6
170°	1514.5	1512.8	1511.0	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0
172.5°	1523.8	1522.1	1520.4	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4
175°	1533.9	1532.2	1530.5	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5
177.5°	1537.6	1536.2	1534.8	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	18.2	18.3	17.6	16.3	15.1	15.0	14.7	14.6	15.1	16.3	18.0
90°	44.8	45.4	39.0	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3
92.5°	41.3	41.2	39.7	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1
95°	83.0	83.0	82.4	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4
97.5°	139.5	139.5	138.4	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2
100°	178.9	178.9	178.1	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7
102.5°	221.7	221.5	220.4	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2
105°	285.8	285.3	284.7	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8
107.5°	355.8	355.5	355.5	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8
110°	403.3	403.3	403.3	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.3	452.0	452.2	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3
115°	523.6	523.8	524.4	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7
117.5°	594.2	594.9	596.5	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8
120°	640.5	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5
122.5°	689.6	690.3	691.9	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1
125°	761.6	762.4	763.3	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6
127.5°	831.4	832.4	833.5	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3
130°	878.5	879.1	879.7	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9
132.5°	925.6	926.8	926.7	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6
135°	992.9	993.2	992.7	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4
137.5°	1058.4	1058.6	1057.8	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5
140°	1102.1	1102.1	1100.7	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0
142.5°	1141.8	1141.6	1140.6	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5
145°	1202.3	1202.0	1200.3	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1
147.5°	1255.0	1254.4	1253.2	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3
150°	1288.4	1287.6	1286.4	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6
152.5°	1321.9	1320.8	1319.4	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8
155°	1364.2	1362.8	1361.9	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0
157.5°	1403.1	1401.2	1400.6	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2
160°	1426.7	1425.0	1424.7	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1
162.5°	1447.7	1445.8	1445.5	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9
165°	1475.0	1473.0	1473.0	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3
167.5°	1497.6	1495.5	1495.6	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7
170°	1510.0	1508.0	1508.3	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2
172.5°	1519.4	1517.3	1517.6	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5
175°	1529.5	1527.4	1528.0	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9
177.5°	1534.8	1533.4	1533.9	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	15.7	13.3	13.4	13.4	15.0	16.3	17.0	18.2	20.1	19.4	19.9
90°	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2
92.5°	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5
95°	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0
97.5°	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5
100°	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9
102.5°	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9
105°	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4
107.5°	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0
110°	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6
115°	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3
117.5°	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5
120°	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5
122.5°	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0
125°	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7
127.5°	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4
130°	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0
132.5°	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3
135°	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7
137.5°	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1
140°	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1
142.5°	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0
145°	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6
147.5°	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6
150°	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3
152.5°	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0
155°	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7
157.5°	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1
160°	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5
162.5°	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7
165°	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0
167.5°	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6
170°	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0
172.5°	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4
175°	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5
177.5°	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	19.2	19.0	19.0	19.1	19.1	19.2	18.6
90°	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331858

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)