

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331860

Luminaire Tested: **S122RDIW-S1005D1240U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331860
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7785.5 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	29	25
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	58	47	39	33	54	43	36	32	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	2.0
10°-20°	435.2	5.6
20°-30°	611.2	7.9
30°-40°	666.5	8.6
40°-50°	612.8	7.9
50°-60°	481.3	6.2
60°-70°	313.8	4.0
70°-80°	161.8	2.1
80°-90°	48.1	0.6
90°-100°	97.4	1.3
100°-110°	302.4	3.9
110°-120°	516.9	6.6
120°-130°	679.7	8.7
130°-140°	762.9	9.8
140°-150°	748.1	9.6
150°-160°	627.4	8.1
160°-170°	416.2	5.3
170°-180°	145.5	1.9
0°-30°	1204.9	15.5
0°-40°	1871.4	24.0
0°-60°	2965.4	38.1
0°-90°	3489.1	44.8
90°-120°	916.6	11.8
90°-150°	3107.4	39.9
90°-180°	4296.0	55.2
0°-180°	7785.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	1	18	45	43	44	6
95°	67	80	83	83	80	77
105°	279	283	285	288	288	294
115°	519	526	524	522	519	513
125°	755	765	762	759	757	674
135°	976	990	993	992	988	754
145°	1185	1194	1202	1203	1198	740
155°	1355	1359	1363	1369	1365	623
165°	1474	1473	1473	1481	1476	416
175°	1534	1530	1527	1536	1529	146
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.9	18.4	16.9	15.4	13.9	13.8	15.1	16.3	17.6	18.9	18.5
90°	1.3	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8
92.5°	23.1	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3
95°	67.4	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0
97.5°	123.2	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5
100°	164.7	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9
102.5°	208.2	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7
105°	278.8	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8
107.5°	349.8	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8
110°	395.5	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.3	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3
115°	518.7	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6
117.5°	591.8	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2
120°	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5
122.5°	685.1	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6
125°	754.6	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6
127.5°	822.3	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4
130°	864.9	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5
132.5°	912.6	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6
135°	976.4	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9
137.5°	1043.5	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4
140°	1084.0	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1
142.5°	1125.5	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8
145°	1185.1	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3
147.5°	1238.3	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0
150°	1274.6	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4
152.5°	1306.8	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9
155°	1355.0	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2
157.5°	1396.2	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1
160°	1421.1	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7
162.5°	1443.9	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7
165°	1474.3	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0
167.5°	1499.7	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6
170°	1513.2	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0
172.5°	1522.5	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4
175°	1533.9	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5
177.5°	1538.6	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	18.1	17.7	17.3	17.2	17.2	17.3	17.3	17.4
90°	44.2	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.5	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	221.9	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	286.4	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.0	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331860

CATALOG NUMBER: S122RDIW-S1005D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.6	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.3	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	593.5	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	689.0	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	760.7	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	830.4	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	878.0	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	924.3	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.7	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1058.1	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.0	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.6	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1255.6	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1365.7	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1405.1	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1428.5	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1449.7	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1477.0	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1499.6	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1512.0	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1521.4	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1531.5	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)