

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331547-830

Luminaire Tested: **S122DIW-S675D1240U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331547-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7219.4 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	78	71	66	62	58	54	51	45	42	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.3
10°-20°	264.8	3.7
20°-30°	389.2	5.4
30°-40°	452.1	6.3
40°-50°	451.6	6.3
50°-60°	393.8	5.5
60°-70°	291.2	4.0
70°-80°	164.9	2.3
80°-90°	48.3	0.7
90°-100°	53.1	0.7
100°-110°	194.9	2.7
110°-120°	521.0	7.2
120°-130°	860.1	11.9
130°-140°	914.7	12.7
140°-150°	850.1	11.8
150°-160°	683.5	9.5
160°-170°	440.5	6.1
170°-180°	151.6	2.1
0°-30°	748.0	10.4
0°-40°	1200.1	16.6
0°-60°	2045.4	28.3
0°-90°	2549.8	35.3
90°-120°	769.1	10.7
90°-150°	3394.0	47.0
90°-180°	4670.0	64.7
0°-180°	7219.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	14	23	29	31	5
95°	75	39	45	50	50	92
105°	350	366	70	83	88	375
115°	663	683	711	203	94	653
125°	937	953	974	982	986	835
135°	1160	1178	1189	1200	1198	896
145°	1346	1346	1364	1371	1366	841
155°	1482	1472	1485	1491	1483	682
165°	1561	1555	1558	1565	1558	441
175°	1597	1589	1591	1598	1588	152
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.0	14.3	14.5	14.8	15.0	15.1	15.2	15.3	15.4	15.4	15.2
90°	1.1	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3
92.5°	23.3	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4
95°	74.9	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3
97.5°	148.7	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2
100°	204.1	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8
102.5°	264.9	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2
105°	350.5	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1
107.5°	448.1	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6
110°	510.8	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.8	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5
115°	663.0	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8
117.5°	746.2	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2
120°	807.1	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2
122.5°	858.8	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4
125°	937.4	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1
127.5°	1008.6	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2
130°	1053.9	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8
132.5°	1099.9	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7
135°	1159.9	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3
137.5°	1220.5	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7
140°	1260.2	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4
142.5°	1293.5	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3
145°	1345.5	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7
147.5°	1390.9	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3
150°	1420.5	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4
152.5°	1445.4	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5
155°	1481.6	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6
157.5°	1510.0	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6
160°	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0
162.5°	1541.3	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1
165°	1561.1	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4
167.5°	1575.9	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0
170°	1584.2	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4
172.5°	1589.7	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9
175°	1596.9	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9
177.5°	1598.0	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	14.9	14.6	14.3	14.2	14.1	14.0	13.9	13.9
90°	25.6	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.1	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	47.5	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	62.2	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	69.8	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	72.9	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	76.0	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	92.7	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	150.5	124.9	99.2	87.0	88.0	89.1	90.1	91.0



TEST NUMBER: P331547-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.0	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	474.1	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	730.6	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	851.3	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	903.2	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	977.9	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1046.8	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1090.6	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1133.1	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1193.8	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1250.2	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1286.8	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1320.4	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1367.5	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1408.6	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1433.9	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1457.0	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1488.1	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1514.4	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1529.7	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1543.9	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1575.7	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1583.2	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1588.7	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1594.7	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1595.3	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)