

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331864

Luminaire Tested: **S122RDIW-S1005D1440U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331864
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8485.4 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	1.9
10°-20°	435.2	5.1
20°-30°	611.2	7.2
30°-40°	666.5	7.9
40°-50°	612.8	7.2
50°-60°	481.3	5.7
60°-70°	313.8	3.7
70°-80°	161.8	1.9
80°-90°	49.1	0.6
90°-100°	113.2	1.3
100°-110°	351.6	4.1
110°-120°	601.0	7.1
120°-130°	790.3	9.3
130°-140°	887.0	10.5
140°-150°	869.7	10.2
150°-160°	729.5	8.6
160°-170°	483.8	5.7
170°-180°	169.1	2.0
0°-30°	1204.9	14.2
0°-40°	1871.4	22.1
0°-60°	2965.4	34.9
0°-90°	3490.1	41.1
90°-120°	1065.7	12.6
90°-150°	3612.8	42.6
90°-180°	4995.0	58.9
0°-180°	8485.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	2	20	53	50	51	7
95°	78	93	96	96	94	90
105°	324	329	332	334	335	342
115°	603	611	609	607	603	596
125°	877	890	886	882	880	784
135°	1135	1151	1155	1153	1149	877
145°	1378	1388	1398	1399	1393	860
155°	1575	1580	1584	1591	1588	725
165°	1714	1713	1713	1722	1716	483
175°	1783	1779	1776	1785	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.9	18.5	17.2	15.8	14.4	14.5	15.9	17.4	18.9	20.4	20.0
90°	1.5	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1
92.5°	26.8	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1
95°	78.4	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5
97.5°	143.2	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2
100°	191.5	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0
102.5°	242.1	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8
105°	324.1	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3
107.5°	406.7	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6
110°	459.8	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	517.7	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7
115°	603.0	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7
117.5°	688.1	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9
120°	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7
122.5°	796.6	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8
125°	877.4	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4
127.5°	956.1	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6
130°	1005.5	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5
132.5°	1061.0	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1
135°	1135.2	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5
137.5°	1213.3	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5
140°	1260.3	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4
142.5°	1308.6	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5
145°	1377.9	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8
147.5°	1439.7	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2
150°	1481.9	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0
152.5°	1519.3	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9
155°	1575.4	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1
157.5°	1623.3	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3
160°	1652.3	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8
162.5°	1678.8	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2
165°	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9
167.5°	1743.6	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2
170°	1759.3	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6
172.5°	1770.2	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5
175°	1783.4	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3
177.5°	1788.9	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	19.5	19.1	18.7	18.6	18.6	18.7	18.8	18.8
90°	51.4	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.2	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.0	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.0	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	413.9	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331864

CATALOG NUMBER: S122RDIW-S1005D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	523.9	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.4	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	690.1	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	801.0	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	884.4	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	965.4	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.8	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1074.7	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1154.1	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.2	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1327.8	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.2	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1459.9	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1587.8	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1633.6	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1660.8	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1685.5	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1717.3	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1743.5	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1758.0	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1768.8	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1780.6	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)