

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331526-830

Luminaire Tested: **S122DIW-S675D435U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331526-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4179.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66																				
1	102	98	94	91	96	92	89	86	82	80	77	72	71	69	64	62	61	57																				
2	93	86	80	75	88	81	76	72	73	69	65	64	61	59	57	55	53	49																				
3	86	76	69	63	80	72	66	61	65	60	55	58	54	50	51	48	45	42																				
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37																				
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32																				
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29																				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	30	35	31	28	26																				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23																				
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21																				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	2.9
10°-20°	346.6	8.3
20°-30°	503.1	12.0
30°-40°	530.9	12.7
40°-50°	470.0	11.2
50°-60°	375.1	9.0
60°-70°	254.9	6.1
70°-80°	130.7	3.1
80°-90°	33.5	0.8
90°-100°	32.1	0.8
100°-110°	99.6	2.4
110°-120°	170.2	4.1
120°-130°	223.9	5.4
130°-140°	251.3	6.0
140°-150°	246.4	5.9
150°-160°	206.6	4.9
160°-170°	137.1	3.3
170°-180°	47.9	1.1
0°-30°	968.9	23.2
0°-40°	1499.8	35.9
0°-60°	2344.9	56.1
0°-90°	2764.1	66.1
90°-120°	301.9	7.2
90°-150°	1023.3	24.5
90°-180°	1415.0	33.9
0°-180°	4179.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	14	0	14	0	14	8
95°	26	22	26	22	26	30
105°	95	92	95	92	95	100
115°	171	171	171	171	171	169
125°	249	248	249	248	249	222
135°	325	322	325	322	325	250
145°	394	390	394	390	394	246
155°	450	446	450	446	450	207
165°	486	486	486	486	486	137
175°	504	505	504	505	504	48
180°	506	506	506	506	506	



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	12.9	12.9	13.3	12.8	12.8	13.2	13.3	12.9	13.4	13.8	13.8
90°	14.5	14.4	14.3	14.2	14.1	14.2	14.4	14.6	14.8	15.0	12.8
92.5°	13.9	13.9	13.8	13.8	13.8	13.8	13.7	13.7	13.6	13.6	13.1
95°	26.5	26.7	26.9	27.1	27.2	27.3	27.3	27.3	27.3	27.3	27.1
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.6
100°	58.5	58.6	58.7	58.8	58.9	58.9	58.9	58.9	58.9	58.9	58.6
102.5°	72.9	73.0	73.0	73.1	73.2	73.2	73.1	73.0	73.0	73.0	72.6
105°	94.8	94.8	94.8	94.8	94.8	94.7	94.5	94.3	94.2	94.0	93.8
107.5°	115.5	115.9	116.3	116.8	117.3	117.4	117.3	117.3	117.2	117.1	117.1
110°	131.5	131.8	132.1	132.3	132.6	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.9	147.1	147.3	147.5	147.7	148.0	148.2	148.5	148.6	148.8	148.9
115°	170.8	171.1	171.4	171.6	171.9	172.1	172.2	172.3	172.4	172.5	172.7
117.5°	193.6	193.9	194.2	194.4	194.7	195.0	195.2	195.5	195.7	196.0	196.4
120°	209.7	210.0	210.3	210.6	210.8	210.9	210.9	210.9	210.9	210.9	211.7
122.5°	225.4	225.6	225.8	226.0	226.2	226.4	226.7	226.9	227.2	227.3	227.9
125°	249.4	249.5	249.6	249.7	249.8	250.0	250.2	250.5	250.8	251.1	251.4
127.5°	271.3	271.5	271.8	272.1	272.5	272.8	273.1	273.4	273.8	274.2	274.5
130°	287.0	287.4	287.8	288.1	288.5	288.8	289.0	289.2	289.4	289.5	289.7
132.5°	302.0	302.3	302.6	302.9	303.2	303.6	304.0	304.4	304.8	305.2	305.2
135°	325.4	325.6	325.9	326.2	326.5	326.7	326.8	326.9	327.0	327.1	326.9
137.5°	346.6	346.9	347.3	347.7	348.1	348.4	348.4	348.5	348.6	348.6	348.4
140°	361.3	361.7	362.0	362.4	362.8	363.0	363.0	363.0	363.0	363.0	362.5
142.5°	374.6	374.9	375.3	375.7	376.1	376.3	376.2	376.1	376.1	376.0	375.6
145°	394.5	394.9	395.3	395.7	396.1	396.2	396.2	396.1	396.0	395.9	395.3
147.5°	412.5	412.7	413.1	413.5	413.9	414.0	413.8	413.5	413.3	413.1	412.7
150°	424.0	424.3	424.6	424.9	425.2	425.2	424.9	424.6	424.3	424.0	423.7
152.5°	435.0	435.4	435.6	436.0	436.4	436.4	436.0	435.6	435.4	435.0	434.5
155°	449.7	450.0	450.3	450.5	450.8	450.7	450.3	449.8	449.3	448.8	448.6
157.5°	462.3	462.8	463.2	463.6	464.1	464.0	463.4	462.7	462.1	461.5	461.3
160°	470.1	470.5	470.9	471.3	471.6	471.6	471.0	470.4	469.9	469.3	469.2
162.5°	477.0	477.4	477.9	478.3	478.8	478.7	478.1	477.4	476.7	476.2	476.1
165°	486.0	486.4	486.9	487.4	487.9	487.8	487.1	486.4	485.8	485.1	485.1
167.5°	493.3	493.8	494.3	494.7	495.3	495.2	494.6	493.9	493.2	492.6	492.6
170°	497.1	497.7	498.2	498.8	499.4	499.3	498.6	497.9	497.3	496.6	496.7
172.5°	500.1	500.7	501.2	501.8	502.4	502.4	501.7	501.1	500.4	499.7	499.8
175°	503.5	504.1	504.6	505.2	505.8	505.7	505.0	504.4	503.7	503.0	503.2
177.5°	505.0	505.5	506.0	506.3	506.8	506.8	506.3	506.0	505.5	505.0	505.1
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	13.7	13.3	12.9	13.3	12.0	11.7	9.9	8.6	8.4	8.2	7.7
90°	10.7	8.7	6.6	5.0	3.9	2.7	1.6	0.5	1.6	2.7	3.9
92.5°	12.6	12.1	11.6	10.9	10.1	9.2	8.5	7.6	8.5	9.2	10.1
95°	27.0	26.8	26.6	26.0	25.1	24.1	23.2	22.2	23.2	24.1	25.1
97.5°	45.2	44.9	44.5	43.9	43.1	42.2	41.4	40.5	41.4	42.2	43.1
100°	58.3	58.1	57.8	57.3	56.6	55.7	55.0	54.2	55.0	55.7	56.6
102.5°	72.2	71.8	71.5	71.0	70.4	69.7	69.2	68.6	69.2	69.7	70.4
105°	93.6	93.4	93.2	92.9	92.7	92.4	92.1	91.8	92.1	92.4	92.7
107.5°	117.1	117.1	117.1	116.9	116.5	116.0	115.6	115.2	115.6	116.0	116.5
110°	132.8	132.8	132.8	132.5	132.0	131.4	130.8	130.3	130.8	131.4	132.0



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	149.0	149.1	149.2	148.9	148.4	147.8	147.2	146.7	147.2	147.8	148.4
115°	172.9	173.1	173.2	173.1	172.5	171.9	171.4	170.8	171.4	171.9	172.5
117.5°	197.0	197.6	198.0	197.9	197.2	196.4	195.7	194.9	195.7	196.4	197.2
120°	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	211.7	212.4	213.2
122.5°	228.4	228.9	229.5	229.3	228.4	227.4	226.6	225.6	226.6	227.4	228.4
125°	251.7	251.9	252.2	251.9	251.1	250.2	249.4	248.5	249.4	250.2	251.1
127.5°	274.8	275.2	275.5	275.1	274.1	273.0	271.9	270.8	271.9	273.0	274.1
130°	289.9	290.1	290.3	289.7	288.5	287.3	286.1	284.8	286.1	287.3	288.5
132.5°	305.2	305.1	305.1	304.5	303.6	302.6	301.5	300.6	301.5	302.6	303.6
135°	326.7	326.5	326.3	325.7	324.7	323.7	322.6	321.6	322.6	323.7	324.7
137.5°	348.2	347.9	347.6	347.0	346.2	345.3	344.5	343.7	344.5	345.3	346.2
140°	362.0	361.6	361.1	360.4	359.6	358.7	357.9	357.0	357.9	358.7	359.6
142.5°	375.3	374.9	374.7	374.1	373.2	372.4	371.6	370.7	371.6	372.4	373.2
145°	394.7	394.2	393.6	392.9	392.3	391.6	391.0	390.3	391.0	391.6	392.3
147.5°	412.4	412.0	411.6	411.0	410.2	409.4	408.6	407.8	408.6	409.4	410.2
150°	423.3	422.9	422.5	422.1	421.5	420.9	420.4	419.8	420.4	420.9	421.5
152.5°	434.0	433.6	433.2	432.6	432.1	431.5	430.9	430.4	430.9	431.5	432.1
155°	448.3	448.0	447.7	447.4	447.1	446.8	446.5	446.2	446.5	446.8	447.1
157.5°	461.1	460.9	460.7	460.6	460.4	460.2	460.1	459.9	460.1	460.2	460.4
160°	469.1	469.0	468.9	468.8	468.6	468.4	468.3	468.1	468.3	468.4	468.6
162.5°	476.0	475.9	475.8	475.7	475.6	475.6	475.6	475.5	475.6	475.6	475.6
165°	485.1	485.1	485.1	485.1	485.2	485.3	485.4	485.5	485.4	485.3	485.2
167.5°	492.6	492.6	492.6	492.8	493.0	493.3	493.6	493.9	493.6	493.3	493.0
170°	496.8	496.9	497.0	497.2	497.5	497.8	498.0	498.3	498.0	497.8	497.5
172.5°	499.9	500.0	500.1	500.3	500.6	500.9	501.1	501.4	501.1	500.9	500.6
175°	503.4	503.6	503.8	504.1	504.4	504.6	504.9	505.2	504.9	504.6	504.4
177.5°	505.3	505.5	505.6	505.8	506.1	506.2	506.5	506.7	506.5	506.2	506.1
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	392.1	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	7.5	7.4	7.5	7.9	7.9	8.0	7.5	7.5	7.5	6.7	6.7
90°	5.0	6.6	8.7	10.7	12.8	15.0	14.8	14.6	14.4	14.2	14.1
92.5°	10.9	11.6	12.1	12.6	13.1	13.6	13.6	13.7	13.7	13.8	13.8
95°	26.0	26.6	26.8	27.0	27.1	27.3	27.3	27.3	27.3	27.3	27.2
97.5°	43.9	44.5	44.9	45.2	45.6	45.9	45.9	45.9	45.9	45.9	45.9
100°	57.3	57.8	58.1	58.3	58.6	58.9	58.9	58.9	58.9	58.9	58.9
102.5°	71.0	71.5	71.8	72.2	72.6	73.0	73.0	73.0	73.1	73.2	73.2
105°	92.9	93.2	93.4	93.6	93.8	94.0	94.2	94.3	94.5	94.7	94.8
107.5°	116.9	117.1	117.1	117.1	117.1	117.1	117.2	117.3	117.3	117.4	117.3
110°	132.5	132.8	132.8	132.8	132.8	132.8	132.8	132.8	132.8	132.8	132.6



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	148.9	149.2	149.1	149.0	148.9	148.8	148.6	148.5	148.2	148.0	147.7
115°	173.1	173.2	173.1	172.9	172.7	172.5	172.4	172.3	172.2	172.1	171.9
117.5°	197.9	198.0	197.6	197.0	196.4	196.0	195.7	195.5	195.2	195.0	194.7
120°	214.0	214.0	213.2	212.4	211.7	210.9	210.9	210.9	210.9	210.9	210.8
122.5°	229.3	229.5	228.9	228.4	227.9	227.3	227.2	226.9	226.7	226.4	226.2
125°	251.9	252.2	251.9	251.7	251.4	251.1	250.8	250.5	250.2	250.0	249.8
127.5°	275.1	275.5	275.2	274.8	274.5	274.2	273.8	273.4	273.1	272.8	272.5
130°	289.7	290.3	290.1	289.9	289.7	289.5	289.4	289.2	289.0	288.8	288.5
132.5°	304.5	305.1	305.1	305.2	305.2	305.2	304.8	304.4	304.0	303.6	303.2
135°	325.7	326.3	326.5	326.7	326.9	327.1	327.0	326.9	326.8	326.7	326.5
137.5°	347.0	347.6	347.9	348.2	348.4	348.6	348.6	348.5	348.4	348.4	348.1
140°	360.4	361.1	361.6	362.0	362.5	363.0	363.0	363.0	363.0	363.0	362.8
142.5°	374.1	374.7	374.9	375.3	375.6	376.0	376.1	376.1	376.2	376.3	376.1
145°	392.9	393.6	394.2	394.7	395.3	395.9	396.0	396.1	396.2	396.2	396.1
147.5°	411.0	411.6	412.0	412.4	412.7	413.1	413.3	413.5	413.8	414.0	413.9
150°	422.1	422.5	422.9	423.3	423.7	424.0	424.3	424.6	424.9	425.2	425.2
152.5°	432.6	433.2	433.6	434.0	434.5	435.0	435.4	435.6	436.0	436.4	436.4
155°	447.4	447.7	448.0	448.3	448.6	448.8	449.3	449.8	450.3	450.7	450.8
157.5°	460.6	460.7	460.9	461.1	461.3	461.5	462.1	462.7	463.4	464.0	464.1
160°	468.8	468.9	469.0	469.1	469.2	469.3	469.9	470.4	471.0	471.6	471.6
162.5°	475.7	475.8	475.9	476.0	476.1	476.2	476.7	477.4	478.1	478.7	478.8
165°	485.1	485.1	485.1	485.1	485.1	485.1	485.8	486.4	487.1	487.8	487.9
167.5°	492.8	492.6	492.6	492.6	492.6	492.6	493.2	493.9	494.6	495.2	495.3
170°	497.2	497.0	496.9	496.8	496.7	496.6	497.3	497.9	498.6	499.3	499.4
172.5°	500.3	500.1	500.0	499.9	499.8	499.7	500.4	501.1	501.7	502.4	502.4
175°	504.1	503.8	503.6	503.4	503.2	503.0	503.7	504.4	505.0	505.7	505.8
177.5°	505.8	505.6	505.5	505.3	505.1	505.0	505.5	506.0	506.3	506.8	506.8
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	6.7	6.3	6.3	5.9	6.3	6.3	6.7	6.7	6.7	7.5	7.5
90°	14.2	14.3	14.4	14.5	14.4	14.3	14.2	14.1	14.2	14.4	14.6
92.5°	13.8	13.8	13.9	13.9	13.9	13.8	13.8	13.8	13.8	13.7	13.7
95°	27.1	26.9	26.7	26.5	26.7	26.9	27.1	27.2	27.3	27.3	27.3
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.8	58.7	58.6	58.5	58.6	58.7	58.8	58.9	58.9	58.9	58.9
102.5°	73.1	73.0	73.0	72.9	73.0	73.0	73.1	73.2	73.2	73.1	73.0
105°	94.8	94.8	94.8	94.8	94.8	94.8	94.8	94.8	94.7	94.5	94.3
107.5°	116.8	116.3	115.9	115.5	115.9	116.3	116.8	117.3	117.4	117.3	117.3
110°	132.3	132.1	131.8	131.5	131.8	132.1	132.3	132.6	132.8	132.8	132.8



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	147.5	147.3	147.1	146.9	147.1	147.3	147.5	147.7	148.0	148.2	148.5
115°	171.6	171.4	171.1	170.8	171.1	171.4	171.6	171.9	172.1	172.2	172.3
117.5°	194.4	194.2	193.9	193.6	193.9	194.2	194.4	194.7	195.0	195.2	195.5
120°	210.6	210.3	210.0	209.7	210.0	210.3	210.6	210.8	210.9	210.9	210.9
122.5°	226.0	225.8	225.6	225.4	225.6	225.8	226.0	226.2	226.4	226.7	226.9
125°	249.7	249.6	249.5	249.4	249.5	249.6	249.7	249.8	250.0	250.2	250.5
127.5°	272.1	271.8	271.5	271.3	271.5	271.8	272.1	272.5	272.8	273.1	273.4
130°	288.1	287.8	287.4	287.0	287.4	287.8	288.1	288.5	288.8	289.0	289.2
132.5°	302.9	302.6	302.3	302.0	302.3	302.6	302.9	303.2	303.6	304.0	304.4
135°	326.2	325.9	325.6	325.4	325.6	325.9	326.2	326.5	326.7	326.8	326.9
137.5°	347.7	347.3	346.9	346.6	346.9	347.3	347.7	348.1	348.4	348.4	348.5
140°	362.4	362.0	361.7	361.3	361.7	362.0	362.4	362.8	363.0	363.0	363.0
142.5°	375.7	375.3	374.9	374.6	374.9	375.3	375.7	376.1	376.3	376.2	376.1
145°	395.7	395.3	394.9	394.5	394.9	395.3	395.7	396.1	396.2	396.2	396.1
147.5°	413.5	413.1	412.7	412.5	412.7	413.1	413.5	413.9	414.0	413.8	413.5
150°	424.9	424.6	424.3	424.0	424.3	424.6	424.9	425.2	425.2	424.9	424.6
152.5°	436.0	435.6	435.4	435.0	435.4	435.6	436.0	436.4	436.4	436.0	435.6
155°	450.5	450.3	450.0	449.7	450.0	450.3	450.5	450.8	450.7	450.3	449.8
157.5°	463.6	463.2	462.8	462.3	462.8	463.2	463.6	464.1	464.0	463.4	462.7
160°	471.3	470.9	470.5	470.1	470.5	470.9	471.3	471.6	471.6	471.0	470.4
162.5°	478.3	477.9	477.4	477.0	477.4	477.9	478.3	478.8	478.7	478.1	477.4
165°	487.4	486.9	486.4	486.0	486.4	486.9	487.4	487.9	487.8	487.1	486.4
167.5°	494.7	494.3	493.8	493.3	493.8	494.3	494.7	495.3	495.2	494.6	493.9
170°	498.8	498.2	497.7	497.1	497.7	498.2	498.8	499.4	499.3	498.6	497.9
172.5°	501.8	501.2	500.7	500.1	500.7	501.2	501.8	502.4	502.4	501.7	501.1
175°	505.2	504.6	504.1	503.5	504.1	504.6	505.2	505.8	505.7	505.0	504.4
177.5°	506.3	506.0	505.5	505.0	505.5	506.0	506.3	506.8	506.8	506.3	506.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	7.5	8.0	7.9	7.9	7.5	7.4	7.5	7.7	8.2	8.4	8.6
90°	14.8	15.0	12.8	10.7	8.7	6.6	5.0	3.9	2.7	1.6	0.5
92.5°	13.6	13.6	13.1	12.6	12.1	11.6	10.9	10.1	9.2	8.5	7.6
95°	27.3	27.3	27.1	27.0	26.8	26.6	26.0	25.1	24.1	23.2	22.2
97.5°	45.9	45.9	45.6	45.2	44.9	44.5	43.9	43.1	42.2	41.4	40.5
100°	58.9	58.9	58.6	58.3	58.1	57.8	57.3	56.6	55.7	55.0	54.2
102.5°	73.0	73.0	72.6	72.2	71.8	71.5	71.0	70.4	69.7	69.2	68.6
105°	94.2	94.0	93.8	93.6	93.4	93.2	92.9	92.7	92.4	92.1	91.8
107.5°	117.2	117.1	117.1	117.1	117.1	117.1	116.9	116.5	116.0	115.6	115.2
110°	132.8	132.8	132.8	132.8	132.8	132.8	132.5	132.0	131.4	130.8	130.3



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	148.6	148.8	148.9	149.0	149.1	149.2	148.9	148.4	147.8	147.2	146.7
115°	172.4	172.5	172.7	172.9	173.1	173.2	173.1	172.5	171.9	171.4	170.8
117.5°	195.7	196.0	196.4	197.0	197.6	198.0	197.9	197.2	196.4	195.7	194.9
120°	210.9	210.9	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9
122.5°	227.2	227.3	227.9	228.4	228.9	229.5	229.3	228.4	227.4	226.6	225.6
125°	250.8	251.1	251.4	251.7	251.9	252.2	251.9	251.1	250.2	249.4	248.5
127.5°	273.8	274.2	274.5	274.8	275.2	275.5	275.1	274.1	273.0	271.9	270.8
130°	289.4	289.5	289.7	289.9	290.1	290.3	289.7	288.5	287.3	286.1	284.8
132.5°	304.8	305.2	305.2	305.2	305.1	305.1	304.5	303.6	302.6	301.5	300.6
135°	327.0	327.1	326.9	326.7	326.5	326.3	325.7	324.7	323.7	322.6	321.6
137.5°	348.6	348.6	348.4	348.2	347.9	347.6	347.0	346.2	345.3	344.5	343.7
140°	363.0	363.0	362.5	362.0	361.6	361.1	360.4	359.6	358.7	357.9	357.0
142.5°	376.1	376.0	375.6	375.3	374.9	374.7	374.1	373.2	372.4	371.6	370.7
145°	396.0	395.9	395.3	394.7	394.2	393.6	392.9	392.3	391.6	391.0	390.3
147.5°	413.3	413.1	412.7	412.4	412.0	411.6	411.0	410.2	409.4	408.6	407.8
150°	424.3	424.0	423.7	423.3	422.9	422.5	422.1	421.5	420.9	420.4	419.8
152.5°	435.4	435.0	434.5	434.0	433.6	433.2	432.6	432.1	431.5	430.9	430.4
155°	449.3	448.8	448.6	448.3	448.0	447.7	447.4	447.1	446.8	446.5	446.2
157.5°	462.1	461.5	461.3	461.1	460.9	460.7	460.6	460.4	460.2	460.1	459.9
160°	469.9	469.3	469.2	469.1	469.0	468.9	468.8	468.6	468.4	468.3	468.1
162.5°	476.7	476.2	476.1	476.0	475.9	475.8	475.7	475.6	475.6	475.6	475.5
165°	485.8	485.1	485.1	485.1	485.1	485.1	485.1	485.2	485.3	485.4	485.5
167.5°	493.2	492.6	492.6	492.6	492.6	492.6	492.8	493.0	493.3	493.6	493.9
170°	497.3	496.6	496.7	496.8	496.9	497.0	497.2	497.5	497.8	498.0	498.3
172.5°	500.4	499.7	499.8	499.9	500.0	500.1	500.3	500.6	500.9	501.1	501.4
175°	503.7	503.0	503.2	503.4	503.6	503.8	504.1	504.4	504.6	504.9	505.2
177.5°	505.5	505.0	505.1	505.3	505.5	505.6	505.8	506.1	506.2	506.5	506.7
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	9.9	11.7	12.0	13.3	12.9	13.3	13.7	13.8	13.8	13.4	12.9
90°	1.6	2.7	3.9	5.0	6.6	8.7	10.7	12.8	15.0	14.8	14.6
92.5°	8.5	9.2	10.1	10.9	11.6	12.1	12.6	13.1	13.6	13.6	13.7
95°	23.2	24.1	25.1	26.0	26.6	26.8	27.0	27.1	27.3	27.3	27.3
97.5°	41.4	42.2	43.1	43.9	44.5	44.9	45.2	45.6	45.9	45.9	45.9
100°	55.0	55.7	56.6	57.3	57.8	58.1	58.3	58.6	58.9	58.9	58.9
102.5°	69.2	69.7	70.4	71.0	71.5	71.8	72.2	72.6	73.0	73.0	73.0
105°	92.1	92.4	92.7	92.9	93.2	93.4	93.6	93.8	94.0	94.2	94.3
107.5°	115.6	116.0	116.5	116.9	117.1	117.1	117.1	117.1	117.1	117.2	117.3
110°	130.8	131.4	132.0	132.5	132.8	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	147.2	147.8	148.4	148.9	149.2	149.1	149.0	148.9	148.8	148.6	148.5
115°	171.4	171.9	172.5	173.1	173.2	173.1	172.9	172.7	172.5	172.4	172.3
117.5°	195.7	196.4	197.2	197.9	198.0	197.6	197.0	196.4	196.0	195.7	195.5
120°	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	210.9	210.9
122.5°	226.6	227.4	228.4	229.3	229.5	228.9	228.4	227.9	227.3	227.2	226.9
125°	249.4	250.2	251.1	251.9	252.2	251.9	251.7	251.4	251.1	250.8	250.5
127.5°	271.9	273.0	274.1	275.1	275.5	275.2	274.8	274.5	274.2	273.8	273.4
130°	286.1	287.3	288.5	289.7	290.3	290.1	289.9	289.7	289.5	289.4	289.2
132.5°	301.5	302.6	303.6	304.5	305.1	305.1	305.2	305.2	305.2	304.8	304.4
135°	322.6	323.7	324.7	325.7	326.3	326.5	326.7	326.9	327.1	327.0	326.9
137.5°	344.5	345.3	346.2	347.0	347.6	347.9	348.2	348.4	348.6	348.6	348.5
140°	357.9	358.7	359.6	360.4	361.1	361.6	362.0	362.5	363.0	363.0	363.0
142.5°	371.6	372.4	373.2	374.1	374.7	374.9	375.3	375.6	376.0	376.1	376.1
145°	391.0	391.6	392.3	392.9	393.6	394.2	394.7	395.3	395.9	396.0	396.1
147.5°	408.6	409.4	410.2	411.0	411.6	412.0	412.4	412.7	413.1	413.3	413.5
150°	420.4	420.9	421.5	422.1	422.5	422.9	423.3	423.7	424.0	424.3	424.6
152.5°	430.9	431.5	432.1	432.6	433.2	433.6	434.0	434.5	435.0	435.4	435.6
155°	446.5	446.8	447.1	447.4	447.7	448.0	448.3	448.6	448.8	449.3	449.8
157.5°	460.1	460.2	460.4	460.6	460.7	460.9	461.1	461.3	461.5	462.1	462.7
160°	468.3	468.4	468.6	468.8	468.9	469.0	469.1	469.2	469.3	469.9	470.4
162.5°	475.6	475.6	475.6	475.7	475.8	475.9	476.0	476.1	476.2	476.7	477.4
165°	485.4	485.3	485.2	485.1	485.1	485.1	485.1	485.1	485.1	485.8	486.4
167.5°	493.6	493.3	493.0	492.8	492.6	492.6	492.6	492.6	492.6	493.2	493.9
170°	498.0	497.8	497.5	497.2	497.0	496.9	496.8	496.7	496.6	497.3	497.9
172.5°	501.1	500.9	500.6	500.3	500.1	500.0	499.9	499.8	499.7	500.4	501.1
175°	504.9	504.6	504.4	504.1	503.8	503.6	503.4	503.2	503.0	503.7	504.4
177.5°	506.5	506.2	506.1	505.8	505.6	505.5	505.3	505.1	505.0	505.5	506.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	13.3	13.2	12.8	12.8	13.3	12.9	12.9
90°	14.4	14.2	14.1	14.2	14.3	14.4	14.5
92.5°	13.7	13.8	13.8	13.8	13.8	13.9	13.9
95°	27.3	27.3	27.2	27.1	26.9	26.7	26.5
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.9	58.9	58.9	58.8	58.7	58.6	58.5
102.5°	73.1	73.2	73.2	73.1	73.0	73.0	72.9
105°	94.5	94.7	94.8	94.8	94.8	94.8	94.8
107.5°	117.3	117.4	117.3	116.8	116.3	115.9	115.5
110°	132.8	132.8	132.6	132.3	132.1	131.8	131.5



TEST NUMBER: P331526-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	148.2	148.0	147.7	147.5	147.3	147.1	146.9
115°	172.2	172.1	171.9	171.6	171.4	171.1	170.8
117.5°	195.2	195.0	194.7	194.4	194.2	193.9	193.6
120°	210.9	210.9	210.8	210.6	210.3	210.0	209.7
122.5°	226.7	226.4	226.2	226.0	225.8	225.6	225.4
125°	250.2	250.0	249.8	249.7	249.6	249.5	249.4
127.5°	273.1	272.8	272.5	272.1	271.8	271.5	271.3
130°	289.0	288.8	288.5	288.1	287.8	287.4	287.0
132.5°	304.0	303.6	303.2	302.9	302.6	302.3	302.0
135°	326.8	326.7	326.5	326.2	325.9	325.6	325.4
137.5°	348.4	348.4	348.1	347.7	347.3	346.9	346.6
140°	363.0	363.0	362.8	362.4	362.0	361.7	361.3
142.5°	376.2	376.3	376.1	375.7	375.3	374.9	374.6
145°	396.2	396.2	396.1	395.7	395.3	394.9	394.5
147.5°	413.8	414.0	413.9	413.5	413.1	412.7	412.5
150°	424.9	425.2	425.2	424.9	424.6	424.3	424.0
152.5°	436.0	436.4	436.4	436.0	435.6	435.4	435.0
155°	450.3	450.7	450.8	450.5	450.3	450.0	449.7
157.5°	463.4	464.0	464.1	463.6	463.2	462.8	462.3
160°	471.0	471.6	471.6	471.3	470.9	470.5	470.1
162.5°	478.1	478.7	478.8	478.3	477.9	477.4	477.0
165°	487.1	487.8	487.9	487.4	486.9	486.4	486.0
167.5°	494.6	495.2	495.3	494.7	494.3	493.8	493.3
170°	498.6	499.3	499.4	498.8	498.2	497.7	497.1
172.5°	501.7	502.4	502.4	501.8	501.2	500.7	500.1
175°	505.0	505.7	505.8	505.2	504.6	504.1	503.5
177.5°	506.3	506.8	506.8	506.3	506.0	505.5	505.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1

(END OF REPORT)