

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331529-830

Luminaire Tested: **S122DIW-S675D435U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331529-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D435U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4178.8 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	59	57	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.1	2.3
10°-20°	264.8	6.3
20°-30°	389.2	9.3
30°-40°	452.1	10.8
40°-50°	451.6	10.8
50°-60°	393.8	9.4
60°-70°	291.2	7.0
70°-80°	164.9	3.9
80°-90°	45.7	1.1
90°-100°	18.6	0.4
100°-110°	68.1	1.6
110°-120°	182.0	4.4
120°-130°	300.5	7.2
130°-140°	319.6	7.6
140°-150°	297.0	7.1
150°-160°	238.8	5.7
160°-170°	153.9	3.7
170°-180°	53.0	1.3
0°-30°	748.0	17.9
0°-40°	1200.1	28.7
0°-60°	2045.4	48.9
0°-90°	2547.3	61.0
90°-120°	268.7	6.4
90°-150°	1185.9	28.4
90°-180°	1632.0	39.1
0°-180°	4178.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	0	5	8	10	11	3
95°	26	14	16	18	17	32
105°	122	128	25	29	31	131
115°	232	239	248	71	33	228
125°	328	333	340	343	344	292
135°	405	412	415	419	419	313
145°	470	470	476	479	477	294
155°	518	514	519	521	518	238
165°	545	543	544	547	544	154
175°	558	555	556	558	555	53
180°	557	557	557	557	557	



TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	13.9	13.8	13.7	13.5	13.4	13.2	13.0	12.8	12.6	12.3	12.0
90°	0.4	1.4	2.4	3.4	4.3	5.2	5.9	6.6	7.4	8.0	8.5
92.5°	8.1	8.0	7.9	7.8	7.8	7.9	8.3	8.7	9.0	9.3	9.6
95°	26.2	23.2	20.3	17.3	14.3	13.2	13.9	14.4	15.1	15.7	16.1
97.5°	51.9	43.6	35.3	27.0	18.7	15.3	16.7	18.1	19.6	21.0	21.4
100°	71.4	59.0	46.8	34.5	22.2	16.9	18.4	19.9	21.4	23.0	23.7
102.5°	92.6	90.0	87.4	84.8	82.2	74.6	61.8	49.1	36.4	23.6	24.5
105°	122.4	125.2	127.8	130.5	133.2	122.3	97.9	73.4	49.0	24.6	25.5
107.5°	156.6	158.7	160.9	163.1	165.2	151.7	122.3	93.0	63.7	34.4	33.4
110°	178.4	180.3	182.2	184.1	186.0	174.0	148.1	122.2	96.3	70.5	61.5



TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.1	200.8	202.5	204.1	205.8	203.4	197.0	190.6	184.2	177.9	145.2
115°	231.7	233.2	234.7	236.2	237.7	239.6	241.9	244.1	246.3	248.5	207.1
117.5°	260.7	262.4	264.1	265.8	267.5	269.2	270.7	272.2	273.8	275.3	265.3
120°	282.0	283.3	284.6	286.1	287.4	288.9	290.5	292.1	293.7	295.3	296.3
122.5°	300.0	301.4	302.8	304.3	305.7	307.3	309.1	310.8	312.5	314.3	315.0
125°	327.5	328.7	329.9	331.0	332.2	333.6	335.4	337.1	338.7	340.4	341.0
127.5°	352.4	353.7	355.0	356.3	357.6	358.8	360.1	361.4	362.7	363.9	364.9
130°	368.3	369.7	371.1	372.5	373.9	375.1	376.2	377.1	378.1	379.1	380.0
132.5°	384.4	385.5	386.7	388.0	389.2	390.3	391.2	392.3	393.2	394.3	395.1
135°	405.3	406.7	408.1	409.5	411.0	412.1	412.9	413.8	414.5	415.4	416.2
137.5°	426.5	427.4	428.5	429.5	430.5	431.4	432.3	433.3	434.1	435.1	435.9
140°	440.4	441.0	441.8	442.4	443.2	444.0	445.1	446.0	447.0	448.0	448.7
142.5°	451.9	452.6	453.2	453.8	454.5	455.4	456.5	457.6	458.7	459.9	460.6
145°	470.1	470.0	470.0	469.9	469.8	470.5	472.0	473.5	475.0	476.5	477.2
147.5°	486.0	485.7	485.3	485.0	484.7	485.2	486.7	488.2	489.7	491.3	491.7
150°	496.3	495.7	495.0	494.5	493.8	494.2	495.7	497.1	498.5	499.9	500.5
152.5°	505.0	504.4	503.6	502.9	502.2	502.6	503.9	505.3	506.6	508.0	508.5
155°	517.6	516.9	516.0	515.3	514.4	514.6	515.7	516.7	517.8	518.9	519.4
157.5°	527.5	526.9	526.2	525.6	524.9	524.9	525.7	526.4	527.2	527.9	528.5
160°	533.4	532.8	532.3	531.8	531.2	531.2	531.8	532.3	532.8	533.4	534.0
162.5°	538.6	538.0	537.4	537.0	536.4	536.4	536.8	537.2	537.7	538.2	538.9
165°	545.4	545.0	544.4	543.8	543.3	543.2	543.5	543.8	544.0	544.2	544.9
167.5°	550.6	550.1	549.6	549.0	548.5	548.4	548.6	548.8	549.1	549.3	550.0
170°	553.6	553.0	552.4	552.0	551.4	551.2	551.4	551.6	551.8	552.0	552.5
172.5°	555.4	555.0	554.4	553.8	553.3	553.2	553.3	553.5	553.6	553.8	554.5
175°	558.0	557.3	556.7	556.1	555.4	555.3	555.4	555.6	555.7	555.9	556.6
177.5°	558.4	557.9	557.3	556.9	556.4	556.1	556.2	556.3	556.4	556.4	556.9
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8



TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	11.5	11.1	10.7	10.4	10.3	10.2	10.0	9.9
90°	9.0	9.4	9.8	10.2	10.4	10.6	10.7	10.8
92.5°	9.8	10.1	10.3	10.5	10.6	10.7	10.7	10.8
95°	16.6	17.1	17.5	17.7	17.6	17.5	17.4	17.3
97.5°	21.8	22.1	22.4	22.7	22.8	22.9	23.0	23.1
100°	24.4	25.1	25.8	26.3	26.5	26.7	26.8	27.0
102.5°	25.4	26.4	27.3	27.9	28.2	28.5	28.7	28.9
105°	26.6	27.5	28.6	29.2	29.5	29.9	30.3	30.6
107.5°	32.4	31.4	30.3	30.1	30.4	30.8	31.1	31.5
110°	52.6	43.6	34.7	30.3	30.7	31.1	31.5	31.9





TEST NUMBER: P331529-830

CATALOG NUMBER: S122DIW-S675D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.5	79.8	47.2	31.0	31.3	31.6	31.9	32.1
115°	165.7	124.2	82.8	58.8	52.4	45.9	39.5	33.0
117.5°	255.2	245.2	235.2	219.6	198.4	177.2	156.1	134.9
120°	297.5	298.5	299.6	294.1	282.0	269.9	257.8	245.7
122.5°	315.6	316.2	316.9	316.0	313.7	311.3	309.0	306.6
125°	341.7	342.3	342.9	343.4	343.7	343.9	344.2	344.4
127.5°	365.8	366.6	367.6	368.1	368.2	368.2	368.3	368.3
130°	381.1	382.0	383.0	383.5	383.4	383.3	383.2	383.1
132.5°	396.0	396.7	397.6	397.9	397.8	397.8	397.8	397.7
135°	417.2	418.0	419.0	419.2	419.1	419.0	418.8	418.6
137.5°	436.9	437.7	438.6	438.8	438.6	438.3	438.0	437.6
140°	449.6	450.4	451.2	451.4	450.9	450.4	450.1	449.6
142.5°	461.4	462.1	462.9	463.0	462.5	462.1	461.7	461.2
145°	477.9	478.4	479.1	479.2	478.7	478.2	477.9	477.4
147.5°	492.2	492.7	493.1	493.1	492.8	492.4	492.0	491.6
150°	501.1	501.5	502.1	502.2	501.7	501.2	500.8	500.4
152.5°	509.1	509.6	510.2	510.1	509.5	509.0	508.3	507.7
155°	520.0	520.5	521.0	520.9	520.2	519.5	518.8	518.1
157.5°	529.1	529.7	530.4	530.3	529.6	528.9	528.2	527.5
160°	534.4	535.0	535.6	535.5	534.9	534.2	533.6	533.0
162.5°	539.4	540.1	540.6	540.5	539.8	539.0	538.3	537.5
165°	545.5	546.1	546.8	546.8	546.1	545.5	544.9	544.2
167.5°	550.6	551.2	551.9	551.8	550.9	550.2	549.3	548.6
170°	553.2	553.8	554.4	554.3	553.6	552.7	552.0	551.1
172.5°	555.1	555.7	556.4	556.3	555.4	554.7	553.8	553.1
175°	557.2	557.8	558.5	558.4	557.4	556.6	555.6	554.8
177.5°	557.4	557.9	558.5	558.4	557.7	557.0	556.4	555.8
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8

(END OF REPORT)