

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331777

Luminaire Tested: **S122RDIW-S290D1240U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331777
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1240U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6088.2 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	24	24	23	16
2	83	76	71	66	73	68	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18	12
4	69	60	52	47	61	53	47	42	40	36	33	29	26	24	18	16	15	11
5	64	53	46	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10
6	59	47	40	35	52	42	36	31	32	28	25	23	21	18	15	13	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	39	32	27	44	35	28	24	27	22	19	19	17	15	12	11	10	7
9	47	35	28	24	41	32	26	21	25	20	17	18	15	13	12	10	9	7
10	43	32	26	21	38	29	23	19	23	18	15	16	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.0
10°-20°	172.7	2.8
20°-30°	222.5	3.7
30°-40°	211.5	3.5
40°-50°	181.1	3.0
50°-60°	137.9	2.3
60°-70°	87.2	1.4
70°-80°	43.5	0.7
80°-90°	15.5	0.3
90°-100°	56.4	0.9
100°-110°	206.8	3.4
110°-120°	552.8	9.1
120°-130°	912.5	15.0
130°-140°	970.4	15.9
140°-150°	902.0	14.8
150°-160°	725.2	11.9
160°-170°	467.3	7.7
170°-180°	160.9	2.6
0°-30°	457.2	7.5
0°-40°	668.6	11.0
0°-60°	987.7	16.2
0°-90°	1134.0	18.6
90°-120°	816.0	13.4
90°-150°	3600.9	59.1
90°-180°	4954.0	81.4
0°-180°	6088.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	10
90°	33	1	33	1	33	15
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	703	100	703	100	251
125°	1046	994	1046	994	1046	905
135°	1271	1231	1271	1231	1271	980
145°	1450	1428	1450	1428	1450	907
155°	1573	1572	1573	1572	1573	726
165°	1653	1656	1653	1656	1653	467
175°	1684	1694	1684	1694	1684	160
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	9.5	9.6	9.5	9.4	9.3	9.1	8.8	8.7	8.3	8.2	7.5
90°	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2	25.8	24.5	22.3
92.5°	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8	29.1	28.4	27.3
95°	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4	49.1	47.7	45.8
97.5°	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0	64.9	63.9	59.5
100°	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1	71.9	69.7	65.1
102.5°	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3	74.5	71.7	110.3
105°	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6	77.6	74.6	148.8
107.5°	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4	101.4	104.5	193.5
110°	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7	186.9	214.1	292.6



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6	440.8	539.9	559.4
115°	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0	628.9	754.8	748.0
117.5°	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1	805.5	836.0	831.3
120°	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2	899.9	896.6	891.8
122.5°	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3	956.3	954.4	949.1
125°	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5	1035.6	1033.7	1028.5
127.5°	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6	1107.9	1105.1	1101.2
130°	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1	1154.1	1151.1	1148.1
132.5°	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2	1199.6	1197.1	1194.1
135°	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6	1263.9	1261.2	1258.7
137.5°	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4	1323.8	1321.1	1318.3
140°	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2	1362.7	1360.3	1357.3
142.5°	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9	1398.7	1396.5	1393.0
145°	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9	1449.0	1447.1	1442.5
147.5°	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5	1493.1	1491.6	1487.1
150°	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3	1519.7	1518.1	1513.7
152.5°	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8	1544.2	1542.5	1538.4
155°	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8	1577.2	1575.6	1572.3
157.5°	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7	1604.8	1603.0	1600.7
160°	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9	1621.2	1619.6	1618.0
162.5°	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0	1636.1	1634.3	1632.9
165°	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6	1651.8
167.5°	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8	1669.9	1668.0	1667.3
170°	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7	1677.8	1675.9	1675.3
172.5°	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5	1683.6	1681.7	1681.2
175°	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9	1690.0	1688.1	1687.6
177.5°	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6	1691.1	1689.6	1689.3
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	7.1	6.9	6.4	5.7	5.3	4.9	5.2	5.5	5.4	5.4	5.7
90°	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7	24.4	24.2	23.9
95°	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5	70.5	61.6	52.6
97.5°	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8	132.5	107.2	82.0
100°	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5	179.3	142.0	104.8
102.5°	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1	273.2	265.3	257.5
105°	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9	380.0	388.2	396.3
107.5°	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4	481.9	488.5	495.1
110°	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9	547.6	553.3	559.0



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5	609.6	614.6	619.7
115°	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4	708.0	712.6	717.2
117.5°	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7	796.9	802.0	807.2
120°	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3	860.4	864.4	868.5
122.5°	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1	915.4	919.7	924.0
125°	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5	998.0	1001.6	1005.1
127.5°	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1	1074.0	1077.9	1081.9
130°	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1	1122.4	1126.8	1131.1
132.5°	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0	1170.7	1174.4	1178.1
135°	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6	1234.9	1239.3	1243.6
137.5°	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9	1298.0	1301.0	1304.1
140°	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0	1339.2	1341.4	1343.5
142.5°	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3	1374.2	1376.2	1378.1
145°	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5	1427.3	1427.0	1426.7
147.5°	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7	1474.7	1473.7	1472.6
150°	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1	1505.2	1503.3	1501.3
152.5°	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5	1531.4	1529.2	1527.1
155°	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9	1569.4	1567.0	1564.5
157.5°	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0	1599.9	1597.8	1595.8
160°	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1618.0	1616.3	1614.7
162.5°	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3	1633.6	1632.0	1630.4
165°	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3	1654.7	1653.0	1651.4
167.5°	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0	1670.3	1668.7	1667.1
170°	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8	1679.1	1677.5	1675.9
172.5°	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6	1685.0	1683.4	1681.7
175°	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2	1692.3	1690.4	1688.5
177.5°	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4	1693.9	1692.4	1690.9
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	6.1	6.4	6.5	6.9	7.4	7.6	7.9	8.0	8.3	8.5	8.5
90°	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2	28.5	29.9	30.9
92.5°	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8	30.5	31.2	31.7
95°	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4	51.8	53.1	53.7
97.5°	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0	67.1	68.2	68.9
100°	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1	76.2	78.4	79.8
102.5°	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3	80.2	83.0	84.8
105°	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6	83.6	86.6	88.6
107.5°	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4	95.3	92.3	91.3
110°	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7	132.5	105.3	92.3



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6	242.5	143.3	94.1
115°	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0	377.2	251.3	178.6
117.5°	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1	744.6	714.2	666.8
120°	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2	906.4	909.7	893.0
122.5°	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3	960.3	962.2	959.6
125°	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5	1039.4	1041.3	1042.6
127.5°	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6	1113.4	1116.2	1117.7
130°	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1	1160.1	1163.0	1164.4
132.5°	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2	1204.7	1207.3	1208.4
135°	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6	1269.3	1272.1	1273.1
137.5°	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4	1329.1	1331.8	1332.6
140°	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2	1367.6	1370.1	1370.6
142.5°	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9	1403.2	1405.4	1405.8
145°	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9	1452.8	1454.7	1455.0
147.5°	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5	1495.9	1497.3	1497.4
150°	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3	1523.0	1524.6	1524.7
152.5°	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8	1547.4	1549.1	1549.0
155°	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8	1580.5	1582.1	1581.8
157.5°	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7	1608.5	1610.4	1610.2
160°	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9	1624.5	1626.1	1626.0
162.5°	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0	1639.8	1641.7	1641.4
165°	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2
167.5°	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8	1673.7	1675.6	1675.4
170°	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7	1681.6	1683.5	1683.2
172.5°	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5	1687.4	1689.3	1689.1
175°	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9	1693.8	1695.7	1695.3
177.5°	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6	1694.1	1695.7	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	8.6	8.6	8.9	8.8	8.9	8.6	8.6	8.5	8.5	8.3	8.0
90°	31.4	31.9	32.5	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2
92.5°	32.0	32.4	32.7	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8
95°	53.4	53.1	52.9	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4
97.5°	69.2	69.6	69.9	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0
100°	80.3	80.9	81.4	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1
102.5°	85.5	86.3	87.1	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3
105°	89.7	90.8	91.9	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6
107.5°	92.4	93.5	94.6	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4
110°	93.4	94.5	95.6	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.0	95.9	96.7	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6
115°	159.0	139.5	119.9	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0
117.5°	602.5	538.2	473.9	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1
120°	856.3	819.6	782.9	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2
122.5°	952.5	945.4	938.3	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3
125°	1043.4	1044.3	1045.1	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5
127.5°	1117.8	1118.0	1118.1	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6
130°	1164.1	1163.9	1163.6	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1
132.5°	1208.2	1207.9	1207.6	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2
135°	1272.6	1272.1	1271.5	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6
137.5°	1331.7	1330.8	1329.9	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4
140°	1369.2	1367.9	1366.5	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2
142.5°	1404.5	1403.1	1401.7	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9
145°	1453.6	1452.3	1450.9	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9
147.5°	1496.3	1495.1	1494.0	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5
150°	1523.4	1522.0	1520.6	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3
152.5°	1547.2	1545.4	1543.6	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8
155°	1579.6	1577.5	1575.3	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8
157.5°	1608.1	1606.0	1603.9	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7
160°	1624.1	1622.2	1620.3	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9
162.5°	1639.1	1636.7	1634.4	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0
165°	1658.3	1656.4	1654.5	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4
167.5°	1672.9	1670.5	1668.0	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8
170°	1680.8	1678.3	1675.9	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7
172.5°	1686.6	1684.2	1681.7	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5
175°	1692.6	1689.9	1687.1	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9
177.5°	1693.5	1691.5	1689.6	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	7.9	7.6	7.4	6.9	6.5	6.4	6.1	5.7	5.4	5.4	5.5
90°	25.8	24.5	22.3	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7
95°	49.1	47.7	45.8	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5
97.5°	64.9	63.9	59.5	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8
100°	71.9	69.7	65.1	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5
102.5°	74.5	71.7	110.3	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1
105°	77.6	74.6	148.8	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9
107.5°	101.4	104.5	193.5	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4
110°	186.9	214.1	292.6	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	440.8	539.9	559.4	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5
115°	628.9	754.8	748.0	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4
117.5°	805.5	836.0	831.3	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7
120°	899.9	896.6	891.8	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3
122.5°	956.3	954.4	949.1	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1
125°	1035.6	1033.7	1028.5	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5
127.5°	1107.9	1105.1	1101.2	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1
130°	1154.1	1151.1	1148.1	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1
132.5°	1199.6	1197.1	1194.1	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0
135°	1263.9	1261.2	1258.7	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6
137.5°	1323.8	1321.1	1318.3	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9
140°	1362.7	1360.3	1357.3	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0
142.5°	1398.7	1396.5	1393.0	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3
145°	1449.0	1447.1	1442.5	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5
147.5°	1493.1	1491.6	1487.1	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7
150°	1519.7	1518.1	1513.7	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1
152.5°	1544.2	1542.5	1538.4	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5
155°	1577.2	1575.6	1572.3	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9
157.5°	1604.8	1603.0	1600.7	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0
160°	1621.2	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6
162.5°	1636.1	1634.3	1632.9	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3
165°	1654.5	1652.6	1651.8	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3
167.5°	1669.9	1668.0	1667.3	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0
170°	1677.8	1675.9	1675.3	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8
172.5°	1683.6	1681.7	1681.2	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6
175°	1690.0	1688.1	1687.6	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2
177.5°	1691.1	1689.6	1689.3	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	5.2	4.9	5.3	5.7	6.4	6.9	7.1	7.5	8.2	8.3	8.7
90°	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2
92.5°	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8
95°	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4
97.5°	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0
100°	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1
102.5°	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3
105°	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6
107.5°	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4
110°	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6
115°	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0
117.5°	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1
120°	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2
122.5°	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3
125°	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5
127.5°	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6
130°	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1
132.5°	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2
135°	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6
137.5°	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4
140°	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2
142.5°	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9
145°	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9
147.5°	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5
150°	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3
152.5°	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8
155°	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8
157.5°	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7
160°	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9
162.5°	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0
165°	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4
167.5°	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8
170°	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7
172.5°	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5
175°	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9
177.5°	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	8.8	9.1	9.3	9.4	9.5	9.6	9.5
90°	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331777

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)