

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331779

Luminaire Tested: **S122RDIW-S290D1240U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331779
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1240U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5990.8 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11
4	69	59	52	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	42	35	30	32	27	24	22	19	17	14	12	11	7
7	54	42	35	29	47	37	31	27	29	24	21	20	17	15	12	11	10	7
8	50	38	31	26	44	34	28	23	26	21	18	18	16	13	11	10	9	6
9	46	35	28	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5
10	43	32	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	0.8
10°-20°	129.0	2.2
20°-30°	181.2	3.0
30°-40°	197.6	3.3
40°-50°	181.6	3.0
50°-60°	142.7	2.4
60°-70°	93.0	1.6
70°-80°	48.0	0.8
80°-90°	16.6	0.3
90°-100°	56.4	0.9
100°-110°	206.8	3.5
110°-120°	552.8	9.2
120°-130°	912.5	15.2
130°-140°	970.4	16.2
140°-150°	902.0	15.1
150°-160°	725.2	12.1
160°-170°	467.3	7.8
170°-180°	160.9	2.7
0°-30°	357.2	6.0
0°-40°	554.7	9.3
0°-60°	879.0	14.7
0°-90°	1036.6	17.3
90°-120°	816.0	13.6
90°-150°	3600.9	60.1
90°-180°	4954.0	82.7
0°-180°	5990.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	14	24	30	33	5
95°	80	42	48	53	53	97
105°	372	388	75	88	93	397
115°	703	725	755	215	100	692
125°	994	1011	1034	1042	1046	886
135°	1231	1250	1261	1273	1271	950
145°	1428	1428	1447	1455	1450	893
155°	1572	1562	1576	1582	1573	724
165°	1656	1650	1653	1660	1653	468
175°	1694	1686	1688	1696	1684	161
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.1	6.0	6.0	5.9	5.9	6.1	6.5	6.9	7.4	7.8	8.0
90°	1.2	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8
92.5°	24.7	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1
95°	79.5	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1
97.5°	157.8	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9
100°	216.5	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9
102.5°	281.1	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5
105°	371.9	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6
107.5°	475.4	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4
110°	541.9	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	604.5	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8
115°	703.4	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9
117.5°	791.7	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5
120°	856.3	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9
122.5°	911.1	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3
125°	994.5	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6
127.5°	1070.1	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9
130°	1118.1	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1
132.5°	1167.0	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6
135°	1230.6	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9
137.5°	1294.9	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8
140°	1337.0	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7
142.5°	1372.3	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7
145°	1427.5	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0
147.5°	1475.7	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1
150°	1507.1	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7
152.5°	1533.5	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2
155°	1571.9	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2
157.5°	1602.0	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8
160°	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2
162.5°	1635.3	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1
165°	1656.3	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5
167.5°	1672.0	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9
170°	1680.8	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8
172.5°	1686.6	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6
175°	1694.2	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0
177.5°	1695.4	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	8.2	8.4	8.6	8.7	8.8	8.9	9.0	9.1
90°	27.2	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	29.8	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	50.4	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	66.0	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	74.1	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	77.3	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	80.6	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	98.4	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	159.7	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331779

CATALOG NUMBER: S122RDIW-S290D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	341.6	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	503.0	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	775.1	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	903.2	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	958.3	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1037.5	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1110.6	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1157.1	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1202.2	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1266.6	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1326.4	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1365.2	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1400.9	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1450.9	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1494.5	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1521.3	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1545.8	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1578.8	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1606.7	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1622.9	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1638.0	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1671.8	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1679.7	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1685.5	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1691.9	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1692.6	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)