

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331535-830

Luminaire Tested: **S122DIW-S675D710U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331535-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5220.5 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	82	75	70	65	63	60	56	53	50	47	43	41	39	34
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25	22
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.8
10°-20°	264.8	5.1
20°-30°	389.2	7.5
30°-40°	452.1	8.7
40°-50°	451.6	8.6
50°-60°	393.8	7.5
60°-70°	291.2	5.6
70°-80°	164.9	3.2
80°-90°	46.6	0.9
90°-100°	30.4	0.6
100°-110°	111.6	2.1
110°-120°	298.2	5.7
120°-130°	492.2	9.4
130°-140°	523.5	10.0
140°-150°	486.5	9.3
150°-160°	391.2	7.5
160°-170°	252.1	4.8
170°-180°	86.8	1.7
0°-30°	748.0	14.3
0°-40°	1200.1	23.0
0°-60°	2045.4	39.2
0°-90°	2548.1	48.8
90°-120°	440.1	8.4
90°-150°	1942.3	37.2
90°-180°	2672.0	51.2
0°-180°	5220.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	8	13	16	18	4
95°	43	23	26	29	28	52
105°	201	209	40	47	50	214
115°	379	391	407	116	54	373
125°	536	545	558	562	564	478
135°	664	674	680	686	686	512
145°	770	770	781	785	782	481
155°	848	843	850	853	849	391
165°	893	890	892	896	892	252
175°	914	910	911	915	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.8	13.7	13.5	13.4	13.0
90°	0.7	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9
92.5°	13.3	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6
95°	42.9	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5
97.5°	85.1	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1
100°	116.8	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7
102.5°	151.7	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2
105°	200.6	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8
107.5°	256.4	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7
110°	292.3	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	326.1	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8
115°	379.4	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2
117.5°	427.1	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5
120°	461.8	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4
122.5°	491.4	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9
125°	536.4	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6
127.5°	577.2	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6
130°	603.0	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5
132.5°	629.5	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1
135°	663.8	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7
137.5°	698.5	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1
140°	721.2	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1
142.5°	740.2	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5
145°	770.1	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7
147.5°	796.0	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4
150°	812.9	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7
152.5°	827.2	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9
155°	847.9	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7
157.5°	864.1	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6
160°	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5
162.5°	882.0	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5
165°	893.4	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5
167.5°	901.8	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8
170°	906.6	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0
172.5°	909.7	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1
175°	913.9	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6
177.5°	914.5	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	12.7	12.3	12.0	11.7	11.6	11.5	11.4	11.2
90°	14.7	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.1	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.2	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	35.6	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	40.0	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	41.8	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	43.5	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	53.1	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	86.1	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331535-830

CATALOG NUMBER: S122DIW-S675D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	184.3	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	271.4	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	418.1	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	487.2	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	516.9	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	559.6	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	599.1	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	624.2	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	648.5	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	683.2	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	715.5	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	736.4	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	755.6	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	782.6	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.2	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	820.6	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	833.8	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	851.6	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	866.7	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	875.3	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	883.5	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	901.8	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	906.1	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	909.2	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	912.7	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.0	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)