

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331772

Luminaire Tested: **S122RDIW-S290D710U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331772
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3494.7 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	93	89	86	82	84	80	77	75	63	61	59	48	47	45	33	33	32	25
2	85	78	73	68	76	71	66	62	56	52	50	42	40	38	30	29	27	22
3	78	69	62	57	70	62	56	52	49	45	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	16
5	66	55	47	41	59	49	43	38	39	35	31	30	27	24	22	20	18	14
6	60	49	41	36	54	44	38	33	36	31	27	27	24	22	20	18	16	13
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11
8	52	40	33	28	46	36	30	25	29	25	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.3
10°-20°	129.0	3.7
20°-30°	181.2	5.2
30°-40°	197.6	5.7
40°-50°	181.6	5.2
50°-60°	142.7	4.1
60°-70°	93.0	2.7
70°-80°	48.0	1.4
80°-90°	16.0	0.5
90°-100°	55.7	1.6
100°-110°	173.1	5.0
110°-120°	295.8	8.5
120°-130°	389.0	11.1
130°-140°	436.6	12.5
140°-150°	428.1	12.2
150°-160°	359.1	10.3
160°-170°	238.2	6.8
170°-180°	83.2	2.4
0°-30°	357.2	10.2
0°-40°	554.7	15.9
0°-60°	879.0	25.2
0°-90°	1035.9	29.6
90°-120°	524.6	15.0
90°-150°	1778.3	50.9
90°-180°	2459.0	70.4
0°-180°	3494.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	10	26	25	25	3
95°	39	46	48	47	46	44
105°	160	162	163	165	165	168
115°	297	301	300	299	297	294
125°	432	438	436	434	433	386
135°	559	567	568	568	565	431
145°	678	683	688	688	686	424
155°	775	778	780	783	781	357
165°	844	843	843	848	844	238
175°	878	876	874	879	875	83
180°	879	879	879	879	879	



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	5.7	5.5	5.2	5.0	5.2	5.9	6.7	7.4	8.1	8.0
90°	0.7	2.7	4.7	6.7	8.7	11.5	15.1	18.7	22.3	26.0	25.6
92.5°	13.2	14.7	16.1	17.6	19.0	20.2	21.0	21.9	22.7	23.6	23.7
95°	38.6	40.2	41.9	43.5	45.2	46.2	46.5	46.8	47.2	47.5	47.5
97.5°	70.5	71.9	73.4	74.8	76.3	77.3	78.0	78.6	79.2	79.8	79.8
100°	94.2	95.6	96.9	98.2	99.5	100.4	100.9	101.4	101.9	102.4	102.4
102.5°	119.2	120.2	121.3	122.3	123.4	124.2	124.9	125.5	126.1	126.7	126.9
105°	159.5	160.0	160.5	161.0	161.5	161.9	162.3	162.6	162.9	163.3	163.6
107.5°	200.2	200.9	201.7	202.4	203.1	203.5	203.5	203.5	203.5	203.5	203.6
110°	226.3	227.3	228.3	229.3	230.3	230.8	230.8	230.8	230.8	230.8	230.8



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.8	255.8	256.8	257.8	258.8	259.2	259.1	258.9	258.8	258.7	258.3
115°	296.8	297.8	298.8	299.8	300.8	301.1	300.8	300.4	300.1	299.8	299.6
117.5°	338.7	340.0	341.3	342.6	343.9	344.1	343.2	342.3	341.4	340.5	340.1
120°	366.6	367.9	369.2	370.5	371.8	371.8	370.5	369.2	367.9	366.6	366.6
122.5°	392.1	393.7	395.3	396.8	398.4	398.8	397.8	396.9	396.0	395.1	394.7
125°	431.9	433.4	434.8	436.3	437.8	438.3	437.8	437.3	436.8	436.3	435.8
127.5°	470.6	472.5	474.4	476.2	478.1	478.8	478.2	477.6	477.0	476.4	475.8
130°	494.9	497.1	499.2	501.4	503.5	504.4	504.1	503.8	503.4	503.1	502.8
132.5°	522.3	524.0	525.8	527.5	529.2	530.2	530.2	530.3	530.4	530.4	529.7
135°	558.8	560.6	562.4	564.2	566.0	567.1	567.4	567.8	568.1	568.4	568.2
137.5°	597.2	598.7	600.2	601.7	603.1	604.1	604.5	605.0	605.4	605.8	605.7
140°	620.4	621.8	623.3	624.8	626.3	627.4	628.3	629.1	629.9	630.7	630.7
142.5°	644.1	645.6	647.1	648.6	650.0	651.1	651.6	652.2	652.7	653.3	653.4
145°	678.2	679.4	680.5	681.7	682.9	683.9	684.9	685.9	686.9	687.9	688.0
147.5°	708.7	710.0	711.4	712.8	714.2	715.2	715.9	716.5	717.2	717.9	718.2
150°	729.4	730.4	731.4	732.4	733.4	734.2	734.9	735.5	736.2	736.9	737.4
152.5°	747.8	748.8	749.8	750.8	751.8	752.7	753.5	754.3	755.1	755.9	756.5
155°	775.4	775.9	776.4	776.9	777.4	777.9	778.4	778.9	779.4	779.9	780.7
157.5°	799.0	799.4	799.7	800.0	800.4	800.7	801.0	801.3	801.6	801.9	803.0
160°	813.3	813.6	813.9	814.3	814.6	814.9	815.0	815.2	815.3	815.5	816.5
162.5°	826.3	826.4	826.5	826.5	826.6	826.7	826.9	827.1	827.2	827.4	828.5
165°	843.7	843.5	843.4	843.2	843.1	843.0	843.0	843.0	843.0	843.0	844.1
167.5°	858.3	857.8	857.3	856.8	856.3	856.0	856.0	855.9	855.9	855.9	857.0
170°	866.0	865.5	865.0	864.5	864.0	863.7	863.5	863.3	863.2	863.0	864.2
172.5°	871.3	870.8	870.3	869.8	869.3	869.0	868.8	868.7	868.5	868.3	869.5
175°	877.8	877.4	876.9	876.4	875.9	875.5	875.1	874.8	874.5	874.1	875.3
177.5°	880.5	880.1	879.7	879.3	878.9	878.6	878.3	878.1	877.8	877.5	878.3
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	7.8	7.7	7.5	7.5	7.5	7.5	7.6	7.6
90°	25.3	25.0	24.7	24.6	24.7	24.9	25.1	25.2
92.5°	23.7	23.8	23.9	23.9	23.9	24.0	24.0	24.0
95°	47.5	47.5	47.5	47.3	47.0	46.7	46.3	46.0
97.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.7	79.7
100°	102.4	102.4	102.4	102.3	102.2	102.0	101.8	101.7
102.5°	127.0	127.1	127.3	127.3	127.1	126.9	126.8	126.6
105°	163.9	164.2	164.6	164.7	164.7	164.7	164.7	164.7
107.5°	203.7	203.9	204.0	203.7	202.9	202.2	201.4	200.7
110°	230.8	230.8	230.8	230.5	230.0	229.5	229.0	228.6



TEST NUMBER: P331772

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.5	257.1	256.7	256.4	256.0	255.6	255.3
115°	299.5	299.3	299.1	298.8	298.3	297.8	297.3	296.8
117.5°	339.7	339.3	338.9	338.4	337.9	337.4	336.9	336.4
120°	366.6	366.6	366.6	366.3	365.8	365.3	364.8	364.3
122.5°	394.3	393.9	393.5	393.1	392.7	392.4	392.0	391.7
125°	435.3	434.8	434.3	434.0	433.9	433.7	433.5	433.4
127.5°	475.2	474.6	474.0	473.5	472.9	472.4	471.9	471.4
130°	502.5	502.1	501.8	501.3	500.6	500.0	499.3	498.7
132.5°	529.0	528.2	527.5	526.9	526.4	525.8	525.3	524.8
135°	568.1	567.9	567.8	567.4	566.9	566.4	565.9	565.4
137.5°	605.5	605.4	605.3	604.9	604.2	603.6	602.9	602.2
140°	630.7	630.7	630.7	630.4	629.8	629.1	628.4	627.8
142.5°	653.6	653.7	653.8	653.6	652.9	652.2	651.6	650.9
145°	688.2	688.4	688.5	688.3	687.6	687.0	686.3	685.7
147.5°	718.6	718.9	719.3	719.2	718.6	717.9	717.3	716.7
150°	737.8	738.3	738.8	738.8	738.3	737.8	737.4	736.9
152.5°	757.1	757.7	758.4	758.4	757.7	757.1	756.5	755.9
155°	781.5	782.4	783.2	783.4	782.9	782.4	781.9	781.4
157.5°	804.1	805.2	806.3	806.5	805.7	804.9	804.1	803.3
160°	817.5	818.5	819.5	819.6	819.0	818.3	817.7	817.0
162.5°	829.6	830.8	831.9	832.0	831.2	830.5	829.7	828.9
165°	845.3	846.4	847.6	847.8	846.9	846.1	845.3	844.5
167.5°	858.2	859.3	860.5	860.6	859.8	858.9	858.1	857.2
170°	865.3	866.5	867.6	867.7	866.7	865.7	864.7	863.7
172.5°	870.7	871.8	873.0	873.0	872.1	871.1	870.1	869.1
175°	876.4	877.6	878.8	878.8	877.8	876.9	875.9	874.9
177.5°	879.1	879.9	880.7	880.7	879.9	879.1	878.3	877.5
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3

(END OF REPORT)