

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331580-830

Luminaire Tested: **S122DIW-S865D1440U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331580-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8305.2 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	1.9
10°-20°	450.6	5.4
20°-30°	653.9	7.9
30°-40°	690.0	8.3
40°-50°	611.0	7.4
50°-60°	487.6	5.9
60°-70°	331.4	4.0
70°-80°	169.9	2.0
80°-90°	47.7	0.6
90°-100°	106.7	1.3
100°-110°	331.4	4.0
110°-120°	566.4	6.8
120°-130°	744.9	9.0
130°-140°	836.1	10.1
140°-150°	819.8	9.9
150°-160°	687.6	8.3
160°-170°	456.0	5.5
170°-180°	159.4	1.9
0°-30°	1259.4	15.2
0°-40°	1949.5	23.5
0°-60°	3048.0	36.7
0°-90°	3597.0	43.3
90°-120°	1004.5	12.1
90°-150°	3405.2	41.0
90°-180°	4708.0	56.7
0°-180°	8305.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	48	1	48	1	48	23
95°	88	74	88	74	88	98
105°	316	306	316	306	316	332
115°	568	568	568	568	568	561
125°	830	827	830	827	830	740
135°	1083	1070	1083	1070	1083	833
145°	1313	1299	1313	1299	1313	820
155°	1496	1485	1496	1485	1496	689
165°	1617	1616	1617	1616	1617	456
175°	1675	1681	1675	1681	1675	159
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	22.7	22.6	23.1	22.5	22.4	22.9	23.1	22.7	23.4	23.9	23.1
90°	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4	49.1	49.8	42.8
92.5°	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4	45.3	45.1	43.5
95°	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0	91.0	91.0	90.3
97.5°	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9	152.9	152.9	151.7
100°	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0	196.0	196.0	195.1
102.5°	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2	243.0	242.7	241.5
105°	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9	313.2	312.6	312.0
107.5°	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1	389.8	389.6	389.6
110°	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8	494.6	495.3	495.6
115°	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4	573.7	574.1	574.7
117.5°	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4	651.2	652.0	653.7
120°	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9	701.9	701.9	704.5
122.5°	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0	755.7	756.5	758.3
125°	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6	834.5	835.5	836.5
127.5°	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9	911.1	912.3	913.4
130°	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1	962.8	963.4	964.0
132.5°	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0	1014.3	1015.7	1015.6
135°	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8	1088.2	1088.4	1087.8
137.5°	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5	1159.8	1160.1	1159.2
140°	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8	1207.8	1207.8	1206.3
142.5°	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5	1251.2	1251.0	1249.9
145°	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9	1317.5	1317.2	1315.3
147.5°	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0	1375.4	1374.6	1373.4
150°	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0	1409.8
152.5°	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4	1445.9
155°	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6	1495.0	1493.4	1492.4
157.5°	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7	1537.6	1535.5	1534.9
160°	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4	1563.5	1561.6	1561.3
162.5°	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7	1586.5	1584.3	1584.0
165°	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6	1616.4	1614.2	1614.2
167.5°	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3	1641.2	1638.9	1639.0
170°	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0	1654.7	1652.6	1652.8
172.5°	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2	1665.0	1662.7	1663.1
175°	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3	1676.1	1673.9	1674.5
177.5°	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4	1680.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	22.1	20.8	19.4	19.3	17.1	16.3	13.6	11.3	11.6	11.8	11.6
90°	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4	5.2	9.0	12.8
92.5°	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3	28.1	30.8	33.6
95°	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9	77.0	80.2	83.3
97.5°	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0	137.8	140.5	143.4
100°	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5	182.9	185.5	188.0
102.5°	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2	230.3	232.2	234.2
105°	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5	306.4	307.4	308.3
107.5°	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3	384.7	386.2	387.6
110°	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4	435.3	437.2	439.0



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0	489.8	491.7	493.6
115°	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4	570.2	572.1	574.1
117.5°	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6	651.0	653.6	656.1
120°	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	704.5	707.0	709.5
122.5°	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8	753.8	756.9	759.9
125°	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0	829.8	832.6	835.5
127.5°	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2	904.7	908.3	912.0
130°	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7	951.9	956.0	960.1
132.5°	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0	1003.4	1006.7	1010.1
135°	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0	1073.5	1076.9	1080.3
137.5°	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6	1146.4	1149.2	1152.1
140°	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9	1190.7	1193.6	1196.5
142.5°	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4	1236.2	1239.1	1241.9
145°	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7	1301.0	1303.2	1305.3
147.5°	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0	1359.6	1362.3	1365.0
150°	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8	1398.6	1400.6	1402.5
152.5°	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0	1433.9	1435.8	1437.7
155°	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9	1485.8	1486.8	1487.7
157.5°	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0	1530.7	1531.3	1532.0
160°	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4	1558.0	1558.6	1559.2
162.5°	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3	1582.5	1582.6	1582.7
165°	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6	1615.3	1615.0	1614.7
167.5°	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4	1642.5	1641.5	1640.6
170°	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2	1657.3	1656.3	1655.4
172.5°	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5	1667.5	1666.6	1665.7
175°	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9	1680.0	1679.0	1678.1
177.5°	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1	1685.4	1684.6	1683.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	11.8	12.4	13.3	14.7	15.6	16.5	15.8	15.7	15.6	14.4	14.4
90°	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4	47.9	47.2	47.0
92.5°	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4	45.5	45.7	45.8
95°	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0	91.0	91.0	90.6
97.5°	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9	152.9	152.9	152.9
100°	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0	196.0	196.0	196.0
102.5°	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2	243.5	243.7	243.6
105°	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9	314.5	315.1	315.5
107.5°	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1	390.4	390.6	390.0
110°	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	441.4



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8	493.0	492.3	491.5
115°	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4	573.1	572.8	572.1
117.5°	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4	649.7	648.9	648.0
120°	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9	701.9	701.9	701.4
122.5°	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0	754.2	753.5	752.7
125°	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6	832.6	831.7	831.1
127.5°	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9	908.8	907.7	906.6
130°	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1	961.5	960.8	959.9
132.5°	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0	1011.5	1010.1	1008.9
135°	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8	1087.5	1087.2	1086.6
137.5°	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5	1159.3	1159.0	1158.3
140°	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8	1207.8	1207.8	1207.2
142.5°	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5	1251.8	1252.0	1251.5
145°	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9	1318.1	1318.4	1318.0
147.5°	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0	1376.7	1377.4	1377.1
150°	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8
152.5°	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2
155°	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6	1498.2	1499.7	1500.1
157.5°	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7	1541.9	1544.1	1544.4
160°	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4	1567.3	1569.1	1569.5
162.5°	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7	1590.8	1592.9	1593.3
165°	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6	1620.8	1623.1	1623.3
167.5°	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3	1645.6	1647.8	1648.0
170°	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0	1659.2	1661.4	1661.5
172.5°	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2	1669.4	1671.6	1671.8
175°	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3	1680.5	1682.7	1682.9
177.5°	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	14.5	14.0	14.1	13.7	14.1	14.0	14.5	14.4	14.4	15.6	15.7
90°	47.4	47.7	48.0	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4
92.5°	45.8	45.9	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4
95°	90.0	89.4	88.7	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0
97.5°	152.8	152.7	152.7	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9
100°	195.6	195.3	195.0	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0
102.5°	243.4	243.1	242.7	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2
105°	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9
107.5°	388.6	387.1	385.7	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1
110°	440.5	439.5	438.6	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	490.9	490.2	489.5	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8
115°	571.2	570.2	569.3	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4
117.5°	647.1	646.1	645.2	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4
120°	700.5	699.6	698.6	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9
122.5°	752.1	751.4	750.6	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0
125°	830.8	830.5	830.2	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6
127.5°	905.6	904.6	903.6	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9
130°	958.7	957.4	956.1	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1
132.5°	1008.0	1006.9	1005.9	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0
135°	1085.6	1084.7	1083.7	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8
137.5°	1157.1	1155.7	1154.5	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5
140°	1205.9	1204.7	1203.3	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8
142.5°	1250.3	1249.0	1247.7	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5
145°	1316.7	1315.5	1314.2	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9
147.5°	1375.9	1374.7	1373.6	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0
150°	1413.8	1412.9	1411.9	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9
152.5°	1451.0	1449.7	1448.6	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7
155°	1499.1	1498.2	1497.2	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6
157.5°	1542.8	1541.3	1539.8	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7
160°	1568.2	1567.0	1565.8	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4
162.5°	1591.8	1590.3	1588.7	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7
165°	1621.7	1620.2	1618.6	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6
167.5°	1646.4	1644.7	1643.1	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3
170°	1659.6	1657.7	1655.9	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0
172.5°	1669.9	1668.0	1666.1	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2
175°	1680.9	1679.0	1677.2	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3
177.5°	1685.0	1683.5	1681.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	15.8	16.5	15.6	14.7	13.3	12.4	11.8	11.6	11.8	11.6	11.3
90°	49.1	49.8	42.8	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4
92.5°	45.3	45.1	43.5	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3
95°	91.0	91.0	90.3	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9
97.5°	152.9	152.9	151.7	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0
100°	196.0	196.0	195.1	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5
102.5°	243.0	242.7	241.5	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2
105°	313.2	312.6	312.0	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5
107.5°	389.8	389.6	389.6	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3
110°	442.0	442.0	442.0	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.6	495.3	495.6	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0
115°	573.7	574.1	574.7	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4
117.5°	651.2	652.0	653.7	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6
120°	701.9	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9
122.5°	755.7	756.5	758.3	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8
125°	834.5	835.5	836.5	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0
127.5°	911.1	912.3	913.4	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2
130°	962.8	963.4	964.0	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7
132.5°	1014.3	1015.7	1015.6	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0
135°	1088.2	1088.4	1087.8	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0
137.5°	1159.8	1160.1	1159.2	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6
140°	1207.8	1207.8	1206.3	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9
142.5°	1251.2	1251.0	1249.9	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4
145°	1317.5	1317.2	1315.3	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7
147.5°	1375.4	1374.6	1373.4	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0
150°	1411.9	1411.0	1409.8	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8
152.5°	1448.6	1447.4	1445.9	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0
155°	1495.0	1493.4	1492.4	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9
157.5°	1537.6	1535.5	1534.9	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0
160°	1563.5	1561.6	1561.3	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4
162.5°	1586.5	1584.3	1584.0	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3
165°	1616.4	1614.2	1614.2	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6
167.5°	1641.2	1638.9	1639.0	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4
170°	1654.7	1652.6	1652.8	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2
172.5°	1665.0	1662.7	1663.1	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5
175°	1676.1	1673.9	1674.5	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9
177.5°	1681.9	1680.4	1680.9	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.6	16.3	17.1	19.3	19.4	20.8	22.1	23.1	23.9	23.4	22.7
90°	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4
92.5°	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4
95°	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0
97.5°	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9
100°	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0
102.5°	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2
105°	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9
107.5°	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1
110°	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8
115°	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4
117.5°	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4
120°	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9
122.5°	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0
125°	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6
127.5°	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9
130°	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1
132.5°	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0
135°	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8
137.5°	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5
140°	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8
142.5°	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5
145°	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9
147.5°	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0
150°	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9
152.5°	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7
155°	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6
157.5°	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7
160°	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4
162.5°	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7
165°	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6
167.5°	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3
170°	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0
172.5°	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2
175°	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3
177.5°	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	23.1	22.9	22.4	22.5	23.1	22.6	22.7
90°	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331580-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)