

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331773

Luminaire Tested: **S122RDIW-S290D970U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331773
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D970U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5003.0 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23				
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	27	27	20				
2	84	77	72	67	74	69	64	60	53	50	47	38	37	35	25	24	23	17				
3	77	68	61	56	68	61	55	51	47	43	40	34	32	30	22	21	20	15				
4	70	60	53	48	62	54	48	43	42	38	34	31	28	26	20	19	18	13				
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	18	17	16	12				
6	60	48	41	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	12	10				
8	51	40	32	27	45	36	29	25	28	24	20	21	18	16	14	13	11	9				
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	13	12	10	8				
10	44	33	26	22	39	30	24	20	24	19	16	18	15	13	12	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.2
10°-20°	172.7	3.5
20°-30°	222.5	4.4
30°-40°	211.5	4.2
40°-50°	181.1	3.6
50°-60°	137.9	2.8
60°-70°	87.2	1.7
70°-80°	43.5	0.9
80°-90°	14.6	0.3
90°-100°	44.1	0.9
100°-110°	161.5	3.2
110°-120°	431.8	8.6
120°-130°	712.8	14.2
130°-140°	758.0	15.2
140°-150°	704.6	14.1
150°-160°	566.5	11.3
160°-170°	365.0	7.3
170°-180°	125.6	2.5
0°-30°	457.2	9.1
0°-40°	668.6	13.4
0°-60°	987.7	19.7
0°-90°	1133.1	22.6
90°-120°	637.4	12.7
90°-150°	2812.8	56.2
90°-180°	3870.0	77.4
0°-180°	5003.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	9
90°	26	1	26	1	26	12
95°	41	62	41	62	41	38
105°	73	290	73	290	73	76
115°	78	549	78	549	78	196
125°	817	777	817	777	817	707
135°	993	961	993	961	993	765
145°	1132	1115	1132	1115	1132	708
155°	1229	1228	1229	1228	1229	567
165°	1291	1294	1291	1294	1291	364
175°	1316	1323	1316	1323	1316	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	8.1	8.2	8.1	8.0	7.9	7.8	7.5	7.5	7.1	7.1	6.6
90°	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2	20.2	19.1	17.4
92.5°	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3	22.7	22.2	21.3
95°	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4	38.3	37.3	35.8
97.5°	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6	50.7	49.9	46.4
100°	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9	56.2	54.5	50.9
102.5°	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4	58.2	56.0	86.2
105°	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0	60.6	58.3	116.3
107.5°	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8	79.2	81.6	151.1
110°	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7	146.0	167.2	228.6



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8	344.3	421.8	436.9
115°	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9	491.2	589.6	584.3
117.5°	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4	629.2	653.0	649.4
120°	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5	703.0	700.4	696.6
122.5°	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6	747.0	745.5	741.3
125°	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4	808.9	807.4	803.4
127.5°	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6	865.4	863.2	860.2
130°	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8	901.5	899.2	896.8
132.5°	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1	937.1	935.1	932.7
135°	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4	987.3	985.2	983.2
137.5°	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1	1034.1	1032.0	1029.8
140°	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4	1064.5	1062.6	1060.2
142.5°	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3	1092.6	1090.8	1088.2
145°	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4	1131.9	1130.4	1126.8
147.5°	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4	1166.3	1165.2	1161.6
150°	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4	1187.1	1185.8	1182.4
152.5°	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5	1206.2	1204.9	1201.7
155°	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3	1232.0	1230.7	1228.2
157.5°	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0	1253.6	1252.1	1250.3
160°	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7	1266.4	1265.1	1263.9
162.5°	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5	1278.0	1276.6	1275.5
165°	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9	1290.3
167.5°	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9	1304.4	1303.0	1302.4
170°	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1	1310.6	1309.1	1308.7
172.5°	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6	1315.2	1313.7	1313.2
175°	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6	1320.1	1318.6	1318.2
177.5°	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2	1321.0	1319.8	1319.6
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	6.2	6.1	5.7	5.1	4.9	4.6	5.0	5.5	5.2	5.1	5.2
90°	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0	3.3	5.6	8.0
92.5°	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3	19.1	18.9	18.7
95°	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1	55.1	48.1	41.1
97.5°	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3	103.5	83.8	64.0
100°	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1	140.0	110.9	81.9
102.5°	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6	213.4	207.3	201.1
105°	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5	296.9	303.2	309.6
107.5°	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3	376.5	381.6	386.7
110°	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3	427.8	432.2	436.7



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2	476.2	480.1	484.1
115°	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4	553.0	556.7	560.3
117.5°	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4	622.5	626.5	630.5
120°	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9	672.1	675.2	678.4
122.5°	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7	715.0	718.4	721.7
125°	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8	779.6	782.4	785.1
127.5°	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9	839.0	842.0	845.1
130°	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4	876.8	880.2	883.5
132.5°	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6	914.5	917.4	920.2
135°	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3	964.7	968.1	971.5
137.5°	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5	1013.9	1016.3	1018.7
140°	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4	1046.1	1047.8	1049.5
142.5°	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9	1073.4	1075.0	1076.5
145°	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1	1114.9	1114.7	1114.5
147.5°	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8	1151.9	1151.1	1150.3
150°	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2	1175.7	1174.2	1172.8
152.5°	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9	1196.2	1194.5	1192.9
155°	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9	1225.9	1224.0	1222.1
157.5°	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4	1249.8	1248.1	1246.5
160°	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1263.9	1262.6	1261.3
162.5°	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4	1276.1	1274.8	1273.5
165°	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8	1292.5	1291.2	1290.0
167.5°	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0	1304.7	1303.5	1302.2
170°	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9	1311.6	1310.4	1309.1
172.5°	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5	1316.2	1314.9	1313.7
175°	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4	1321.9	1320.4	1319.0
177.5°	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4	1323.2	1322.0	1320.8
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	5.5	5.7	5.7	6.1	6.4	6.5	6.8	6.8	7.0	7.2	7.2
90°	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2	22.3	23.4	24.1
92.5°	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3	23.8	24.4	24.8
95°	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4	40.5	41.5	41.9
97.5°	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6	52.4	53.3	53.8
100°	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9	59.6	61.3	62.3
102.5°	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4	62.6	64.8	66.2
105°	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0	65.3	67.6	69.2
107.5°	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8	74.5	72.1	71.3
110°	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7	103.5	82.3	72.1



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8	189.4	111.9	73.5
115°	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9	294.6	196.3	139.5
117.5°	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4	581.7	557.9	520.9
120°	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5	708.0	710.6	697.5
122.5°	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6	750.1	751.6	749.6
125°	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4	811.9	813.4	814.4
127.5°	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6	869.7	871.9	873.0
130°	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8	906.2	908.5	909.6
132.5°	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1	941.1	943.1	944.0
135°	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4	991.5	993.6	994.5
137.5°	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1	1038.2	1040.3	1041.0
140°	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4	1068.3	1070.2	1070.6
142.5°	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3	1096.1	1097.8	1098.1
145°	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4	1134.9	1136.3	1136.6
147.5°	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4	1168.5	1169.6	1169.7
150°	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4	1189.6	1190.9	1191.0
152.5°	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5	1208.7	1210.0	1210.0
155°	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3	1234.5	1235.8	1235.6
157.5°	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0	1256.5	1257.9	1257.8
160°	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7	1268.9	1270.2	1270.1
162.5°	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5	1280.9	1282.4	1282.2
165°	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9
167.5°	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9	1307.4	1308.9	1308.7
170°	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1	1313.5	1315.0	1314.8
172.5°	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6	1318.1	1319.6	1319.4
175°	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6	1323.1	1324.6	1324.3
177.5°	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2	1323.3	1324.5	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	7.3	7.2	7.4	7.3	7.4	7.2	7.3	7.2	7.2	7.0	6.8
90°	24.5	24.9	25.4	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2
92.5°	25.0	25.3	25.5	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3
95°	41.7	41.5	41.3	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4
97.5°	54.1	54.3	54.6	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6
100°	62.7	63.2	63.6	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9
102.5°	66.8	67.4	68.0	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4
105°	70.1	70.9	71.8	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0
107.5°	72.2	73.0	73.9	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8
110°	72.9	73.8	74.6	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	74.2	74.9	75.6	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8
115°	124.2	108.9	93.6	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9
117.5°	470.6	420.4	370.2	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4
120°	668.9	640.2	611.5	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5
122.5°	744.0	738.5	732.9	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6
125°	815.1	815.7	816.3	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4
127.5°	873.2	873.3	873.4	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6
130°	909.3	909.1	908.9	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8
132.5°	943.7	943.5	943.3	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1
135°	994.1	993.6	993.2	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4
137.5°	1040.3	1039.5	1038.8	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1
140°	1069.6	1068.5	1067.4	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4
142.5°	1097.1	1096.0	1095.0	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3
145°	1135.5	1134.4	1133.4	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4
147.5°	1168.8	1167.9	1167.0	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4
150°	1190.0	1188.9	1187.8	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4
152.5°	1208.6	1207.2	1205.8	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5
155°	1233.9	1232.2	1230.5	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3
157.5°	1256.1	1254.5	1252.8	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0
160°	1268.6	1267.1	1265.7	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7
162.5°	1280.3	1278.5	1276.7	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5
165°	1295.4	1293.9	1292.4	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9
167.5°	1306.8	1304.9	1303.0	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9
170°	1312.9	1311.0	1309.1	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1
172.5°	1317.5	1315.6	1313.7	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6
175°	1322.1	1320.0	1317.9	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6
177.5°	1322.8	1321.3	1319.8	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	6.8	6.5	6.4	6.1	5.7	5.7	5.5	5.2	5.1	5.2	5.5
90°	20.2	19.1	17.4	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0
92.5°	22.7	22.2	21.3	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3
95°	38.3	37.3	35.8	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1
97.5°	50.7	49.9	46.4	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3
100°	56.2	54.5	50.9	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1
102.5°	58.2	56.0	86.2	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6
105°	60.6	58.3	116.3	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5
107.5°	79.2	81.6	151.1	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3
110°	146.0	167.2	228.6	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	344.3	421.8	436.9	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2
115°	491.2	589.6	584.3	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4
117.5°	629.2	653.0	649.4	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4
120°	703.0	700.4	696.6	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9
122.5°	747.0	745.5	741.3	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7
125°	808.9	807.4	803.4	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8
127.5°	865.4	863.2	860.2	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9
130°	901.5	899.2	896.8	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4
132.5°	937.1	935.1	932.7	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6
135°	987.3	985.2	983.2	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3
137.5°	1034.1	1032.0	1029.8	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5
140°	1064.5	1062.6	1060.2	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4
142.5°	1092.6	1090.8	1088.2	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9
145°	1131.9	1130.4	1126.8	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1
147.5°	1166.3	1165.2	1161.6	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8
150°	1187.1	1185.8	1182.4	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2
152.5°	1206.2	1204.9	1201.7	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9
155°	1232.0	1230.7	1228.2	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9
157.5°	1253.6	1252.1	1250.3	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4
160°	1266.4	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1
162.5°	1278.0	1276.6	1275.5	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4
165°	1292.4	1290.9	1290.3	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8
167.5°	1304.4	1303.0	1302.4	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0
170°	1310.6	1309.1	1308.7	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9
172.5°	1315.2	1313.7	1313.2	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5
175°	1320.1	1318.6	1318.2	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4
177.5°	1321.0	1319.8	1319.6	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	5.0	4.6	4.9	5.1	5.7	6.1	6.2	6.6	7.1	7.1	7.5
90°	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2
92.5°	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3
95°	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4
97.5°	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6
100°	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9
102.5°	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4
105°	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0
107.5°	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8
110°	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8
115°	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9
117.5°	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4
120°	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5
122.5°	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6
125°	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4
127.5°	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6
130°	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8
132.5°	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1
135°	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4
137.5°	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1
140°	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4
142.5°	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3
145°	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4
147.5°	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4
150°	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4
152.5°	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5
155°	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3
157.5°	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0
160°	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7
162.5°	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5
165°	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9
167.5°	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9
170°	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1
172.5°	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6
175°	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6
177.5°	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	7.5	7.8	7.9	8.0	8.1	8.2	8.1
90°	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	103.5	82.3	72.1	72.9	73.8	74.6	75.5



TEST NUMBER: P331773

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)