

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331561-830

Luminaire Tested: **S122DIW-S865D710U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331561-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D710U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6264.8 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	67	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31	28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.0	2.5
10°-20°	450.6	7.2
20°-30°	653.9	10.4
30°-40°	690.0	11.0
40°-50°	611.0	9.8
50°-60°	487.6	7.8
60°-70°	331.4	5.3
70°-80°	169.9	2.7
80°-90°	43.2	0.7
90°-100°	30.4	0.5
100°-110°	111.6	1.8
110°-120°	298.2	4.8
120°-130°	492.2	7.9
130°-140°	523.5	8.4
140°-150°	486.5	7.8
150°-160°	391.2	6.2
160°-170°	252.1	4.0
170°-180°	86.8	1.4
0°-30°	1259.4	20.1
0°-40°	1949.5	31.1
0°-60°	3048.0	48.7
0°-90°	3592.5	57.3
90°-120°	440.1	7.0
90°-150°	1942.3	31.0
90°-180°	2672.0	42.7
0°-180°	6264.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	18	1	18	1	18	10
95°	28	43	28	43	28	26
105°	50	201	50	201	50	52
115°	54	379	54	379	54	136
125°	564	536	564	536	564	488
135°	686	664	686	664	686	528
145°	782	770	782	770	782	489
155°	849	848	849	848	849	392
165°	892	893	892	893	892	252
175°	909	914	909	914	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	16.6	16.5	17.0	16.4	16.3	16.8	16.6	15.9	16.3	16.7	16.9
90°	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7	13.9	13.2	12.1
92.5°	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1	15.6	15.3	14.7
95°	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2	26.5	25.7	24.7
97.5°	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6	35.1	34.4	32.0
100°	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0	38.7	37.6	35.2
102.5°	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8	40.2	38.6	35.5
105°	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5	41.8	40.2	38.3
107.5°	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1	54.7	56.4	104.3
110°	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1	100.9	115.5	157.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3	237.8	291.2	301.7
115°	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4	339.2	407.1	403.4
117.5°	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1	434.5	450.9	448.4
120°	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2	485.4	483.6	481.0
122.5°	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9	515.9	514.8	511.9
125°	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6	558.6	557.5	554.8
127.5°	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1	597.6	596.1	594.0
130°	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2	622.5	620.9	619.3
132.5°	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5	647.1	645.7	644.1
135°	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2	681.7	680.3	679.0
137.5°	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5	714.1	712.7	711.1
140°	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4	735.1	733.8	732.1
142.5°	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6	754.5	753.3	751.4
145°	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6	781.7	780.6	778.1
147.5°	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2	805.4	804.6	802.1
150°	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6	819.7	818.9	816.5
152.5°	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8	832.9	832.1	829.8
155°	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6	850.7	849.9	848.1
157.5°	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7	865.6	864.6	863.4
160°	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3	874.5	873.6	872.7
162.5°	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5	882.5	881.6	880.8
165°	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5	891.0
167.5°	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8	900.8	899.8	899.4
170°	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1	905.0	904.0	903.7
172.5°	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2	908.1	907.1	906.8
175°	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7	911.6	910.6	910.3
177.5°	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0	912.2	911.3	911.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	17.2	17.0	16.7	17.4	15.6	15.3	13.0	11.1	10.9	10.7	10.1
90°	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7	2.3	3.9	5.5
92.5°	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3	13.2	13.0	12.9
95°	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9	38.1	33.2	28.4
97.5°	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1	71.4	57.9	44.2
100°	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8	96.7	76.6	56.6
102.5°	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7	147.4	143.1	138.8
105°	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6	205.0	209.4	213.8
107.5°	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4	260.0	263.5	267.0
110°	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3	295.4	298.5	301.5





TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1	328.9	331.6	334.2
115°	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4	381.9	384.4	386.9
117.5°	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1	429.8	432.6	435.4
120°	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8	464.1	466.3	468.4
122.5°	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4	493.8	496.1	498.4
125°	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4	538.4	540.3	542.2
127.5°	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2	579.3	581.5	583.5
130°	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0	605.4	607.8	610.1
132.5°	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5	631.5	633.5	635.5
135°	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8	666.1	668.5	670.8
137.5°	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5	700.1	701.8	703.4
140°	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2	722.4	723.5	724.7
142.5°	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2	741.2	742.3	743.4
145°	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1	769.9	769.8	769.6
147.5°	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0	795.5	794.9	794.4
150°	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9	811.9	810.9	809.8
152.5°	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2	826.0	824.9	823.7
155°	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9	846.6	845.3	844.0
157.5°	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1	863.0	861.9	860.7
160°	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	872.7	871.9	871.0
162.5°	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0	881.2	880.3	879.4
165°	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4	892.5	891.6	890.8
167.5°	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8	901.0	900.1	899.2
170°	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6	905.7	904.8	904.0
172.5°	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7	908.9	908.0	907.1
175°	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9	912.9	911.8	910.8
177.5°	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5	913.7	912.9	912.1
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	9.9	9.7	9.4	9.7	9.4	9.1	8.8	9.0	9.0	8.2	8.3
90°	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7	15.4	16.1	16.7
92.5°	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1	16.5	16.9	17.2
95°	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2	27.9	28.7	28.9
97.5°	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6	36.2	36.8	37.1
100°	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0	41.1	42.3	43.1
102.5°	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8	43.3	44.8	45.7
105°	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5	45.1	46.7	47.8
107.5°	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1	51.5	49.8	49.3
110°	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1	71.4	56.8	49.8



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3	130.8	77.3	50.8
115°	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4	203.4	135.5	96.3
117.5°	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1	401.6	385.2	359.7
120°	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2	488.9	490.7	481.6
122.5°	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9	517.9	519.1	517.6
125°	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6	560.6	561.7	562.4
127.5°	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1	600.6	602.1	602.9
130°	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2	625.8	627.4	628.1
132.5°	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5	649.9	651.2	651.9
135°	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2	684.7	686.2	686.7
137.5°	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5	716.9	718.4	718.9
140°	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4	737.7	739.0	739.3
142.5°	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6	756.9	758.1	758.3
145°	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6	783.6	784.7	784.9
147.5°	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2	806.9	807.7	807.8
150°	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6	821.5	822.4	822.5
152.5°	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8	834.7	835.6	835.6
155°	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6	852.5	853.4	853.2
157.5°	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7	867.6	868.6	868.6
160°	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3	876.3	877.1	877.0
162.5°	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5	884.5	885.5	885.4
165°	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5	894.5	895.5	895.5
167.5°	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8	902.9	903.8	903.7
170°	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1	907.0	908.0	908.0
172.5°	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2	910.2	911.3	911.1
175°	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7	913.6	914.6	914.5
177.5°	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0	913.8	914.6	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	8.4	7.9	8.0	7.5	8.0	7.9	8.4	8.3	8.2	9.0	9.0
90°	17.0	17.2	17.5	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7
92.5°	17.2	17.4	17.6	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1
95°	28.8	28.7	28.6	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6
100°	43.4	43.6	43.9	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0
102.5°	46.2	46.6	46.9	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8
105°	48.4	49.0	49.6	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5
107.5°	49.9	50.4	51.0	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1
110°	50.3	51.0	51.6	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	51.3	51.7	52.2	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3
115°	85.8	75.2	64.7	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4
117.5°	325.0	290.3	255.6	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1
120°	461.8	442.1	422.3	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2
122.5°	513.8	509.9	506.1	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9
125°	562.8	563.3	563.7	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6
127.5°	602.9	603.0	603.1	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1
130°	627.9	627.8	627.6	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2
132.5°	651.7	651.6	651.4	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5
135°	686.5	686.2	685.9	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2
137.5°	718.3	717.8	717.4	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5
140°	738.6	737.8	737.1	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4
142.5°	757.6	756.9	756.1	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6
145°	784.1	783.3	782.6	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6
147.5°	807.1	806.5	805.9	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2
150°	821.7	821.0	820.2	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6
152.5°	834.5	833.6	832.6	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8
155°	852.1	850.9	849.7	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6
157.5°	867.4	866.3	865.2	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7
160°	876.0	875.0	874.0	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3
162.5°	884.1	882.9	881.6	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5
165°	894.5	893.5	892.5	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5
167.5°	902.4	901.1	899.8	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8
170°	906.6	905.3	904.0	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1
172.5°	909.7	908.4	907.1	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2
175°	912.9	911.5	910.0	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7
177.5°	913.5	912.4	911.3	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	8.8	9.1	9.4	9.7	9.4	9.7	9.9	10.1	10.7	10.9	11.1
90°	13.9	13.2	12.1	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7
92.5°	15.6	15.3	14.7	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3
95°	26.5	25.7	24.7	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9
97.5°	35.1	34.4	32.0	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1
100°	38.7	37.6	35.2	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8
102.5°	40.2	38.6	59.5	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7
105°	41.8	40.2	80.3	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6
107.5°	54.7	56.4	104.3	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4
110°	100.9	115.5	157.9	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	237.8	291.2	301.7	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1
115°	339.2	407.1	403.4	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4
117.5°	434.5	450.9	448.4	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1
120°	485.4	483.6	481.0	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8
122.5°	515.9	514.8	511.9	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4
125°	558.6	557.5	554.8	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4
127.5°	597.6	596.1	594.0	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2
130°	622.5	620.9	619.3	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0
132.5°	647.1	645.7	644.1	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5
135°	681.7	680.3	679.0	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8
137.5°	714.1	712.7	711.1	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5
140°	735.1	733.8	732.1	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2
142.5°	754.5	753.3	751.4	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2
145°	781.7	780.6	778.1	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1
147.5°	805.4	804.6	802.1	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0
150°	819.7	818.9	816.5	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9
152.5°	832.9	832.1	829.8	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2
155°	850.7	849.9	848.1	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9
157.5°	865.6	864.6	863.4	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1
160°	874.5	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6
162.5°	882.5	881.6	880.8	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0
165°	892.5	891.5	891.0	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4
167.5°	900.8	899.8	899.4	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8
170°	905.0	904.0	903.7	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6
172.5°	908.1	907.1	906.8	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7
175°	911.6	910.6	910.3	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9
177.5°	912.2	911.3	911.3	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.0	15.3	15.6	17.4	16.7	17.0	17.2	16.9	16.7	16.3	15.9
90°	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7
92.5°	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1
95°	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2
97.5°	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6
100°	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0
102.5°	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8
105°	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5
107.5°	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1
110°	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1





TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3
115°	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4
117.5°	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1
120°	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2
122.5°	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9
125°	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6
127.5°	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1
130°	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2
132.5°	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5
135°	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2
137.5°	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5
140°	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4
142.5°	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6
145°	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6
147.5°	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2
150°	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6
152.5°	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8
155°	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6
157.5°	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7
160°	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3
162.5°	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5
165°	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5
167.5°	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8
170°	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1
172.5°	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2
175°	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7
177.5°	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	16.6	16.8	16.3	16.4	17.0	16.5	16.6
90°	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331561-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)