

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331562-830

Luminaire Tested: **S122DIW-S865D710U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331562-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D710U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5911.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42	39
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	26
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	2.6
10°-20°	450.6	7.6
20°-30°	653.9	11.1
30°-40°	690.0	11.7
40°-50°	611.0	10.3
50°-60°	487.6	8.2
60°-70°	331.4	5.6
70°-80°	169.9	2.9
80°-90°	44.3	0.7
90°-100°	52.5	0.9
100°-110°	163.1	2.8
110°-120°	278.8	4.7
120°-130°	366.6	6.2
130°-140°	411.5	7.0
140°-150°	403.5	6.8
150°-160°	338.4	5.7
160°-170°	224.5	3.8
170°-180°	78.5	1.3
0°-30°	1259.4	21.3
0°-40°	1949.5	33.0
0°-60°	3048.0	51.6
0°-90°	3593.5	60.8
90°-120°	494.4	8.4
90°-150°	1676.1	28.4
90°-180°	2317.0	39.2
0°-180°	5911.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	24	1	24	1	24	12
95°	43	36	43	36	43	48
105°	155	150	155	150	155	163
115°	280	280	280	280	280	276
125°	408	407	408	407	408	364
135°	533	527	533	527	533	410
145°	646	639	646	639	646	404
155°	736	731	736	731	736	339
165°	796	795	796	795	796	224
175°	825	827	825	827	825	78
180°	829	829	829	829	829	



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	17.7	17.7	18.2	17.6	17.6	18.2	18.2	17.8	18.4	18.9	18.8
90°	23.8	23.7	23.5	23.3	23.2	23.3	23.6	23.8	24.1	24.5	21.0
92.5°	22.6	22.6	22.6	22.5	22.5	22.5	22.4	22.3	22.3	22.2	21.4
95°	43.4	43.6	44.0	44.3	44.6	44.8	44.8	44.8	44.8	44.8	44.5
97.5°	75.1	75.1	75.2	75.2	75.2	75.2	75.2	75.2	75.2	75.2	74.6
100°	95.9	96.0	96.1	96.3	96.4	96.5	96.5	96.5	96.5	96.5	96.0
102.5°	119.3	119.5	119.6	119.8	120.0	120.0	119.8	119.7	119.6	119.4	118.9
105°	155.2	155.2	155.2	155.2	155.2	155.1	154.8	154.5	154.2	153.9	153.5
107.5°	189.2	189.8	190.6	191.2	192.0	192.3	192.2	192.0	191.9	191.8	191.8
110°	215.5	215.8	216.3	216.8	217.3	217.5	217.5	217.5	217.5	217.5	217.5



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.6	240.9	241.3	241.7	242.0	242.3	242.7	243.1	243.5	243.8	243.9
115°	279.7	280.2	280.7	281.2	281.6	281.9	282.1	282.3	282.4	282.6	282.9
117.5°	317.1	317.5	318.0	318.5	319.0	319.4	319.8	320.2	320.6	320.9	321.8
120°	343.4	343.8	344.3	344.8	345.3	345.5	345.5	345.5	345.5	345.5	346.8
122.5°	369.2	369.5	369.9	370.1	370.5	370.9	371.3	371.6	372.0	372.4	373.2
125°	408.5	408.6	408.8	409.0	409.1	409.3	409.8	410.3	410.8	411.2	411.7
127.5°	444.3	444.8	445.3	445.7	446.3	446.8	447.3	447.9	448.5	449.0	449.6
130°	470.0	470.6	471.3	471.8	472.5	473.0	473.3	473.6	473.9	474.2	474.5
132.5°	494.6	495.1	495.6	496.2	496.6	497.2	497.9	498.6	499.3	499.9	499.9
135°	532.9	533.4	533.9	534.3	534.8	535.2	535.3	535.5	535.6	535.7	535.5
137.5°	567.6	568.3	568.9	569.5	570.1	570.5	570.6	570.7	570.9	571.0	570.6
140°	591.7	592.3	593.0	593.6	594.2	594.5	594.5	594.5	594.5	594.5	593.7
142.5°	613.5	614.2	614.7	615.4	616.0	616.2	616.1	616.0	615.9	615.8	615.2
145°	646.3	646.9	647.5	648.1	648.8	648.9	648.8	648.7	648.5	648.4	647.4
147.5°	675.5	676.1	676.7	677.3	677.9	678.0	677.6	677.3	676.9	676.7	676.0
150°	694.6	695.0	695.4	695.9	696.4	696.4	695.9	695.4	695.0	694.6	693.9
152.5°	712.5	713.0	713.6	714.2	714.8	714.8	714.2	713.6	713.0	712.5	711.7
155°	736.5	737.0	737.4	737.9	738.4	738.2	737.4	736.6	735.8	735.1	734.6
157.5°	757.1	757.9	758.7	759.4	760.2	760.0	758.9	757.9	756.9	755.8	755.5
160°	770.1	770.7	771.3	771.9	772.5	772.4	771.5	770.5	769.6	768.6	768.5
162.5°	781.3	782.0	782.8	783.4	784.2	784.1	783.1	781.9	780.9	779.9	779.7
165°	796.0	796.7	797.5	798.2	799.1	798.9	797.8	796.7	795.6	794.6	794.6
167.5°	807.9	808.8	809.5	810.4	811.2	811.1	809.9	808.9	807.8	806.7	806.7
170°	814.1	815.0	816.0	816.9	817.8	817.7	816.7	815.6	814.5	813.4	813.6
172.5°	819.2	820.1	821.0	822.0	822.8	822.8	821.7	820.7	819.5	818.4	818.6
175°	824.6	825.6	826.5	827.4	828.3	828.3	827.2	826.0	825.0	823.9	824.3
177.5°	827.1	827.8	828.6	829.3	830.1	830.1	829.3	828.6	827.8	827.1	827.4
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	18.6	17.8	17.2	17.6	15.7	15.4	13.0	11.1	11.0	10.9	10.3
90°	17.6	14.2	10.8	8.2	6.3	4.4	2.5	0.7	2.5	4.4	6.3
92.5°	20.6	19.8	19.0	17.9	16.6	15.2	13.9	12.4	13.9	15.2	16.6
95°	44.1	43.8	43.5	42.6	41.0	39.5	37.9	36.4	37.9	39.5	41.0
97.5°	74.1	73.5	72.9	71.9	70.5	69.2	67.8	66.4	67.8	69.2	70.5
100°	95.6	95.1	94.6	93.8	92.6	91.3	90.1	88.8	90.1	91.3	92.6
102.5°	118.3	117.7	117.1	116.3	115.3	114.3	113.3	112.4	113.3	114.3	115.3
105°	153.3	153.0	152.6	152.2	151.7	151.3	150.8	150.3	150.8	151.3	151.7
107.5°	191.8	191.8	191.8	191.4	190.8	190.1	189.4	188.7	189.4	190.1	190.8
110°	217.5	217.5	217.5	217.1	216.1	215.2	214.2	213.3	214.2	215.2	216.1



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	244.0	244.2	244.3	243.9	243.0	242.0	241.1	240.2	241.1	242.0	243.0
115°	283.1	283.5	283.8	283.5	282.6	281.6	280.7	279.7	280.7	281.6	282.6
117.5°	322.6	323.5	324.3	324.1	322.9	321.7	320.5	319.2	320.5	321.7	322.9
120°	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	346.8	348.0	349.2
122.5°	374.1	374.9	375.9	375.5	374.0	372.6	371.1	369.6	371.1	372.6	374.0
125°	412.2	412.6	413.1	412.6	411.2	409.8	408.5	407.1	408.5	409.8	411.2
127.5°	450.2	450.7	451.3	450.6	448.8	447.1	445.4	443.6	445.4	447.1	448.8
130°	474.9	475.1	475.4	474.6	472.6	470.5	468.5	466.5	468.5	470.5	472.6
132.5°	499.8	499.7	499.7	498.8	497.2	495.6	493.9	492.3	493.9	495.6	497.2
135°	535.2	534.8	534.5	533.5	531.8	530.1	528.4	526.7	528.4	530.1	531.8
137.5°	570.2	569.8	569.4	568.4	567.1	565.7	564.3	562.9	564.3	565.7	567.1
140°	593.0	592.2	591.4	590.3	588.9	587.5	586.1	584.8	586.1	587.5	588.9
142.5°	614.7	614.2	613.7	612.7	611.3	609.9	608.5	607.1	608.5	609.9	611.3
145°	646.5	645.5	644.6	643.7	642.5	641.4	640.4	639.2	640.4	641.4	642.5
147.5°	675.3	674.8	674.1	673.2	671.8	670.5	669.2	668.0	669.2	670.5	671.8
150°	693.2	692.7	692.0	691.3	690.3	689.4	688.4	687.5	688.4	689.4	690.3
152.5°	711.0	710.2	709.5	708.6	707.7	706.7	705.8	704.8	705.8	706.7	707.7
155°	734.1	733.7	733.2	732.7	732.3	731.8	731.3	730.8	731.3	731.8	732.3
157.5°	755.3	755.0	754.7	754.4	754.0	753.8	753.5	753.1	753.5	753.8	754.0
160°	768.4	768.2	768.1	767.8	767.5	767.1	766.9	766.6	766.9	767.1	767.5
162.5°	779.6	779.4	779.2	779.1	779.0	779.0	778.9	778.8	778.9	779.0	779.0
165°	794.6	794.6	794.6	794.7	794.8	794.9	795.0	795.2	795.0	794.9	794.8
167.5°	806.7	806.8	806.8	807.1	807.6	808.0	808.5	809.0	808.5	808.0	807.6
170°	813.7	813.9	814.1	814.4	814.8	815.3	815.8	816.2	815.8	815.3	814.8
172.5°	818.8	818.9	819.1	819.4	819.8	820.3	820.8	821.2	820.8	820.3	819.8
175°	824.5	824.8	825.2	825.6	826.0	826.5	827.0	827.4	827.0	826.5	826.0
177.5°	827.6	827.8	828.1	828.4	828.8	829.2	829.5	829.9	829.5	829.2	828.8
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	10.2	10.2	10.4	11.0	11.2	11.4	10.8	10.7	10.7	9.6	9.6
90°	8.2	10.8	14.2	17.6	21.0	24.5	24.1	23.8	23.6	23.3	23.2
92.5°	17.9	19.0	19.8	20.6	21.4	22.2	22.3	22.3	22.4	22.5	22.5
95°	42.6	43.5	43.8	44.1	44.5	44.8	44.8	44.8	44.8	44.8	44.6
97.5°	71.9	72.9	73.5	74.1	74.6	75.2	75.2	75.2	75.2	75.2	75.2
100°	93.8	94.6	95.1	95.6	96.0	96.5	96.5	96.5	96.5	96.5	96.4
102.5°	116.3	117.1	117.7	118.3	118.9	119.4	119.6	119.7	119.8	120.0	120.0
105°	152.2	152.6	153.0	153.3	153.5	153.9	154.2	154.5	154.8	155.1	155.2
107.5°	191.4	191.8	191.8	191.8	191.8	191.8	191.9	192.0	192.2	192.3	192.0
110°	217.1	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.3



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	243.9	244.3	244.2	244.0	243.9	243.8	243.5	243.1	242.7	242.3	242.0
115°	283.5	283.8	283.5	283.1	282.9	282.6	282.4	282.3	282.1	281.9	281.6
117.5°	324.1	324.3	323.5	322.6	321.8	320.9	320.6	320.2	319.8	319.4	319.0
120°	350.4	350.4	349.2	348.0	346.8	345.5	345.5	345.5	345.5	345.5	345.3
122.5°	375.5	375.9	374.9	374.1	373.2	372.4	372.0	371.6	371.3	370.9	370.5
125°	412.6	413.1	412.6	412.2	411.7	411.2	410.8	410.3	409.8	409.3	409.1
127.5°	450.6	451.3	450.7	450.2	449.6	449.0	448.5	447.9	447.3	446.8	446.3
130°	474.6	475.4	475.1	474.9	474.5	474.2	473.9	473.6	473.3	473.0	472.5
132.5°	498.8	499.7	499.7	499.8	499.9	499.9	499.3	498.6	497.9	497.2	496.6
135°	533.5	534.5	534.8	535.2	535.5	535.7	535.6	535.5	535.3	535.2	534.8
137.5°	568.4	569.4	569.8	570.2	570.6	571.0	570.9	570.7	570.6	570.5	570.1
140°	590.3	591.4	592.2	593.0	593.7	594.5	594.5	594.5	594.5	594.5	594.2
142.5°	612.7	613.7	614.2	614.7	615.2	615.8	615.9	616.0	616.1	616.2	616.0
145°	643.7	644.6	645.5	646.5	647.4	648.4	648.5	648.7	648.8	648.9	648.8
147.5°	673.2	674.1	674.8	675.3	676.0	676.7	676.9	677.3	677.6	678.0	677.9
150°	691.3	692.0	692.7	693.2	693.9	694.6	695.0	695.4	695.9	696.4	696.4
152.5°	708.6	709.5	710.2	711.0	711.7	712.5	713.0	713.6	714.2	714.8	714.8
155°	732.7	733.2	733.7	734.1	734.6	735.1	735.8	736.6	737.4	738.2	738.4
157.5°	754.4	754.7	755.0	755.3	755.5	755.8	756.9	757.9	758.9	760.0	760.2
160°	767.8	768.1	768.2	768.4	768.5	768.6	769.6	770.5	771.5	772.4	772.5
162.5°	779.1	779.2	779.4	779.6	779.7	779.9	780.9	781.9	783.1	784.1	784.2
165°	794.7	794.6	794.6	794.6	794.6	794.6	795.6	796.7	797.8	798.9	799.1
167.5°	807.1	806.8	806.8	806.7	806.7	806.7	807.8	808.9	809.9	811.1	811.2
170°	814.4	814.1	813.9	813.7	813.6	813.4	814.5	815.6	816.7	817.7	817.8
172.5°	819.4	819.1	818.9	818.8	818.6	818.4	819.5	820.7	821.7	822.8	822.8
175°	825.6	825.2	824.8	824.5	824.3	823.9	825.0	826.0	827.2	828.3	828.3
177.5°	828.4	828.1	827.8	827.6	827.4	827.1	827.8	828.6	829.3	830.1	830.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	9.7	9.2	9.2	8.8	9.2	9.2	9.7	9.6	9.6	10.7	10.7
90°	23.3	23.5	23.7	23.8	23.7	23.5	23.3	23.2	23.3	23.6	23.8
92.5°	22.5	22.6	22.6	22.6	22.6	22.6	22.5	22.5	22.5	22.4	22.3
95°	44.3	44.0	43.6	43.4	43.6	44.0	44.3	44.6	44.8	44.8	44.8
97.5°	75.2	75.2	75.1	75.1	75.1	75.2	75.2	75.2	75.2	75.2	75.2
100°	96.3	96.1	96.0	95.9	96.0	96.1	96.3	96.4	96.5	96.5	96.5
102.5°	119.8	119.6	119.5	119.3	119.5	119.6	119.8	120.0	120.0	119.8	119.7
105°	155.2	155.2	155.2	155.2	155.2	155.2	155.2	155.2	155.1	154.8	154.5
107.5°	191.2	190.6	189.8	189.2	189.8	190.6	191.2	192.0	192.3	192.2	192.0
110°	216.8	216.3	215.8	215.5	215.8	216.3	216.8	217.3	217.5	217.5	217.5



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	241.7	241.3	240.9	240.6	240.9	241.3	241.7	242.0	242.3	242.7	243.1
115°	281.2	280.7	280.2	279.7	280.2	280.7	281.2	281.6	281.9	282.1	282.3
117.5°	318.5	318.0	317.5	317.1	317.5	318.0	318.5	319.0	319.4	319.8	320.2
120°	344.8	344.3	343.8	343.4	343.8	344.3	344.8	345.3	345.5	345.5	345.5
122.5°	370.1	369.9	369.5	369.2	369.5	369.9	370.1	370.5	370.9	371.3	371.6
125°	409.0	408.8	408.6	408.5	408.6	408.8	409.0	409.1	409.3	409.8	410.3
127.5°	445.7	445.3	444.8	444.3	444.8	445.3	445.7	446.3	446.8	447.3	447.9
130°	471.8	471.3	470.6	470.0	470.6	471.3	471.8	472.5	473.0	473.3	473.6
132.5°	496.2	495.6	495.1	494.6	495.1	495.6	496.2	496.6	497.2	497.9	498.6
135°	534.3	533.9	533.4	532.9	533.4	533.9	534.3	534.8	535.2	535.3	535.5
137.5°	569.5	568.9	568.3	567.6	568.3	568.9	569.5	570.1	570.5	570.6	570.7
140°	593.6	593.0	592.3	591.7	592.3	593.0	593.6	594.2	594.5	594.5	594.5
142.5°	615.4	614.7	614.2	613.5	614.2	614.7	615.4	616.0	616.2	616.1	616.0
145°	648.1	647.5	646.9	646.3	646.9	647.5	648.1	648.8	648.9	648.8	648.7
147.5°	677.3	676.7	676.1	675.5	676.1	676.7	677.3	677.9	678.0	677.6	677.3
150°	695.9	695.4	695.0	694.6	695.0	695.4	695.9	696.4	696.4	695.9	695.4
152.5°	714.2	713.6	713.0	712.5	713.0	713.6	714.2	714.8	714.8	714.2	713.6
155°	737.9	737.4	737.0	736.5	737.0	737.4	737.9	738.4	738.2	737.4	736.6
157.5°	759.4	758.7	757.9	757.1	757.9	758.7	759.4	760.2	760.0	758.9	757.9
160°	771.9	771.3	770.7	770.1	770.7	771.3	771.9	772.5	772.4	771.5	770.5
162.5°	783.4	782.8	782.0	781.3	782.0	782.8	783.4	784.2	784.1	783.1	781.9
165°	798.2	797.5	796.7	796.0	796.7	797.5	798.2	799.1	798.9	797.8	796.7
167.5°	810.4	809.5	808.8	807.9	808.8	809.5	810.4	811.2	811.1	809.9	808.9
170°	816.9	816.0	815.0	814.1	815.0	816.0	816.9	817.8	817.7	816.7	815.6
172.5°	822.0	821.0	820.1	819.2	820.1	821.0	822.0	822.8	822.8	821.7	820.7
175°	827.4	826.5	825.6	824.6	825.6	826.5	827.4	828.3	828.3	827.2	826.0
177.5°	829.3	828.6	827.8	827.1	827.8	828.6	829.3	830.1	830.1	829.3	828.6
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	10.8	11.4	11.2	11.0	10.4	10.2	10.2	10.3	10.9	11.0	11.1
90°	24.1	24.5	21.0	17.6	14.2	10.8	8.2	6.3	4.4	2.5	0.7
92.5°	22.3	22.2	21.4	20.6	19.8	19.0	17.9	16.6	15.2	13.9	12.4
95°	44.8	44.8	44.5	44.1	43.8	43.5	42.6	41.0	39.5	37.9	36.4
97.5°	75.2	75.2	74.6	74.1	73.5	72.9	71.9	70.5	69.2	67.8	66.4
100°	96.5	96.5	96.0	95.6	95.1	94.6	93.8	92.6	91.3	90.1	88.8
102.5°	119.6	119.4	118.9	118.3	117.7	117.1	116.3	115.3	114.3	113.3	112.4
105°	154.2	153.9	153.5	153.3	153.0	152.6	152.2	151.7	151.3	150.8	150.3
107.5°	191.9	191.8	191.8	191.8	191.8	191.8	191.4	190.8	190.1	189.4	188.7
110°	217.5	217.5	217.5	217.5	217.5	217.5	217.1	216.1	215.2	214.2	213.3



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.5	243.8	243.9	244.0	244.2	244.3	243.9	243.0	242.0	241.1	240.2
115°	282.4	282.6	282.9	283.1	283.5	283.8	283.5	282.6	281.6	280.7	279.7
117.5°	320.6	320.9	321.8	322.6	323.5	324.3	324.1	322.9	321.7	320.5	319.2
120°	345.5	345.5	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5
122.5°	372.0	372.4	373.2	374.1	374.9	375.9	375.5	374.0	372.6	371.1	369.6
125°	410.8	411.2	411.7	412.2	412.6	413.1	412.6	411.2	409.8	408.5	407.1
127.5°	448.5	449.0	449.6	450.2	450.7	451.3	450.6	448.8	447.1	445.4	443.6
130°	473.9	474.2	474.5	474.9	475.1	475.4	474.6	472.6	470.5	468.5	466.5
132.5°	499.3	499.9	499.9	499.8	499.7	499.7	498.8	497.2	495.6	493.9	492.3
135°	535.6	535.7	535.5	535.2	534.8	534.5	533.5	531.8	530.1	528.4	526.7
137.5°	570.9	571.0	570.6	570.2	569.8	569.4	568.4	567.1	565.7	564.3	562.9
140°	594.5	594.5	593.7	593.0	592.2	591.4	590.3	588.9	587.5	586.1	584.8
142.5°	615.9	615.8	615.2	614.7	614.2	613.7	612.7	611.3	609.9	608.5	607.1
145°	648.5	648.4	647.4	646.5	645.5	644.6	643.7	642.5	641.4	640.4	639.2
147.5°	676.9	676.7	676.0	675.3	674.8	674.1	673.2	671.8	670.5	669.2	668.0
150°	695.0	694.6	693.9	693.2	692.7	692.0	691.3	690.3	689.4	688.4	687.5
152.5°	713.0	712.5	711.7	711.0	710.2	709.5	708.6	707.7	706.7	705.8	704.8
155°	735.8	735.1	734.6	734.1	733.7	733.2	732.7	732.3	731.8	731.3	730.8
157.5°	756.9	755.8	755.5	755.3	755.0	754.7	754.4	754.0	753.8	753.5	753.1
160°	769.6	768.6	768.5	768.4	768.2	768.1	767.8	767.5	767.1	766.9	766.6
162.5°	780.9	779.9	779.7	779.6	779.4	779.2	779.1	779.0	779.0	778.9	778.8
165°	795.6	794.6	794.6	794.6	794.6	794.6	794.7	794.8	794.9	795.0	795.2
167.5°	807.8	806.7	806.7	806.7	806.8	806.8	807.1	807.6	808.0	808.5	809.0
170°	814.5	813.4	813.6	813.7	813.9	814.1	814.4	814.8	815.3	815.8	816.2
172.5°	819.5	818.4	818.6	818.8	818.9	819.1	819.4	819.8	820.3	820.8	821.2
175°	825.0	823.9	824.3	824.5	824.8	825.2	825.6	826.0	826.5	827.0	827.4
177.5°	827.8	827.1	827.4	827.6	827.8	828.1	828.4	828.8	829.2	829.5	829.9
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.0	15.4	15.7	17.6	17.2	17.8	18.6	18.8	18.9	18.4	17.8
90°	2.5	4.4	6.3	8.2	10.8	14.2	17.6	21.0	24.5	24.1	23.8
92.5°	13.9	15.2	16.6	17.9	19.0	19.8	20.6	21.4	22.2	22.3	22.3
95°	37.9	39.5	41.0	42.6	43.5	43.8	44.1	44.5	44.8	44.8	44.8
97.5°	67.8	69.2	70.5	71.9	72.9	73.5	74.1	74.6	75.2	75.2	75.2
100°	90.1	91.3	92.6	93.8	94.6	95.1	95.6	96.0	96.5	96.5	96.5
102.5°	113.3	114.3	115.3	116.3	117.1	117.7	118.3	118.9	119.4	119.6	119.7
105°	150.8	151.3	151.7	152.2	152.6	153.0	153.3	153.5	153.9	154.2	154.5
107.5°	189.4	190.1	190.8	191.4	191.8	191.8	191.8	191.8	191.8	191.9	192.0
110°	214.2	215.2	216.1	217.1	217.5	217.5	217.5	217.5	217.5	217.5	217.5



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	241.1	242.0	243.0	243.9	244.3	244.2	244.0	243.9	243.8	243.5	243.1
115°	280.7	281.6	282.6	283.5	283.8	283.5	283.1	282.9	282.6	282.4	282.3
117.5°	320.5	321.7	322.9	324.1	324.3	323.5	322.6	321.8	320.9	320.6	320.2
120°	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	345.5	345.5
122.5°	371.1	372.6	374.0	375.5	375.9	374.9	374.1	373.2	372.4	372.0	371.6
125°	408.5	409.8	411.2	412.6	413.1	412.6	412.2	411.7	411.2	410.8	410.3
127.5°	445.4	447.1	448.8	450.6	451.3	450.7	450.2	449.6	449.0	448.5	447.9
130°	468.5	470.5	472.6	474.6	475.4	475.1	474.9	474.5	474.2	473.9	473.6
132.5°	493.9	495.6	497.2	498.8	499.7	499.7	499.8	499.9	499.9	499.3	498.6
135°	528.4	530.1	531.8	533.5	534.5	534.8	535.2	535.5	535.7	535.6	535.5
137.5°	564.3	565.7	567.1	568.4	569.4	569.8	570.2	570.6	571.0	570.9	570.7
140°	586.1	587.5	588.9	590.3	591.4	592.2	593.0	593.7	594.5	594.5	594.5
142.5°	608.5	609.9	611.3	612.7	613.7	614.2	614.7	615.2	615.8	615.9	616.0
145°	640.4	641.4	642.5	643.7	644.6	645.5	646.5	647.4	648.4	648.5	648.7
147.5°	669.2	670.5	671.8	673.2	674.1	674.8	675.3	676.0	676.7	676.9	677.3
150°	688.4	689.4	690.3	691.3	692.0	692.7	693.2	693.9	694.6	695.0	695.4
152.5°	705.8	706.7	707.7	708.6	709.5	710.2	711.0	711.7	712.5	713.0	713.6
155°	731.3	731.8	732.3	732.7	733.2	733.7	734.1	734.6	735.1	735.8	736.6
157.5°	753.5	753.8	754.0	754.4	754.7	755.0	755.3	755.5	755.8	756.9	757.9
160°	766.9	767.1	767.5	767.8	768.1	768.2	768.4	768.5	768.6	769.6	770.5
162.5°	778.9	779.0	779.0	779.1	779.2	779.4	779.6	779.7	779.9	780.9	781.9
165°	795.0	794.9	794.8	794.7	794.6	794.6	794.6	794.6	794.6	795.6	796.7
167.5°	808.5	808.0	807.6	807.1	806.8	806.8	806.7	806.7	806.7	807.8	808.9
170°	815.8	815.3	814.8	814.4	814.1	813.9	813.7	813.6	813.4	814.5	815.6
172.5°	820.8	820.3	819.8	819.4	819.1	818.9	818.8	818.6	818.4	819.5	820.7
175°	827.0	826.5	826.0	825.6	825.2	824.8	824.5	824.3	823.9	825.0	826.0
177.5°	829.5	829.2	828.8	828.4	828.1	827.8	827.6	827.4	827.1	827.8	828.6
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	18.2	18.2	17.6	17.6	18.2	17.7	17.7
90°	23.6	23.3	23.2	23.3	23.5	23.7	23.8
92.5°	22.4	22.5	22.5	22.5	22.6	22.6	22.6
95°	44.8	44.8	44.6	44.3	44.0	43.6	43.4
97.5°	75.2	75.2	75.2	75.2	75.2	75.1	75.1
100°	96.5	96.5	96.4	96.3	96.1	96.0	95.9
102.5°	119.8	120.0	120.0	119.8	119.6	119.5	119.3
105°	154.8	155.1	155.2	155.2	155.2	155.2	155.2
107.5°	192.2	192.3	192.0	191.2	190.6	189.8	189.2
110°	217.5	217.5	217.3	216.8	216.3	215.8	215.5



TEST NUMBER: P331562-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.7	242.3	242.0	241.7	241.3	240.9	240.6
115°	282.1	281.9	281.6	281.2	280.7	280.2	279.7
117.5°	319.8	319.4	319.0	318.5	318.0	317.5	317.1
120°	345.5	345.5	345.3	344.8	344.3	343.8	343.4
122.5°	371.3	370.9	370.5	370.1	369.9	369.5	369.2
125°	409.8	409.3	409.1	409.0	408.8	408.6	408.5
127.5°	447.3	446.8	446.3	445.7	445.3	444.8	444.3
130°	473.3	473.0	472.5	471.8	471.3	470.6	470.0
132.5°	497.9	497.2	496.6	496.2	495.6	495.1	494.6
135°	535.3	535.2	534.8	534.3	533.9	533.4	532.9
137.5°	570.6	570.5	570.1	569.5	568.9	568.3	567.6
140°	594.5	594.5	594.2	593.6	593.0	592.3	591.7
142.5°	616.1	616.2	616.0	615.4	614.7	614.2	613.5
145°	648.8	648.9	648.8	648.1	647.5	646.9	646.3
147.5°	677.6	678.0	677.9	677.3	676.7	676.1	675.5
150°	695.9	696.4	696.4	695.9	695.4	695.0	694.6
152.5°	714.2	714.8	714.8	714.2	713.6	713.0	712.5
155°	737.4	738.2	738.4	737.9	737.4	737.0	736.5
157.5°	758.9	760.0	760.2	759.4	758.7	757.9	757.1
160°	771.5	772.4	772.5	771.9	771.3	770.7	770.1
162.5°	783.1	784.1	784.2	783.4	782.8	782.0	781.3
165°	797.8	798.9	799.1	798.2	797.5	796.7	796.0
167.5°	809.9	811.1	811.2	810.4	809.5	808.8	807.9
170°	816.7	817.7	817.8	816.9	816.0	815.0	814.1
172.5°	821.7	822.8	822.8	822.0	821.0	820.1	819.2
175°	827.2	828.3	828.3	827.4	826.5	825.6	824.6
177.5°	829.3	830.1	830.1	829.3	828.6	827.8	827.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8

(END OF REPORT)