

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331799

Luminaire Tested: **S122RDIW-S485D1240U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331799
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6655.7 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	88	85	82	82	79	76	73	61	59	57	45	44	43	30	29	29	22				
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	22	21	16				
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14				
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12				
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	1.2
10°-20°	212.1	3.2
20°-30°	297.8	4.5
30°-40°	324.8	4.9
40°-50°	298.6	4.5
50°-60°	234.5	3.5
60°-70°	152.9	2.3
70°-80°	78.8	1.2
80°-90°	24.6	0.4
90°-100°	56.4	0.8
100°-110°	206.8	3.1
110°-120°	552.8	8.3
120°-130°	912.5	13.7
130°-140°	970.4	14.6
140°-150°	902.0	13.6
150°-160°	725.2	10.9
160°-170°	467.3	7.0
170°-180°	160.9	2.4
0°-30°	587.2	8.8
0°-40°	912.0	13.7
0°-60°	1445.1	21.7
0°-90°	1701.5	25.6
90°-120°	816.0	12.3
90°-150°	3600.9	54.1
90°-180°	4954.0	74.4
0°-180°	6655.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	1	14	24	30	33	5
95°	80	42	48	53	53	97
105°	372	388	75	88	93	397
115°	703	725	755	215	100	692
125°	994	1011	1034	1042	1046	886
135°	1231	1250	1261	1273	1271	950
145°	1428	1428	1447	1455	1450	893
155°	1572	1562	1576	1582	1573	724
165°	1656	1650	1653	1660	1653	468
175°	1694	1686	1688	1696	1684	161
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.8	9.3	8.9	8.4	7.9	7.9	8.4	8.8	9.2	9.7	9.8
90°	1.2	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8
92.5°	24.7	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1
95°	79.5	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1
97.5°	157.8	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9
100°	216.5	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9
102.5°	281.1	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5
105°	371.9	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6
107.5°	475.4	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4
110°	541.9	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	604.5	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8
115°	703.4	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9
117.5°	791.7	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5
120°	856.3	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9
122.5°	911.1	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3
125°	994.5	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6
127.5°	1070.1	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9
130°	1118.1	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1
132.5°	1167.0	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6
135°	1230.6	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9
137.5°	1294.9	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8
140°	1337.0	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7
142.5°	1372.3	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7
145°	1427.5	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0
147.5°	1475.7	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1
150°	1507.1	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7
152.5°	1533.5	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2
155°	1571.9	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2
157.5°	1602.0	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8
160°	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2
162.5°	1635.3	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1
165°	1656.3	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5
167.5°	1672.0	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9
170°	1680.8	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8
172.5°	1686.6	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6
175°	1694.2	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0
177.5°	1695.4	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	10.0	10.1	10.2	10.4	10.5	10.6	10.7	10.8
90°	27.2	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	29.8	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	50.4	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	66.0	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	74.1	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	77.3	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	80.6	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	98.4	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	159.7	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331799

CATALOG NUMBER: S122RDIW-S485D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	341.6	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	503.0	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	775.1	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	903.2	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	958.3	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1037.5	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1110.6	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1157.1	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1202.2	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1266.6	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1326.4	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1365.2	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1400.9	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1450.9	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1494.5	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1521.3	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1545.8	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1578.8	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1606.7	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1622.9	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1638.0	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1671.8	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1679.7	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1685.5	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1691.9	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1692.6	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)