

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331571-830

Luminaire Tested: **S122DIW-S865D970U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331571-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D970U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6959.8 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	24	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	23	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	1.8
10°-20°	344.2	4.9
20°-30°	505.9	7.3
30°-40°	587.6	8.4
40°-50°	587.0	8.4
50°-60°	511.9	7.4
60°-70°	378.5	5.4
70°-80°	214.4	3.1
80°-90°	60.7	0.9
90°-100°	41.5	0.6
100°-110°	152.3	2.2
110°-120°	407.0	5.8
120°-130°	671.8	9.7
130°-140°	714.5	10.3
140°-150°	664.1	9.5
150°-160°	533.9	7.7
160°-170°	344.1	4.9
170°-180°	118.4	1.7
0°-30°	972.3	14.0
0°-40°	1559.9	22.4
0°-60°	2658.7	38.2
0°-90°	3312.3	47.6
90°-120°	600.8	8.6
90°-150°	2651.1	38.1
90°-180°	3648.0	52.4
0°-180°	6959.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	11	18	22	24	5
95°	58	31	35	39	39	72
105°	274	286	55	64	68	293
115°	518	534	556	158	74	510
125°	732	744	761	767	770	653
135°	906	920	929	937	936	700
145°	1051	1051	1066	1071	1067	657
155°	1157	1150	1160	1165	1158	533
165°	1220	1215	1217	1222	1217	344
175°	1247	1242	1243	1248	1240	119
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.2	18.2	18.2	18.2	18.2	18.1	18.0	17.8	17.7	17.6	17.2
90°	0.9	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0
92.5°	18.2	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4
95°	58.5	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1
97.5°	116.2	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8
100°	159.4	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0
102.5°	207.0	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9
105°	273.8	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1
107.5°	350.0	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6
110°	399.0	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.1	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5
115°	517.8	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0
117.5°	582.9	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0
120°	630.5	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6
122.5°	670.8	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1
125°	732.2	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4
127.5°	787.9	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7
130°	823.2	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7
132.5°	859.2	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3
135°	906.1	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6
137.5°	953.4	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7
140°	984.4	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3
142.5°	1010.3	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8
145°	1051.0	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9
147.5°	1086.6	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3
150°	1109.6	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9
152.5°	1129.1	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9
155°	1157.3	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2
157.5°	1179.5	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6
160°	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6
162.5°	1204.0	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6
165°	1219.5	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1
167.5°	1231.0	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5
170°	1237.5	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3
172.5°	1241.8	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6
175°	1247.4	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3
177.5°	1248.3	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	16.7	16.2	15.7	15.5	15.3	15.2	15.0	14.9
90°	20.0	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.0	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	37.1	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	48.6	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	54.6	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	56.9	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	59.4	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	72.4	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	117.5	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331571-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	251.5	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	370.3	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	570.6	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	665.0	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	705.6	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	763.8	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	817.7	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	851.9	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	885.1	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	932.6	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	976.6	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1005.1	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1031.4	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1068.3	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1100.3	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1120.1	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1138.1	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1162.4	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1182.9	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1194.9	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1206.0	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1230.9	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1236.7	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1241.0	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1245.7	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1246.2	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)