

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331861-830

Luminaire Tested: **S122RDIW-S1005D1440U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331861-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1440U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9026.1 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.1	2.2
10°-20°	549.1	6.1
20°-30°	707.5	7.8
30°-40°	672.4	7.4
40°-50°	576.0	6.4
50°-60°	438.6	4.9
60°-70°	277.3	3.1
70°-80°	138.5	1.5
80°-90°	40.6	0.4
90°-100°	61.8	0.7
100°-110°	226.6	2.5
110°-120°	605.8	6.7
120°-130°	1000.0	11.1
130°-140°	1063.4	11.8
140°-150°	988.4	11.0
150°-160°	794.7	8.8
160°-170°	512.1	5.7
170°-180°	176.3	2.0
0°-30°	1453.7	16.1
0°-40°	2126.0	23.6
0°-60°	3140.7	34.8
0°-90°	3597.0	39.9
90°-120°	894.2	9.9
90°-150°	3946.0	43.7
90°-180°	5429.0	60.1
0°-180°	9026.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	29
90°	36	1	36	1	36	17
95°	58	87	58	87	58	54
105°	102	408	102	408	102	106
115°	110	771	110	771	110	275
125°	1146	1090	1146	1090	1146	992
135°	1393	1349	1393	1349	1393	1073
145°	1589	1564	1589	1564	1589	993
155°	1724	1723	1724	1723	1724	795
165°	1811	1815	1811	1815	1811	511
175°	1846	1857	1846	1857	1846	176
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	16.5	17.0	16.8	16.7	16.6	16.4	16.1	16.4	15.5	15.7	14.7
90°	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8	28.3	26.8	24.4
92.5°	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6	31.9	31.1	29.9
95°	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2	53.7	52.3	50.2
97.5°	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4	71.2	69.9	65.1
100°	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2	78.8	76.4	71.4
102.5°	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7	81.6	78.5	72.9
105°	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3	85.0	81.8	76.1
107.5°	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8	111.1	114.5	120.0
110°	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0	204.8	234.6	320.7



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4	483.1	591.7	612.9
115°	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3	689.2	827.1	819.6
117.5°	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4	882.8	916.2	911.0
120°	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8	986.2	982.6	977.2
122.5°	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2	1048.0	1045.8	1040.0
125°	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9	1134.8	1132.7	1127.1
127.5°	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1	1214.1	1211.1	1206.8
130°	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0	1264.7	1261.4	1258.1
132.5°	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4	1314.7	1311.8	1308.5
135°	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0	1385.1	1382.1	1379.4
137.5°	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6	1450.7	1447.7	1444.7
140°	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0	1493.4	1490.6	1487.4
142.5°	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2	1532.8	1530.3	1526.5
145°	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0	1587.9	1585.8	1580.7
147.5°	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8	1636.2	1634.7	1629.7
150°	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2	1665.4	1663.6	1658.8
152.5°	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9	1692.1	1690.4	1685.8
155°	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1	1728.3	1726.5	1723.1
157.5°	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7	1758.7	1756.6	1754.1
160°	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4	1776.6	1774.8	1773.0
162.5°	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0	1793.0	1790.9	1789.4
165°	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0	1810.2
167.5°	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1	1830.0	1828.0	1827.1
170°	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7	1838.6	1836.5	1835.9
172.5°	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1	1845.0	1843.0	1842.4
175°	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1	1852.0	1849.9	1849.4
177.5°	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8	1853.2	1851.5	1851.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	14.2	14.3	13.9	12.7	12.6	12.5	14.8	17.1	15.4	14.3	13.8
90°	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3	4.6	7.9	11.2
92.5°	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1	26.8	26.5	26.2
95°	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1	77.3	67.5	57.7
97.5°	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0	145.2	117.5	89.8
100°	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2	196.4	155.6	114.8
102.5°	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0	299.4	290.8	282.1
105°	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6	416.4	425.4	434.3
107.5°	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9	528.1	535.4	542.5
110°	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9	600.1	606.3	612.7





TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5	668.0	673.5	679.1
115°	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8	775.9	780.9	786.0
117.5°	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6	873.3	878.9	884.6
120°	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4	942.8	947.3	951.8
122.5°	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4	1003.1	1007.9	1012.6
125°	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9	1093.7	1097.6	1101.5
127.5°	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7	1177.0	1181.3	1185.5
130°	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2	1230.0	1234.7	1239.5
132.5°	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8	1282.9	1286.9	1291.0
135°	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6	1353.3	1358.1	1362.8
137.5°	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1	1422.4	1425.8	1429.1
140°	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2	1467.5	1470.0	1472.3
142.5°	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8	1505.9	1508.1	1510.2
145°	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4	1564.1	1563.8	1563.5
147.5°	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2	1616.1	1615.0	1613.8
150°	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5	1649.4	1647.4	1645.3
152.5°	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5	1678.2	1675.8	1673.5
155°	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6	1719.9	1717.2	1714.5
157.5°	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6	1753.3	1751.1	1748.8
160°	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1773.0	1771.3	1769.5
162.5°	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0	1790.3	1788.5	1786.7
165°	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1	1813.3	1811.5	1809.7
167.5°	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2	1830.4	1828.6	1826.8
170°	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9	1840.1	1838.3	1836.5
172.5°	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3	1846.5	1844.7	1843.0
175°	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6	1854.5	1852.5	1850.4
177.5°	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9	1856.3	1854.6	1852.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	13.9	13.9	13.2	13.7	14.1	14.0	14.3	14.0	14.3	14.6	14.2
90°	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8	31.3	32.8	33.8
92.5°	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6	33.5	34.2	34.8
95°	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2	56.7	58.2	58.8
97.5°	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4	73.5	74.7	75.5
100°	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2	83.6	86.0	87.5
102.5°	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7	87.8	91.0	92.9
105°	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3	91.6	94.9	97.1
107.5°	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8	104.4	101.1	100.1
110°	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0	145.2	115.5	101.1



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4	265.7	157.0	103.1
115°	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3	413.3	275.4	195.7
117.5°	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4	816.1	782.7	730.8
120°	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8	993.3	996.9	978.5
122.5°	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2	1052.3	1054.4	1051.6
125°	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9	1139.0	1141.0	1142.6
127.5°	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1	1220.1	1223.1	1224.8
130°	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0	1271.3	1274.5	1276.0
132.5°	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4	1320.2	1323.0	1324.3
135°	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0	1391.0	1394.0	1395.2
137.5°	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6	1456.5	1459.4	1460.4
140°	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0	1498.7	1501.4	1501.9
142.5°	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2	1537.7	1540.1	1540.6
145°	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0	1592.0	1594.2	1594.5
147.5°	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8	1639.3	1640.9	1641.0
150°	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2	1669.0	1670.8	1670.8
152.5°	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9	1695.7	1697.5	1697.4
155°	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1	1731.9	1733.7	1733.4
157.5°	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7	1762.6	1764.7	1764.5
160°	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4	1780.2	1782.0	1781.9
162.5°	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0	1797.1	1799.0	1798.7
165°	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4
167.5°	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1	1834.2	1836.3	1836.0
170°	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7	1842.8	1844.8	1844.6
172.5°	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1	1849.2	1851.2	1851.0
175°	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1	1856.1	1858.2	1857.8
177.5°	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8	1856.5	1858.2	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	14.4	13.9	14.6	14.1	14.6	13.9	14.4	14.2	14.6	14.3	14.0
90°	34.4	35.0	35.6	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8
92.5°	35.2	35.4	35.8	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6
95°	58.5	58.2	58.0	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2
97.5°	75.9	76.3	76.6	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4
100°	88.0	88.6	89.3	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2
102.5°	93.8	94.5	95.4	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7
105°	98.3	99.5	100.7	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3
107.5°	101.2	102.5	103.7	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8
110°	102.4	103.5	104.7	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	104.2	105.1	106.0	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4
115°	174.3	152.8	131.4	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3
117.5°	660.3	589.7	519.2	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4
120°	938.4	898.1	857.9	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8
122.5°	1043.8	1036.0	1028.2	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2
125°	1143.5	1144.3	1145.3	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9
127.5°	1224.9	1225.1	1225.3	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1
130°	1275.7	1275.4	1275.2	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0
132.5°	1324.0	1323.7	1323.4	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4
135°	1394.6	1394.0	1393.4	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0
137.5°	1459.3	1458.4	1457.4	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6
140°	1500.5	1499.0	1497.5	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0
142.5°	1539.1	1537.6	1536.2	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2
145°	1593.0	1591.5	1590.0	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0
147.5°	1639.7	1638.5	1637.2	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8
150°	1669.4	1667.9	1666.4	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2
152.5°	1695.4	1693.6	1691.6	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9
155°	1731.1	1728.7	1726.3	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1
157.5°	1762.3	1759.9	1757.6	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7
160°	1779.8	1777.6	1775.6	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4
162.5°	1796.2	1793.7	1791.1	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0
165°	1817.3	1815.2	1813.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2
167.5°	1833.3	1830.6	1828.0	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1
170°	1841.9	1839.2	1836.5	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7
172.5°	1848.3	1845.6	1843.0	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1
175°	1854.8	1851.8	1848.9	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1
177.5°	1855.8	1853.7	1851.5	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	14.3	14.0	14.1	13.7	13.2	13.9	13.9	13.8	14.3	15.4	17.1
90°	28.3	26.8	24.4	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3
92.5°	31.9	31.1	29.9	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1
95°	53.7	52.3	50.2	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1
97.5°	71.2	69.9	65.1	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0
100°	78.8	76.4	71.4	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2
102.5°	81.6	78.5	120.9	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0
105°	85.0	81.8	163.1	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6
107.5°	111.1	114.5	212.0	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9
110°	204.8	234.6	320.7	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	483.1	591.7	612.9	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5
115°	689.2	827.1	819.6	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8
117.5°	882.8	916.2	911.0	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6
120°	986.2	982.6	977.2	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4
122.5°	1048.0	1045.8	1040.0	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4
125°	1134.8	1132.7	1127.1	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9
127.5°	1214.1	1211.1	1206.8	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7
130°	1264.7	1261.4	1258.1	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2
132.5°	1314.7	1311.8	1308.5	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8
135°	1385.1	1382.1	1379.4	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6
137.5°	1450.7	1447.7	1444.7	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1
140°	1493.4	1490.6	1487.4	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2
142.5°	1532.8	1530.3	1526.5	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8
145°	1587.9	1585.8	1580.7	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4
147.5°	1636.2	1634.7	1629.7	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2
150°	1665.4	1663.6	1658.8	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5
152.5°	1692.1	1690.4	1685.8	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5
155°	1728.3	1726.5	1723.1	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6
157.5°	1758.7	1756.6	1754.1	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6
160°	1776.6	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8
162.5°	1793.0	1790.9	1789.4	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0
165°	1813.2	1811.0	1810.2	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1
167.5°	1830.0	1828.0	1827.1	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2
170°	1838.6	1836.5	1835.9	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9
172.5°	1845.0	1843.0	1842.4	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3
175°	1852.0	1849.9	1849.4	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6
177.5°	1853.2	1851.5	1851.2	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.8	12.5	12.6	12.7	13.9	14.3	14.2	14.7	15.7	15.5	16.4
90°	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8
92.5°	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6
95°	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2
97.5°	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4
100°	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2
102.5°	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7
105°	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3
107.5°	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8
110°	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0





TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4
115°	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3
117.5°	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4
120°	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8
122.5°	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2
125°	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9
127.5°	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1
130°	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0
132.5°	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4
135°	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0
137.5°	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6
140°	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0
142.5°	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2
145°	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0
147.5°	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8
150°	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2
152.5°	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9
155°	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1
157.5°	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7
160°	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4
162.5°	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0
165°	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2
167.5°	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1
170°	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7
172.5°	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1
175°	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1
177.5°	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	16.1	16.4	16.6	16.7	16.8	17.0	16.5
90°	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331861-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)