

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331789

Luminaire Tested: **S122RDIW-S485D710U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331789
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4695.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17354	17354	17354	17354
5°	19379	17462	15483	17462
10°	21502	17339	13421	17339
15°	22559	17085	10574	17085
20°	19557	16708	9149	16708
25°	12827	16192	8170	16192
30°	8634	15567	7394	15567
35°	6993	14781	6668	14781
40°	6218	13923	6171	13923
45°	5628	12919	5507	12919
50°	5122	11921	5102	11921
55°	4814	10818	4752	10818
60°	4027	9804	3978	9804
65°	3396	8902	3851	8902
70°	3139	7950	3630	7950
75°	2938	6918	3356	6918
80°	2706	5690	2985	5690
85°	2482	4502	2631	4502



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	2.2
10°-20°	283.9	6.0
20°-30°	365.8	7.8
30°-40°	347.6	7.4
40°-50°	297.8	6.3
50°-60°	226.8	4.8
60°-70°	143.4	3.1
70°-80°	71.6	1.5
80°-90°	21.0	0.4
90°-100°	32.3	0.7
100°-110°	118.3	2.5
110°-120°	316.3	6.7
120°-130°	522.2	11.1
130°-140°	555.4	11.8
140°-150°	516.2	11.0
150°-160°	415.0	8.8
160°-170°	267.4	5.7
170°-180°	92.1	2.0
0°-30°	751.6	16.0
0°-40°	1099.2	23.4
0°-60°	1623.8	34.6
0°-90°	1859.8	39.6
90°-120°	467.0	9.9
90°-150°	2060.7	43.9
90°-180°	2835.0	60.4
0°-180°	4695.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1196	1077	955	1077	1196	118
15°	1350	1022	633	1022	1350	364
25°	720	909	459	909	720	342
35°	355	750	338	750	355	227
45°	246	566	241	566	246	191
55°	171	384	169	384	171	150
65°	89	233	101	233	89	90
75°	47	111	54	111	47	50
85°	13	24	14	24	13	15
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	53	213	53	213	53	55
115°	57	402	57	402	57	144
125°	598	569	598	569	598	518
135°	727	704	727	704	727	561
145°	830	817	830	817	830	519
155°	900	900	900	900	900	415
165°	946	948	946	948	946	267
175°	964	970	964	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1118.4	1119.3	1120.2	1118.1	1118.1	1116.3	1112.4	1109.4	1101.0	1099.8	1099.8
5°	1195.7	1195.0	1196.5	1191.6	1184.9	1183.4	1176.3	1167.0	1157.3	1146.4	1144.2
7.5°	1272.7	1271.6	1268.6	1267.7	1262.6	1251.3	1239.9	1227.7	1211.6	1195.8	1187.9
10°	1311.5	1323.8	1316.4	1303.3	1305.9	1288.4	1279.0	1263.0	1249.5	1226.0	1220.8
12.5°	1349.7	1354.6	1352.2	1344.8	1341.5	1329.3	1316.7	1302.7	1277.9	1256.8	1238.4
15°	1349.6	1356.7	1358.6	1356.3	1358.2	1357.4	1350.7	1339.1	1317.5	1294.3	1274.2
17.5°	1250.0	1254.9	1267.1	1275.4	1285.9	1308.0	1318.9	1323.2	1319.9	1306.7	1292.5
20°	1138.2	1130.0	1164.4	1181.9	1196.9	1234.2	1266.3	1278.6	1298.4	1298.1	1294.3
22.5°	979.9	981.8	1014.4	1035.2	1078.9	1116.2	1152.8	1199.2	1237.5	1262.8	1277.6
25°	720.0	734.2	766.7	795.0	843.6	913.1	976.2	1049.4	1118.4	1173.0	1224.9
27.5°	540.7	541.8	567.5	593.8	622.6	679.5	759.0	846.4	944.9	1026.1	1119.6
30°	463.1	460.8	471.7	487.7	512.4	556.4	616.2	702.1	800.3	922.8	1031.8
32.5°	408.1	408.2	416.4	428.3	448.7	478.4	519.4	589.1	682.0	802.4	930.2
35°	354.8	354.4	360.4	369.0	377.5	396.6	424.6	461.2	525.1	637.5	768.2
37.5°	316.5	318.2	321.1	326.5	335.9	346.5	363.4	387.9	433.4	499.9	609.7
40°	295.0	295.8	299.9	304.4	310.0	318.2	332.0	351.8	385.0	438.0	518.3
42.5°	275.3	276.0	279.0	283.1	287.5	295.8	307.2	324.3	351.3	392.6	458.9
45°	246.5	246.5	249.1	250.9	255.8	263.3	272.6	286.8	305.5	336.1	380.2
47.5°	219.4	219.5	221.2	224.4	227.5	233.3	242.5	254.1	267.7	291.4	329.0
50°	203.9	204.3	205.4	208.0	209.9	215.1	222.2	232.3	246.5	264.8	296.1
52.5°	191.3	191.1	192.5	193.7	194.9	198.7	204.0	212.9	225.6	241.5	267.5
55°	171.0	169.5	171.8	173.6	174.8	176.3	179.2	184.9	195.7	209.1	228.5
57.5°	145.6	145.0	146.6	148.3	151.8	155.9	158.4	162.0	167.6	177.2	196.5
60°	124.7	124.7	128.1	129.2	133.3	138.5	143.8	146.8	152.4	158.7	172.9
62.5°	106.2	106.5	108.1	109.2	111.5	117.9	125.3	131.8	137.1	143.2	152.6
65°	88.9	89.6	89.6	90.4	91.9	93.4	96.3	101.6	110.9	119.5	126.6
67.5°	75.4	75.7	75.9	76.6	77.0	78.6	79.8	82.2	84.3	92.5	101.3
70°	66.5	67.6	67.2	68.0	68.3	69.1	70.6	71.7	75.1	76.9	82.2
72.5°	58.1	58.9	58.9	59.3	60.3	60.4	61.6	62.7	64.9	66.5	69.3
75°	47.1	46.7	47.1	47.8	48.2	48.5	48.5	50.0	51.2	52.7	54.5
77.5°	36.3	36.7	36.6	36.7	36.7	37.4	37.3	38.0	39.1	39.9	40.8
80°	29.1	29.5	29.1	29.5	29.9	30.2	29.9	30.2	31.4	32.1	32.1
82.5°	22.6	22.6	22.9	22.9	23.0	23.1	23.6	23.7	24.5	24.3	24.6
85°	13.4	13.1	13.1	13.1	13.4	13.8	13.4	13.4	13.8	13.8	13.8
87.5°	8.6	8.8	8.7	8.7	8.6	8.5	8.3	8.5	8.0	8.2	7.6
90°	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6	14.8	14.0	12.8
92.5°	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1	16.6	16.2	15.6
95°	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9	28.1	27.3	26.2
97.5°	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8	37.2	36.5	34.0
100°	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4	41.1	39.9	37.3
102.5°	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3	42.6	41.0	63.1
105°	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1	44.4	42.7	85.2
107.5°	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3	58.0	59.8	110.7
110°	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4	107.0	122.5	167.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5	252.3	309.0	320.1
115°	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9	359.9	431.9	428.0
117.5°	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6	461.0	478.4	475.7
120°	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9	515.0	513.1	510.3
122.5°	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4	547.3	546.2	543.1
125°	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7	592.6	591.5	588.6
127.5°	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6	634.0	632.4	630.2
130°	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2	660.5	658.8	657.0
132.5°	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0	686.5	685.1	683.4
135°	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9	723.3	721.8	720.4
137.5°	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1	757.6	756.1	754.5
140°	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3	779.9	778.5	776.7
142.5°	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7	800.5	799.2	797.2
145°	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3	829.3	828.2	825.5
147.5°	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3	854.5	853.6	851.0
150°	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6	869.7	868.8	866.3
152.5°	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6	883.7	882.8	880.4
155°	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5	902.6	901.7	899.8
157.5°	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5	918.4	917.3	916.0
160°	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7	927.8	926.9	925.9
162.5°	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4	936.3	935.3	934.5
165°	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8	945.3
167.5°	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8	955.7	954.6	954.2
170°	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3	960.2	959.1	958.8
172.5°	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6	963.5	962.4	962.1
175°	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3	967.2	966.1	965.8
177.5°	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7	967.8	966.9	966.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1100.4	1098.1	1096.0	1090.6	1087.9	1081.9	1081.0	1080.7	1073.0	1065.5	1063.4
5°	1138.2	1132.3	1123.3	1112.8	1102.0	1090.8	1083.3	1077.4	1062.4	1048.2	1040.0
7.5°	1176.3	1163.5	1148.0	1128.2	1111.7	1093.2	1079.5	1067.1	1045.9	1025.6	1011.9
10°	1204.7	1183.8	1163.3	1136.0	1114.7	1093.8	1074.4	1057.6	1033.7	1006.8	987.7
12.5°	1222.3	1199.3	1171.0	1144.4	1116.8	1090.2	1064.2	1042.6	1014.6	986.8	964.1
15°	1246.2	1221.5	1187.2	1149.1	1113.6	1078.9	1049.0	1022.1	985.5	952.3	924.6
17.5°	1265.7	1231.7	1194.8	1150.8	1109.7	1065.6	1027.1	992.7	952.0	911.9	879.4
20°	1271.9	1238.3	1195.7	1151.7	1103.1	1051.2	1009.8	972.4	928.7	885.0	847.7
22.5°	1268.0	1241.9	1194.5	1141.8	1092.1	1037.8	991.0	947.6	899.2	854.6	811.3
25°	1241.7	1232.7	1187.9	1130.4	1073.6	1010.5	956.4	908.9	853.7	805.9	758.8
27.5°	1180.2	1199.6	1171.8	1110.5	1047.4	979.7	918.9	864.9	807.5	753.7	706.8
30°	1121.1	1165.5	1153.5	1096.8	1026.2	959.7	891.4	835.0	773.8	718.5	672.2
32.5°	1040.1	1113.5	1125.2	1077.7	1004.7	931.6	860.0	803.9	740.0	681.7	636.6
35°	911.2	1021.0	1071.4	1041.1	967.9	889.2	815.2	749.9	685.6	628.1	583.3
37.5°	757.4	906.9	991.0	993.1	925.9	844.0	763.5	698.6	632.8	576.4	527.9
40°	657.6	819.7	929.1	953.4	896.6	808.1	726.7	660.6	596.4	541.1	485.5
42.5°	568.0	729.5	864.0	906.2	861.1	773.2	691.5	622.4	559.9	507.6	450.8
45°	459.3	600.5	748.7	824.2	799.2	717.7	631.5	565.8	507.1	461.9	407.4
47.5°	387.5	487.0	630.4	732.5	732.0	657.7	572.9	509.9	455.5	413.2	369.0
50°	346.5	433.2	554.6	670.3	680.0	617.7	537.0	474.6	423.9	379.4	343.9
52.5°	309.8	381.2	490.3	601.3	628.9	574.9	496.7	439.1	389.8	348.9	318.5
55°	261.8	317.0	400.0	503.8	545.6	507.5	438.0	384.3	344.3	310.0	283.8
57.5°	221.4	262.9	329.4	413.0	461.7	437.7	380.5	336.8	302.6	271.5	250.9
60°	196.1	230.0	286.4	356.3	410.0	393.2	344.3	303.6	274.5	247.6	228.2
62.5°	172.2	201.4	249.7	306.4	355.7	348.7	308.8	274.6	249.1	224.6	208.2
65°	138.5	159.8	197.5	242.0	281.6	284.9	256.2	233.0	210.2	190.8	176.3
67.5°	110.3	124.2	150.8	188.2	217.9	228.5	210.9	193.2	175.1	160.1	147.5
70°	93.0	104.2	123.6	153.9	181.1	192.3	182.2	168.4	152.7	140.4	129.6
72.5°	75.4	86.3	100.6	122.8	146.2	158.3	154.8	144.8	132.1	121.9	111.7
75°	56.8	60.1	69.8	84.8	103.1	113.5	116.1	110.9	100.8	93.0	87.0
77.5°	42.0	44.0	48.6	56.5	68.4	77.7	81.6	81.0	74.0	69.5	63.9
80°	33.6	34.7	37.0	40.3	49.3	58.6	61.2	61.2	56.4	54.5	48.9
82.5°	25.5	26.4	27.7	29.6	33.8	41.9	44.8	45.4	42.3	39.9	35.5
85°	14.6	14.2	14.9	16.1	16.8	19.0	23.5	24.3	23.5	20.5	19.4
87.5°	7.4	7.4	7.2	6.6	6.5	6.5	7.7	8.8	8.0	7.4	7.1
90°	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1	14.0	13.8	13.7
95°	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5	40.4	35.2	30.1
97.5°	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3	75.8	61.4	46.9
100°	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9	102.6	81.3	60.0
102.5°	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9	156.4	151.8	147.3
105°	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8	217.5	222.2	226.8
107.5°	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0	275.8	279.6	283.3
110°	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1	313.4	316.7	319.9



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0	348.9	351.8	354.6
115°	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5	405.2	407.8	410.5
117.5°	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1	456.0	459.0	461.9
120°	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0	492.4	494.7	497.0
122.5°	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4	523.9	526.3	528.8
125°	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1	571.2	573.2	575.2
127.5°	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4	614.6	616.9	619.1
130°	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8	642.3	644.8	647.3
132.5°	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9	670.0	672.1	674.2
135°	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3	706.7	709.2	711.7
137.5°	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1	742.8	744.6	746.3
140°	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2	766.4	767.6	768.9
142.5°	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3	786.4	787.6	788.7
145°	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0	816.8	816.7	816.5
147.5°	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5	844.0	843.4	842.8
150°	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5	861.4	860.3	859.2
152.5°	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6	876.4	875.2	873.9
155°	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6	898.2	896.8	895.4
157.5°	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8	915.6	914.4	913.2
160°	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	925.9	925.0	924.1
162.5°	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8	934.9	934.0	933.0
165°	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9	946.9	946.0	945.1
167.5°	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8	955.9	955.0	954.0
170°	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9	960.9	960.0	959.1
172.5°	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2	964.3	963.4	962.4
175°	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6	968.5	967.4	966.3
177.5°	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3	969.4	968.5	967.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1059.5	1057.4	1053.5	1047.6	1044.0	1037.7	1033.5	1035.9	1036.5	1035.9	1035.3
5°	1031.1	1023.2	1012.4	1001.9	992.2	981.8	975.8	973.2	967.9	965.0	963.5
7.5°	996.6	983.1	967.8	949.6	934.1	917.9	909.6	905.5	894.8	889.0	883.9
10°	970.9	949.6	934.3	910.4	895.9	874.6	860.0	860.4	845.8	837.6	831.6
12.5°	942.6	919.2	893.7	872.2	852.0	834.9	817.3	810.2	794.7	786.8	770.7
15°	895.5	868.2	841.4	812.2	791.7	765.2	739.8	708.8	683.8	662.1	656.1
17.5°	844.1	810.4	783.4	749.2	714.0	669.4	640.0	622.0	606.9	595.5	587.0
20°	808.9	774.5	745.8	694.2	646.8	616.5	594.9	581.1	565.4	553.1	546.3
22.5°	771.8	736.0	696.8	639.2	602.3	578.0	558.7	542.8	532.2	522.6	516.5
25°	719.2	680.0	615.4	575.8	546.0	520.6	507.1	497.4	486.2	473.1	467.2
27.5°	663.7	601.3	554.9	525.5	497.0	480.5	468.4	453.9	443.9	438.0	431.8
30°	622.1	559.8	523.6	491.4	471.3	453.0	438.8	430.6	420.9	410.8	406.7
32.5°	575.8	526.0	491.3	464.6	444.1	428.5	417.3	404.0	397.0	390.8	382.2
35°	518.3	480.6	448.9	427.2	407.8	395.1	382.0	374.2	361.5	356.3	352.9
37.5°	469.6	436.9	413.2	390.4	375.0	361.0	353.0	340.5	335.0	327.7	320.6
40°	442.1	410.0	387.3	368.6	351.4	340.9	330.9	320.8	312.6	309.2	300.6
42.5°	414.1	387.9	365.1	344.7	333.2	322.1	309.4	302.0	293.4	288.0	282.7
45°	375.3	352.2	332.7	315.9	303.2	291.7	283.4	271.1	266.3	255.4	250.9
47.5°	341.2	319.7	301.2	285.2	272.8	265.3	253.3	243.6	235.9	229.2	223.5
50°	317.0	299.1	281.2	267.0	255.8	245.0	232.7	227.8	215.8	212.5	209.1
52.5°	294.9	277.9	261.5	247.6	236.4	225.9	215.0	208.7	200.6	197.2	194.8
55°	264.0	247.6	231.9	219.6	208.4	197.5	190.8	183.0	179.2	176.6	173.6
57.5°	232.9	218.2	206.1	193.7	182.4	173.8	166.0	161.3	157.4	154.0	150.4
60°	213.2	199.0	188.2	176.6	165.1	158.0	152.0	146.4	141.9	136.7	135.2
62.5°	192.3	179.9	170.0	158.7	148.6	142.1	136.5	131.2	125.8	118.2	116.1
65°	163.6	153.9	143.4	134.1	125.1	118.8	110.5	104.6	102.3	101.6	101.2
67.5°	137.6	128.4	119.4	109.9	101.7	95.8	91.6	90.7	89.2	88.7	87.7
70°	120.2	111.7	102.7	93.7	85.9	84.8	83.3	81.8	79.9	79.2	78.4
72.5°	104.7	95.8	86.9	79.7	76.3	74.9	73.4	71.9	70.7	69.9	69.5
75°	80.3	72.1	66.1	63.5	61.6	60.5	58.3	57.1	56.4	55.3	54.9
77.5°	57.8	53.2	50.4	48.8	46.8	45.6	44.4	43.2	42.4	42.2	41.6
80°	44.1	41.8	40.0	37.7	37.0	35.5	35.1	34.0	34.4	33.2	33.2
82.5°	34.2	31.4	29.8	28.8	28.0	26.8	26.4	25.9	26.0	25.2	25.2
85°	17.6	16.8	16.1	15.3	15.3	14.2	14.6	14.2	14.2	13.4	13.1
87.5°	7.2	7.2	6.8	7.1	7.3	7.3	7.4	7.3	7.4	7.6	7.4
90°	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1	17.7
92.5°	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1	17.5	17.9	18.2
95°	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9	29.6	30.4	30.7
97.5°	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8	38.4	39.0	39.4
100°	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4	43.6	44.9	45.7
102.5°	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3	45.9	47.5	48.5
105°	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1	47.8	49.5	50.7
107.5°	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3	54.6	52.8	52.3
110°	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4	75.8	60.3	52.8



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5	138.8	82.0	53.9
115°	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9	215.8	143.8	102.2
117.5°	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6	426.1	408.7	381.6
120°	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9	518.7	520.6	511.0
122.5°	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4	549.5	550.7	549.2
125°	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7	594.8	595.9	596.7
127.5°	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6	637.2	638.8	639.6
130°	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2	663.9	665.6	666.4
132.5°	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0	689.5	690.9	691.6
135°	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9	726.4	728.0	728.6
137.5°	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1	760.6	762.2	762.7
140°	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3	782.7	784.1	784.4
142.5°	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7	803.0	804.3	804.5
145°	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3	831.4	832.5	832.7
147.5°	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3	856.1	856.9	857.0
150°	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6	871.6	872.5	872.6
152.5°	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6	885.6	886.5	886.5
155°	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5	904.5	905.4	905.2
157.5°	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5	920.5	921.6	921.5
160°	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7	929.7	930.6	930.5
162.5°	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4	938.4	939.5	939.4
165°	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0	949.0	950.1	950.1
167.5°	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8	957.9	958.9	958.8
170°	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3	962.3	963.4	963.3
172.5°	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6	965.7	966.8	966.6
175°	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3	969.3	970.4	970.2
177.5°	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7	969.5	970.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1032.0	1032.6	1031.7	1032.3	1031.7	1032.6	1032.0	1035.3	1035.9	1036.5	1035.9
5°	961.6	957.1	956.4	955.3	956.4	957.1	961.6	963.5	965.0	967.9	973.2
7.5°	877.5	876.8	875.0	872.3	875.0	876.8	877.5	883.9	889.0	894.8	905.5
10°	823.4	821.6	821.2	818.6	821.2	821.6	823.4	831.6	837.6	845.8	860.4
12.5°	760.1	748.1	746.8	740.3	746.8	748.1	760.1	770.7	786.8	794.7	810.2
15°	647.2	644.9	637.5	632.6	637.5	644.9	647.2	656.1	662.1	683.8	708.8
17.5°	582.6	575.3	573.0	572.0	573.0	575.3	582.6	587.0	595.5	606.9	622.0
20°	541.1	534.4	533.3	532.5	533.3	534.4	541.1	546.3	553.1	565.4	581.1
22.5°	512.4	505.4	502.5	500.3	502.5	505.4	512.4	516.5	522.6	532.2	542.8
25°	463.4	460.8	459.3	458.6	459.3	460.8	463.4	467.2	473.1	486.2	497.4
27.5°	425.1	419.4	418.2	416.3	418.2	419.4	425.1	431.8	438.0	443.9	453.9
30°	403.3	401.4	398.8	396.6	398.8	401.4	403.3	406.7	410.8	420.9	430.6
32.5°	377.6	376.1	373.7	372.7	373.7	376.1	377.6	382.2	390.8	397.0	404.0
35°	349.2	343.9	341.7	338.3	341.7	343.9	349.2	352.9	356.3	361.5	374.2
37.5°	319.1	316.3	313.2	314.3	313.2	316.3	319.1	320.6	327.7	335.0	340.5
40°	295.8	293.9	293.1	292.8	293.1	293.9	295.8	300.6	309.2	312.6	320.8
42.5°	277.2	272.1	270.1	270.1	270.1	272.1	277.2	282.7	288.0	293.4	302.0
45°	249.1	244.2	240.9	241.2	240.9	244.2	249.1	250.9	255.4	266.3	271.1
47.5°	220.3	220.1	218.0	218.7	218.0	220.1	220.3	223.5	229.2	235.9	243.6
50°	206.5	204.3	202.8	203.1	202.8	204.3	206.5	209.1	212.5	215.8	227.8
52.5°	193.4	191.4	190.2	191.8	190.2	191.4	193.4	194.8	197.2	200.6	208.7
55°	171.8	169.5	169.2	168.8	169.2	169.5	171.8	173.6	176.6	179.2	183.0
57.5°	147.7	146.2	143.9	143.0	143.9	146.2	147.7	150.4	154.0	157.4	161.3
60°	130.3	127.3	123.6	123.2	123.6	127.3	130.3	135.2	136.7	141.9	146.4
62.5°	114.5	113.9	113.2	113.1	113.2	113.9	114.5	116.1	118.2	125.8	131.2
65°	100.5	100.1	100.5	100.8	100.5	100.1	100.5	101.2	101.6	102.3	104.6
67.5°	87.5	86.9	86.2	86.5	86.2	86.9	87.5	87.7	88.7	89.2	90.7
70°	77.7	77.3	76.9	76.9	76.9	77.3	77.7	78.4	79.2	79.9	81.8
72.5°	68.1	68.0	67.7	67.4	67.7	68.0	68.1	69.5	69.9	70.7	71.9
75°	54.5	53.8	53.8	53.8	53.8	53.8	54.5	54.9	55.3	56.4	57.1
77.5°	41.5	41.2	40.8	40.5	40.8	41.2	41.5	41.6	42.2	42.4	43.2
80°	32.9	32.5	32.1	32.1	32.1	32.5	32.9	33.2	33.2	34.4	34.0
82.5°	25.1	24.7	24.6	24.3	24.6	24.7	25.1	25.2	25.2	26.0	25.9
85°	13.4	13.8	13.4	14.2	13.4	13.8	13.4	13.1	13.4	14.2	14.2
87.5°	7.5	7.2	7.6	7.4	7.6	7.2	7.5	7.4	7.6	7.4	7.3
90°	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6
92.5°	18.3	18.5	18.7	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1
95°	30.6	30.4	30.3	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9
97.5°	39.6	39.8	40.0	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8
100°	46.0	46.3	46.6	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4
102.5°	49.0	49.4	49.8	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3
105°	51.3	52.0	52.6	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1
107.5°	52.9	53.5	54.1	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3
110°	53.4	54.1	54.7	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.4	54.9	55.4	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5
115°	91.0	79.8	68.6	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9
117.5°	344.8	308.0	271.2	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6
120°	490.0	469.0	448.0	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9
122.5°	545.1	541.0	537.0	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4
125°	597.1	597.6	598.1	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7
127.5°	639.7	639.8	639.9	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6
130°	666.2	666.1	665.9	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2
132.5°	691.4	691.3	691.1	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0
135°	728.3	728.0	727.7	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9
137.5°	762.1	761.6	761.1	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1
140°	783.6	782.8	782.0	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3
142.5°	803.8	803.0	802.2	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7
145°	831.9	831.1	830.3	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3
147.5°	856.3	855.7	855.0	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3
150°	871.8	871.0	870.2	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6
152.5°	885.4	884.4	883.4	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6
155°	904.0	902.8	901.5	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5
157.5°	920.3	919.1	917.9	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5
160°	929.4	928.3	927.3	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7
162.5°	938.0	936.7	935.3	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4
165°	949.0	948.0	946.9	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0
167.5°	957.4	956.0	954.6	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8
170°	961.9	960.5	959.1	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3
172.5°	965.2	963.8	962.4	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6
175°	968.6	967.1	965.5	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3
177.5°	969.2	968.0	966.9	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1033.5	1037.7	1044.0	1047.6	1053.5	1057.4	1059.5	1063.4	1065.5	1073.0	1080.7
5°	975.8	981.8	992.2	1001.9	1012.4	1023.2	1031.1	1040.0	1048.2	1062.4	1077.4
7.5°	909.6	917.9	934.1	949.6	967.8	983.1	996.6	1011.9	1025.6	1045.9	1067.1
10°	860.0	874.6	895.9	910.4	934.3	949.6	970.9	987.7	1006.8	1033.7	1057.6
12.5°	817.3	834.9	852.0	872.2	893.7	919.2	942.6	964.1	986.8	1014.6	1042.6
15°	739.8	765.2	791.7	812.2	841.4	868.2	895.5	924.6	952.3	985.5	1022.1
17.5°	640.0	669.4	714.0	749.2	783.4	810.4	844.1	879.4	911.9	952.0	992.7
20°	594.9	616.5	646.8	694.2	745.8	774.5	808.9	847.7	885.0	928.7	972.4
22.5°	558.7	578.0	602.3	639.2	696.8	736.0	771.8	811.3	854.6	899.2	947.6
25°	507.1	520.6	546.0	575.8	615.4	680.0	719.2	758.8	805.9	853.7	908.9
27.5°	468.4	480.5	497.0	525.5	554.9	601.3	663.7	706.8	753.7	807.5	864.9
30°	438.8	453.0	471.3	491.4	523.6	559.8	622.1	672.2	718.5	773.8	835.0
32.5°	417.3	428.5	444.1	464.6	491.3	526.0	575.8	636.6	681.7	740.0	803.9
35°	382.0	395.1	407.8	427.2	448.9	480.6	518.3	583.3	628.1	685.6	749.9
37.5°	353.0	361.0	375.0	390.4	413.2	436.9	469.6	527.9	576.4	632.8	698.6
40°	330.9	340.9	351.4	368.6	387.3	410.0	442.1	485.5	541.1	596.4	660.6
42.5°	309.4	322.1	333.2	344.7	365.1	387.9	414.1	450.8	507.6	559.9	622.4
45°	283.4	291.7	303.2	315.9	332.7	352.2	375.3	407.4	461.9	507.1	565.8
47.5°	253.3	265.3	272.8	285.2	301.2	319.7	341.2	369.0	413.2	455.5	509.9
50°	232.7	245.0	255.8	267.0	281.2	299.1	317.0	343.9	379.4	423.9	474.6
52.5°	215.0	225.9	236.4	247.6	261.5	277.9	294.9	318.5	348.9	389.8	439.1
55°	190.8	197.5	208.4	219.6	231.9	247.6	264.0	283.8	310.0	344.3	384.3
57.5°	166.0	173.8	182.4	193.7	206.1	218.2	232.9	250.9	271.5	302.6	336.8
60°	152.0	158.0	165.1	176.6	188.2	199.0	213.2	228.2	247.6	274.5	303.6
62.5°	136.5	142.1	148.6	158.7	170.0	179.9	192.3	208.2	224.6	249.1	274.6
65°	110.5	118.8	125.1	134.1	143.4	153.9	163.6	176.3	190.8	210.2	233.0
67.5°	91.6	95.8	101.7	109.9	119.4	128.4	137.6	147.5	160.1	175.1	193.2
70°	83.3	84.8	85.9	93.7	102.7	111.7	120.2	129.6	140.4	152.7	168.4
72.5°	73.4	74.9	76.3	79.7	86.9	95.8	104.7	111.7	121.9	132.1	144.8
75°	58.3	60.5	61.6	63.5	66.1	72.1	80.3	87.0	93.0	100.8	110.9
77.5°	44.4	45.6	46.8	48.8	50.4	53.2	57.8	63.9	69.5	74.0	81.0
80°	35.1	35.5	37.0	37.7	40.0	41.8	44.1	48.9	54.5	56.4	61.2
82.5°	26.4	26.8	28.0	28.8	29.8	31.4	34.2	35.5	39.9	42.3	45.4
85°	14.6	14.2	15.3	15.3	16.1	16.8	17.6	19.4	20.5	23.5	24.3
87.5°	7.4	7.3	7.3	7.1	6.8	7.2	7.2	7.1	7.4	8.0	8.8
90°	14.8	14.0	12.8	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7
92.5°	16.6	16.2	15.6	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1
95°	28.1	27.3	26.2	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5
97.5°	37.2	36.5	34.0	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3
100°	41.1	39.9	37.3	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9
102.5°	42.6	41.0	63.1	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9
105°	44.4	42.7	85.2	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8
107.5°	58.0	59.8	110.7	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0
110°	107.0	122.5	167.5	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	252.3	309.0	320.1	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0
115°	359.9	431.9	428.0	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5
117.5°	461.0	478.4	475.7	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1
120°	515.0	513.1	510.3	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0
122.5°	547.3	546.2	543.1	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4
125°	592.6	591.5	588.6	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1
127.5°	634.0	632.4	630.2	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4
130°	660.5	658.8	657.0	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8
132.5°	686.5	685.1	683.4	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9
135°	723.3	721.8	720.4	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3
137.5°	757.6	756.1	754.5	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1
140°	779.9	778.5	776.7	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2
142.5°	800.5	799.2	797.2	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3
145°	829.3	828.2	825.5	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0
147.5°	854.5	853.6	851.0	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5
150°	869.7	868.8	866.3	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5
152.5°	883.7	882.8	880.4	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6
155°	902.6	901.7	899.8	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6
157.5°	918.4	917.3	916.0	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8
160°	927.8	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9
162.5°	936.3	935.3	934.5	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8
165°	946.9	945.8	945.3	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9
167.5°	955.7	954.6	954.2	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8
170°	960.2	959.1	958.8	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9
172.5°	963.5	962.4	962.1	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2
175°	967.2	966.1	965.8	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6
177.5°	967.8	966.9	966.8	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1081.0	1081.9	1087.9	1090.6	1096.0	1098.1	1100.4	1099.8	1099.8	1101.0	1109.4
5°	1083.3	1090.8	1102.0	1112.8	1123.3	1132.3	1138.2	1144.2	1146.4	1157.3	1167.0
7.5°	1079.5	1093.2	1111.7	1128.2	1148.0	1163.5	1176.3	1187.9	1195.8	1211.6	1227.7
10°	1074.4	1093.8	1114.7	1136.0	1163.3	1183.8	1204.7	1220.8	1226.0	1249.5	1263.0
12.5°	1064.2	1090.2	1116.8	1144.4	1171.0	1199.3	1222.3	1238.4	1256.8	1277.9	1302.7
15°	1049.0	1078.9	1113.6	1149.1	1187.2	1221.5	1246.2	1274.2	1294.3	1317.5	1339.1
17.5°	1027.1	1065.6	1109.7	1150.8	1194.8	1231.7	1265.7	1292.5	1306.7	1319.9	1323.2
20°	1009.8	1051.2	1103.1	1151.7	1195.7	1238.3	1271.9	1294.3	1298.1	1298.4	1278.6
22.5°	991.0	1037.8	1092.1	1141.8	1194.5	1241.9	1268.0	1277.6	1262.8	1237.5	1199.2
25°	956.4	1010.5	1073.6	1130.4	1187.9	1232.7	1241.7	1224.9	1173.0	1118.4	1049.4
27.5°	918.9	979.7	1047.4	1110.5	1171.8	1199.6	1180.2	1119.6	1026.1	944.9	846.4
30°	891.4	959.7	1026.2	1096.8	1153.5	1165.5	1121.1	1031.8	922.8	800.3	702.1
32.5°	860.0	931.6	1004.7	1077.7	1125.2	1113.5	1040.1	930.2	802.4	682.0	589.1
35°	815.2	889.2	967.9	1041.1	1071.4	1021.0	911.2	768.2	637.5	525.1	461.2
37.5°	763.5	844.0	925.9	993.1	991.0	906.9	757.4	609.7	499.9	433.4	387.9
40°	726.7	808.1	896.6	953.4	929.1	819.7	657.6	518.3	438.0	385.0	351.8
42.5°	691.5	773.2	861.1	906.2	864.0	729.5	568.0	458.9	392.6	351.3	324.3
45°	631.5	717.7	799.2	824.2	748.7	600.5	459.3	380.2	336.1	305.5	286.8
47.5°	572.9	657.7	732.0	732.5	630.4	487.0	387.5	329.0	291.4	267.7	254.1
50°	537.0	617.7	680.0	670.3	554.6	433.2	346.5	296.1	264.8	246.5	232.3
52.5°	496.7	574.9	628.9	601.3	490.3	381.2	309.8	267.5	241.5	225.6	212.9
55°	438.0	507.5	545.6	503.8	400.0	317.0	261.8	228.5	209.1	195.7	184.9
57.5°	380.5	437.7	461.7	413.0	329.4	262.9	221.4	196.5	177.2	167.6	162.0
60°	344.3	393.2	410.0	356.3	286.4	230.0	196.1	172.9	158.7	152.4	146.8
62.5°	308.8	348.7	355.7	306.4	249.7	201.4	172.2	152.6	143.2	137.1	131.8
65°	256.2	284.9	281.6	242.0	197.5	159.8	138.5	126.6	119.5	110.9	101.6
67.5°	210.9	228.5	217.9	188.2	150.8	124.2	110.3	101.3	92.5	84.3	82.2
70°	182.2	192.3	181.1	153.9	123.6	104.2	93.0	82.2	76.9	75.1	71.7
72.5°	154.8	158.3	146.2	122.8	100.6	86.3	75.4	69.3	66.5	64.9	62.7
75°	116.1	113.5	103.1	84.8	69.8	60.1	56.8	54.5	52.7	51.2	50.0
77.5°	81.6	77.7	68.4	56.5	48.6	44.0	42.0	40.8	39.9	39.1	38.0
80°	61.2	58.6	49.3	40.3	37.0	34.7	33.6	32.1	32.1	31.4	30.2
82.5°	44.8	41.9	33.8	29.6	27.7	26.4	25.5	24.6	24.3	24.5	23.7
85°	23.5	19.0	16.8	16.1	14.9	14.2	14.6	13.8	13.8	13.8	13.4
87.5°	7.7	6.5	6.5	6.6	7.2	7.4	7.4	7.6	8.2	8.0	8.5
90°	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6
92.5°	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1
95°	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9
97.5°	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8
100°	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4
102.5°	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3
105°	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1
107.5°	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3
110°	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5
115°	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9
117.5°	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6
120°	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9
122.5°	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4
125°	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7
127.5°	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6
130°	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2
132.5°	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0
135°	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9
137.5°	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1
140°	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3
142.5°	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7
145°	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3
147.5°	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3
150°	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6
152.5°	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6
155°	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5
157.5°	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5
160°	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7
162.5°	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4
165°	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0
167.5°	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8
170°	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3
172.5°	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6
175°	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3
177.5°	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1112.4	1116.3	1118.1	1118.1	1120.2	1119.3	1118.4
5°	1176.3	1183.4	1184.9	1191.6	1196.5	1195.0	1195.7
7.5°	1239.9	1251.3	1262.6	1267.7	1268.6	1271.6	1272.7
10°	1279.0	1288.4	1305.9	1303.3	1316.4	1323.8	1311.5
12.5°	1316.7	1329.3	1341.5	1344.8	1352.2	1354.6	1349.7
15°	1350.7	1357.4	1358.2	1356.3	1358.6	1356.7	1349.6
17.5°	1318.9	1308.0	1285.9	1275.4	1267.1	1254.9	1250.0
20°	1266.3	1234.2	1196.9	1181.9	1164.4	1130.0	1138.2
22.5°	1152.8	1116.2	1078.9	1035.2	1014.4	981.8	979.9
25°	976.2	913.1	843.6	795.0	766.7	734.2	720.0
27.5°	759.0	679.5	622.6	593.8	567.5	541.8	540.7
30°	616.2	556.4	512.4	487.7	471.7	460.8	463.1
32.5°	519.4	478.4	448.7	428.3	416.4	408.2	408.1
35°	424.6	396.6	377.5	369.0	360.4	354.4	354.8
37.5°	363.4	346.5	335.9	326.5	321.1	318.2	316.5
40°	332.0	318.2	310.0	304.4	299.9	295.8	295.0
42.5°	307.2	295.8	287.5	283.1	279.0	276.0	275.3
45°	272.6	263.3	255.8	250.9	249.1	246.5	246.5
47.5°	242.5	233.3	227.5	224.4	221.2	219.5	219.4
50°	222.2	215.1	209.9	208.0	205.4	204.3	203.9
52.5°	204.0	198.7	194.9	193.7	192.5	191.1	191.3
55°	179.2	176.3	174.8	173.6	171.8	169.5	171.0
57.5°	158.4	155.9	151.8	148.3	146.6	145.0	145.6
60°	143.8	138.5	133.3	129.2	128.1	124.7	124.7
62.5°	125.3	117.9	111.5	109.2	108.1	106.5	106.2
65°	96.3	93.4	91.9	90.4	89.6	89.6	88.9
67.5°	79.8	78.6	77.0	76.6	75.9	75.7	75.4
70°	70.6	69.1	68.3	68.0	67.2	67.6	66.5
72.5°	61.6	60.4	60.3	59.3	58.9	58.9	58.1
75°	48.5	48.5	48.2	47.8	47.1	46.7	47.1
77.5°	37.3	37.4	36.7	36.7	36.6	36.7	36.3
80°	29.9	30.2	29.9	29.5	29.1	29.5	29.1
82.5°	23.6	23.1	23.0	22.9	22.9	22.6	22.6
85°	13.4	13.8	13.4	13.1	13.1	13.1	13.4
87.5°	8.3	8.5	8.6	8.7	8.7	8.8	8.6
90°	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331789

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)