

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331849-830

Luminaire Tested: **S122RDIW-S1005D710U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331849-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6267.1 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	3.1
10°-20°	549.1	8.8
20°-30°	707.5	11.3
30°-40°	672.4	10.7
40°-50°	576.0	9.2
50°-60°	438.6	7.0
60°-70°	277.3	4.4
70°-80°	138.5	2.2
80°-90°	38.3	0.6
90°-100°	30.4	0.5
100°-110°	111.6	1.8
110°-120°	298.2	4.8
120°-130°	492.2	7.9
130°-140°	523.5	8.4
140°-150°	486.5	7.8
150°-160°	391.2	6.2
160°-170°	252.1	4.0
170°-180°	86.8	1.4
0°-30°	1453.7	23.2
0°-40°	2126.0	33.9
0°-60°	3140.7	50.1
0°-90°	3594.7	57.4
90°-120°	440.1	7.0
90°-150°	1942.3	31.0
90°-180°	2672.0	42.6
0°-180°	6267.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	28
90°	18	1	18	1	18	9
95°	28	43	28	43	28	26
105°	50	201	50	201	50	52
115°	54	379	54	379	54	136
125°	564	536	564	536	564	488
135°	686	664	686	664	686	528
145°	782	770	782	770	782	489
155°	849	848	849	848	849	392
165°	892	893	892	893	892	252
175°	909	914	909	914	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	12.8	13.3	13.3	13.2	13.2	13.0	12.9	13.3	12.6	13.0	12.3
90°	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7	13.9	13.2	12.1
92.5°	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1	15.6	15.3	14.7
95°	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2	26.5	25.7	24.7
97.5°	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6	35.1	34.4	32.0
100°	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0	38.7	37.6	35.2
102.5°	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8	40.2	38.6	35.5
105°	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5	41.8	40.2	38.3
107.5°	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1	54.7	56.4	104.3
110°	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1	100.9	115.5	157.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3	237.8	291.2	301.7
115°	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4	339.2	407.1	403.4
117.5°	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1	434.5	450.9	448.4
120°	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2	485.4	483.6	481.0
122.5°	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9	515.9	514.8	511.9
125°	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6	558.6	557.5	554.8
127.5°	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1	597.6	596.1	594.0
130°	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2	622.5	620.9	619.3
132.5°	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5	647.1	645.7	644.1
135°	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2	681.7	680.3	679.0
137.5°	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5	714.1	712.7	711.1
140°	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4	735.1	733.8	732.1
142.5°	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6	754.5	753.3	751.4
145°	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6	781.7	780.6	778.1
147.5°	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2	805.4	804.6	802.1
150°	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6	819.7	818.9	816.5
152.5°	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8	832.9	832.1	829.8
155°	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6	850.7	849.9	848.1
157.5°	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7	865.6	864.6	863.4
160°	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3	874.5	873.6	872.7
162.5°	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5	882.5	881.6	880.8
165°	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5	891.0
167.5°	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8	900.8	899.8	899.4
170°	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1	905.0	904.0	903.7
172.5°	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2	908.1	907.1	906.8
175°	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7	911.6	910.6	910.3
177.5°	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0	912.2	911.3	911.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	12.0	12.3	12.1	11.2	11.5	11.8	14.3	16.9	14.9	13.5	12.6
90°	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7	2.3	3.9	5.5
92.5°	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3	13.2	13.0	12.9
95°	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9	38.1	33.2	28.4
97.5°	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1	71.4	57.9	44.2
100°	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8	96.7	76.6	56.6
102.5°	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7	147.4	143.1	138.8
105°	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6	205.0	209.4	213.8
107.5°	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4	260.0	263.5	267.0
110°	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3	295.4	298.5	301.5



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1	328.9	331.6	334.2
115°	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4	381.9	384.4	386.9
117.5°	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1	429.8	432.6	435.4
120°	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8	464.1	466.3	468.4
122.5°	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4	493.8	496.1	498.4
125°	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4	538.4	540.3	542.2
127.5°	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2	579.3	581.5	583.5
130°	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0	605.4	607.8	610.1
132.5°	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5	631.5	633.5	635.5
135°	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8	666.1	668.5	670.8
137.5°	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5	700.1	701.8	703.4
140°	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2	722.4	723.5	724.7
142.5°	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2	741.2	742.3	743.4
145°	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1	769.9	769.8	769.6
147.5°	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0	795.5	794.9	794.4
150°	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9	811.9	810.9	809.8
152.5°	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2	826.0	824.9	823.7
155°	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9	846.6	845.3	844.0
157.5°	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1	863.0	861.9	860.7
160°	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	872.7	871.9	871.0
162.5°	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0	881.2	880.3	879.4
165°	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4	892.5	891.6	890.8
167.5°	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8	901.0	900.1	899.2
170°	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6	905.7	904.8	904.0
172.5°	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7	908.9	908.0	907.1
175°	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9	912.9	911.8	910.8
177.5°	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5	913.7	912.9	912.1
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	12.4	12.1	11.2	11.4	11.7	11.3	11.5	11.0	11.1	11.3	10.8
90°	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7	15.4	16.1	16.7
92.5°	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1	16.5	16.9	17.2
95°	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2	27.9	28.7	28.9
97.5°	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6	36.2	36.8	37.1
100°	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0	41.1	42.3	43.1
102.5°	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8	43.3	44.8	45.7
105°	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5	45.1	46.7	47.8
107.5°	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1	51.5	49.8	49.3
110°	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1	71.4	56.8	49.8



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3	130.8	77.3	50.8
115°	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4	203.4	135.5	96.3
117.5°	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1	401.6	385.2	359.7
120°	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2	488.9	490.7	481.6
122.5°	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9	517.9	519.1	517.6
125°	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6	560.6	561.7	562.4
127.5°	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1	600.6	602.1	602.9
130°	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2	625.8	627.4	628.1
132.5°	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5	649.9	651.2	651.9
135°	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2	684.7	686.2	686.7
137.5°	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5	716.9	718.4	718.9
140°	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4	737.7	739.0	739.3
142.5°	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6	756.9	758.1	758.3
145°	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6	783.6	784.7	784.9
147.5°	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2	806.9	807.7	807.8
150°	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6	821.5	822.4	822.5
152.5°	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8	834.7	835.6	835.6
155°	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6	852.5	853.4	853.2
157.5°	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7	867.6	868.6	868.6
160°	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3	876.3	877.1	877.0
162.5°	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5	884.5	885.5	885.4
165°	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5	894.5	895.5	895.5
167.5°	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8	902.9	903.8	903.7
170°	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1	907.0	908.0	908.0
172.5°	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2	910.2	911.3	911.1
175°	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7	913.6	914.6	914.5
177.5°	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0	913.8	914.6	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	10.9	10.4	11.0	10.5	11.0	10.4	10.9	10.8	11.3	11.1	11.0
90°	17.0	17.2	17.5	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7
92.5°	17.2	17.4	17.6	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1
95°	28.8	28.7	28.6	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6
100°	43.4	43.6	43.9	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0
102.5°	46.2	46.6	46.9	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8
105°	48.4	49.0	49.6	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5
107.5°	49.9	50.4	51.0	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1
110°	50.3	51.0	51.6	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	51.3	51.7	52.2	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3
115°	85.8	75.2	64.7	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4
117.5°	325.0	290.3	255.6	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1
120°	461.8	442.1	422.3	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2
122.5°	513.8	509.9	506.1	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9
125°	562.8	563.3	563.7	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6
127.5°	602.9	603.0	603.1	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1
130°	627.9	627.8	627.6	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2
132.5°	651.7	651.6	651.4	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5
135°	686.5	686.2	685.9	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2
137.5°	718.3	717.8	717.4	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5
140°	738.6	737.8	737.1	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4
142.5°	757.6	756.9	756.1	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6
145°	784.1	783.3	782.6	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6
147.5°	807.1	806.5	805.9	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2
150°	821.7	821.0	820.2	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6
152.5°	834.5	833.6	832.6	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8
155°	852.1	850.9	849.7	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6
157.5°	867.4	866.3	865.2	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7
160°	876.0	875.0	874.0	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3
162.5°	884.1	882.9	881.6	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5
165°	894.5	893.5	892.5	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5
167.5°	902.4	901.1	899.8	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8
170°	906.6	905.3	904.0	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1
172.5°	909.7	908.4	907.1	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2
175°	912.9	911.5	910.0	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7
177.5°	913.5	912.4	911.3	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	11.5	11.3	11.7	11.4	11.2	12.1	12.4	12.6	13.5	14.9	16.9
90°	13.9	13.2	12.1	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7
92.5°	15.6	15.3	14.7	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3
95°	26.5	25.7	24.7	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9
97.5°	35.1	34.4	32.0	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1
100°	38.7	37.6	35.2	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8
102.5°	40.2	38.6	59.5	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7
105°	41.8	40.2	80.3	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6
107.5°	54.7	56.4	104.3	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4
110°	100.9	115.5	157.9	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	237.8	291.2	301.7	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1
115°	339.2	407.1	403.4	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4
117.5°	434.5	450.9	448.4	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1
120°	485.4	483.6	481.0	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8
122.5°	515.9	514.8	511.9	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4
125°	558.6	557.5	554.8	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4
127.5°	597.6	596.1	594.0	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2
130°	622.5	620.9	619.3	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0
132.5°	647.1	645.7	644.1	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5
135°	681.7	680.3	679.0	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8
137.5°	714.1	712.7	711.1	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5
140°	735.1	733.8	732.1	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2
142.5°	754.5	753.3	751.4	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2
145°	781.7	780.6	778.1	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1
147.5°	805.4	804.6	802.1	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0
150°	819.7	818.9	816.5	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9
152.5°	832.9	832.1	829.8	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2
155°	850.7	849.9	848.1	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9
157.5°	865.6	864.6	863.4	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1
160°	874.5	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6
162.5°	882.5	881.6	880.8	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0
165°	892.5	891.5	891.0	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4
167.5°	900.8	899.8	899.4	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8
170°	905.0	904.0	903.7	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6
172.5°	908.1	907.1	906.8	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7
175°	911.6	910.6	910.3	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9
177.5°	912.2	911.3	911.3	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.3	11.8	11.5	11.2	12.1	12.3	12.0	12.3	13.0	12.6	13.3
90°	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7
92.5°	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1
95°	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2
97.5°	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6
100°	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0
102.5°	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8
105°	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5
107.5°	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1
110°	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3
115°	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4
117.5°	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1
120°	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2
122.5°	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9
125°	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6
127.5°	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1
130°	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2
132.5°	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5
135°	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2
137.5°	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5
140°	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4
142.5°	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6
145°	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6
147.5°	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2
150°	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6
152.5°	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8
155°	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6
157.5°	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7
160°	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3
162.5°	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5
165°	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5
167.5°	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8
170°	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1
172.5°	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2
175°	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7
177.5°	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	12.9	13.0	13.2	13.2	13.3	13.3	12.8
90°	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331849-830

CATALOG NUMBER: S122RDIW-S1005D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)