

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331792

Luminaire Tested: **S122RDIW-S485D710U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331792
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4159.6 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41								
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35								
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30								
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26								
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23								
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20								
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18								
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16								
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14								
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13								
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	1.9
10°-20°	212.1	5.1
20°-30°	297.8	7.2
30°-40°	324.8	7.8
40°-50°	298.6	7.2
50°-60°	234.5	5.6
60°-70°	152.9	3.7
70°-80°	78.8	1.9
80°-90°	24.0	0.6
90°-100°	55.7	1.3
100°-110°	173.1	4.2
110°-120°	295.8	7.1
120°-130°	389.0	9.4
130°-140°	436.6	10.5
140°-150°	428.1	10.3
150°-160°	359.1	8.6
160°-170°	238.2	5.7
170°-180°	83.2	2.0
0°-30°	587.2	14.1
0°-40°	912.0	21.9
0°-60°	1445.1	34.7
0°-90°	1700.9	40.9
90°-120°	524.6	12.6
90°-150°	1778.3	42.8
90°-180°	2459.0	59.1
0°-180°	4159.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	1	10	26	25	25	3
95°	39	46	48	47	46	44
105°	160	162	163	165	165	168
115°	297	301	300	299	297	294
125°	432	438	436	434	433	386
135°	559	567	568	568	565	431
145°	678	683	688	688	686	424
155°	775	778	780	783	781	357
165°	844	843	843	848	844	238
175°	878	876	874	879	875	83
180°	879	879	879	879	879	



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.7	9.0	8.4	7.7	7.0	7.1	7.8	8.5	9.2	10.0	9.8
90°	0.7	2.7	4.7	6.7	8.7	11.5	15.1	18.7	22.3	26.0	25.6
92.5°	13.2	14.7	16.1	17.6	19.0	20.2	21.0	21.9	22.7	23.6	23.7
95°	38.6	40.2	41.9	43.5	45.2	46.2	46.5	46.8	47.2	47.5	47.5
97.5°	70.5	71.9	73.4	74.8	76.3	77.3	78.0	78.6	79.2	79.8	79.8
100°	94.2	95.6	96.9	98.2	99.5	100.4	100.9	101.4	101.9	102.4	102.4
102.5°	119.2	120.2	121.3	122.3	123.4	124.2	124.9	125.5	126.1	126.7	126.9
105°	159.5	160.0	160.5	161.0	161.5	161.9	162.3	162.6	162.9	163.3	163.6
107.5°	200.2	200.9	201.7	202.4	203.1	203.5	203.5	203.5	203.5	203.5	203.6
110°	226.3	227.3	228.3	229.3	230.3	230.8	230.8	230.8	230.8	230.8	230.8



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.8	255.8	256.8	257.8	258.8	259.2	259.1	258.9	258.8	258.7	258.3
115°	296.8	297.8	298.8	299.8	300.8	301.1	300.8	300.4	300.1	299.8	299.6
117.5°	338.7	340.0	341.3	342.6	343.9	344.1	343.2	342.3	341.4	340.5	340.1
120°	366.6	367.9	369.2	370.5	371.8	371.8	370.5	369.2	367.9	366.6	366.6
122.5°	392.1	393.7	395.3	396.8	398.4	398.8	397.8	396.9	396.0	395.1	394.7
125°	431.9	433.4	434.8	436.3	437.8	438.3	437.8	437.3	436.8	436.3	435.8
127.5°	470.6	472.5	474.4	476.2	478.1	478.8	478.2	477.6	477.0	476.4	475.8
130°	494.9	497.1	499.2	501.4	503.5	504.4	504.1	503.8	503.4	503.1	502.8
132.5°	522.3	524.0	525.8	527.5	529.2	530.2	530.2	530.3	530.4	530.4	529.7
135°	558.8	560.6	562.4	564.2	566.0	567.1	567.4	567.8	568.1	568.4	568.2
137.5°	597.2	598.7	600.2	601.7	603.1	604.1	604.5	605.0	605.4	605.8	605.7
140°	620.4	621.8	623.3	624.8	626.3	627.4	628.3	629.1	629.9	630.7	630.7
142.5°	644.1	645.6	647.1	648.6	650.0	651.1	651.6	652.2	652.7	653.3	653.4
145°	678.2	679.4	680.5	681.7	682.9	683.9	684.9	685.9	686.9	687.9	688.0
147.5°	708.7	710.0	711.4	712.8	714.2	715.2	715.9	716.5	717.2	717.9	718.2
150°	729.4	730.4	731.4	732.4	733.4	734.2	734.9	735.5	736.2	736.9	737.4
152.5°	747.8	748.8	749.8	750.8	751.8	752.7	753.5	754.3	755.1	755.9	756.5
155°	775.4	775.9	776.4	776.9	777.4	777.9	778.4	778.9	779.4	779.9	780.7
157.5°	799.0	799.4	799.7	800.0	800.4	800.7	801.0	801.3	801.6	801.9	803.0
160°	813.3	813.6	813.9	814.3	814.6	814.9	815.0	815.2	815.3	815.5	816.5
162.5°	826.3	826.4	826.5	826.5	826.6	826.7	826.9	827.1	827.2	827.4	828.5
165°	843.7	843.5	843.4	843.2	843.1	843.0	843.0	843.0	843.0	843.0	844.1
167.5°	858.3	857.8	857.3	856.8	856.3	856.0	856.0	855.9	855.9	855.9	857.0
170°	866.0	865.5	865.0	864.5	864.0	863.7	863.5	863.3	863.2	863.0	864.2
172.5°	871.3	870.8	870.3	869.8	869.3	869.0	868.8	868.7	868.5	868.3	869.5
175°	877.8	877.4	876.9	876.4	875.9	875.5	875.1	874.8	874.5	874.1	875.3
177.5°	880.5	880.1	879.7	879.3	878.9	878.6	878.3	878.1	877.8	877.5	878.3
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	9.6	9.4	9.2	9.1	9.1	9.2	9.2	9.2
90°	25.3	25.0	24.7	24.6	24.7	24.9	25.1	25.2
92.5°	23.7	23.8	23.9	23.9	23.9	24.0	24.0	24.0
95°	47.5	47.5	47.5	47.3	47.0	46.7	46.3	46.0
97.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.7	79.7
100°	102.4	102.4	102.4	102.3	102.2	102.0	101.8	101.7
102.5°	127.0	127.1	127.3	127.3	127.1	126.9	126.8	126.6
105°	163.9	164.2	164.6	164.7	164.7	164.7	164.7	164.7
107.5°	203.7	203.9	204.0	203.7	202.9	202.2	201.4	200.7
110°	230.8	230.8	230.8	230.5	230.0	229.5	229.0	228.6



TEST NUMBER: P331792

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.5	257.1	256.7	256.4	256.0	255.6	255.3
115°	299.5	299.3	299.1	298.8	298.3	297.8	297.3	296.8
117.5°	339.7	339.3	338.9	338.4	337.9	337.4	336.9	336.4
120°	366.6	366.6	366.6	366.3	365.8	365.3	364.8	364.3
122.5°	394.3	393.9	393.5	393.1	392.7	392.4	392.0	391.7
125°	435.3	434.8	434.3	434.0	433.9	433.7	433.5	433.4
127.5°	475.2	474.6	474.0	473.5	472.9	472.4	471.9	471.4
130°	502.5	502.1	501.8	501.3	500.6	500.0	499.3	498.7
132.5°	529.0	528.2	527.5	526.9	526.4	525.8	525.3	524.8
135°	568.1	567.9	567.8	567.4	566.9	566.4	565.9	565.4
137.5°	605.5	605.4	605.3	604.9	604.2	603.6	602.9	602.2
140°	630.7	630.7	630.7	630.4	629.8	629.1	628.4	627.8
142.5°	653.6	653.7	653.8	653.6	652.9	652.2	651.6	650.9
145°	688.2	688.4	688.5	688.3	687.6	687.0	686.3	685.7
147.5°	718.6	718.9	719.3	719.2	718.6	717.9	717.3	716.7
150°	737.8	738.3	738.8	738.8	738.3	737.8	737.4	736.9
152.5°	757.1	757.7	758.4	758.4	757.7	757.1	756.5	755.9
155°	781.5	782.4	783.2	783.4	782.9	782.4	781.9	781.4
157.5°	804.1	805.2	806.3	806.5	805.7	804.9	804.1	803.3
160°	817.5	818.5	819.5	819.6	819.0	818.3	817.7	817.0
162.5°	829.6	830.8	831.9	832.0	831.2	830.5	829.7	828.9
165°	845.3	846.4	847.6	847.8	846.9	846.1	845.3	844.5
167.5°	858.2	859.3	860.5	860.6	859.8	858.9	858.1	857.2
170°	865.3	866.5	867.6	867.7	866.7	865.7	864.7	863.7
172.5°	870.7	871.8	873.0	873.0	872.1	871.1	870.1	869.1
175°	876.4	877.6	878.8	878.8	877.8	876.9	875.9	874.9
177.5°	879.1	879.9	880.7	880.7	879.9	879.1	878.3	877.5
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3

(END OF REPORT)