

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331795

Luminaire Tested: **S122RDIW-S485D970U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331795  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D970U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5570.5 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	29	24	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	19	16	15	12
8	52	40	33	28	47	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	27	22	40	31	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.2	1.4
10°-20°	212.1	3.8
20°-30°	297.8	5.3
30°-40°	324.8	5.8
40°-50°	298.6	5.4
50°-60°	234.5	4.2
60°-70°	152.9	2.7
70°-80°	78.8	1.4
80°-90°	23.7	0.4
90°-100°	44.1	0.8
100°-110°	161.5	2.9
110°-120°	431.8	7.8
120°-130°	712.8	12.8
130°-140°	758.0	13.6
140°-150°	704.6	12.6
150°-160°	566.5	10.2
160°-170°	365.0	6.6
170°-180°	125.6	2.3
0°-30°	587.2	10.5
0°-40°	912.0	16.4
0°-60°	1445.1	25.9
0°-90°	1700.6	30.5
90°-120°	637.4	11.4
90°-150°	2812.8	50.5
90°-180°	3870.0	69.5
0°-180°	5570.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	1	11	19	24	26	4
95°	62	33	37	42	41	76
105°	290	303	58	68	73	310
115°	549	566	590	168	78	541
125°	777	790	807	814	817	692
135°	961	976	985	994	993	742
145°	1115	1115	1130	1136	1132	697
155°	1228	1220	1231	1236	1229	566
165°	1294	1289	1291	1297	1291	365
175°	1323	1317	1319	1324	1316	126
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.8	9.2	8.6	8.0	7.4	7.2	7.6	7.9	8.3	8.6	8.7
90°	1.0	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2
92.5°	19.3	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7
95°	62.1	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3
97.5°	123.3	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7
100°	169.1	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2
102.5°	219.6	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2
105°	290.5	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6
107.5°	371.3	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2
110°	423.3	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0



TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	472.2	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3
115°	549.4	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2
117.5°	618.4	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2
120°	668.9	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0
122.5°	711.7	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0
125°	776.8	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9
127.5°	835.9	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4
130°	873.4	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5
132.5°	911.6	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1
135°	961.3	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3
137.5°	1011.5	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1
140°	1044.4	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5
142.5°	1071.9	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6
145°	1115.1	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9
147.5°	1152.8	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3
150°	1177.2	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1
152.5°	1197.9	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2
155°	1227.9	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0
157.5°	1251.4	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6
160°	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4
162.5°	1277.4	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0
165°	1293.8	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4
167.5°	1306.0	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4
170°	1312.9	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6
172.5°	1317.5	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2
175°	1323.4	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1
177.5°	1324.4	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	8.8	8.8	8.9	9.0	9.1	9.2	9.3	9.3
90°	21.2	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.3	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	39.4	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	51.6	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	57.9	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	60.4	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	63.0	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	76.8	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	124.7	103.5	82.3	72.1	72.9	73.8	74.6	75.5





TEST NUMBER: P331795

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	266.8	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	392.9	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	605.4	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	705.5	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	748.6	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	810.4	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	867.6	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	903.8	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	939.1	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	989.4	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1036.1	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1066.4	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1094.3	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1133.4	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1167.4	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1188.4	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1207.5	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1233.3	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1255.0	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1267.7	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1279.5	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1305.9	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1312.1	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1316.6	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1321.6	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1322.2	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)