

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331824

Luminaire Tested: **S122RDIW-S675D1440U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331824
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7322.5 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	51	44	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	18
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	1.4
10°-20°	289.9	4.0
20°-30°	407.1	5.6
30°-40°	443.9	6.1
40°-50°	408.2	5.6
50°-60°	320.6	4.4
60°-70°	209.0	2.9
70°-80°	107.8	1.5
80°-90°	35.1	0.5
90°-100°	113.2	1.5
100°-110°	351.6	4.8
110°-120°	601.0	8.2
120°-130°	790.3	10.8
130°-140°	887.0	12.1
140°-150°	869.7	11.9
150°-160°	729.5	10.0
160°-170°	483.8	6.6
170°-180°	169.1	2.3
0°-30°	802.6	11.0
0°-40°	1246.6	17.0
0°-60°	1975.3	27.0
0°-90°	2327.2	31.8
90°-120°	1065.7	14.6
90°-150°	3612.8	49.3
90°-180°	4995.0	68.2
0°-180°	7322.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	2	20	53	50	51	6
95°	78	93	96	96	94	90
105°	324	329	332	334	335	342
115°	603	611	609	607	603	596
125°	877	890	886	882	880	784
135°	1135	1151	1155	1153	1149	877
145°	1378	1388	1398	1399	1393	860
155°	1575	1580	1584	1591	1588	725
165°	1714	1713	1713	1722	1716	483
175°	1783	1779	1776	1785	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.4	12.7	12.1	11.4	10.8	11.2	12.7	14.1	15.6	17.1	16.8
90°	1.5	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1
92.5°	26.8	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1
95°	78.4	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5
97.5°	143.2	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2
100°	191.5	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0
102.5°	242.1	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8
105°	324.1	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3
107.5°	406.7	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6
110°	459.8	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	517.7	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7
115°	603.0	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7
117.5°	688.1	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9
120°	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7
122.5°	796.6	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8
125°	877.4	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4
127.5°	956.1	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6
130°	1005.5	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5
132.5°	1061.0	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1
135°	1135.2	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5
137.5°	1213.3	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5
140°	1260.3	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4
142.5°	1308.6	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5
145°	1377.9	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8
147.5°	1439.7	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2
150°	1481.9	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0
152.5°	1519.3	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9
155°	1575.4	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1
157.5°	1623.3	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3
160°	1652.3	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8
162.5°	1678.8	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2
165°	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9
167.5°	1743.6	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2
170°	1759.3	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6
172.5°	1770.2	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5
175°	1783.4	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3
177.5°	1788.9	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	16.5	16.1	15.8	15.7	15.8	15.8	15.9	16.0
90°	51.4	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.2	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.0	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.0	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	413.9	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331824

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	523.9	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.4	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	690.1	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	801.0	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	884.4	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	965.4	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.8	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1074.7	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1154.1	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.2	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1327.8	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.2	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1459.9	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1587.8	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1633.6	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1660.8	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1685.5	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1717.3	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1743.5	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1758.0	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1768.8	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1780.6	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)