

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331783-830

Luminaire Tested: **S122RDIW-S290D1440U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331783-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6406.7 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	99	99	99	99	87	87	87	87	64	64	64	43	43	43	24	24	24	15																												
1	90	86	82	79	79	76	73	70	56	54	52	38	37	36	22	21	21	13																												
2	82	75	70	65	72	66	62	58	49	46	44	34	32	30	19	18	18	11																												
3	75	66	59	54	65	58	53	48	43	40	37	30	28	26	17	16	15	10																												
4	68	58	51	46	60	52	45	41	39	34	31	27	24	22	15	14	13	8																												
5	63	52	44	39	55	46	40	35	34	30	27	24	21	19	14	12	11	7																												
6	58	46	39	33	50	41	35	30	31	27	23	21	19	17	13	11	10	7																												
7	53	42	34	29	47	37	31	26	28	24	20	19	17	15	11	10	9	6																												
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	10	9	8	5																												
9	46	34	27	22	40	30	24	20	23	19	16	16	13	12	10	8	7	5																												
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	0.7
10°-20°	121.6	1.9
20°-30°	170.8	2.7
30°-40°	186.2	2.9
40°-50°	171.2	2.7
50°-60°	134.5	2.1
60°-70°	87.7	1.4
70°-80°	45.2	0.7
80°-90°	16.3	0.3
90°-100°	61.8	1.0
100°-110°	226.6	3.5
110°-120°	605.8	9.5
120°-130°	1000.0	15.6
130°-140°	1063.4	16.6
140°-150°	988.4	15.4
150°-160°	794.7	12.4
160°-170°	512.1	8.0
170°-180°	176.3	2.8
0°-30°	336.6	5.3
0°-40°	522.8	8.2
0°-60°	828.5	12.9
0°-90°	977.7	15.3
90°-120°	894.2	14.0
90°-150°	3946.0	61.6
90°-180°	5429.0	84.7
0°-180°	6406.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	1	16	27	33	36	5
95°	87	46	52	58	58	107
105°	408	425	82	96	102	435
115°	771	794	827	236	110	759
125°	1090	1108	1133	1142	1146	971
135°	1349	1369	1382	1395	1393	1041
145°	1564	1564	1586	1594	1589	978
155°	1723	1712	1726	1734	1724	793
165°	1815	1808	1811	1819	1811	513
175°	1857	1848	1850	1858	1846	177
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.7	5.7	5.8	5.8	5.9	6.2	6.7	7.2	7.6	8.1	8.3
90°	1.3	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3
92.5°	27.1	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9
95°	87.1	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7
97.5°	173.0	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2
100°	237.2	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8
102.5°	308.0	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6
105°	407.6	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0
107.5°	520.9	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1
110°	593.9	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	662.5	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1
115°	770.8	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2
117.5°	867.6	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8
120°	938.4	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2
122.5°	998.4	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0
125°	1089.9	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8
127.5°	1172.7	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1
130°	1225.2	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7
132.5°	1278.8	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7
135°	1348.6	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1
137.5°	1419.1	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7
140°	1465.2	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4
142.5°	1503.8	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8
145°	1564.4	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9
147.5°	1617.2	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2
150°	1651.5	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4
152.5°	1680.5	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1
155°	1722.6	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3
157.5°	1755.6	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7
160°	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6
162.5°	1792.0	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0
165°	1815.1	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2
167.5°	1832.2	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0
170°	1841.9	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6
172.5°	1848.3	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0
175°	1856.6	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0
177.5°	1857.9	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	8.6	8.8	9.0	9.1	9.2	9.4	9.5	9.6
90°	29.8	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	32.6	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	55.2	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	72.4	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	81.2	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	84.7	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	88.3	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	107.8	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	175.0	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331783-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	374.4	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	551.3	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	849.4	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	989.8	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1050.2	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1136.9	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1217.1	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1268.0	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1317.4	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1388.0	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1453.6	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1496.0	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1535.2	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1590.0	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1637.8	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1667.2	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1693.9	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1730.1	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1760.7	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1778.4	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1795.0	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1832.1	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1840.7	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1847.1	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1854.1	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1854.8	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)