

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331805

Luminaire Tested: **S122RDIW-S675D435U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331805
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4271.4 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	58	57	52
2	93	86	80	75	86	80	75	71	70	67	63	61	59	56	53	51	49	45
3	85	76	69	64	79	72	66	61	63	58	55	55	52	49	48	45	43	39
4	78	68	61	55	73	64	58	52	57	52	48	50	46	43	43	40	38	35
5	73	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34	31
6	67	56	48	42	63	53	46	41	47	41	37	42	37	34	36	33	30	28
7	63	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	28	25
8	58	46	39	34	55	44	37	33	40	34	30	35	31	28	31	28	25	23
9	55	43	35	31	51	41	34	29	37	31	27	33	28	25	29	26	23	21
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	3.3
10°-20°	388.0	9.1
20°-30°	500.0	11.7
30°-40°	475.2	11.1
40°-50°	407.1	9.5
50°-60°	310.0	7.3
60°-70°	196.0	4.6
70°-80°	97.9	2.3
80°-90°	26.9	0.6
90°-100°	19.7	0.5
100°-110°	72.3	1.7
110°-120°	193.1	4.5
120°-130°	318.8	7.5
130°-140°	339.1	7.9
140°-150°	315.2	7.4
150°-160°	253.4	5.9
160°-170°	163.3	3.8
170°-180°	56.2	1.3
0°-30°	1027.3	24.1
0°-40°	1502.5	35.2
0°-60°	2219.6	52.0
0°-90°	2540.4	59.5
90°-120°	285.1	6.7
90°-150°	1258.2	29.5
90°-180°	1731.0	40.5
0°-180°	4271.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	130	32	130	32	34
115°	35	246	35	246	35	88
125°	365	348	365	348	365	316
135°	444	430	444	430	444	342
145°	506	499	506	499	506	317
155°	550	549	550	549	550	254
165°	577	579	577	579	577	163
175°	589	592	589	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	8.8	9.2	9.2	9.1	9.1	9.0	8.9	9.3	8.7	9.1	8.5
90°	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5	9.0	8.5	7.8
92.5°	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4	10.2	9.9	9.5
95°	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6	17.1	16.7	16.0
97.5°	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1	22.7	22.3	20.8
100°	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9	25.1	24.4	22.7
102.5°	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0	26.0	25.0	38.6
105°	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2	27.1	26.1	52.0
107.5°	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4	35.4	36.5	67.6
110°	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8	65.3	74.8	102.2



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4	154.0	188.7	195.4
115°	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8	219.7	263.7	261.3
117.5°	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8	281.5	292.1	290.5
120°	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6	314.4	313.3	311.6
122.5°	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8	334.2	333.5	331.6
125°	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5	361.8	361.2	359.4
127.5°	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1	387.1	386.1	384.8
130°	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3	403.2	402.2	401.2
132.5°	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1	419.2	418.3	417.2
135°	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6	441.6	440.7	439.8
137.5°	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5	462.5	461.6	460.6
140°	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0	476.1	475.3	474.2
142.5°	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5	488.7	487.9	486.7
145°	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0	506.3	505.6	504.0
147.5°	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2	521.7	521.2	519.6
150°	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6	531.0	530.4	528.9
152.5°	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1	539.5	539.0	537.5
155°	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7	551.1	550.5	549.4
157.5°	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4	560.7	560.1	559.3
160°	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0	566.5	565.9	565.3
162.5°	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3	571.7	571.0	570.5
165°	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4	577.2
167.5°	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2	583.5	582.8	582.6
170°	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9	586.2	585.6	585.4
172.5°	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9	588.3	587.6	587.4
175°	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2	590.5	589.8	589.6
177.5°	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4	590.9	590.3	590.3
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	8.3	8.6	8.5	7.9	8.1	8.3	10.1	11.9	10.5	9.5	8.9
90°	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8	24.6	21.5	18.4
97.5°	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1	46.3	37.5	28.6
100°	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7	62.6	49.6	36.6
102.5°	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2	95.5	92.7	90.0
105°	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9	132.8	135.6	138.5
107.5°	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1	168.4	170.7	173.0
110°	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3	191.3	193.3	195.3



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2	213.0	214.8	216.5
115°	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8	247.4	249.0	250.6
117.5°	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6	278.4	280.2	282.0
120°	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2	300.6	302.0	303.5
122.5°	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3	319.8	321.3	322.8
125°	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5	348.7	350.0	351.2
127.5°	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9	375.3	376.6	378.0
130°	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7	392.2	393.7	395.2
132.5°	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8	409.0	410.3	411.6
135°	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0	431.5	433.0	434.5
137.5°	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5	453.5	454.6	455.7
140°	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2	467.9	468.7	469.4
142.5°	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5	480.2	480.8	481.5
145°	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5
147.5°	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6	515.3	514.9	514.6
150°	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6	525.9	525.2	524.6
152.5°	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8	535.1	534.3	533.6
155°	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2	548.4	547.5	546.7
157.5°	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7	559.0	558.3	557.6
160°	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	565.3	564.8	564.2
162.5°	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4	570.8	570.2	569.7
165°	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7	578.2	577.6	577.0
167.5°	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2	583.6	583.1	582.5
170°	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3	586.7	586.1	585.6
172.5°	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3	588.8	588.2	587.6
175°	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0	591.3	590.6	590.0
177.5°	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4	591.9	591.3	590.8
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	8.7	8.5	7.8	7.9	8.1	7.8	7.9	7.6	7.7	7.8	7.5
90°	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5	10.0	10.4	10.8
92.5°	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4	10.7	10.9	11.1
95°	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6	18.1	18.6	18.8
97.5°	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1	23.5	23.8	24.1
100°	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9	26.6	27.4	27.9
102.5°	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0	28.0	29.0	29.6
105°	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2	29.2	30.3	31.0
107.5°	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4	33.3	32.2	31.9
110°	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8	46.3	36.8	32.2



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4	84.7	50.1	32.9
115°	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8	131.8	87.8	62.4
117.5°	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8	260.2	249.5	233.0
120°	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6	316.7	317.9	312.0
122.5°	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8	335.5	336.2	335.3
125°	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5	363.2	363.8	364.3
127.5°	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1	389.0	390.0	390.5
130°	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3	405.3	406.4	406.9
132.5°	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1	420.9	421.8	422.2
135°	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6	443.5	444.5	444.8
137.5°	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5	464.4	465.3	465.6
140°	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0	477.9	478.7	478.9
142.5°	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5	490.3	491.1	491.2
145°	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0	507.6	508.3	508.4
147.5°	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2	522.7	523.2	523.2
150°	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6	532.1	532.7	532.8
152.5°	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1	540.7	541.3	541.2
155°	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7	552.2	552.8	552.7
157.5°	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4	562.0	562.7	562.6
160°	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0	567.6	568.2	568.1
162.5°	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3	573.0	573.6	573.5
165°	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8	579.4	580.1	580.1
167.5°	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2	584.8	585.5	585.4
170°	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9	587.6	588.2	588.1
172.5°	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9	589.6	590.3	590.2
175°	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2	591.8	592.5	592.4
177.5°	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4	591.9	592.5	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	7.5	7.1	7.6	7.2	7.6	7.1	7.5	7.5	7.8	7.7	7.6
90°	11.0	11.2	11.4	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4
95°	18.7	18.6	18.5	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6
97.5°	24.2	24.3	24.4	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1
100°	28.1	28.3	28.4	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9
102.5°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0
105°	31.3	31.7	32.1	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2
107.5°	32.3	32.7	33.0	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4
110°	32.6	33.0	33.4	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.2	33.5	33.8	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4
115°	55.6	48.7	41.9	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8
117.5°	210.5	188.0	165.6	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8
120°	299.2	286.4	273.5	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6
122.5°	332.8	330.3	327.8	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8
125°	364.6	364.9	365.2	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5
127.5°	390.6	390.6	390.7	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1
130°	406.8	406.7	406.6	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3
132.5°	422.1	422.0	422.0	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1
135°	444.7	444.5	444.3	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6
137.5°	465.3	465.0	464.7	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5
140°	478.4	477.9	477.5	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0
142.5°	490.7	490.3	489.8	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5
145°	507.9	507.4	507.0	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0
147.5°	522.8	522.4	522.0	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2
150°	532.3	531.8	531.3	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6
152.5°	540.6	540.0	539.3	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1
155°	551.9	551.2	550.4	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7
157.5°	561.9	561.1	560.4	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4
160°	567.5	566.8	566.1	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0
162.5°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3
165°	579.4	578.8	578.1	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8
167.5°	584.5	583.7	582.8	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2
170°	587.3	586.4	585.6	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9
172.5°	589.3	588.5	587.6	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9
175°	591.4	590.5	589.5	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2
177.5°	591.7	591.0	590.3	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	7.9	7.8	8.1	7.9	7.8	8.5	8.7	8.9	9.5	10.5	11.9
90°	9.0	8.5	7.8	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4
92.5°	10.2	9.9	9.5	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6
95°	17.1	16.7	16.0	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8
97.5°	22.7	22.3	20.8	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1
100°	25.1	24.4	22.7	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7
102.5°	26.0	25.0	38.6	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2
105°	27.1	26.1	52.0	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9
107.5°	35.4	36.5	67.6	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1
110°	65.3	74.8	102.2	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.0	188.7	195.4	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2
115°	219.7	263.7	261.3	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8
117.5°	281.5	292.1	290.5	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6
120°	314.4	313.3	311.6	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2
122.5°	334.2	333.5	331.6	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3
125°	361.8	361.2	359.4	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5
127.5°	387.1	386.1	384.8	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9
130°	403.2	402.2	401.2	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7
132.5°	419.2	418.3	417.2	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8
135°	441.6	440.7	439.8	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0
137.5°	462.5	461.6	460.6	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5
140°	476.1	475.3	474.2	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2
142.5°	488.7	487.9	486.7	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5
145°	506.3	505.6	504.0	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8
147.5°	521.7	521.2	519.6	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6
150°	531.0	530.4	528.9	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6
152.5°	539.5	539.0	537.5	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8
155°	551.1	550.5	549.4	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2
157.5°	560.7	560.1	559.3	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7
160°	566.5	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9
162.5°	571.7	571.0	570.5	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4
165°	578.1	577.4	577.2	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7
167.5°	583.5	582.8	582.6	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2
170°	586.2	585.6	585.4	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3
172.5°	588.3	587.6	587.4	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3
175°	590.5	589.8	589.6	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0
177.5°	590.9	590.3	590.3	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.1	8.3	8.1	7.9	8.5	8.6	8.3	8.5	9.1	8.7	9.3
90°	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4
95°	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6
97.5°	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1
100°	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9
102.5°	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0
105°	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2
107.5°	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4
110°	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4
115°	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8
117.5°	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8
120°	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6
122.5°	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8
125°	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5
127.5°	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1
130°	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3
132.5°	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1
135°	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6
137.5°	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5
140°	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0
142.5°	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5
145°	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0
147.5°	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2
150°	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6
152.5°	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1
155°	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7
157.5°	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4
160°	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0
162.5°	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3
165°	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8
167.5°	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2
170°	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9
172.5°	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9
175°	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2
177.5°	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	8.9	9.0	9.1	9.1	9.2	9.2	8.8
90°	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331805

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)