

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331811

Luminaire Tested: **S122RDIW-S675D710U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331811  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D710U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5157.7 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	37	35	33	29				
4	74	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	19				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.6	2.0
10°-20°	289.9	5.6
20°-30°	407.1	7.9
30°-40°	443.9	8.6
40°-50°	408.2	7.9
50°-60°	320.6	6.2
60°-70°	209.0	4.1
70°-80°	107.8	2.1
80°-90°	30.3	0.6
90°-100°	32.3	0.6
100°-110°	118.3	2.3
110°-120°	316.3	6.1
120°-130°	522.2	10.1
130°-140°	555.4	10.8
140°-150°	516.2	10.0
150°-160°	415.0	8.0
160°-170°	267.4	5.2
170°-180°	92.1	1.8
0°-30°	802.6	15.6
0°-40°	1246.6	24.2
0°-60°	1975.3	38.3
0°-90°	2322.5	45.0
90°-120°	467.0	9.1
90°-150°	2060.7	40.0
90°-180°	2835.0	55.0
0°-180°	5157.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	8	14	17	19	4
95°	46	24	27	31	30	56
105°	213	222	43	50	53	227
115°	402	415	432	123	57	396
125°	569	578	592	596	598	507
135°	704	715	722	728	727	544
145°	817	817	828	833	830	511
155°	900	894	902	905	900	414
165°	948	944	946	950	946	268
175°	970	965	966	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.2	12.1	11.0	9.9	8.8	8.3	8.6	8.8	9.1	9.3	9.3
90°	0.7	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8
92.5°	14.1	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6
95°	45.5	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1
97.5°	90.3	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2
100°	123.9	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1
102.5°	160.9	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6
105°	212.8	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4
107.5°	272.0	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0
110°	310.1	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0



TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.0	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3
115°	402.5	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9
117.5°	453.1	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0
120°	490.0	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0
122.5°	521.4	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3
125°	569.1	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6
127.5°	612.4	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0
130°	639.8	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5
132.5°	667.9	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5
135°	704.3	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3
137.5°	741.1	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6
140°	765.2	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9
142.5°	785.3	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5
145°	817.0	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3
147.5°	844.5	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5
150°	862.5	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7
152.5°	877.6	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7
155°	899.6	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6
157.5°	916.8	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4
160°	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8
162.5°	935.8	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3
165°	947.9	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9
167.5°	956.8	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7
170°	961.9	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2
172.5°	965.2	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5
175°	969.6	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2
177.5°	970.3	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	9.3	9.3	9.2	9.2	9.3	9.4	9.4	9.5
90°	15.6	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.1	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	28.9	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	37.8	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	42.4	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	44.3	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	46.1	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	56.3	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	91.4	75.8	60.3	52.8	53.4	54.1	54.7	55.3





TEST NUMBER: P331811

CATALOG NUMBER: S122RDIW-S675D710U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	195.5	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	287.9	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	443.6	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	516.9	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	548.4	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	593.7	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	635.6	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	662.2	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	688.0	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	724.9	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	759.1	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	781.3	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	801.7	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	830.3	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	855.3	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	870.6	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	884.6	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	903.5	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	919.5	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	928.7	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	937.4	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	956.8	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	961.3	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	964.6	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	968.3	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	968.7	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)