

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331776-830

Luminaire Tested: **S122RDIW-S290D970U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331776-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D970U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4140.8 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	18	17	15	11
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	14	10
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.3	1.1
10°-20°	121.6	2.9
20°-30°	170.8	4.1
30°-40°	186.2	4.5
40°-50°	171.2	4.1
50°-60°	134.5	3.2
60°-70°	87.7	2.1
70°-80°	45.2	1.1
80°-90°	16.2	0.4
90°-100°	71.7	1.7
100°-110°	222.6	5.4
110°-120°	380.6	9.2
120°-130°	500.5	12.1
130°-140°	561.7	13.6
140°-150°	550.8	13.3
150°-160°	462.0	11.2
160°-170°	306.4	7.4
170°-180°	107.1	2.6
0°-30°	336.6	8.1
0°-40°	522.8	12.6
0°-60°	828.5	20.0
0°-90°	977.6	23.6
90°-120°	674.9	16.3
90°-150°	2287.8	55.2
90°-180°	3163.0	76.4
0°-180°	4140.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	1	13	33	32	32	3
95°	50	59	61	61	59	57
105°	205	208	210	212	212	217
115°	382	387	386	385	382	378
125°	556	564	561	559	558	496
135°	719	729	731	730	728	555
145°	872	879	885	886	882	545
155°	998	1000	1003	1008	1005	459
165°	1085	1085	1084	1090	1086	306
175°	1129	1126	1124	1131	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.7	5.6	5.5	5.4	5.3	5.7	6.6	7.5	8.5	9.4	9.2
90°	0.9	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0
92.5°	17.0	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4
95°	49.7	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1
97.5°	90.7	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7
100°	121.2	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8
102.5°	153.4	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2
105°	205.3	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5
107.5°	257.6	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9
110°	291.2	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.8	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2
115°	381.8	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5
117.5°	435.7	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5
120°	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6
122.5°	504.4	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7
125°	555.6	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7
127.5°	605.5	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1
130°	636.8	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9
132.5°	671.8	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5
135°	718.9	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0
137.5°	768.3	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2
140°	798.1	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4
142.5°	828.7	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7
145°	872.5	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1
147.5°	911.7	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0
150°	938.4	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6
152.5°	962.1	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2
155°	997.6	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4
157.5°	1027.9	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0
160°	1046.3	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5
162.5°	1063.1	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9
165°	1085.4	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0
167.5°	1104.2	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6
170°	1114.1	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7
172.5°	1121.0	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6
175°	1129.4	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1
177.5°	1132.8	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	9.1	9.0	8.8	8.8	8.8	8.8	8.9	8.9
90°	32.5	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.5	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.4	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	210.8	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.1	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.9	296.6	296.0	295.3	294.6	294.1





TEST NUMBER: P331776-830

CATALOG NUMBER: S122RDIW-S290D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.8	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.2	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	437.0	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	507.3	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	560.1	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	611.3	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.4	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	680.5	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.8	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	779.0	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	840.8	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.4	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.4	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1005.5	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1034.5	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1051.7	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1067.3	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1087.5	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1104.1	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1113.2	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1120.1	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1127.6	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)