

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331814

Luminaire Tested: **S122RDIW-S675D970U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331814
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5899.8 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	71	68	67	57	56	55	45	44	43	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	40	39	38	33
3	81	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	45	42	41	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	36	38	34	31	30	28	26	22
6	64	52	45	39	58	48	42	37	41	36	32	34	30	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29	31	28	25	26	23	21	18
8	55	43	36	31	50	40	34	29	34	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	24	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	2.4
10°-20°	388.0	6.6
20°-30°	500.0	8.5
30°-40°	475.2	8.1
40°-50°	407.1	6.9
50°-60°	310.0	5.3
60°-70°	196.0	3.3
70°-80°	97.9	1.7
80°-90°	30.3	0.5
90°-100°	76.0	1.3
100°-110°	236.2	4.0
110°-120°	403.8	6.8
120°-130°	531.0	9.0
130°-140°	595.9	10.1
140°-150°	584.3	9.9
150°-160°	490.1	8.3
160°-170°	325.1	5.5
170°-180°	113.6	1.9
0°-30°	1027.3	17.4
0°-40°	1502.5	25.5
0°-60°	2219.6	37.6
0°-90°	2543.7	43.1
90°-120°	716.0	12.1
90°-150°	2427.3	41.1
90°-180°	3356.0	56.9
0°-180°	5899.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	21
90°	34	1	34	1	34	16
95°	63	53	63	53	63	70
105°	225	218	225	218	225	237
115°	405	405	405	405	405	400
125°	592	590	592	590	592	527
135°	772	763	772	763	772	594
145°	936	926	936	926	936	584
155°	1066	1058	1066	1058	1066	491
165°	1153	1152	1153	1152	1153	325
175°	1194	1198	1194	1198	1194	113
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	13.4	13.8	13.7	13.7	13.6	13.7	13.8	14.3	13.9	14.4	13.0
90°	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5	35.0	35.4	30.5
92.5°	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4	32.3	32.2	31.0
95°	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8	64.8	64.8	64.4
97.5°	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0	109.0	109.0	108.1
100°	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8	139.8	139.8	139.1
102.5°	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4	173.2	173.0	172.1
105°	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7	223.3	222.8	222.4
107.5°	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1	277.9	277.7	277.7
110°	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0	352.5	353.1	353.3
115°	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7	409.0	409.2	409.6
117.5°	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6	464.2	464.7	466.0
120°	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4	500.4	500.4	502.2
122.5°	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2	538.7	539.2	540.5
125°	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2	594.9	595.6	596.2
127.5°	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6	649.4	650.3	651.1
130°	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8	686.3	686.7	687.2
132.5°	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0	723.0	724.0	723.9
135°	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4	775.6	775.8	775.4
137.5°	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5	826.7	826.9	826.3
140°	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9	860.9	860.9	859.8
142.5°	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1	891.9	891.7	891.0
145°	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4	939.1	938.9	937.6
147.5°	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8	980.3	979.8	978.9
150°	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8	1004.9
152.5°	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7	1030.6
155°	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8	1065.6	1064.5	1063.8
157.5°	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6	1096.0	1094.5	1094.1
160°	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8	1114.5	1113.1	1112.9
162.5°	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4	1130.9	1129.3	1129.1
165°	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8	1152.2	1150.6	1150.6
167.5°	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4	1169.8	1168.2	1168.3
170°	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1	1179.5	1178.0	1178.2
172.5°	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4	1186.8	1185.2	1185.5
175°	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3	1194.7	1193.1	1193.6
177.5°	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8	1198.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	12.1	11.5	10.5	9.3	9.2	9.0	10.5	12.0	11.0	10.3	10.0
90°	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0	20.0	22.0	24.0
95°	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7	54.9	57.2	59.4
97.5°	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2	98.2	100.2	102.2
100°	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6	130.4	132.2	134.0
102.5°	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7	164.1	165.5	167.0
105°	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8	218.4	219.1	219.8
107.5°	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3	274.3	275.2	276.2
110°	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9	310.3	311.6	313.0



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8	349.2	350.5	351.9
115°	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1	406.5	407.8	409.2
117.5°	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3	464.1	465.9	467.7
120°	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	502.2	504.0	505.8
122.5°	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2	537.4	539.5	541.7
125°	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5	591.5	593.5	595.6
127.5°	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4	644.9	647.5	650.1
130°	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6	678.5	681.4	684.4
132.5°	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8	715.2	717.6	720.0
135°	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7	765.2	767.6	770.1
137.5°	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1	817.2	819.2	821.2
140°	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7	848.8	850.8	852.8
142.5°	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2	881.2	883.2	885.2
145°	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7	927.3	928.9	930.5
147.5°	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3	969.2	971.1	972.9
150°	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6	997.0	998.3	999.7
152.5°	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8	1022.1	1023.5	1024.8
155°	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4	1059.1	1059.8	1060.5
157.5°	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6	1091.1	1091.5	1092.0
160°	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1	1110.5	1111.0	1111.4
162.5°	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9	1128.0	1128.1	1128.2
165°	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6	1151.4	1151.2	1150.9
167.5°	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5	1170.8	1170.1	1169.4
170°	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0	1181.3	1180.7	1180.0
172.5°	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3	1188.6	1187.9	1187.3
175°	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2	1197.5	1196.9	1196.2
177.5°	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9	1201.3	1200.8	1200.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	10.1	10.5	10.7	11.6	12.6	13.2	13.1	12.6	12.5	12.4	12.0
90°	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5	34.1	33.6	33.5
92.5°	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4	32.5	32.6	32.6
95°	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8	64.8	64.8	64.6
97.5°	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0	109.0	109.0	109.0
100°	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8	139.8	139.8	139.7
102.5°	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4	173.5	173.7	173.7
105°	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.6	224.9
107.5°	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1	278.3	278.4	278.0
110°	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	314.7



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0	351.5	350.9	350.4
115°	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7	408.5	408.3	407.8
117.5°	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6	463.1	462.5	461.9
120°	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4	500.4	500.4	500.0
122.5°	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2	537.6	537.1	536.6
125°	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2	593.5	592.9	592.4
127.5°	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6	647.8	647.0	646.2
130°	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8	685.4	684.9	684.2
132.5°	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0	721.0	720.0	719.2
135°	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4	775.2	774.9	774.5
137.5°	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5	826.4	826.2	825.6
140°	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9	860.9	860.9	860.5
142.5°	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1	892.3	892.4	892.1
145°	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4	939.6	939.8	939.5
147.5°	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8	981.3	981.8	981.6
150°	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5
152.5°	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1
155°	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8	1067.9	1069.0	1069.2
157.5°	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6	1099.1	1100.6	1100.8
160°	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8	1117.2	1118.5	1118.8
162.5°	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4	1133.9	1135.5	1135.7
165°	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8	1155.3	1156.9	1157.1
167.5°	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4	1173.0	1174.5	1174.7
170°	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1	1182.7	1184.3	1184.4
172.5°	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4	1190.0	1191.5	1191.7
175°	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3	1197.9	1199.4	1199.6
177.5°	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	12.1	11.7	12.2	11.8	12.2	11.7	12.1	12.0	12.4	12.5	12.6
90°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5
92.5°	32.7	32.7	32.8	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4
95°	64.1	63.7	63.2	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8
97.5°	108.9	108.9	108.8	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0
100°	139.4	139.2	139.0	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8
102.5°	173.5	173.2	173.0	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4
105°	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7
107.5°	277.0	275.9	274.9	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1
110°	314.0	313.3	312.6	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0
115°	407.2	406.5	405.8	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7
117.5°	461.3	460.6	459.9	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6
120°	499.3	498.7	498.0	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4
122.5°	536.1	535.6	535.1	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2
125°	592.2	592.0	591.7	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2
127.5°	645.5	644.8	644.1	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6
130°	683.3	682.4	681.5	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8
132.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0
135°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4
137.5°	824.7	823.8	822.9	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5
140°	859.6	858.7	857.8	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9
142.5°	891.2	890.3	889.4	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1
145°	938.6	937.7	936.8	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4
147.5°	980.8	979.9	979.1	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8
150°	1007.8	1007.1	1006.4	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1
152.5°	1034.3	1033.4	1032.5	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4
155°	1068.6	1067.9	1067.2	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8
157.5°	1099.8	1098.7	1097.6	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6
160°	1117.9	1117.0	1116.1	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8
162.5°	1134.6	1133.5	1132.4	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4
165°	1156.0	1154.9	1153.8	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8
167.5°	1173.6	1172.4	1171.2	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4
170°	1183.0	1181.7	1180.3	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1
172.5°	1190.3	1189.0	1187.6	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4
175°	1198.2	1196.9	1195.5	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3
177.5°	1201.0	1200.0	1198.9	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	13.1	13.2	12.6	11.6	10.7	10.5	10.1	10.0	10.3	11.0	12.0
90°	35.0	35.4	30.5	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0
92.5°	32.3	32.2	31.0	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0
95°	64.8	64.8	64.4	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7
97.5°	109.0	109.0	108.1	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2
100°	139.8	139.8	139.1	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6
102.5°	173.2	173.0	172.1	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7
105°	223.3	222.8	222.4	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8
107.5°	277.9	277.7	277.7	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3
110°	315.0	315.0	315.0	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	352.5	353.1	353.3	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8
115°	409.0	409.2	409.6	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1
117.5°	464.2	464.7	466.0	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3
120°	500.4	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4
122.5°	538.7	539.2	540.5	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2
125°	594.9	595.6	596.2	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5
127.5°	649.4	650.3	651.1	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4
130°	686.3	686.7	687.2	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6
132.5°	723.0	724.0	723.9	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8
135°	775.6	775.8	775.4	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7
137.5°	826.7	826.9	826.3	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1
140°	860.9	860.9	859.8	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7
142.5°	891.9	891.7	891.0	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2
145°	939.1	938.9	937.6	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7
147.5°	980.3	979.8	978.9	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3
150°	1006.4	1005.8	1004.9	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6
152.5°	1032.5	1031.7	1030.6	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8
155°	1065.6	1064.5	1063.8	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4
157.5°	1096.0	1094.5	1094.1	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6
160°	1114.5	1113.1	1112.9	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1
162.5°	1130.9	1129.3	1129.1	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9
165°	1152.2	1150.6	1150.6	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6
167.5°	1169.8	1168.2	1168.3	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5
170°	1179.5	1178.0	1178.2	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0
172.5°	1186.8	1185.2	1185.5	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3
175°	1194.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2
177.5°	1198.9	1197.8	1198.2	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.5	9.0	9.2	9.3	10.5	11.5	12.1	13.0	14.4	13.9	14.3
90°	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5
92.5°	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4
95°	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8
97.5°	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0
100°	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8
102.5°	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4
105°	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7
107.5°	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1
110°	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0
115°	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7
117.5°	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6
120°	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4
122.5°	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2
125°	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2
127.5°	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6
130°	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8
132.5°	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0
135°	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4
137.5°	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5
140°	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9
142.5°	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1
145°	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4
147.5°	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8
150°	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1
152.5°	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4
155°	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8
157.5°	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6
160°	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8
162.5°	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4
165°	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8
167.5°	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4
170°	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1
172.5°	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4
175°	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3
177.5°	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	13.8	13.7	13.6	13.7	13.7	13.8	13.4
90°	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331814

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)