

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331788-830

Luminaire Tested: **S122RDIW-S485D435U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331788-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3016.8 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	44	39
3	83	74	67	61	77	69	62	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	2.4
10°-20°	199.9	6.6
20°-30°	280.7	9.3
30°-40°	306.1	10.1
40°-50°	281.5	9.3
50°-60°	221.1	7.3
60°-70°	144.1	4.8
70°-80°	74.3	2.5
80°-90°	21.3	0.7
90°-100°	32.1	1.1
100°-110°	99.6	3.3
110°-120°	170.2	5.6
120°-130°	223.9	7.4
130°-140°	251.3	8.3
140°-150°	246.4	8.2
150°-160°	206.6	6.8
160°-170°	137.1	4.5
170°-180°	47.9	1.6
0°-30°	553.4	18.3
0°-40°	859.6	28.5
0°-60°	1362.1	45.2
0°-90°	1601.8	53.1
90°-120°	301.9	10.0
90°-150°	1023.3	33.9
90°-180°	1415.0	46.9
0°-180°	3016.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	0	6	15	14	14	2
95°	22	26	27	27	26	25
105°	92	93	94	95	95	97
115°	171	173	172	172	171	169
125°	248	252	251	250	249	222
135°	322	326	327	327	325	248
145°	390	393	396	396	394	244
155°	446	448	449	451	450	205
165°	486	485	485	488	486	137
175°	505	504	503	506	504	48
180°	506	506	506	506	506	



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.1	8.3	7.5	6.8	6.0	5.8	6.2	6.7	7.1	7.5	7.4
90°	0.5	1.6	2.7	3.9	5.0	6.6	8.7	10.7	12.8	15.0	14.8
92.5°	7.6	8.5	9.2	10.1	10.9	11.6	12.1	12.6	13.1	13.6	13.6
95°	22.2	23.2	24.1	25.1	26.0	26.6	26.8	27.0	27.1	27.3	27.3
97.5°	40.5	41.4	42.2	43.1	43.9	44.5	44.9	45.2	45.6	45.9	45.9
100°	54.2	55.0	55.7	56.6	57.3	57.8	58.1	58.3	58.6	58.9	58.9
102.5°	68.6	69.2	69.7	70.4	71.0	71.5	71.8	72.2	72.6	73.0	73.0
105°	91.8	92.1	92.4	92.7	92.9	93.2	93.4	93.6	93.8	94.0	94.2
107.5°	115.2	115.6	116.0	116.5	116.9	117.1	117.1	117.1	117.1	117.1	117.2
110°	130.3	130.8	131.4	132.0	132.5	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.7	147.2	147.8	148.4	148.9	149.2	149.1	149.0	148.9	148.8	148.6
115°	170.8	171.4	171.9	172.5	173.1	173.2	173.1	172.9	172.7	172.5	172.4
117.5°	194.9	195.7	196.4	197.2	197.9	198.0	197.6	197.0	196.4	196.0	195.7
120°	210.9	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	210.9
122.5°	225.6	226.6	227.4	228.4	229.3	229.5	228.9	228.4	227.9	227.3	227.2
125°	248.5	249.4	250.2	251.1	251.9	252.2	251.9	251.7	251.4	251.1	250.8
127.5°	270.8	271.9	273.0	274.1	275.1	275.5	275.2	274.8	274.5	274.2	273.8
130°	284.8	286.1	287.3	288.5	289.7	290.3	290.1	289.9	289.7	289.5	289.4
132.5°	300.6	301.5	302.6	303.6	304.5	305.1	305.1	305.2	305.2	305.2	304.8
135°	321.6	322.6	323.7	324.7	325.7	326.3	326.5	326.7	326.9	327.1	327.0
137.5°	343.7	344.5	345.3	346.2	347.0	347.6	347.9	348.2	348.4	348.6	348.6
140°	357.0	357.9	358.7	359.6	360.4	361.1	361.6	362.0	362.5	363.0	363.0
142.5°	370.7	371.6	372.4	373.2	374.1	374.7	374.9	375.3	375.6	376.0	376.1
145°	390.3	391.0	391.6	392.3	392.9	393.6	394.2	394.7	395.3	395.9	396.0
147.5°	407.8	408.6	409.4	410.2	411.0	411.6	412.0	412.4	412.7	413.1	413.3
150°	419.8	420.4	420.9	421.5	422.1	422.5	422.9	423.3	423.7	424.0	424.3
152.5°	430.4	430.9	431.5	432.1	432.6	433.2	433.6	434.0	434.5	435.0	435.4
155°	446.2	446.5	446.8	447.1	447.4	447.7	448.0	448.3	448.6	448.8	449.3
157.5°	459.9	460.1	460.2	460.4	460.6	460.7	460.9	461.1	461.3	461.5	462.1
160°	468.1	468.3	468.4	468.6	468.8	468.9	469.0	469.1	469.2	469.3	469.9
162.5°	475.5	475.6	475.6	475.6	475.7	475.8	475.9	476.0	476.1	476.2	476.7
165°	485.5	485.4	485.3	485.2	485.1	485.1	485.1	485.1	485.1	485.1	485.8
167.5°	493.9	493.6	493.3	493.0	492.8	492.6	492.6	492.6	492.6	492.6	493.2
170°	498.3	498.0	497.8	497.5	497.2	497.0	496.9	496.8	496.7	496.6	497.3
172.5°	501.4	501.1	500.9	500.6	500.3	500.1	500.0	499.9	499.8	499.7	500.4
175°	505.2	504.9	504.6	504.4	504.1	503.8	503.6	503.4	503.2	503.0	503.7
177.5°	506.7	506.5	506.2	506.1	505.8	505.6	505.5	505.3	505.1	505.0	505.5
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	7.2	7.0	6.9	6.8	6.8	6.8	6.8	6.9
90°	14.6	14.4	14.2	14.1	14.2	14.3	14.4	14.5
92.5°	13.7	13.7	13.8	13.8	13.8	13.8	13.9	13.9
95°	27.3	27.3	27.3	27.2	27.1	26.9	26.7	26.5
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.9	58.9	58.9	58.9	58.8	58.7	58.6	58.5
102.5°	73.0	73.1	73.2	73.2	73.1	73.0	73.0	72.9
105°	94.3	94.5	94.7	94.8	94.8	94.8	94.8	94.8
107.5°	117.3	117.3	117.4	117.3	116.8	116.3	115.9	115.5
110°	132.8	132.8	132.8	132.6	132.3	132.1	131.8	131.5



TEST NUMBER: P331788-830

CATALOG NUMBER: S122RDIW-S485D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	148.5	148.2	148.0	147.7	147.5	147.3	147.1	146.9
115°	172.3	172.2	172.1	171.9	171.6	171.4	171.1	170.8
117.5°	195.5	195.2	195.0	194.7	194.4	194.2	193.9	193.6
120°	210.9	210.9	210.9	210.8	210.6	210.3	210.0	209.7
122.5°	226.9	226.7	226.4	226.2	226.0	225.8	225.6	225.4
125°	250.5	250.2	250.0	249.8	249.7	249.6	249.5	249.4
127.5°	273.4	273.1	272.8	272.5	272.1	271.8	271.5	271.3
130°	289.2	289.0	288.8	288.5	288.1	287.8	287.4	287.0
132.5°	304.4	304.0	303.6	303.2	302.9	302.6	302.3	302.0
135°	326.9	326.8	326.7	326.5	326.2	325.9	325.6	325.4
137.5°	348.5	348.4	348.4	348.1	347.7	347.3	346.9	346.6
140°	363.0	363.0	363.0	362.8	362.4	362.0	361.7	361.3
142.5°	376.1	376.2	376.3	376.1	375.7	375.3	374.9	374.6
145°	396.1	396.2	396.2	396.1	395.7	395.3	394.9	394.5
147.5°	413.5	413.8	414.0	413.9	413.5	413.1	412.7	412.5
150°	424.6	424.9	425.2	425.2	424.9	424.6	424.3	424.0
152.5°	435.6	436.0	436.4	436.4	436.0	435.6	435.4	435.0
155°	449.8	450.3	450.7	450.8	450.5	450.3	450.0	449.7
157.5°	462.7	463.4	464.0	464.1	463.6	463.2	462.8	462.3
160°	470.4	471.0	471.6	471.6	471.3	470.9	470.5	470.1
162.5°	477.4	478.1	478.7	478.8	478.3	477.9	477.4	477.0
165°	486.4	487.1	487.8	487.9	487.4	486.9	486.4	486.0
167.5°	493.9	494.6	495.2	495.3	494.7	494.3	493.8	493.3
170°	497.9	498.6	499.3	499.4	498.8	498.2	497.7	497.1
172.5°	501.1	501.7	502.4	502.4	501.8	501.2	500.7	500.1
175°	504.4	505.0	505.7	505.8	505.2	504.6	504.1	503.5
177.5°	506.0	506.3	506.8	506.8	506.3	506.0	505.5	505.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1

(END OF REPORT)