

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331837

Luminaire Tested: **S122RDIW-S865D1240U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331837
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1240U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8258.5 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	89	85	87	84	81	78	69	67	65	55	54	53	42	42	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	33	31	26
4	74	64	57	51	67	59	52	48	49	44	41	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	33	30	28	26	24	21
6	63	52	44	39	58	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	37	31	28	30	26	24	24	22	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	48	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.2
10°-20°	504.4	6.1
20°-30°	650.0	7.9
30°-40°	617.7	7.5
40°-50°	529.1	6.4
50°-60°	402.9	4.9
60°-70°	254.7	3.1
70°-80°	127.2	1.5
80°-90°	37.3	0.5
90°-100°	56.4	0.7
100°-110°	206.8	2.5
110°-120°	552.8	6.7
120°-130°	912.5	11.0
130°-140°	970.4	11.8
140°-150°	902.0	10.9
150°-160°	725.2	8.8
160°-170°	467.3	5.7
170°-180°	160.9	1.9
0°-30°	1335.4	16.2
0°-40°	1953.1	23.6
0°-60°	2885.1	34.9
0°-90°	3304.3	40.0
90°-120°	816.0	9.9
90°-150°	3600.9	43.6
90°-180°	4954.0	60.0
0°-180°	8258.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	27
90°	33	1	33	1	33	16
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	703	100	703	100	251
125°	1046	994	1046	994	1046	905
135°	1271	1231	1271	1231	1271	980
145°	1450	1428	1450	1428	1450	907
155°	1573	1572	1573	1572	1573	726
165°	1653	1656	1653	1656	1653	467
175°	1684	1694	1684	1694	1684	160
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	15.1	15.5	15.4	15.3	15.2	15.0	14.7	15.0	14.2	14.4	13.5
90°	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2	25.8	24.5	22.3
92.5°	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8	29.1	28.4	27.3
95°	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4	49.1	47.7	45.8
97.5°	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0	64.9	63.9	59.5
100°	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1	71.9	69.7	65.1
102.5°	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3	74.5	71.7	110.3
105°	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6	77.6	74.6	148.8
107.5°	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4	101.4	104.5	193.5
110°	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7	186.9	214.1	292.6



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6	440.8	539.9	559.4
115°	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0	628.9	754.8	748.0
117.5°	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1	805.5	836.0	831.3
120°	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2	899.9	896.6	891.8
122.5°	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3	956.3	954.4	949.1
125°	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5	1035.6	1033.7	1028.5
127.5°	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6	1107.9	1105.1	1101.2
130°	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1	1154.1	1151.1	1148.1
132.5°	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2	1199.6	1197.1	1194.1
135°	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6	1263.9	1261.2	1258.7
137.5°	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4	1323.8	1321.1	1318.3
140°	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2	1362.7	1360.3	1357.3
142.5°	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9	1398.7	1396.5	1393.0
145°	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9	1449.0	1447.1	1442.5
147.5°	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5	1493.1	1491.6	1487.1
150°	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3	1519.7	1518.1	1513.7
152.5°	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8	1544.2	1542.5	1538.4
155°	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8	1577.2	1575.6	1572.3
157.5°	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7	1604.8	1603.0	1600.7
160°	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9	1621.2	1619.6	1618.0
162.5°	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0	1636.1	1634.3	1632.9
165°	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6	1651.8
167.5°	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8	1669.9	1668.0	1667.3
170°	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7	1677.8	1675.9	1675.3
172.5°	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5	1683.6	1681.7	1681.2
175°	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9	1690.0	1688.1	1687.6
177.5°	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6	1691.1	1689.6	1689.3
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	13.0	13.1	12.7	11.7	11.6	11.5	13.6	15.6	14.1	13.1	12.7
90°	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7	24.4	24.2	23.9
95°	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5	70.5	61.6	52.6
97.5°	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8	132.5	107.2	82.0
100°	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5	179.3	142.0	104.8
102.5°	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1	273.2	265.3	257.5
105°	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9	380.0	388.2	396.3
107.5°	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4	481.9	488.5	495.1
110°	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9	547.6	553.3	559.0



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5	609.6	614.6	619.7
115°	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4	708.0	712.6	717.2
117.5°	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7	796.9	802.0	807.2
120°	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3	860.4	864.4	868.5
122.5°	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1	915.4	919.7	924.0
125°	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5	998.0	1001.6	1005.1
127.5°	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1	1074.0	1077.9	1081.9
130°	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1	1122.4	1126.8	1131.1
132.5°	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0	1170.7	1174.4	1178.1
135°	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6	1234.9	1239.3	1243.6
137.5°	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9	1298.0	1301.0	1304.1
140°	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0	1339.2	1341.4	1343.5
142.5°	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3	1374.2	1376.2	1378.1
145°	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5	1427.3	1427.0	1426.7
147.5°	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7	1474.7	1473.7	1472.6
150°	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1	1505.2	1503.3	1501.3
152.5°	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5	1531.4	1529.2	1527.1
155°	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9	1569.4	1567.0	1564.5
157.5°	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0	1599.9	1597.8	1595.8
160°	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1618.0	1616.3	1614.7
162.5°	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3	1633.6	1632.0	1630.4
165°	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3	1654.7	1653.0	1651.4
167.5°	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0	1670.3	1668.7	1667.1
170°	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8	1679.1	1677.5	1675.9
172.5°	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6	1685.0	1683.4	1681.7
175°	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2	1692.3	1690.4	1688.5
177.5°	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4	1693.9	1692.4	1690.9
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	12.7	12.7	12.1	12.5	13.0	12.9	13.1	12.9	13.1	13.4	13.1
90°	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2	28.5	29.9	30.9
92.5°	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8	30.5	31.2	31.7
95°	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4	51.8	53.1	53.7
97.5°	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0	67.1	68.2	68.9
100°	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1	76.2	78.4	79.8
102.5°	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3	80.2	83.0	84.8
105°	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6	83.6	86.6	88.6
107.5°	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4	95.3	92.3	91.3
110°	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7	132.5	105.3	92.3



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6	242.5	143.3	94.1
115°	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0	377.2	251.3	178.6
117.5°	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1	744.6	714.2	666.8
120°	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2	906.4	909.7	893.0
122.5°	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3	960.3	962.2	959.6
125°	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5	1039.4	1041.3	1042.6
127.5°	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6	1113.4	1116.2	1117.7
130°	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1	1160.1	1163.0	1164.4
132.5°	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2	1204.7	1207.3	1208.4
135°	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6	1269.3	1272.1	1273.1
137.5°	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4	1329.1	1331.8	1332.6
140°	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2	1367.6	1370.1	1370.6
142.5°	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9	1403.2	1405.4	1405.8
145°	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9	1452.8	1454.7	1455.0
147.5°	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5	1495.9	1497.3	1497.4
150°	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3	1523.0	1524.6	1524.7
152.5°	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8	1547.4	1549.1	1549.0
155°	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8	1580.5	1582.1	1581.8
157.5°	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7	1608.5	1610.4	1610.2
160°	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9	1624.5	1626.1	1626.0
162.5°	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0	1639.8	1641.7	1641.4
165°	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2
167.5°	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8	1673.7	1675.6	1675.4
170°	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7	1681.6	1683.5	1683.2
172.5°	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5	1687.4	1689.3	1689.1
175°	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9	1693.8	1695.7	1695.3
177.5°	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6	1694.1	1695.7	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	13.2	12.8	13.4	13.0	13.4	12.8	13.2	13.1	13.4	13.1	12.9
90°	31.4	31.9	32.5	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2
92.5°	32.0	32.4	32.7	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8
95°	53.4	53.1	52.9	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4
97.5°	69.2	69.6	69.9	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0
100°	80.3	80.9	81.4	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1
102.5°	85.5	86.3	87.1	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3
105°	89.7	90.8	91.9	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6
107.5°	92.4	93.5	94.6	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4
110°	93.4	94.5	95.6	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.0	95.9	96.7	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6
115°	159.0	139.5	119.9	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0
117.5°	602.5	538.2	473.9	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1
120°	856.3	819.6	782.9	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2
122.5°	952.5	945.4	938.3	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3
125°	1043.4	1044.3	1045.1	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5
127.5°	1117.8	1118.0	1118.1	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6
130°	1164.1	1163.9	1163.6	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1
132.5°	1208.2	1207.9	1207.6	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2
135°	1272.6	1272.1	1271.5	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6
137.5°	1331.7	1330.8	1329.9	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4
140°	1369.2	1367.9	1366.5	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2
142.5°	1404.5	1403.1	1401.7	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9
145°	1453.6	1452.3	1450.9	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9
147.5°	1496.3	1495.1	1494.0	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5
150°	1523.4	1522.0	1520.6	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3
152.5°	1547.2	1545.4	1543.6	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8
155°	1579.6	1577.5	1575.3	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8
157.5°	1608.1	1606.0	1603.9	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7
160°	1624.1	1622.2	1620.3	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9
162.5°	1639.1	1636.7	1634.4	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0
165°	1658.3	1656.4	1654.5	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4
167.5°	1672.9	1670.5	1668.0	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8
170°	1680.8	1678.3	1675.9	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7
172.5°	1686.6	1684.2	1681.7	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5
175°	1692.6	1689.9	1687.1	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9
177.5°	1693.5	1691.5	1689.6	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	13.1	12.9	13.0	12.5	12.1	12.7	12.7	12.7	13.1	14.1	15.6
90°	25.8	24.5	22.3	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7
95°	49.1	47.7	45.8	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5
97.5°	64.9	63.9	59.5	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8
100°	71.9	69.7	65.1	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5
102.5°	74.5	71.7	110.3	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1
105°	77.6	74.6	148.8	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9
107.5°	101.4	104.5	193.5	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4
110°	186.9	214.1	292.6	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	440.8	539.9	559.4	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5
115°	628.9	754.8	748.0	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4
117.5°	805.5	836.0	831.3	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7
120°	899.9	896.6	891.8	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3
122.5°	956.3	954.4	949.1	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1
125°	1035.6	1033.7	1028.5	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5
127.5°	1107.9	1105.1	1101.2	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1
130°	1154.1	1151.1	1148.1	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1
132.5°	1199.6	1197.1	1194.1	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0
135°	1263.9	1261.2	1258.7	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6
137.5°	1323.8	1321.1	1318.3	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9
140°	1362.7	1360.3	1357.3	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0
142.5°	1398.7	1396.5	1393.0	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3
145°	1449.0	1447.1	1442.5	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5
147.5°	1493.1	1491.6	1487.1	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7
150°	1519.7	1518.1	1513.7	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1
152.5°	1544.2	1542.5	1538.4	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5
155°	1577.2	1575.6	1572.3	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9
157.5°	1604.8	1603.0	1600.7	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0
160°	1621.2	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6
162.5°	1636.1	1634.3	1632.9	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3
165°	1654.5	1652.6	1651.8	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3
167.5°	1669.9	1668.0	1667.3	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0
170°	1677.8	1675.9	1675.3	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8
172.5°	1683.6	1681.7	1681.2	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6
175°	1690.0	1688.1	1687.6	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2
177.5°	1691.1	1689.6	1689.3	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.6	11.5	11.6	11.7	12.7	13.1	13.0	13.5	14.4	14.2	15.0
90°	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2
92.5°	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8
95°	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4
97.5°	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0
100°	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1
102.5°	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3
105°	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6
107.5°	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4
110°	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6
115°	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0
117.5°	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1
120°	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2
122.5°	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3
125°	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5
127.5°	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6
130°	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1
132.5°	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2
135°	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6
137.5°	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4
140°	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2
142.5°	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9
145°	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9
147.5°	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5
150°	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3
152.5°	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8
155°	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8
157.5°	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7
160°	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9
162.5°	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0
165°	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4
167.5°	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8
170°	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7
172.5°	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5
175°	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9
177.5°	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	14.7	15.0	15.2	15.3	15.4	15.5	15.1
90°	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331837

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)