

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331792-830

Luminaire Tested: **S122RDIW-S485D710U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331792-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3920.6 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35																				
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30																				
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26																				
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23																				
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18																				
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16																				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.9
10°-20°	199.9	5.1
20°-30°	280.7	7.2
30°-40°	306.1	7.8
40°-50°	281.5	7.2
50°-60°	221.1	5.6
60°-70°	144.1	3.7
70°-80°	74.3	1.9
80°-90°	22.6	0.6
90°-100°	52.5	1.3
100°-110°	163.1	4.2
110°-120°	278.8	7.1
120°-130°	366.6	9.4
130°-140°	411.5	10.5
140°-150°	403.5	10.3
150°-160°	338.4	8.6
160°-170°	224.5	5.7
170°-180°	78.5	2.0
0°-30°	553.4	14.1
0°-40°	859.6	21.9
0°-60°	1362.1	34.7
0°-90°	1603.1	40.9
90°-120°	494.4	12.6
90°-150°	1676.1	42.8
90°-180°	2317.0	59.1
0°-180°	3920.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	10	24	23	24	3
95°	36	43	45	45	43	42
105°	150	152	154	155	155	159
115°	280	284	283	282	280	277
125°	407	413	411	409	408	364
135°	527	534	536	535	533	407
145°	639	644	648	649	646	399
155°	731	733	735	738	736	336
165°	795	795	795	799	796	224
175°	827	825	824	828	825	79
180°	829	829	829	829	829	



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.1	8.5	7.9	7.3	6.6	6.7	7.4	8.0	8.7	9.4	9.2
90°	0.7	2.5	4.4	6.3	8.2	10.8	14.2	17.6	21.0	24.5	24.1
92.5°	12.4	13.9	15.2	16.6	17.9	19.0	19.8	20.6	21.4	22.2	22.3
95°	36.4	37.9	39.5	41.0	42.6	43.5	43.8	44.1	44.5	44.8	44.8
97.5°	66.4	67.8	69.2	70.5	71.9	72.9	73.5	74.1	74.6	75.2	75.2
100°	88.8	90.1	91.3	92.6	93.8	94.6	95.1	95.6	96.0	96.5	96.5
102.5°	112.4	113.3	114.3	115.3	116.3	117.1	117.7	118.3	118.9	119.4	119.6
105°	150.3	150.8	151.3	151.7	152.2	152.6	153.0	153.3	153.5	153.9	154.2
107.5°	188.7	189.4	190.1	190.8	191.4	191.8	191.8	191.8	191.8	191.8	191.9
110°	213.3	214.2	215.2	216.1	217.1	217.5	217.5	217.5	217.5	217.5	217.5



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.2	241.1	242.0	243.0	243.9	244.3	244.2	244.0	243.9	243.8	243.5
115°	279.7	280.7	281.6	282.6	283.5	283.8	283.5	283.1	282.9	282.6	282.4
117.5°	319.2	320.5	321.7	322.9	324.1	324.3	323.5	322.6	321.8	320.9	320.6
120°	345.5	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	345.5
122.5°	369.6	371.1	372.6	374.0	375.5	375.9	374.9	374.1	373.2	372.4	372.0
125°	407.1	408.5	409.8	411.2	412.6	413.1	412.6	412.2	411.7	411.2	410.8
127.5°	443.6	445.4	447.1	448.8	450.6	451.3	450.7	450.2	449.6	449.0	448.5
130°	466.5	468.5	470.5	472.6	474.6	475.4	475.1	474.9	474.5	474.2	473.9
132.5°	492.3	493.9	495.6	497.2	498.8	499.7	499.7	499.8	499.9	499.9	499.3
135°	526.7	528.4	530.1	531.8	533.5	534.5	534.8	535.2	535.5	535.7	535.6
137.5°	562.9	564.3	565.7	567.1	568.4	569.4	569.8	570.2	570.6	571.0	570.9
140°	584.8	586.1	587.5	588.9	590.3	591.4	592.2	593.0	593.7	594.5	594.5
142.5°	607.1	608.5	609.9	611.3	612.7	613.7	614.2	614.7	615.2	615.8	615.9
145°	639.2	640.4	641.4	642.5	643.7	644.6	645.5	646.5	647.4	648.4	648.5
147.5°	668.0	669.2	670.5	671.8	673.2	674.1	674.8	675.3	676.0	676.7	676.9
150°	687.5	688.4	689.4	690.3	691.3	692.0	692.7	693.2	693.9	694.6	695.0
152.5°	704.8	705.8	706.7	707.7	708.6	709.5	710.2	711.0	711.7	712.5	713.0
155°	730.8	731.3	731.8	732.3	732.7	733.2	733.7	734.1	734.6	735.1	735.8
157.5°	753.1	753.5	753.8	754.0	754.4	754.7	755.0	755.3	755.5	755.8	756.9
160°	766.6	766.9	767.1	767.5	767.8	768.1	768.2	768.4	768.5	768.6	769.6
162.5°	778.8	778.9	779.0	779.0	779.1	779.2	779.4	779.6	779.7	779.9	780.9
165°	795.2	795.0	794.9	794.8	794.7	794.6	794.6	794.6	794.6	794.6	795.6
167.5°	809.0	808.5	808.0	807.6	807.1	806.8	806.8	806.7	806.7	806.7	807.8
170°	816.2	815.8	815.3	814.8	814.4	814.1	813.9	813.7	813.6	813.4	814.5
172.5°	821.2	820.8	820.3	819.8	819.4	819.1	818.9	818.8	818.6	818.4	819.5
175°	827.4	827.0	826.5	826.0	825.6	825.2	824.8	824.5	824.3	823.9	825.0
177.5°	829.9	829.5	829.2	828.8	828.4	828.1	827.8	827.6	827.4	827.1	827.8
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	9.0	8.9	8.7	8.6	8.6	8.7	8.7	8.7
90°	23.8	23.6	23.3	23.2	23.3	23.5	23.7	23.8
92.5°	22.3	22.4	22.5	22.5	22.5	22.6	22.6	22.6
95°	44.8	44.8	44.8	44.6	44.3	44.0	43.6	43.4
97.5°	75.2	75.2	75.2	75.2	75.2	75.2	75.1	75.1
100°	96.5	96.5	96.5	96.4	96.3	96.1	96.0	95.9
102.5°	119.7	119.8	120.0	120.0	119.8	119.6	119.5	119.3
105°	154.5	154.8	155.1	155.2	155.2	155.2	155.2	155.2
107.5°	192.0	192.2	192.3	192.0	191.2	190.6	189.8	189.2
110°	217.5	217.5	217.5	217.3	216.8	216.3	215.8	215.5



TEST NUMBER: P331792-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	243.1	242.7	242.3	242.0	241.7	241.3	240.9	240.6
115°	282.3	282.1	281.9	281.6	281.2	280.7	280.2	279.7
117.5°	320.2	319.8	319.4	319.0	318.5	318.0	317.5	317.1
120°	345.5	345.5	345.5	345.3	344.8	344.3	343.8	343.4
122.5°	371.6	371.3	370.9	370.5	370.1	369.9	369.5	369.2
125°	410.3	409.8	409.3	409.1	409.0	408.8	408.6	408.5
127.5°	447.9	447.3	446.8	446.3	445.7	445.3	444.8	444.3
130°	473.6	473.3	473.0	472.5	471.8	471.3	470.6	470.0
132.5°	498.6	497.9	497.2	496.6	496.2	495.6	495.1	494.6
135°	535.5	535.3	535.2	534.8	534.3	533.9	533.4	532.9
137.5°	570.7	570.6	570.5	570.1	569.5	568.9	568.3	567.6
140°	594.5	594.5	594.5	594.2	593.6	593.0	592.3	591.7
142.5°	616.0	616.1	616.2	616.0	615.4	614.7	614.2	613.5
145°	648.7	648.8	648.9	648.8	648.1	647.5	646.9	646.3
147.5°	677.3	677.6	678.0	677.9	677.3	676.7	676.1	675.5
150°	695.4	695.9	696.4	696.4	695.9	695.4	695.0	694.6
152.5°	713.6	714.2	714.8	714.8	714.2	713.6	713.0	712.5
155°	736.6	737.4	738.2	738.4	737.9	737.4	737.0	736.5
157.5°	757.9	758.9	760.0	760.2	759.4	758.7	757.9	757.1
160°	770.5	771.5	772.4	772.5	771.9	771.3	770.7	770.1
162.5°	781.9	783.1	784.1	784.2	783.4	782.8	782.0	781.3
165°	796.7	797.8	798.9	799.1	798.2	797.5	796.7	796.0
167.5°	808.9	809.9	811.1	811.2	810.4	809.5	808.8	807.9
170°	815.6	816.7	817.7	817.8	816.9	816.0	815.0	814.1
172.5°	820.7	821.7	822.8	822.8	822.0	821.0	820.1	819.2
175°	826.0	827.2	828.3	828.3	827.4	826.5	825.6	824.6
177.5°	828.6	829.3	830.1	830.1	829.3	828.6	827.8	827.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8

(END OF REPORT)