

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331838

Luminaire Tested: **S122RDIW-S865D1240U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331838  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1240U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7602.7 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.0	2.4
10°-20°	504.4	6.6
20°-30°	650.0	8.5
30°-40°	617.7	8.1
40°-50°	529.1	7.0
50°-60°	402.9	5.3
60°-70°	254.7	3.4
70°-80°	127.2	1.7
80°-90°	39.2	0.5
90°-100°	97.4	1.3
100°-110°	302.4	4.0
110°-120°	516.9	6.8
120°-130°	679.7	8.9
130°-140°	762.9	10.0
140°-150°	748.1	9.8
150°-160°	627.4	8.3
160°-170°	416.2	5.5
170°-180°	145.5	1.9
0°-30°	1335.4	17.6
0°-40°	1953.1	25.7
0°-60°	2885.1	37.9
0°-90°	3306.3	43.5
90°-120°	916.6	12.1
90°-150°	3107.4	40.9
90°-180°	4296.0	56.5
0°-180°	7602.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	27
90°	44	1	44	1	44	20
95°	80	67	80	67	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	512
125°	757	755	757	755	757	675
135°	988	976	988	976	988	761
145°	1198	1185	1198	1185	1198	748
155°	1365	1355	1365	1355	1365	628
165°	1476	1474	1476	1474	1476	416
175°	1529	1534	1529	1534	1529	145
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	17.3	17.8	17.7	17.7	17.6	17.6	17.8	18.4	18.0	18.6	16.8
90°	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2	44.8	45.4	39.0
92.5°	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5	41.3	41.2	39.7
95°	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0	83.0	83.0	82.4
97.5°	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5	139.5	139.5	138.4
100°	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9	178.9	178.9	178.1
102.5°	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9	221.7	221.5	220.4
105°	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4	285.8	285.3	284.7
107.5°	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0	355.8	355.5	355.5
110°	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6	451.3	452.0	452.2
115°	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3	523.6	523.8	524.4
117.5°	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5	594.2	594.9	596.5
120°	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5	640.5	640.5	642.8
122.5°	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0	689.6	690.3	691.9
125°	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7	761.6	762.4	763.3
127.5°	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4	831.4	832.4	833.5
130°	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0	878.5	879.1	879.7
132.5°	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3	925.6	926.8	926.7
135°	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7	992.9	993.2	992.7
137.5°	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1	1058.4	1058.6	1057.8
140°	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1	1102.1	1102.1	1100.7
142.5°	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0	1141.8	1141.6	1140.6
145°	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6	1202.3	1202.0	1200.3
147.5°	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6	1255.0	1254.4	1253.2
150°	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6	1286.4
152.5°	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8	1319.4
155°	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7	1364.2	1362.8	1361.9
157.5°	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1	1403.1	1401.2	1400.6
160°	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5	1426.7	1425.0	1424.7
162.5°	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7	1447.7	1445.8	1445.5
165°	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0	1475.0	1473.0	1473.0
167.5°	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6	1497.6	1495.5	1495.6
170°	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0	1510.0	1508.0	1508.3
172.5°	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4	1519.4	1517.3	1517.6
175°	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5	1529.5	1527.4	1528.0
177.5°	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4	1533.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	15.6	14.8	13.6	12.0	11.9	11.7	13.7	15.7	14.2	13.3	13.0
90°	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1	25.6	28.2	30.7
95°	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4	70.3	73.2	76.1
97.5°	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2	125.7	128.3	130.8
100°	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7	167.0	169.3	171.6
102.5°	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2	210.1	211.9	213.8
105°	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8	279.6	280.5	281.4
107.5°	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8	351.1	352.4	353.6
110°	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5	397.2	398.9	400.7





TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3	447.0	448.7	450.5
115°	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7	520.4	522.1	523.8
117.5°	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8	594.1	596.4	598.7
120°	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	642.8	645.2	647.5
122.5°	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1	687.9	690.7	693.4
125°	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6	757.2	759.8	762.4
127.5°	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3	825.6	828.9	832.2
130°	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9	868.6	872.4	876.1
132.5°	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6	915.6	918.7	921.7
135°	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4	979.5	982.7	985.9
137.5°	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5	1046.1	1048.7	1051.3
140°	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0	1086.6	1089.2	1091.8
142.5°	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5	1128.1	1130.7	1133.3
145°	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1	1187.2	1189.2	1191.2
147.5°	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3	1240.7	1243.1	1245.6
150°	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6	1276.3	1278.1	1279.8
152.5°	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8	1308.5	1310.2	1311.9
155°	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0	1355.9	1356.7	1357.6
157.5°	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2	1396.8	1397.4	1398.0
160°	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1	1421.7	1422.3	1422.9
162.5°	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9	1444.1	1444.2	1444.3
165°	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3	1474.0	1473.7	1473.4
167.5°	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7	1498.8	1498.0	1497.1
170°	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2	1512.3	1511.5	1510.6
172.5°	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5	1521.7	1520.8	1519.9
175°	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9	1533.1	1532.2	1531.3
177.5°	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6	1537.9	1537.2	1536.5
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	13.1	13.6	13.8	15.0	16.3	17.0	16.9	16.3	16.2	16.0	15.5
90°	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2	43.7	43.1	42.9
92.5°	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5	41.6	41.7	41.8
95°	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0	83.0	83.0	82.7
97.5°	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5	139.5	139.5	139.5
100°	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9	178.9	178.9	178.8
102.5°	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9	222.2	222.4	222.4
105°	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4	287.0	287.6	287.9
107.5°	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0	356.2	356.5	355.9
110°	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	402.8



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6	449.9	449.2	448.6
115°	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3	523.0	522.7	522.1
117.5°	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5	592.8	592.1	591.4
120°	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5	640.5	640.5	640.1
122.5°	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0	688.3	687.6	686.9
125°	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7	759.8	759.0	758.4
127.5°	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4	829.3	828.3	827.3
130°	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0	877.4	876.8	876.0
132.5°	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3	923.0	921.8	920.7
135°	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7	992.4	992.1	991.5
137.5°	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1	1057.9	1057.7	1057.0
140°	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1	1102.1	1102.1	1101.6
142.5°	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0	1142.3	1142.5	1142.0
145°	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6	1202.9	1203.1	1202.7
147.5°	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6	1256.3	1256.9	1256.7
150°	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0
152.5°	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1
155°	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7	1367.1	1368.5	1368.8
157.5°	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1	1407.0	1409.0	1409.3
160°	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5	1430.2	1431.9	1432.2
162.5°	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7	1451.6	1453.6	1453.9
165°	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0	1479.0	1481.1	1481.3
167.5°	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6	1501.6	1503.6	1503.9
170°	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0	1514.0	1516.1	1516.2
172.5°	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4	1523.4	1525.4	1525.5
175°	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5	1533.5	1535.5	1535.7
177.5°	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	15.5	15.1	15.7	15.2	15.7	15.1	15.5	15.5	16.0	16.2	16.3
90°	43.2	43.5	43.8	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5
95°	82.1	81.5	81.0	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0
97.5°	139.4	139.4	139.3	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5
100°	178.5	178.2	177.9	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9
102.5°	222.1	221.8	221.5	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9
105°	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4
107.5°	354.6	353.3	351.9	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0
110°	402.0	401.1	400.2	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	447.9	447.3	446.7	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6
115°	521.3	520.4	519.5	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3
117.5°	590.5	589.6	588.8	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5
120°	639.2	638.4	637.5	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5
122.5°	686.3	685.6	685.0	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0
125°	758.1	757.8	757.5	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7
127.5°	826.4	825.5	824.6	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4
130°	874.8	873.7	872.5	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0
132.5°	919.8	918.8	917.9	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3
135°	990.6	989.8	988.9	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7
137.5°	1055.8	1054.7	1053.5	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1
140°	1100.4	1099.3	1098.1	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1
142.5°	1140.9	1139.7	1138.6	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0
145°	1201.6	1200.4	1199.3	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6
147.5°	1255.6	1254.5	1253.4	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6
150°	1290.2	1289.3	1288.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3
152.5°	1324.0	1323.0	1321.9	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0
155°	1368.0	1367.1	1366.2	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7
157.5°	1407.9	1406.5	1405.1	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1
160°	1431.1	1429.9	1428.8	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5
162.5°	1452.5	1451.1	1449.7	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7
165°	1479.9	1478.5	1477.0	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0
167.5°	1502.4	1500.9	1499.4	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6
170°	1514.5	1512.8	1511.0	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0
172.5°	1523.8	1522.1	1520.4	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4
175°	1533.9	1532.2	1530.5	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5
177.5°	1537.6	1536.2	1534.8	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	16.9	17.0	16.3	15.0	13.8	13.6	13.1	13.0	13.3	14.2	15.7
90°	44.8	45.4	39.0	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3
92.5°	41.3	41.2	39.7	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1
95°	83.0	83.0	82.4	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4
97.5°	139.5	139.5	138.4	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2
100°	178.9	178.9	178.1	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7
102.5°	221.7	221.5	220.4	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2
105°	285.8	285.3	284.7	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8
107.5°	355.8	355.5	355.5	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8
110°	403.3	403.3	403.3	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.3	452.0	452.2	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3
115°	523.6	523.8	524.4	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7
117.5°	594.2	594.9	596.5	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8
120°	640.5	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5
122.5°	689.6	690.3	691.9	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1
125°	761.6	762.4	763.3	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6
127.5°	831.4	832.4	833.5	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3
130°	878.5	879.1	879.7	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9
132.5°	925.6	926.8	926.7	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6
135°	992.9	993.2	992.7	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4
137.5°	1058.4	1058.6	1057.8	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5
140°	1102.1	1102.1	1100.7	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0
142.5°	1141.8	1141.6	1140.6	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5
145°	1202.3	1202.0	1200.3	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1
147.5°	1255.0	1254.4	1253.2	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3
150°	1288.4	1287.6	1286.4	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6
152.5°	1321.9	1320.8	1319.4	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8
155°	1364.2	1362.8	1361.9	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0
157.5°	1403.1	1401.2	1400.6	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2
160°	1426.7	1425.0	1424.7	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1
162.5°	1447.7	1445.8	1445.5	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9
165°	1475.0	1473.0	1473.0	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3
167.5°	1497.6	1495.5	1495.6	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7
170°	1510.0	1508.0	1508.3	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2
172.5°	1519.4	1517.3	1517.6	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5
175°	1529.5	1527.4	1528.0	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9
177.5°	1534.8	1533.4	1533.9	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.7	11.7	11.9	12.0	13.6	14.8	15.6	16.8	18.6	18.0	18.4
90°	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2
92.5°	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5
95°	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0
97.5°	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5
100°	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9
102.5°	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9
105°	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4
107.5°	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0
110°	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3





TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6
115°	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3
117.5°	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5
120°	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5
122.5°	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0
125°	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7
127.5°	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4
130°	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0
132.5°	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3
135°	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7
137.5°	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1
140°	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1
142.5°	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0
145°	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6
147.5°	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6
150°	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3
152.5°	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0
155°	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7
157.5°	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1
160°	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5
162.5°	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7
165°	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0
167.5°	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6
170°	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0
172.5°	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4
175°	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5
177.5°	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	17.8	17.6	17.6	17.7	17.7	17.8	17.3
90°	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331838

CATALOG NUMBER: S122RDIW-S865D1240U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)