

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331795-830

Luminaire Tested: **S122RDIW-S485D970U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331795-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5250.4 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	29	24	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	19	16	15	12
8	52	40	33	28	47	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	27	22	40	31	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.4
10°-20°	199.9	3.8
20°-30°	280.7	5.3
30°-40°	306.1	5.8
40°-50°	281.5	5.4
50°-60°	221.1	4.2
60°-70°	144.1	2.7
70°-80°	74.3	1.4
80°-90°	22.4	0.4
90°-100°	41.5	0.8
100°-110°	152.3	2.9
110°-120°	407.0	7.8
120°-130°	671.8	12.8
130°-140°	714.5	13.6
140°-150°	664.1	12.6
150°-160°	533.9	10.2
160°-170°	344.1	6.6
170°-180°	118.4	2.3
0°-30°	553.4	10.5
0°-40°	859.6	16.4
0°-60°	1362.1	25.9
0°-90°	1602.9	30.5
90°-120°	600.8	11.4
90°-150°	2651.1	50.5
90°-180°	3648.0	69.5
0°-180°	5250.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	11	18	22	24	4
95°	58	31	35	39	39	72
105°	274	286	55	64	68	293
115°	518	534	556	158	74	510
125°	732	744	761	767	770	653
135°	906	920	929	937	936	700
145°	1051	1051	1066	1071	1067	657
155°	1157	1150	1160	1165	1158	533
165°	1220	1215	1217	1222	1217	344
175°	1247	1242	1243	1248	1240	119
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.2	8.7	8.1	7.5	7.0	6.8	7.2	7.4	7.8	8.1	8.2
90°	0.9	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0
92.5°	18.2	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4
95°	58.5	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1
97.5°	116.2	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8
100°	159.4	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0
102.5°	207.0	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9
105°	273.8	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1
107.5°	350.0	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6
110°	399.0	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.1	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5
115°	517.8	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0
117.5°	582.9	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0
120°	630.5	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6
122.5°	670.8	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1
125°	732.2	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4
127.5°	787.9	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7
130°	823.2	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7
132.5°	859.2	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3
135°	906.1	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6
137.5°	953.4	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7
140°	984.4	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3
142.5°	1010.3	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8
145°	1051.0	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9
147.5°	1086.6	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3
150°	1109.6	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9
152.5°	1129.1	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9
155°	1157.3	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2
157.5°	1179.5	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6
160°	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6
162.5°	1204.0	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6
165°	1219.5	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1
167.5°	1231.0	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5
170°	1237.5	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3
172.5°	1241.8	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6
175°	1247.4	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3
177.5°	1248.3	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	8.3	8.3	8.4	8.5	8.6	8.7	8.8	8.8
90°	20.0	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.0	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	37.1	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	48.6	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	54.6	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	56.9	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	59.4	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	72.4	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	117.5	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331795-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	251.5	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	370.3	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	570.6	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	665.0	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	705.6	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	763.8	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	817.7	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	851.9	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	885.1	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	932.6	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	976.6	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1005.1	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1031.4	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1068.3	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1100.3	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1120.1	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1138.1	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1162.4	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1182.9	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1194.9	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1206.0	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1230.9	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1236.7	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1241.0	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1245.7	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1246.2	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)