

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331827

Luminaire Tested: **S122RDIW-S865D435U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331827
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D435U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4748.2 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	49	46	44	40
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	35
5	72	61	53	47	68	57	50	45	51	46	41	46	41	37	40	37	34	31
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.9
10°-20°	376.8	7.9
20°-30°	529.2	11.1
30°-40°	577.1	12.2
40°-50°	530.6	11.2
50°-60°	416.7	8.8
60°-70°	271.7	5.7
70°-80°	140.1	2.9
80°-90°	37.8	0.8
90°-100°	19.7	0.4
100°-110°	72.3	1.5
110°-120°	193.1	4.1
120°-130°	318.8	6.7
130°-140°	339.1	7.1
140°-150°	315.2	6.6
150°-160°	253.4	5.3
160°-170°	163.3	3.4
170°-180°	56.2	1.2
0°-30°	1043.3	22.0
0°-40°	1620.3	34.1
0°-60°	2567.6	54.1
0°-90°	3017.2	63.5
90°-120°	285.1	6.0
90°-150°	1258.2	26.5
90°-180°	1731.0	36.5
0°-180°	4748.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	0	5	8	11	12	4
95°	28	15	17	19	18	34
105°	130	136	26	31	32	139
115°	246	253	264	75	35	242
125°	348	353	361	364	365	310
135°	430	437	441	445	444	332
145°	499	499	506	508	506	312
155°	549	546	550	553	550	253
165°	579	576	577	580	577	163
175°	592	589	590	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.1	15.4	13.7	12.0	10.4	9.6	9.7	9.9	10.1	10.2	10.1
90°	0.4	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2
95°	27.8	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1
97.5°	55.1	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7
100°	75.7	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1
102.5°	98.2	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0
105°	129.9	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1
107.5°	166.1	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4
110°	189.3	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0
115°	245.8	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7
117.5°	276.6	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5
120°	299.2	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4
122.5°	318.3	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2
125°	347.5	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8
127.5°	373.9	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1
130°	390.7	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2
132.5°	407.8	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2
135°	430.0	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6
137.5°	452.5	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5
140°	467.2	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1
142.5°	479.5	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7
145°	498.8	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3
147.5°	515.6	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7
150°	526.6	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0
152.5°	535.8	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5
155°	549.2	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1
157.5°	559.7	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7
160°	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5
162.5°	571.4	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7
165°	578.7	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1
167.5°	584.2	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5
170°	587.3	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2
172.5°	589.3	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3
175°	592.0	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5
177.5°	592.4	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	9.9	9.8	9.6	9.6	9.6	9.7	9.7	9.7
90°	9.5	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	17.6	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.1	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	25.9	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	27.0	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	28.2	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	34.4	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	55.8	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331827

CATALOG NUMBER: S122RDIW-S865D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	119.4	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	175.8	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	270.8	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	315.6	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	334.8	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	362.5	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	388.1	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	404.3	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.1	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	442.6	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	463.5	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.0	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	489.5	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.0	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.2	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	531.6	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.1	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	551.7	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	561.4	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.0	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	572.3	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.2	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	586.9	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	588.9	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.2	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.4	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)