

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331796-830

Luminaire Tested: **S122RDIW-S485D970U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331796-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4767.5 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	28	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	15				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.5
10°-20°	199.9	4.2
20°-30°	280.7	5.9
30°-40°	306.1	6.4
40°-50°	281.5	5.9
50°-60°	221.1	4.6
60°-70°	144.1	3.0
70°-80°	74.3	1.6
80°-90°	23.8	0.5
90°-100°	71.7	1.5
100°-110°	222.6	4.7
110°-120°	380.6	8.0
120°-130°	500.5	10.5
130°-140°	561.7	11.8
140°-150°	550.8	11.6
150°-160°	462.0	9.7
160°-170°	306.4	6.4
170°-180°	107.1	2.2
0°-30°	553.4	11.6
0°-40°	859.6	18.0
0°-60°	1362.1	28.6
0°-90°	1604.3	33.7
90°-120°	674.9	14.2
90°-150°	2287.8	48.0
90°-180°	3163.0	66.3
0°-180°	4767.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	13	33	32	32	4
95°	50	59	61	61	59	57
105°	205	208	210	212	212	217
115°	382	387	386	385	382	378
125°	556	564	561	559	558	496
135°	719	729	731	730	728	555
145°	872	879	885	886	882	545
155°	998	1000	1003	1008	1005	459
165°	1085	1085	1084	1090	1086	306
175°	1129	1126	1124	1131	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.2	8.7	8.2	7.7	7.3	7.4	8.4	9.3	10.3	11.2	10.9
90°	0.9	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0
92.5°	17.0	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4
95°	49.7	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1
97.5°	90.7	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7
100°	121.2	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8
102.5°	153.4	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2
105°	205.3	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5
107.5°	257.6	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9
110°	291.2	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.8	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2
115°	381.8	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5
117.5°	435.7	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5
120°	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6
122.5°	504.4	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7
125°	555.6	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7
127.5°	605.5	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1
130°	636.8	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9
132.5°	671.8	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5
135°	718.9	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0
137.5°	768.3	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2
140°	798.1	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4
142.5°	828.7	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7
145°	872.5	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1
147.5°	911.7	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0
150°	938.4	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6
152.5°	962.1	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2
155°	997.6	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4
157.5°	1027.9	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0
160°	1046.3	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5
162.5°	1063.1	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9
165°	1085.4	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0
167.5°	1104.2	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6
170°	1114.1	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7
172.5°	1121.0	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6
175°	1129.4	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1
177.5°	1132.8	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	10.7	10.6	10.4	10.3	10.3	10.4	10.4	10.5
90°	32.5	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.5	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.4	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	210.8	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.1	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.9	296.6	296.0	295.3	294.6	294.1



TEST NUMBER: P331796-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.8	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.2	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	437.0	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	507.3	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	560.1	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	611.3	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.4	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	680.5	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.8	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	779.0	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	840.8	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.4	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.4	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1005.5	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1034.5	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1051.7	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1067.3	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1087.5	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1104.1	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1113.2	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1120.1	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1127.6	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)