

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331820-830

Luminaire Tested: **S122RDIW-S675D1240U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331820-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6242.1 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	1.6
10°-20°	273.3	4.4
20°-30°	383.7	6.1
30°-40°	418.4	6.7
40°-50°	384.7	6.2
50°-60°	302.2	4.8
60°-70°	197.0	3.2
70°-80°	101.6	1.6
80°-90°	32.1	0.5
90°-100°	91.8	1.5
100°-110°	285.0	4.6
110°-120°	487.2	7.8
120°-130°	640.7	10.3
130°-140°	719.1	11.5
140°-150°	705.1	11.3
150°-160°	591.4	9.5
160°-170°	392.2	6.3
170°-180°	137.1	2.2
0°-30°	756.5	12.1
0°-40°	1174.9	18.8
0°-60°	1861.8	29.8
0°-90°	2192.6	35.1
90°-120°	864.0	13.8
90°-150°	2928.8	46.9
90°-180°	4050.0	64.9
0°-180°	6242.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	17	43	40	42	5
95°	64	75	78	78	76	73
105°	263	266	269	271	271	277
115°	489	496	494	492	489	483
125°	711	721	719	715	714	635
135°	920	933	936	935	931	711
145°	1117	1126	1133	1134	1129	698
155°	1277	1281	1284	1290	1287	588
165°	1390	1388	1388	1396	1391	392
175°	1446	1442	1440	1447	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.5	11.9	11.1	10.4	9.7	9.9	11.1	12.3	13.5	14.7	14.4
90°	1.2	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2
92.5°	21.8	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9
95°	63.5	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2
97.5°	116.1	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5
100°	155.2	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6
102.5°	196.2	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0
105°	262.8	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4
107.5°	329.7	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4
110°	372.8	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.7	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4
115°	488.9	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5
117.5°	557.8	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1
120°	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7
122.5°	645.7	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0
125°	711.2	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8
127.5°	775.1	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6
130°	815.2	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0
132.5°	860.2	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4
135°	920.3	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9
137.5°	983.5	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6
140°	1021.7	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8
142.5°	1060.8	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2
145°	1117.0	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2
147.5°	1167.2	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9
150°	1201.4	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4
152.5°	1231.7	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9
155°	1277.1	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8
157.5°	1316.0	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5
160°	1339.4	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7
162.5°	1360.9	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5
165°	1389.6	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3
167.5°	1413.5	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6
170°	1426.3	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2
172.5°	1435.0	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1
175°	1445.8	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6
177.5°	1450.2	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	14.1	13.9	13.6	13.5	13.6	13.6	13.7	13.7
90°	41.7	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.1	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.2	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	269.9	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.5	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331820-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	424.7	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	493.2	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	559.4	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	649.4	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	717.0	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	782.7	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.6	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	871.2	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.7	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.3	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.4	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.5	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1183.5	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1287.2	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1324.4	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1346.4	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1366.4	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1392.1	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1413.4	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1425.1	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1434.0	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1443.5	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)